



產品說明

MASTERColour CDM-R 陶瓷複金屬燈

精巧、高效率放電式反射燈具，光色歷久如新，光線清晰明亮

优点

- 高效率燈具，節省電費支出，降低光照熱度
- 使用壽命優於白熾燈與鹵素燈
- 歷久如新的穩定光色
- 設計獨特，提升應用彈性，更讓如此小巧低調的燈具，帶來強大大照明效果
- CDM-R 燈管可用於開放式燈具，大幅簡化燈具設計
- 熱度較其他燈具為低，使顧客與工作人員更感舒適
- 內建紫外線濾鏡，減少商品褪色風險

特点

- 清晰明亮的白色光
- 絕佳的演色性
- 輕巧型反射燈，提供高強度光束，既簡單又有效率

应用

- 店面和商品櫥窗、辦公室與公共建築
- 戶外裝飾照明：泛光照明與行人徒步區

安全提示

- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use only with electronic control gear. Color 830 lamps may also use electromagnetic gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


MASTERColour CDM-R 陶瓷複金屬燈

Versions




LPPR CDM-R 0001

二维绘图




Product	D (max)	D	C (max)	C
MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT	97 mm	95 mm	123 mm	120 mm




MASTERCoulour CDM-R 陶瓷複金屬燈

Accent Diagrams



Accent Diagram - MASTERC CDM-R 35W/830
E27 PAR30L 30D 1CT

Beam Diagrams



Beam diagram - MASTERC CDM-R 35W/830
E27 PAR30L 30D 1CT

