



Beautiful sparkle, reliable life

MASTERColour CDM-T

Range of single-ended, compact, high-efficiency, discharge lamps with a stable color over lifetime and a crisp, sparkling light

Benefits

- Stable color impression over lifetime
- High lamp efficacy results in low operating costs and low heat generation
- Long lamp life compared with incandescent and halogen lamps
- Relatively low heat output enhances comfort for shoppers and staff
- All types are UV-Block for reduced fading risks

Features

- Crisp white light
- Superior color quality
- Allows small-size luminaire designs that give high beam intensities

Application


- Shops and shop windows, offices and public buildings
- Decorative outdoor: floodlighting and pedestrian areas

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTERC colour CDM-T

Dimensional drawing



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T 150W/830 G12 1CT	20 mm	0.75 in	9 mm	55 mm	57 mm	56 mm	110 mm
MASTERC CDM-T 150W/942 G12 1CT	20 mm	0.75 in	8 mm	55 mm	57 mm	56 mm	110 mm
MASTERC CDM-T 35W/830 G12 1CT/12	20 mm	0.75 in	5 mm	55 mm	57 mm	56 mm	103 mm
MASTERC CDM-T 35W/842 G12 1CT/12	20 mm	0.75 in	5 mm	55 mm	57 mm	56 mm	103 mm
MASTERC CDM-T 70W/830 G12 1CT/12	20 mm	0.75 in	7 mm	55 mm	57 mm	56 mm	103 mm
MASTERC CDM-T 70W/942 G12 1CT/12	20 mm	0.75 in	6 mm	55 mm	57 mm	56 mm	103 mm

General Information

Cap base	G12
Operating position	UNIVERSAL

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Lamp Finish	Clear
Bulb shape	T19

Light Technical

Order Code	Full Product Name	Chromaticity	Chromaticity	Colour designation	Correlated Colour Temperature (Nom)	Colour	Luminous efficacy (rated) (nom.)	Luminous Flux
		Coordinate X (Nom)	Coordinate Y (Nom)			rendering index (CRI)		
928082305125	MASTERC CDM-T 70W/830 G12 1CT/12	0.434	0.398	Warm White (WW)	3000 K	84	85 lm/W	6,200 lm
928083105125	MASTERC CDM-T 35W/830 G12 1CT/12	0.434	0.398	Warm White (WW)	3000 K	83	79 lm/W	3,100 lm
928083705125	MASTERC CDM-T 150W/830 G12 1CT	0.434	0.398	Warm White (WW)	3000 K	88	88 lm/W	13,000 lm
928084505131	MASTERC CDM-T 70W/942 G12 1CT/12	0.371	0.366	Cool White (CW)	4200 K	92	85 lm/W	6,200 lm
928084605131	MASTERC CDM-T 150W/942 G12 1CT	0.371	0.366	Cool White (CW)	4200 K	96	82 lm/W	12,100 lm
928094305125	MASTERC CDM-T 35W/842 G12 1CT/12	0.371	0.366	Cool White (CW)	4200 K	84	77 lm/W	3,000 lm

Operating and Electrical

Order Code	Full Product Name	Voltage (nom.)	Power Consumption	Order Code	Full Product Name	Voltage (nom.)	Power Consumption
928082305125	MASTERC CDM-T 70W/830 G12 1CT/12	88 V	73.2 W	928083105125	MASTERC CDM-T 35W/830 G12 1CT/12	82 V	39.1 W



MASTERC colour CDM-T

Order Code	Full Product Name	Voltage (nom.)	Power Consumption
928083705125	MASTERC CDM-T 150W/830 G12 1CT	96 V	150.1 W
928084505131	MASTERC CDM-T 70W/942 G12 1CT/12	88 V	73.2 W

Order Code	Full Product Name	Voltage (nom.)	Power Consumption
928084605131	MASTERC CDM-T 150W/942 G12 1CT	90 V	150.1 W
928094305125	MASTERC CDM-T 35W/842 G12 1CT/12	85 V	39.1 W

Approval and Application

Order Code	Full Product Name	Energy consumption kWh/1,000 hours	Mercury (Hg) content (max.)	Mercury (Hg) content (nom.)
928082305125	MASTERC CDM-T 70W/830 G12 1CT/12	74 kWh	4.6 mg	4.6 mg
928083105125	MASTERC CDM-T 35W/830 G12 1CT/12	40 kWh	3.2 mg	3.1 mg
928083705125	MASTERC CDM-T 150W/830 G12 1CT	151 kWh	14.3 mg	14.3 mg
928084505131	MASTERC CDM-T 70W/942 G12 1CT/12	74 kWh	6.1 mg	6.1 mg
928084605131	MASTERC CDM-T 150W/942 G12 1CT	151 kWh	10.4 mg	10.4 mg
928094305125	MASTERC CDM-T 35W/842 G12 1CT/12	40 kWh	2.7 mg	2.7 mg



MASTERColour CDM-T

