



The easiest switch to comfortable white light

MASTER CityWhite CDO-ET

Ceramic metal halide lamp, with opalized ovoid outer bulb shape, used in outdoor offering pleasant white light

Benefits

- White warm colour impression providing comfort and safety
- Easy upgrade from SON to white light without additional cost
- Flexible light levels and reduced energy consumption possible via dimming option

Features

- High-quality white light
- Directly retrofit on HPS (SON/NAV) installations for upgrade from yellow to white light
- "Plus" concept with high efficacy translates into high light output and improved lumen maintenance
- Good colour rendering and harmonized warm white colour temperature
- Dimmable

Application

- Beautification and functional lighting for City centers, shopping centers and pedestrian areas, residential areas, road lighting and floodlighting

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Lamps may use electronic or electromagnetic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)


MASTER CityWhite CDO-ET

Versions



LPPR CDO-ET E27

Dimensional drawing



Product	D (max)	C (max)
MASTER CityWh CDO-ET Plus 100W/828 E40	76 mm	186 mm
MASTER CityWh CDO-ET Plus 150W/828 E40	91 mm	227 mm
MASTER CityWh CDO-ET Plus 70W/828 E27	71 mm	156 mm

General Information

Operating position UNIVERSAL

Light Technical

Chromaticity Coordinate X (Nom) 0.447

Chromaticity Coordinate Y (Nom) 0.4

Colour designation Warm White (WW)

Correlated Colour Temperature (Nom) 2800 K

Controls and Dimming

Dimmable Yes

Mechanical and Housing

Lamp Finish Coated glass

General Information

Order Code	Full Product Name	Cap base
928154708835	MASTER CityWh CDO-ET Plus 70W/828 E27	E27
928154808835	MASTER CityWh CDO-ET Plus 100W/828 E40	E40

Order Code	Full Product Name	Cap base
928154908835	MASTER CityWh CDO-ET Plus 150W/828 E40	E40

Light Technical

