



Classic look & feel

Classic frosted LED Lamps

Featuring a classic heritage design, LED frosted Classic bulbs deliver beautiful, decorative warm-white light while saving around 90% on energy costs. The familiar shapes of the LED frosted Classic lamps are a perfect fit for your existing fixtures.

Benefits

- Around 90% energy saving
- Very long lifetime that reduces the need for replacement
- Easy replacement of classic conventional lamps

Features

- Pure and elegant heritage design with classic shape
- Perfect fit and high quality finishing
- High color rendering (CRI > 80) for vivid colors
- Environmentally friendly: contains no mercury or other hazardous substances
- Instant full light on: Philips LED light bulbs provide their full level of brightness immediately upon switching on

Application

- Domestic applications
- Hospitality: restaurants and hotels

Classic frosted LED Lamps

Versions




7 W (60 W) E27 Warm white Bulb - RFT



4.5W (40W) E27 cap Warm white Bulb - RFT

Dimensional drawing



Product	D	C
4.5W (40W) E27 cap Warm white Non-dimmable Bulb	60 mm	110 mm
7 W (60 W) E27 Warm white Non-dimmable Bulb	60 mm	110 mm

Classic frosted LED Lamps

General Information

Cap-Base	E27
Rated Lifetime (Hours)	15,000 hour(s)
Switching Cycle	30,000
Nominal lifetime	15,000 hour(s)

Light Technical

Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	80
Color Code	827
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical

Input Frequency	50 Hz
Line Frequency	50 Hz
Starting Time (Nom)	0.5 s

Temperature

T-Case Maximum (Nom)	50 °C
----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Frosted
Bulb Shape	A60

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Luminous Flux
929001243082	7 W (60 W) E27 Warm white Non-dimmable Bulb	300 degree(s)	806 lm
929001242982	4.5W (40W) E27 cap Warm white Non-dimmable Bulb	-	470 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
929001243082	7 W (60 W) E27 Warm white Non-dimmable Bulb	7 W
929001242982	4.5W (40W) E27 cap Warm white Non-dimmable Bulb	4.5 W


Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929001243082	7 W (60 W) E27 Warm white Non-dimmable Bulb	7 kWh
929001242982	4.5W (40W) E27 cap Warm white Non-dimmable Bulb	5 kWh

Classic frosted LED Lamps

120°

90°



Classic frosted LED Lamps

