



產品說明

HPI-T 複金屬燈

石英複金屬燈，透明外部燈泡

优点

- 高度安全，照明舒適，歷久如新
- 維護成本極低

特点

- 透明外管
- 獨特的 3 段技術，有效提升流明效率，亮度始終如一
- 產生自然色白光，光色穩定

应用

- 運動照明，建物和紀念碑泛光照明、區域照明 (如港口和建築工地) 等

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- For use with control gear designed for high-pressure mercury lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


HPI-T 複金屬燈

Versions




HPI-T 1000W E40

二维绘图



Product	D (max)	O	L	C (max)
HPI-T 1000W/543 E40 1SL/4	66 mm	80 mm	240 mm	382 mm



Product	D (max)	O	L	C (max)
HPI-T 2000W/542 E40 380V 1SL/4	101.5 mm	120 mm	267 mm	430 mm
HPI-T 2000W/646 E40 220V CRP/4	101.5 mm	89 mm	290 mm	430 mm

一般資訊

燈座基底 E40

照明技術

色彩名稱 冷白光 (CW)

控制與調光

可調光 否

機械與外罩

燈泡表層 透明

HPI-T 複金屬燈

一般資訊

Order Code	Full Product Name	操作位置
928482600096	HPI-T 1000W/543 E40 1SL/4	P
928073609231	HPI-T 2000W/646 E40 220V CRP/4	P75

Order Code	Full Product Name	操作位置
928074209228	HPI-T 2000W/542 E40 380V 1SL/4	P20

照明技術

Order Code	Full Product Name	色度坐標 X (標稱)	色度坐標 Y (Nom)	相關色溫 (標稱)	演色性指數 (CRI)	光效 (額定) (標準)
928482600096	HPI-T 1000W/543 E40 1SL/4	370	380	4300 K	57	83 lm/W
928073609231	HPI-T 2000W/646 E40 220V CRP/4	375	385	4200 K	63	95 lm/W
928074209228	HPI-T 2000W/542 E40 380V 1SL/4	387	403	3800 K	59	101 lm/W

運轉與電力

Order Code	Full Product Name	電壓 (標稱)	耗電量
928482600096	HPI-T 1000W/543 E40 1SL/4	130 V	990 W
928073609231	HPI-T 2000W/646 E40 220V CRP/4	130 V	1,980 W

Order Code	Full Product Name	電壓 (標稱)	耗電量
928074209228	HPI-T 2000W/542 E40 380V 1SL/4	232 V	1,980 W

機械與外罩

Order Code	Full Product Name	燈泡形狀
928482600096	HPI-T 1000W/543 E40 1SL/4	T65
928073609231	HPI-T 2000W/646 E40 220V CRP/4	T100

Order Code	Full Product Name	燈泡形狀
928074209228	HPI-T 2000W/542 E40 380V 1SL/4	T100

認證與應用

Order Code	Full Product Name	能源消耗 kWh/ 1000 h	汞 (Hg) 含量 (標 稱)
928482600096	HPI-T 1000W/543 E40 1SL/4	1,089 kWh	86 mg
928073609231	HPI-T 2000W/646 E40 220V CRP/4	2,178 kWh	155 mg

Order Code	Full Product Name	能源消耗 kWh/ 1000 h	汞 (Hg) 含量 (標 稱)
928074209228	HPI-T 2000W/542 E40 380V 1SL/4	2,178 kWh	256 mg

