



# GreenUp deep recessed downlight G2: The most affordable deep recessed downlight

## GreenUp deep recessed downlight G2

The GreenUp deep recessed downlight G2 line offers a selection of popular LED luminaires that not only capture the trend of deep recessed but also come with high levels of Philips quality at a competitive price. Reliable, energy-efficient and affordable—just what you need.

### Benefits

- Philips quality and reliability
- Energy-efficient
- Comfortable, diffused light

### Features


- 100–110 lm/W
- Deep recessed design
- Multiple sizes and light levels available
- Multiple color temperatures available

### Application

- Offices
- Corridors
- Rest rooms

# GreenUp deep recessed downlight G2

## Dimensional drawing



### Light Technical

Color rendering index (CRI)	80
<b>Operating and Electrical</b>	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz

### Controls and Dimming

Dimmable	No
----------	----

### Mechanical and Housing

Optical cover type	Polycarbonate Diffuser
Housing Color	Black
Mech. impact protection code	IK03
Ingress protection code	IP20

### Approval and Application

Ambient temperature range	-20 to +40 °C
CE mark	Yes

### Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +20%
-------------------------	-------------

### Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401565143	DN035B D200 LED22/830 PSU WH G2	3000 K	99 lm/W	1,980 lm
911401565243	DN035B D200 LED22/840 PSU WH G2	4000 K	110 lm/W	2,200 lm
911401565343	DN035B D200 LED22/865 PSU WH G2	6500 K	110 lm/W	2,200 lm
911401565443	DN035B D200 LED32/830 PSU WH G2	3000 K	99 lm/W	2,880 lm
911401565543	DN035B D200 LED32/840 PSU WH G2	4000 K	110 lm/W	3,200 lm
911401565643	DN035B D200 LED32/865 PSU WH G2	6500 K	110 lm/W	3,200 lm
911401563643	DN035B D75 LED6/830 PSU WH G2	3000 K	90 lm/W	540 lm
911401563743	DN035B D75 LED6/840 PSU WH G2	4000 K	100 lm/W	600 lm
911401563843	DN035B D75 LED6/865 PSU WH G2	6500 K	100 lm/W	600 lm
911401563943	DN035B D100 LED6/830 PSU WH G2	3000 K	90 lm/W	558 lm
911401564043	DN035B D100 LED6/840 PSU WH G2	4000 K	100 lm/W	620 lm
911401564143	DN035B D100 LED6/865 PSU WH G2	6500 K	100 lm/W	620 lm

## GreenUp deep recessed downlight G2

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401564243	DN035B D100 LED10/830 PSU WH G2	3000 K	99 lm/W	855 lm
911401564343	DN035B D100 LED10/840 PSU WH G2	4000 K	110 lm/W	950 lm
911401564443	DN035B D100 LED10/865 PSU WH G2	6500 K	110 lm/W	950 lm
911401564543	DN035B D150 LED16/830 PSU WH G2	3000 K	99 lm/W	1,440 lm
911401564643	DN035B D150 LED16/840 PSU WH G2	4000 K	110 lm/W	1,600 lm
911401564743	DN035B D150 LED16/865 PSU WH G2	6500 K	110 lm/W	1,600 lm
911401564843	DN035B D150 LED20/830 PSU WH G2	3000 K	99 lm/W	1,800 lm
911401564943	DN035B D150 LED20/840 PSU WH G2	4000 K	110 lm/W	2,000 lm
911401565043	DN035B D150 LED20/865 PSU WH G2	6500 K	110 lm/W	2,000 lm

### Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401565143	DN035B D200 LED22/830 PSU WH G2	18 W	911401564143	DN035B D100 LED6/865 PSU WH G2	6 W
911401565243	DN035B D200 LED22/840 PSU WH G2	18 W	911401564243	DN035B D100 LED10/830 PSU WH G2	8.5 W
911401565343	DN035B D200 LED22/865 PSU WH G2	18 W	911401564343	DN035B D100 LED10/840 PSU WH G2	8.5 W
911401565443	DN035B D200 LED32/830 PSU WH G2	26 W	911401564443	DN035B D100 LED10/865 PSU WH G2	8.5 W
911401565543	DN035B D200 LED32/840 PSU WH G2	26 W	911401564543	DN035B D150 LED16/830 PSU WH G2	13 W
911401565643	DN035B D200 LED32/865 PSU WH G2	26 W	911401564643	DN035B D150 LED16/840 PSU WH G2	13 W
911401563643	DN035B D75 LED6/830 PSU WH G2	5.5 W	911401564743	DN035B D150 LED16/865 PSU WH G2	13 W
911401563743	DN035B D75 LED6/840 PSU WH G2	5.5 W	911401564843	DN035B D150 LED20/830 PSU WH G2	16.5 W
911401563843	DN035B D75 LED6/865 PSU WH G2	5.5 W	911401564943	DN035B D150 LED20/840 PSU WH G2	16.5 W
911401563943	DN035B D100 LED6/830 PSU WH G2	6 W	911401565043	DN035B D150 LED20/865 PSU WH G2	16.5 W
911401564043	DN035B D100 LED6/840 PSU WH G2	6 W			

