



Simply great LED

Ledinaire SlimDownlight

The LEDINAIRE range contains a selection of popular off-the-shelf LED luminaires that come with the high Philips quality levels at a competitive price. Reliable, energy-efficient and affordable – just what you need

Benefits

- Philips quality and reliability
- Energy saving
- Comfortable diffuse surface of light

Features

- Multiple sizes and light levels available
- Multiple light colors available
- Ultra slim design

Application

- Corridors
- Rest rooms
- Waiting rooms

Ledinaire SlimDownlight

Versions





LEDINAIRE SlimDownlight-DN065B LED10S



DN065B G4 LED12 12W D150 RD

Dimensional drawing



Product details

Philips Ledinaire slim downlight
recessed DT03



Philips Ledinaire slim downlight
recessed DT01



Philips Ledinaire slim downlight
recessed Back DT01



Philips Ledinaire slim downlight
recessed DT02



Ledinaire SlimDownlight

Product details



Philips Ledinaire slim downlight
recessed DT04

General Information	
Driver included	Yes
Light source replaceable	No
Light Technical	
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	80
Luminous Efficacy (rated) (Nom)	100 lm/W
Luminous Flux	1,200 lm
Optic type	Beam angle 110°
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	12 W
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Color	White
Mech. impact protection code	IK03
Ingress protection code	IP20/44
Approval and Application	
Ambient temperature range	-20 to +40 °C
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	0.7
Stroboscopic effect visibility measure (SVM)	0.4
Initial Performance (IEC Compliant)	
Initial chromaticity	(0.44, 0.403) SDCM≤5
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	All-in Type
929003250532	DN065B G4 LED12/830 12W 220-240V D150 RD	-
929003251332	DN065B G4 LED12/830_840_865 12W D150 RD	All-in, Multi Color Temperature

Ledinaire SlimDownlight

