

PHILIPS

Lighting



Simply great LED

Ledinaire SlimDownlight

The LEDINAIRE range contains a selection of popular off-the-shelf LED luminaires that come with the high Philips quality levels at a competitive price. Reliable, energy-efficient and affordable – just what you need

Benefits

- Philips quality and reliability
- Energy saving
- Comfortable diffuse surface of light



Features

- Multiple sizes and light levels available
- Multiple light colors available
- Ultra slim design

Application

- Corridors
- Rest rooms
- Waiting rooms

Dimensional drawing



Ledinaire SlimDownlight

Product details



additional photo

General Information			
Driver included	Yes		
Light source replaceable	No		
Light Technical			
Correlated Color Temperature (Nom)	4000 K		
Color rendering index (CRI)	80		
Optic type	Beam angle 110°		
Operating and Electrical			
Protection class IEC	Safety class II		
Input Voltage	220 to 240 V		
Line Frequency	50 or 60 Hz		
Controls and Dimming			
Dimmable	No		
Mechanical and Housing			
Housing Color	White		
Mech. impact protection code	IK03		
Ingress protection code	IP20/40		
Approval and Application			
Ambient temperature range	-20 to +40 °C		
CE mark	Yes		
Flammability mark	For mounting on normally flammable surfaces		
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	0.7		
Stroboscopic effect visibility measure (SVM)	0.4		
Initial Performance (IEC Compliant)			
Initial chromaticity	(0.38, 0.38)		
	SDCM≤5		
Luminous flux tolerance	+/-10%		
Light Technical			
			Luminous Efficacy (rated)
Order Code			(Nom)
929003251632	DN065C G4 LED12/840 12W 220-240V 6-D175	108 lm/W	1,200 lm
929003251832	DN065C G4 LED20/840 19W 220-240V 8-	105 lm/W	2,000 lm
	D225		

Operating and Electrical

Ledinaire SlimDownlight

Order Code	Full Product Name	Power Consumption
929003251632	DN065C G4 LED12/840 12W 220-240V 6-D175	12 W
929003251832	DN065C G4 LED20/840 19W 220-240V 8-D225	19 W

