



Proven quality. Effortless installation. Every time Your dependable and affordable choice for every job

The LEDINAIRE range contains a selection of popular off-the-shelf LED luminaires that come with the high Philips quality levels at a competitive price. Reliable, energy-efficient and affordable – just what you need

Benefits

- Philips quality and reliability
- Energy saving
- Comfortable diffuse surface of light

Applications

- Corridors
- Rest rooms
- Waiting rooms

Features


- Multiple sizes and light levels available
- Multiple light colors available
- Ultra slim design

Versions

LEDINAIRE SlimDownlight-
 DN065B LED10S



Dimensional drawing



DN065B G4 LED20/840 19W 220-240V D200 RD

Product details



additional photo

General Information

Light source replaceable	No
Driver included	Yes

Light Technical

Luminous Flux	2,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	105 lm/W
Color rendering index (CRI)	80
Optic type	Beam angle 110°

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	19 W
Protection class IEC	Safety class II

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing Color	White
Ingress protection code	IP20/40 [Finger-protected;Wire-protected]
Mech. impact protection code	IK03 [0.3 J]

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	0.7
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM≤5