



Install smarter, finish sooner Choose long-lasting reliability and performance

CoreLine Downlight gen5

Philips CoreLine Downlight delivers on the CoreLine promise of innovative, easy to use and high-quality recessed downlights. The CoreLine Downlight range is suitable for one-to-one conventional luminaire replacements, with an attractive TCO that helps your customers make the switch to LED. These recessed indoor downlights offer uniform light distribution for use in general lighting and office applications (UGR 19). They also deliver instant energy savings and have a much longer lifetime, creating a solution that's environmentally friendly and real value-for-money. CoreLine DN142B recessed downlights are easy to install thanks to their standard cut-out size and push-in connectors. An Interact ready option with integrated wireless communications is also available in this family, which can be used with Interact gateways, sensors and software.

Benefits

- Energy saving and longer lifetime to reduce overall operating costs
- One-to-one replacement makes it easy to switch to LED
- Low glare suitable for office applications

CoreLine Downlight gen5

Features

- Available in two cut-out sizes (150mm and 200mm)
- White reflector downlight UGR 25
- Aluminum reflector downlight UGR 19
- Energy efficient: up to 120 lm/W
- Choice of color temperatures: 3000K and 4000K
- Choice of drivers; DALI and wireless with Interact ready
- Optional emergency lighting versions available
- Optional IP54 versions available

Application

- Offices
- Indoor general areas
- Reception and lounge
- Meeting rooms
- Corridors





Warnings and Safety

- Do not apply excessive force to the cable & DC connector, make sure the connector clip is locked before the power is on.

Specifications

Ceiling type	Plaster (board) ceiling	Color Rendering index - >80
Dimming	PSU: non-Dimmable PSD: Dimmable (DALI-broadcasting)WIA: Wireless control, compatible with Interact	CRI
Control gear failure rate at median useful life	5%	Driver replaceable Yes
50.000h		

Dimensional drawing



CoreLine Downlight gen5


Product details




CoreLine Downlight DN142B
Compact with White Reflector
(WR)



CoreLine Downlight DN142B
Compact with White Reflector
(WR)



CoreLine Downlight DN142B
Compact with UGR19



CoreLine Downlight DN142B
Compact with UGR19



Product Detail Photo Coreline



Product Detail Photo Coreline

CoreLine Downlight gen5

General Information

Driver included	Yes
Number of gear units	1 unit
Service tag	Yes

Light Technical

Beam angle of light source	- degree(s)
Color rendering index (CRI)	>80

Operating and Electrical

Protection class IEC	Safety class II
Line Frequency	50 to 60 Hz
Suitable for random switching	Yes

Mechanical and Housing

Housing Color	White
Mech. impact protection code	IK02

Approval and Application

Ambient temperature range	-20 to +40 °C
CE mark	Yes
ENEC mark	-
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Stroboscopic effect visibility measure (SVM)	1

General Information

Order Code	Full Product Name	Light source replaceable
910505103586	DN142B 10S/830 PSD-E WR	-
910505103587	DN142B 10S/830 PSD-E WR IP54	-
910505103590	DN142B 10S/840 PSD-E WR	-
910505103591	DN142B 10S/840 PSD-E WR IP54	-
910505103603	DN142B 10S/830 PSD-E WR ELB3	-
910505103605	DN142B 10S/840 PSD-E WR ELB3	-
911401551032	DN142B 10S/830 PSU-E WR	No
911401551132	DN142B 10S/830 PSU-E WR IP54	No
911401551432	DN142B 10S/840 PSU-E WR	No
911401551532	DN142B 10S/840 PSU-E WR IP54	No
910505103596	DN142B 20S/830 PSD-E UGR19	-
910505103597	DN142B 20S/830 PSD-E UGR19 IP54	-
910505103601	DN142B 20S/840 PSD-E UGR19	-
910505103602	DN142B 20S/840 PSD-E UGR19 IP54	-
910505103608	DN142B 20S/830 PSD-E UGR19 ELB3	-
910505103610	DN142B 20S/840 PSD-E UGR19 ELB3	-
910505103612	DN142B 20S/830 WIA-E UGR19 IP54	-
910505103614	DN142B 20S/840 WIA-E UGR19 IP54	-
910505103616	DN142B 20S/830 WIA-E UGR19 ELB3 IP54	-
910505103618	DN142B 20S/840 WIA-E UGR19 ELB3 IP54	-
911401552032	DN142B 20S/830 PSU-E UGR19	No
911401552132	DN142B 20S/830 PSU-E UGR19 IP54	No
911401552432	DN142B 20S/840 PSU-E UGR19	No
911401552532	DN142B 20S/840 PSU-E UGR19 IP54	No
910505103588	DN142B 10S/830 PSD-E UGR19	-
910505103589	DN142B 10S/830 PSD-E UGR19 IP54	-
910505103592	DN142B 10S/840 PSD-E UGR19	-
910505103593	DN142B 10S/840 PSD-E UGR19 IP54	-
910505103604	DN142B 10S/830 PSD-E UGR19 ELB3	-
910505103606	DN142B 10S/840 PSD-E UGR19 ELB3	-
911401551232	DN142B 10S/830 PSU-E UGR19	No
911401551332	DN142B 10S/830 PSU-E UGR19 IP54	No
911401551632	DN142B 10S/840 PSU-E UGR19	No
911401551732	DN142B 10S/840 PSU-E UGR19 IP54	No
910505103594	DN142B 20S/830 PSD-E WR	-
910505103595	DN142B 20S/830 PSD-E WR IP54	-
910505103598	DN142B 20S/840 PSD-E WR	-
910505103599	DN142B 20S/840 PSD-E WR IP54	-
910505103607	DN142B 20S/830 PSD-E WR ELB3	-
910505103609	DN142B 20S/840 PSD-E WR ELB3	-
910505103611	DN142B 20S/830 WIA-E WR IP54	-
910505103613	DN142B 20S/840 WIA-E WR IP54	-
910505103615	DN142B 20S/830 WIA-E WR ELB3 IP54	-
910505103617	DN142B 20S/840 WIA-E WR ELB3 IP54	-
911401551832	DN142B 20S/830 PSU-E WR	No
911401551932	DN142B 20S/830 PSU-E WR IP54	No
911401552232	DN142B 20S/840 PSU-E WR	No
911401552332	DN142B 20S/840 PSU-E WR IP54	No

Light Technical

CoreLine Downlight gen5

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
		(K)	(lm/W)	(lm)	
910505103586	DN142B 10S/830 PSD-E WR	3000 K	112 lm/W	1,000 lm	White reflector perforated without louver
910505103587	DN142B 10S/830 PSD-E WR IP54	3000 K	112 lm/W	1,000 lm	White reflector perforated without louver
910505103590	DN142B 10S/840 PSD-E WR	4000 K	112 lm/W	1,000 lm	White reflector perforated without louver
910505103591	DN142B 10S/840 PSD-E WR IP54	4000 K	112 lm/W	1,000 lm	White reflector perforated without louver
910505103603	DN142B 10S/830 PSD-E WR ELB3	3000 K	115 lm/W	1,000 lm	White reflector perforated without louver
910505103605	DN142B 10S/840 PSD-E WR ELB3	4000 K	115 lm/W	1,000 lm	White reflector perforated without louver
911401551032	DN142B 10S/830 PSU-E WR	3000 K	120 lm/W	1,200 lm	-
911401551132	DN142B 10S/830 PSU-E WR IP54	3000 K	120 lm/W	1,200 lm	-
911401551432	DN142B 10S/840 PSU-E WR	4000 K	120 lm/W	1,200 lm	-
911401551532	DN142B 10S/840 PSU-E WR IP54	4000 K	120 lm/W	1,200 lm	-
910505103596	DN142B 20S/830 PSD-E UGR19	3000 K	110 lm/W	2,000 lm	Facetted reflector
910505103597	DN142B 20S/830	3000 K	110 lm/W	2,000 lm	Facetted reflector

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
		(K)	(lm/W)	(lm)	
	PSD-E UGR19 IP54				
910505103601	DN142B 20S/840 PSD-E UGR19	4000 K	110 lm/W	2,000 lm	Facetted reflector
910505103602	DN142B 20S/840 PSD-E UGR19 IP54	4000 K	110 lm/W	2,000 lm	Facetted reflector
910505103608	DN142B 20S/830 PSD-E UGR19 ELB3	3000 K	113 lm/W	2,000 lm	Facetted reflector
910505103610	DN142B 20S/840 PSD-E UGR19 ELB3	4000 K	113 lm/W	2,000 lm	Facetted reflector
910505103612	DN142B 20S/830 WIA-E UGR19 IP54	3000 K	111 lm/W	2,000 lm	Facetted reflector
910505103614	DN142B 20S/840 WIA-E UGR19 IP54	4000 K	111 lm/W	2,000 lm	Facetted reflector
910505103616	DN142B 20S/830 WIA-E UGR19 ELB3 IP54	3000 K	111 lm/W	2,000 lm	Facetted reflector
910505103618	DN142B 20S/840 WIA-E UGR19 ELB3 IP54	4000 K	111 lm/W	2,000 lm	Facetted reflector
911401552032	DN142B 20S/830 PSU-E UGR19	3000 K	120 lm/W	2,350 lm	-
911401552132	DN142B 20S/830 PSU-E UGR19 IP54	3000 K	120 lm/W	2,350 lm	-
911401552432	DN142B 20S/840 PSU-E UGR19	4000 K	120 lm/W	2,350 lm	-
911401552532	DN142B 20S/840 PSU-E UGR19 IP54	4000 K	120 lm/W	2,350 lm	-

CoreLine Downlight gen5

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
		(K)	(lm/W)	(lm)	
910505103588	DN142B 10S/830 PSD-E UGR19	3000 K	107 lm/W	1,000 lm	Facetted reflector
910505103589	DN142B 10S/830 PSD-E UGR19 IP54	3000 K	107 lm/W	1,000 lm	Facetted reflector
910505103592	DN142B 10S/840 PSD-E UGR19	4000 K	107 lm/W	1,000 lm	Facetted reflector
910505103593	DN142B 10S/840 PSD-E UGR19 IP54	4000 K	107 lm/W	1,000 lm	Facetted reflector
910505103604	DN142B 10S/830 PSD-E UGR19 ELB3	3000 K	109 lm/W	1,000 lm	Facetted reflector
910505103606	DN142B 10S/840 PSD-E UGR19 ELB3	4000 K	109 lm/W	1,000 lm	Facetted reflector
911401551232	DN142B 10S/830 PSU-E UGR19	3000 K	120 lm/W	1,200 lm	-
911401551332	DN142B 10S/830 PSU-E UGR19 IP54	3000 K	120 lm/W	1,200 lm	-
911401551632	DN142B 10S/840 PSU-E UGR19	4000 K	120 lm/W	1,200 lm	-
911401551732	DN142B 10S/840 PSU-E UGR19 IP54	4000 K	120 lm/W	1,200 lm	-
910505103594	DN142B 20S/830 PSD-E WR	3000 K	116 lm/W	2,000 lm	White reflector perforated without louver
910505103595	DN142B 20S/830 PSD-E WR IP54	3000 K	116 lm/W	2,000 lm	White reflector perforated without louver
910505103598	DN142B 20S/840 PSD-E WR	4000 K	116 lm/W	2,000 lm	White reflector perforated

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
		(K)	(lm/W)	(lm)	
910505103599	DN142B 20S/840 PSD-E WR IP54	4000 K	116 lm/W	2,000 lm	White reflector perforated without louver
910505103607	DN142B 20S/830 PSD-E WR ELB3	3000 K	119 lm/W	2,000 lm	White reflector perforated without louver
910505103609	DN142B 20S/840 PSD-E WR ELB3	4000 K	119 lm/W	2,000 lm	White reflector perforated without louver
910505103611	DN142B 20S/830 WIA-E WR IP54	3000 K	116 lm/W	2,000 lm	White reflector perforated without louver
910505103613	DN142B 20S/840 WIA-E WR IP54	4000 K	117 lm/W	2,000 lm	White reflector perforated without louver
910505103615	DN142B 20S/830 WIA-E WR ELB3 IP54	3000 K	116 lm/W	2,000 lm	White reflector perforated without louver
910505103617	DN142B 20S/840 WIA-E WR ELB3 IP54	4000 K	116 lm/W	2,000 lm	White reflector perforated without louver
911401551832	DN142B 20S/830 PSU-E WR	3000 K	120 lm/W	2,350 lm	-
911401551932	DN142B 20S/830 PSU-E WR IP54	3000 K	120 lm/W	2,350 lm	-
911401552232	DN142B 20S/840 PSU-E WR	4000 K	120 lm/W	2,350 lm	-
911401552332	DN142B 20S/840	4000 K	120 lm/W	2,350 lm	-

CoreLine Downlight gen5

Order Code	Full Product Name	Correlated Color Temperature	Luminous Efficacy (rated)	Luminous Flux	Optic type
		(Nom)	(Nom)		
	PSU-E WR				
	IP54				

Operating and Electrical

Order Code	Full Product Name	Input Voltage	Power Consumption
910505103586	DN142B 10S/830 PSD-E WR	220 to 240 V	10.7 W
910505103587	DN142B 10S/830 PSD-E WR IP54	220 to 240 V	10.7 W
910505103590	DN142B 10S/840 PSD-E WR	220 to 240 V	10.7 W
910505103591	DN142B 10S/840 PSD-E WR IP54	220 to 240 V	10.7 W
910505103603	DN142B 10S/830 PSD-E WR ELB3	220 to 240 V	14.9 W
910505103605	DN142B 10S/840 PSD-E WR ELB3	220 to 240 V	14.9 W
911401551032	DN142B 10S/830 PSU-E WR	220-240 V	9.8 W
911401551132	DN142B 10S/830 PSU-E WR IP54	220-240 V	9.8 W
911401551432	DN142B 10S/840 PSU-E WR	220-240 V	9.8 W
911401551532	DN142B 10S/840 PSU-E WR IP54	220-240 V	9.8 W
910505103596	DN142B 20S/830 PSD-E UGR19	220 to 240 V	20.5 W
910505103597	DN142B 20S/830 PSD-E UGR19 IP54	220 to 240 V	20.5 W
910505103601	DN142B 20S/840 PSD-E UGR19	220 to 240 V	20.5 W
910505103602	DN142B 20S/840 PSD-E UGR19 IP54	220 to 240 V	20.5 W
910505103608	DN142B 20S/830 PSD-E UGR19 ELB3	220 to 240 V	24.5 W
910505103610	DN142B 20S/840 PSD-E UGR19 ELB3	220 to 240 V	24.5 W
910505103612	DN142B 20S/830 WIA-E UGR19 IP54	220 to 240 V	20.4 W
910505103614	DN142B 20S/840 WIA-E UGR19 IP54	220 to 240 V	20.4 W
910505103616	DN142B 20S/830 WIA-E UGR19 ELB3 IP54	220 to 240 V	24.9 W
910505103618	DN142B 20S/840 WIA-E UGR19 ELB3 IP54	220 to 240 V	24.9 W
911401552032	DN142B 20S/830 PSU-E UGR19	220-240 V	19.2 W
911401552132	DN142B 20S/830 PSU-E UGR19 IP54	220-240 V	19.2 W
911401552432	DN142B 20S/840 PSU-E UGR19	220-240 V	19.2 W
911401552532	DN142B 20S/840 PSU-E UGR19 IP54	220-240 V	19.2 W

Order Code	Full Product Name	Input Voltage	Power Consumption
910505103588	DN142B 10S/830 PSD-E UGR19	220 to 240 V	10.7 W
910505103589	DN142B 10S/830 PSD-E UGR19 IP54	220 to 240 V	10.7 W
910505103592	DN142B 10S/840 PSD-E UGR19	220 to 240 V	10.7 W
910505103593	DN142B 10S/840 PSD-E UGR19 IP54	220 to 240 V	10.7 W
910505103604	DN142B 10S/830 PSD-E UGR19 ELB3	220 to 240 V	14.9 W
910505103606	DN142B 10S/840 PSD-E UGR19 ELB3	220 to 240 V	14.9 W
911401551232	DN142B 10S/830 PSU-E UGR19	220-240 V	9.8 W
911401551332	DN142B 10S/830 PSU-E UGR19 IP54	220-240 V	9.8 W
911401551632	DN142B 10S/840 PSU-E UGR19	220-240 V	9.8 W
911401551732	DN142B 10S/840 PSU-E UGR19 IP54	220-240 V	9.8 W
910505103594	DN142B 20S/830 PSD-E WR	220 to 240 V	20.5 W
910505103595	DN142B 20S/830 PSD-E WR IP54	220 to 240 V	20.5 W
910505103598	DN142B 20S/840 PSD-E WR	220 to 240 V	20.5 W
910505103599	DN142B 20S/840 PSD-E WR IP54	220 to 240 V	20.5 W
910505103607	DN142B 20S/830 PSD-E WR ELB3	220 to 240 V	24.5 W
910505103609	DN142B 20S/840 PSD-E WR ELB3	220 to 240 V	24.5 W
910505103611	DN142B 20S/830 WIA-E WR IP54	220 to 240 V	20.4 W
910505103613	DN142B 20S/840 WIA-E WR IP54	220 to 240 V	20.4 W
910505103615	DN142B 20S/830 WIA-E WR ELB3 IP54	220 to 240 V	24.9 W
910505103617	DN142B 20S/840 WIA-E WR ELB3 IP54	220 to 240 V	24.9 W
911401551832	DN142B 20S/830 PSU-E WR	220-240 V	19.2 W
911401551932	DN142B 20S/830 PSU-E WR IP54	220-240 V	19.2 W
911401552232	DN142B 20S/840 PSU-E WR	220-240 V	19.2 W
911401552332	DN142B 20S/840 PSU-E WR IP54	220-240 V	19.2 W

Controls and Dimming

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
910505103586	DN142B 10S/830 PSD-E WR	Yes	-
910505103587	DN142B 10S/830 PSD-E WR IP54	Yes	-
910505103590	DN142B 10S/840 PSD-E WR	Yes	-

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
910505103591	DN142B 10S/840 PSD-E WR IP54	Yes	-
910505103603	DN142B 10S/830 PSD-E WR ELB3	Yes	-
910505103605	DN142B 10S/840 PSD-E WR ELB3	Yes	-

CoreLine Downlight gen5

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
911401551032	DN142B 10S/830 PSU-E WR	No	Not applicable
911401551132	DN142B 10S/830 PSU-E WR IP54	No	Not applicable
911401551432	DN142B 10S/840 PSU-E WR	No	Not applicable
911401551532	DN142B 10S/840 PSU-E WR IP54	No	Not applicable
910505103596	DN142B 20S/830 PSD-E UGR19	Yes	-
910505103597	DN142B 20S/830 PSD-E UGR19 IP54	Yes	-
910505103601	DN142B 20S/840 PSD-E UGR19	Yes	-
910505103602	DN142B 20S/840 PSD-E UGR19 IP54	Yes	-
910505103608	DN142B 20S/830 PSD-E UGR19 ELB3	Yes	-
910505103610	DN142B 20S/840 PSD-E UGR19 ELB3	Yes	-
910505103612	DN142B 20S/830 WIA-E UGR19 IP54	Yes	-
910505103614	DN142B 20S/840 WIA-E UGR19 IP54	Yes	-
910505103616	DN142B 20S/830 WIA-E UGR19 ELB3 IP54	Yes	-
910505103618	DN142B 20S/840 WIA-E UGR19 ELB3 IP54	Yes	-
911401552032	DN142B 20S/830 PSU-E UGR19	No	Not applicable
911401552132	DN142B 20S/830 PSU-E UGR19 IP54	No	Not applicable
911401552432	DN142B 20S/840 PSU-E UGR19	No	Not applicable
911401552532	DN142B 20S/840 PSU-E UGR19 IP54	No	Not applicable
910505103588	DN142B 10S/830 PSD-E UGR19	Yes	-
910505103589	DN142B 10S/830 PSD-E UGR19 IP54	Yes	-

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
910505103592	DN142B 10S/840 PSD-E UGR19	Yes	-
910505103593	DN142B 10S/840 PSD-E UGR19 IP54	Yes	-
910505103604	DN142B 10S/830 PSD-E UGR19 ELB3	Yes	-
910505103606	DN142B 10S/840 PSD-E UGR19 ELB3	Yes	-
911401551232	DN142B 10S/830 PSU-E UGR19	No	Not applicable
911401551332	DN142B 10S/830 PSU-E UGR19 IP54	No	Not applicable
911401551632	DN142B 10S/840 PSU-E UGR19	No	Not applicable
911401551732	DN142B 10S/840 PSU-E UGR19 IP54	No	Not applicable
910505103594	DN142B 20S/830 PSD-E WR	Yes	-
910505103595	DN142B 20S/830 PSD-E WR IP54	Yes	-
910505103598	DN142B 20S/840 PSD-E WR	Yes	-
910505103599	DN142B 20S/840 PSD-E WR IP54	Yes	-
910505103607	DN142B 20S/830 PSD-E WR ELB3	Yes	-
910505103609	DN142B 20S/840 PSD-E WR ELB3	Yes	-
910505103611	DN142B 20S/830 WIA-E WR IP54	Yes	-
910505103613	DN142B 20S/840 WIA-E WR IP54	Yes	-
910505103615	DN142B 20S/830 WIA-E WR ELB3 IP54	Yes	-
910505103617	DN142B 20S/840 WIA-E WR ELB3 IP54	Yes	-
911401551832	DN142B 20S/830 PSU-E WR	No	Not applicable
911401551932	DN142B 20S/830 PSU-E WR IP54	No	Not applicable
911401552232	DN142B 20S/840 PSU-E WR	No	Not applicable
911401552332	DN142B 20S/840 PSU-E WR IP54	No	Not applicable

Mechanical and Housing

Order Code	Full Product Name	Ingress protection code
910505103586	DN142B 10S/830 PSD-E WR	IP20
910505103587	DN142B 10S/830 PSD-E WR IP54	IP20/54
910505103590	DN142B 10S/840 PSD-E WR	IP20
910505103591	DN142B 10S/840 PSD-E WR IP54	IP20/54
910505103603	DN142B 10S/830 PSD-E WR ELB3	IP20
910505103605	DN142B 10S/840 PSD-E WR ELB3	IP20
911401551032	DN142B 10S/830 PSU-E WR	IP20
911401551132	DN142B 10S/830 PSU-E WR IP54	IP20/54
911401551432	DN142B 10S/840 PSU-E WR	IP20
911401551532	DN142B 10S/840 PSU-E WR IP54	IP20/54
910505103596	DN142B 20S/830 PSD-E UGR19	IP20
910505103597	DN142B 20S/830 PSD-E UGR19 IP54	IP20/54
910505103601	DN142B 20S/840 PSD-E UGR19	IP20
910505103602	DN142B 20S/840 PSD-E UGR19 IP54	IP20/54
910505103608	DN142B 20S/830 PSD-E UGR19 ELB3	IP20
910505103610	DN142B 20S/840 PSD-E UGR19 ELB3	IP20
910505103612	DN142B 20S/830 WIA-E UGR19 IP54	IP20/54
910505103614	DN142B 20S/840 WIA-E UGR19 IP54	IP20/54
910505103616	DN142B 20S/830 WIA-E UGR19 ELB3 IP54	IP20/54
910505103618	DN142B 20S/840 WIA-E UGR19 ELB3 IP54	IP20/54
911401552032	DN142B 20S/830 PSU-E UGR19	IP20
911401552132	DN142B 20S/830 PSU-E UGR19 IP54	IP20/54
911401552432	DN142B 20S/840 PSU-E UGR19	IP20
911401552532	DN142B 20S/840 PSU-E UGR19 IP54	IP20/54

Order Code	Full Product Name	Ingress protection code
910505103588	DN142B 10S/830 PSD-E UGR19	IP20
910505103589	DN142B 10S/830 PSD-E UGR19 IP54	IP20/54
910505103592	DN142B 10S/840 PSD-E UGR19	IP20
910505103593	DN142B 10S/840 PSD-E UGR19 IP54	IP20/54
910505103604	DN142B 10S/830 PSD-E UGR19 ELB3	IP20
910505103606	DN142B 10S/840 PSD-E UGR19 ELB3	IP20
911401551232	DN142B 10S/830 PSU-E UGR19	IP20
911401551332	DN142B 10S/830 PSU-E UGR19 IP54	IP20/54
911401551632	DN142B 10S/840 PSU-E UGR19	IP20
911401551732	DN142B 10S/840 PSU-E UGR19 IP54	IP20/54
910505103594	DN142B 20S/830 PSD-E WR	IP20
910505103595	DN142B 20S/830 PSD-E WR IP54	IP20/54
910505103598	DN142B 20S/840 PSD-E WR	IP20
910505103599	DN142B 20S/840 PSD-E WR IP54	IP20/54
910505103607	DN142B 20S/830 PSD-E WR ELB3	IP20
910505103609	DN142B 20S/840 PSD-E WR ELB3	IP20
910505103611	DN142B 20S/830 WIA-E WR IP54	IP20/54
910505103613	DN142B 20S/840 WIA-E WR IP54	IP20/54
910505103615	DN142B 20S/830 WIA-E WR ELB3 IP54	IP20/54
910505103617	DN142B 20S/840 WIA-E WR ELB3 IP54	IP20/54
911401551832	DN142B 20S/830 PSU-E WR	IP20
911401551932	DN142B 20S/830 PSU-E WR IP54	IP20/54
911401552232	DN142B 20S/840 PSU-E WR	IP20
911401552332	DN142B 20S/840 PSU-E WR IP54	IP20/54

CoreLine Downlight gen5

Emergency Operation

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910505103586	DN142B 10S/830 PSD-E WR	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory	-
910505103587	DN142B 10S/830 PSD-E WR IP54	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory	-
910505103590	DN142B 10S/840 PSD-E WR	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory	-
910505103591	DN142B 10S/840 PSD-E WR IP54	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory	-
910505103603	DN142B 10S/830 PSD-E WR ELB3	No	Emergency lighting 3 hours duration basic version	3 hour(s)
910505103605	DN142B 10S/840 PSD-E WR ELB3	No	Emergency lighting 3 hours duration basic version	3 hour(s)
911401551032	DN142B 10S/830 PSU-E WR	-	-	-
911401551132	DN142B 10S/830 PSU-E WR IP54	-	-	-
911401551432	DN142B 10S/840 PSU-E WR	-	-	-
911401551532	DN142B 10S/840 PSU-E WR IP54	-	-	-
910505103596	DN142B 20S/830 PSD-E UGR19	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory	-
910505103597	DN142B 20S/830 PSD-E UGR19 IP54	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910505103601	DN142B 20S/840 PSD-E UGR19	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory	-
910505103602	DN142B 20S/840 PSD-E UGR19 IP54	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory	-
910505103608	DN142B 20S/830 PSD-E UGR19 ELB3	No	Emergency lighting 3 hours duration basic version	3 hour(s)
910505103610	DN142B 20S/840 PSD-E UGR19 ELB3	No	Emergency lighting 3 hours duration basic version	3 hour(s)
910505103612	DN142B 20S/830 WIA-E UGR19 IP54	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory	-
910505103614	DN142B 20S/840 WIA-E UGR19 IP54	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory	-
910505103616	DN142B 20S/830 WIA-E UGR19 ELB3 IP54	No	Emergency lighting 3 hours duration basic version	3 hour(s)
910505103618	DN142B 20S/840 WIA-E UGR19 ELB3 IP54	No	Emergency lighting 3 hours duration basic version	3 hour(s)
911401552032	DN142B 20S/830 PSU-E UGR19	-	-	-
911401552132	DN142B 20S/830 PSU-E UGR19 IP54	-	-	-
911401552432	DN142B 20S/840 PSU-E UGR19	-	-	-

CoreLine Downlight gen5

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
911401552532	DN142B 20S/840 PSU-E UGR19 IP54	-	-	-
910505103588	DN142B 10S/830 PSD-E UGR19	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory	-
910505103589	DN142B 10S/830 PSD-E UGR19 IP54	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory	-
910505103592	DN142B 10S/840 PSD-E UGR19	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory	-
910505103593	DN142B 10S/840 PSD-E UGR19 IP54	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory	-
910505103604	DN142B 10S/830 PSD-E UGR19 ELB3	No	Emergency lighting 3 hours duration basic version	3 hour(s)
910505103606	DN142B 10S/840 PSD-E UGR19 ELB3	No	Emergency lighting 3 hours duration basic version	3 hour(s)
911401551232	DN142B 10S/830 PSU-E UGR19	-	-	-
911401551332	DN142B 10S/830 PSU-E UGR19 IP54	-	-	-
911401551632	DN142B 10S/840 PSU-E UGR19	-	-	-
911401551732	DN142B 10S/840 PSU-E UGR19 IP54	-	-	-
910505103594	DN142B 20S/830 PSD-E WR	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910505103595	DN142B 20S/830 PSD-E WR IP54	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory	-
910505103598	DN142B 20S/840 PSD-E WR	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory	-
910505103599	DN142B 20S/840 PSD-E WR IP54	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory	-
910505103607	DN142B 20S/830 PSD-E WR ELB3	No	Emergency lighting 3 hours duration basic version	3 hour(s)
910505103609	DN142B 20S/840 PSD-E WR ELB3	No	Emergency lighting 3 hours duration basic version	3 hour(s)
910505103611	DN142B 20S/830 WIA-E WR IP54	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory	-
910505103613	DN142B 20S/840 WIA-E WR IP54	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory	-
910505103615	DN142B 20S/830 WIA-E WR ELB3 IP54	No	Emergency lighting 3 hours duration basic version	3 hour(s)
910505103617	DN142B 20S/840 WIA-E WR ELB3 IP54	No	Emergency lighting 3 hours duration basic version	3 hour(s)
911401551832	DN142B 20S/830 PSU-E WR	-	-	-
911401551932	DN142B 20S/830 PSU-E WR IP54	-	-	-
911401552232	DN142B 20S/840 PSU-E WR	-	-	-

CoreLine Downlight gen5

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
911401552332	DN142B 20S/840 PSU-E WR IP54	-	-	-

Approval and Application

Order Code	Full Product Name	Flickering value (PstLM) - Flickering value as per EN 61000-3-3
910505103586	DN142B 10S/830 PSD-E WR	-
910505103587	DN142B 10S/830 PSD-E WR IP54	-
910505103590	DN142B 10S/840 PSD-E WR	-
910505103591	DN142B 10S/840 PSD-E WR IP54	-
910505103603	DN142B 10S/830 PSD-E WR ELB3	-
910505103605	DN142B 10S/840 PSD-E WR ELB3	-
911401551032	DN142B 10S/830 PSU-E WR	0.5
911401551132	DN142B 10S/830 PSU-E WR IP54	0.5
911401551432	DN142B 10S/840 PSU-E WR	0.5
911401551532	DN142B 10S/840 PSU-E WR IP54	0.5
910505103596	DN142B 20S/830 PSD-E UGR19	-
910505103597	DN142B 20S/830 PSD-E UGR19 IP54	-
910505103601	DN142B 20S/840 PSD-E UGR19	-
910505103602	DN142B 20S/840 PSD-E UGR19 IP54	-
910505103608	DN142B 20S/830 PSD-E UGR19 ELB3	-
910505103610	DN142B 20S/840 PSD-E UGR19 ELB3	-
910505103612	DN142B 20S/830 WIA-E UGR19 IP54	-
910505103614	DN142B 20S/840 WIA-E UGR19 IP54	-
910505103616	DN142B 20S/830 WIA-E UGR19 ELB3 IP54	-
910505103618	DN142B 20S/840 WIA-E UGR19 ELB3 IP54	-
911401552032	DN142B 20S/830 PSU-E UGR19	0.5
911401552132	DN142B 20S/830 PSU-E UGR19 IP54	0.5
911401552432	DN142B 20S/840 PSU-E UGR19	0.5
911401552532	DN142B 20S/840 PSU-E UGR19 IP54	0.5

Order Code	Full Product Name	Flickering value (PstLM) - Flickering value as per EN 61000-3-3
910505103588	DN142B 10S/830 PSD-E UGR19	-
910505103589	DN142B 10S/830 PSD-E UGR19 IP54	-
910505103592	DN142B 10S/840 PSD-E UGR19	-
910505103593	DN142B 10S/840 PSD-E UGR19 IP54	-
910505103604	DN142B 10S/830 PSD-E UGR19 ELB3	-
910505103606	DN142B 10S/840 PSD-E UGR19 ELB3	-
911401551232	DN142B 10S/830 PSU-E UGR19	0.5
911401551332	DN142B 10S/830 PSU-E UGR19 IP54	0.5
911401551632	DN142B 10S/840 PSU-E UGR19	0.5
911401551732	DN142B 10S/840 PSU-E UGR19 IP54	0.5
910505103594	DN142B 20S/830 PSD-E WR	-
910505103595	DN142B 20S/830 PSD-E WR IP54	-
910505103598	DN142B 20S/840 PSD-E WR	-
910505103599	DN142B 20S/840 PSD-E WR IP54	-
910505103607	DN142B 20S/830 PSD-E WR ELB3	-
910505103609	DN142B 20S/840 PSD-E WR ELB3	-
910505103611	DN142B 20S/830 WIA-E WR IP54	-
910505103613	DN142B 20S/840 WIA-E WR IP54	-
910505103615	DN142B 20S/830 WIA-E WR ELB3 IP54	-
910505103617	DN142B 20S/840 WIA-E WR ELB3 IP54	-
911401551832	DN142B 20S/830 PSU-E WR	0.5
911401551932	DN142B 20S/830 PSU-E WR IP54	0.5
911401552232	DN142B 20S/840 PSU-E WR	0.5
911401552332	DN142B 20S/840 PSU-E WR IP54	0.5

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
910505103586	DN142B 10S/830 PSD-E WR	(0.432,0.404) SDCM≤5	-10% / +10%
910505103587	DN142B 10S/830 PSD-E WR IP54	(0.435,0.405) SDCM≤5	-10% / +10%
910505103590	DN142B 10S/840 PSD-E WR	(0.380,0.377) SDCM≤5	-10% / +10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
910505103591	DN142B 10S/840 PSD-E WR IP54	(0.380,0.377) SDCM≤5	-10% / +10%
910505103603	DN142B 10S/830 PSD-E WR ELB3	(0.435,0.405) SDCM≤5	-10% / +10%
910505103605	DN142B 10S/840 PSD-E WR ELB3	(0.380,0.377) SDCM≤5	-10% / +10%

CoreLine Downlight gen5

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401551032	DN142B 10S/830 PSU-E WR	(0.432,0.404) SDCM \leq 5	+/-10%
911401551132	DN142B 10S/830 PSU-E WR IP54	(0.435,0.405) SDCM \leq 5	+/-10%
911401551432	DN142B 10S/840 PSU-E WR	(0.380,0.377) SDCM \leq 5	+/-10%
911401551532	DN142B 10S/840 PSU-E WR IP54	(0.380,0.377) SDCM \leq 5	+/-10%
910505103596	DN142B 20S/830 PSD-E UGR19	(0.435,0.404) SDCM \leq 5	-10% / +10%
910505103597	DN142B 20S/830 PSD-E UGR19 IP54	(0.435,0.404) SDCM \leq 5	-10% / +10%
910505103601	DN142B 20S/840 PSD-E UGR19	(0.380,0.377) SDCM \leq 5	-10% / +10%
910505103602	DN142B 20S/840 PSD-E UGR19 IP54	(0.380,0.377) SDCM \leq 5	-10% / +10%
910505103608	DN142B 20S/830 PSD-E UGR19 ELB3	(0.435,0.404) SDCM \leq 5	-10% / +10%
910505103610	DN142B 20S/840 PSD-E UGR19 ELB3	(0.380,0.377) SDCM \leq 5	-10% / +10%
910505103612	DN142B 20S/830 WIA-E UGR19 IP54	(0.435,0.404) SDCM \leq 5	-10% / +10%
910505103614	DN142B 20S/840 WIA-E UGR19 IP54	(0.380,0.377) SDCM \leq 5	-10% / +10%
910505103616	DN142B 20S/830 WIA-E UGR19 ELB3 IP54	(0.435,0.404) SDCM \leq 5	-10% / +10%
910505103618	DN142B 20S/840 WIA-E UGR19 ELB3 IP54	(0.380,0.377) SDCM \leq 5	-10% / +10%
911401552032	DN142B 20S/830 PSU-E UGR19	(0.435,0.404) SDCM \leq 5	+/-10%
911401552132	DN142B 20S/830 PSU-E UGR19 IP54	(0.435,0.404) SDCM \leq 5	+/-10%
911401552432	DN142B 20S/840 PSU-E UGR19	(0.380,0.377) SDCM \leq 5	+/-10%
911401552532	DN142B 20S/840 PSU-E UGR19 IP54	(0.380,0.377) SDCM \leq 5	+/-10%
910505103588	DN142B 10S/830 PSD-E UGR19	(0.432,0.404) SDCM \leq 5	-10% / +10%
910505103589	DN142B 10S/830 PSD-E UGR19 IP54	(0.435,0.405) SDCM \leq 5	-10% / +10%
910505103592	DN142B 10S/840 PSD-E UGR19	(0.380,0.377) SDCM \leq 5	-10% / +10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
910505103593	DN142B 10S/840 PSD-E UGR19 IP54	(0.380,0.377) SDCM \leq 5	-10% / +10%
910505103604	DN142B 10S/830 PSD-E UGR19 ELB3	(0.435,0.405) SDCM \leq 5	-10% / +10%
910505103606	DN142B 10S/840 PSD-E UGR19 ELB3	(0.380,0.377) SDCM \leq 5	-10% / +10%
911401551232	DN142B 10S/830 PSU-E UGR19	(0.435,0.404) SDCM \leq 5	+/-10%
911401551332	DN142B 10S/830 PSU-E UGR19 IP54	(0.435,0.405) SDCM \leq 5	+/-10%
911401551632	DN142B 10S/840 PSU-E UGR19	(0.380,0.377) SDCM \leq 5	+/-10%
911401551732	DN142B 10S/840 PSU-E UGR19 IP54	(0.380,0.377) SDCM \leq 5	+/-10%
910505103594	DN142B 20S/830 PSD-E WR	(0.435,0.404) SDCM \leq 5	-10% / +10%
910505103595	DN142B 20S/830 PSD-E WR IP54	(0.435,0.404) SDCM \leq 5	-10% / +10%
910505103598	DN142B 20S/840 PSD-E WR	(0.380,0.377) SDCM \leq 5	-10% / +10%
910505103599	DN142B 20S/840 PSD-E WR IP54	(0.380,0.377) SDCM \leq 5	-10% / +10%
910505103607	DN142B 20S/830 PSD-E WR ELB3	(0.435,0.404) SDCM \leq 5	-10% / +10%
910505103609	DN142B 20S/840 PSD-E WR ELB3	(0.380,0.377) SDCM \leq 5	-10% / +10%
910505103611	DN142B 20S/830 WIA-E WR IP54	(0.435,0.404) SDCM \leq 5	-10% / +10%
910505103613	DN142B 20S/840 WIA-E WR IP54	(0.380,0.377) SDCM \leq 5	-10% / +10%
910505103615	DN142B 20S/830 WIA-E WR ELB3 IP54	(0.435,0.404) SDCM \leq 5	-10% / +10%
910505103617	DN142B 20S/840 WIA-E WR ELB3 IP54	(0.380,0.377) SDCM \leq 5	-10% / +10%
911401551832	DN142B 20S/830 PSU-E WR	(0.435,0.404) SDCM \leq 5	+/-10%
911401551932	DN142B 20S/830 PSU-E WR IP54	(0.435,0.404) SDCM \leq 5	+/-10%
911401552232	DN142B 20S/840 PSU-E WR	(0.380,0.377) SDCM \leq 5	+/-10%
911401552332	DN142B 20S/840 PSU-E WR IP54	(0.380,0.377) SDCM \leq 5	+/-10%

Product Data

Order Code	Full Product Name	Product family code
910505103586	DN142B 10S/830 PSD-E WR	DN142B
910505103587	DN142B 10S/830 PSD-E WR IP54	DN142B
910505103590	DN142B 10S/840 PSD-E WR	DN142B
910505103591	DN142B 10S/840 PSD-E WR IP54	DN142B
910505103603	DN142B 10S/830 PSD-E WR ELB3	DN142B


Order Code	Full Product Name	Product family code
910505103605	DN142B 10S/840 PSD-E WR ELB3	DN142B
911401551032	DN142B 10S/830 PSU-E WR	-
911401551132	DN142B 10S/830 PSU-E WR IP54	-
911401551432	DN142B 10S/840 PSU-E WR	-
911401551532	DN142B 10S/840 PSU-E WR IP54	-

CoreLine Downlight gen5


Order Code	Full Product Name	Product family code
910505103596	DN142B 20S/830 PSD-E UGR19	DN142B
910505103597	DN142B 20S/830 PSD-E UGR19 IP54	DN142B
910505103601	DN142B 20S/840 PSD-E UGR19	DN142B
910505103602	DN142B 20S/840 PSD-E UGR19 IP54	DN142B
910505103608	DN142B 20S/830 PSD-E UGR19 ELB3	DN142B
910505103610	DN142B 20S/840 PSD-E UGR19 ELB3	DN142B
910505103612	DN142B 20S/830 WIA-E UGR19 IP54	DN142B
910505103614	DN142B 20S/840 WIA-E UGR19 IP54	DN142B
910505103616	DN142B 20S/830 WIA-E UGR19 ELB3 IP54	DN142B
910505103618	DN142B 20S/840 WIA-E UGR19 ELB3 IP54	DN142B
911401552032	DN142B 20S/830 PSU-E UGR19	-
911401552132	DN142B 20S/830 PSU-E UGR19 IP54	-
911401552432	DN142B 20S/840 PSU-E UGR19	-
911401552532	DN142B 20S/840 PSU-E UGR19 IP54	-
910505103588	DN142B 10S/830 PSD-E UGR19	DN142B
910505103589	DN142B 10S/830 PSD-E UGR19 IP54	DN142B
910505103592	DN142B 10S/840 PSD-E UGR19	DN142B
910505103593	DN142B 10S/840 PSD-E UGR19 IP54	DN142B
910505103604	DN142B 10S/830 PSD-E UGR19 ELB3	DN142B

Order Code	Full Product Name	Product family code
910505103606	DN142B 10S/840 PSD-E UGR19 ELB3	DN142B
911401551232	DN142B 10S/830 PSU-E UGR19	-
911401551332	DN142B 10S/830 PSU-E UGR19 IP54	-
911401551632	DN142B 10S/840 PSU-E UGR19	-
911401551732	DN142B 10S/840 PSU-E UGR19 IP54	-
910505103594	DN142B 20S/830 PSD-E WR	DN142B
910505103595	DN142B 20S/830 PSD-E WR IP54	DN142B
910505103598	DN142B 20S/840 PSD-E WR	DN142B
910505103599	DN142B 20S/840 PSD-E WR IP54	DN142B
910505103607	DN142B 20S/830 PSD-E WR ELB3	DN142B
910505103609	DN142B 20S/840 PSD-E WR ELB3	DN142B
910505103611	DN142B 20S/830 WIA-E WR IP54	DN142B
910505103613	DN142B 20S/840 WIA-E WR IP54	DN142B
910505103615	DN142B 20S/830 WIA-E WR ELB3 IP54	DN142B
910505103617	DN142B 20S/840 WIA-E WR ELB3 IP54	DN142B
911401551832	DN142B 20S/830 PSU-E WR	-
911401551932	DN142B 20S/830 PSU-E WR IP54	-
911401552232	DN142B 20S/840 PSU-E WR	-
911401552332	DN142B 20S/840 PSU-E WR IP54	-


Polar Wide Diagrams




Polar Normal (separate) - DN142BI - 910505103586




Polar Normal (separate) - DN142BI - 910505103618




Polar Normal (separate) - DN142BI - 910505103597



Polar Normal (separate) - DN142BI - 910505103605




Polar Normal (separate) - DN142BI - 910505103603




Polar Normal (separate) - DN142BI - 910505103591

CoreLine Downlight gen5


Polar Wide Diagrams




Polar Normal (separate) - DN142BI - 910505103607




Polar Normal (separate) - DN142BI - 910505103615




Polar Normal (separate) - DN142BI - 910505103611




Polar Normal (separate) - DN142BI - 910505103596




Polar Normal (separate) - DN142BI - 910505103616




Polar Normal (separate) - DN142BI - 910505103612



Polar Normal (separate) - DN142BI - 910505103601




Polar Normal (separate) - DN142BI - 910505103589




Polar Normal (separate) - DN142BI - 910505103604

CoreLine Downlight gen5


Polar Wide Diagrams




Polar Normal (separate) - DN142BI - 910505103590




Polar Normal (separate) - DN142BI - 910505103595




Polar Normal (separate) - DN142BI - 910505103593




Polar Normal (separate) - DN142BI - 910505103613




Polar Normal (separate) - DN142BI - 910505103592




Polar Normal (separate) - DN142BI - 910505103602



Polar Normal (separate) - DN142BI - 910505103614




Polar Normal (separate) - DN142BI - 910505103608




Polar Normal (separate) - DN142BI - 910505103594

CoreLine Downlight gen5


Polar Wide Diagrams




Polar Normal (separate) - DN142BI - 910505103610




Polar Normal (separate) - DN142BI - 910505103599




Polar Normal (separate) - DN142BI - 910505103587




Polar Normal (separate) - DN142BI - 910505103609




Polar Normal (separate) - DN142BI - 910505103598




Polar Normal (separate) - DN142BI - 910505103617




Polar Normal (separate) - DN142BI - 910505103606



Polar Normal (separate) - DN142BI - 910505103588




Polar Normal (separate) - 911401551032




Polar Normal (separate) - 911401551132

CoreLine Downlight gen5


Polar Wide Diagrams




Polar Normal (separate) - 911401551232




Polar Normal (separate) - 911401551332




Polar Normal (separate) - 911401551432




Polar Normal (separate) - 911401551532




Polar Normal (separate) - 911401551732




Polar Normal (separate) - 911401551632




Polar Normal (separate) - 911401551832




Polar Normal (separate) - 911401551932




Polar Normal (separate) - 911401552032



Polar Normal (separate) - 911401552132





Polar Normal (separate) - 911401552232



Polar Normal (separate) - 911401552332

CoreLine Downlight gen5

Polar Wide Diagrams



Polar Normal (separate) - 911401552432

Polar Normal (separate) - 911401552532

