

LuxSpace Compact, recessed

DN610B



LuxSpace Compact, recessed: UltraEfficient , stylish, and designed for circularity

Philips LuxSpace is designed to provide the perfect combination of efficiency, high visual comfort, and stylish design without compromising on lighting performance. LuxSpace offers a long lifetime and efficacy of up to 185 lm/W, along with excellent color rendering and light distribution which have a major influence on the visual and non-visual effects of light on human health and well-being. The LuxSpace downlight family offers a wide choice of options for creating the desired ambience and supporting user comfort, no matter what the application is. For office applications, LuxSpace offers dedicated tunable white luminaires with lighting controls for circadian lighting solutions and office-compliant versions (UGR19).

Benefits

- Best-in-class efficacy of up to 185 lm/ W
- Gentle, natural light ensures visual comfort
- Extensive design options with mounting types, rim colors, and reflectors
- Perfect ceiling integration with narrow rim or rimless versions for plaster ceilings
- Improved glare control complies with office lighting standards
- High color rendering up to CRI 90 (R9>50)

- Provides uniform lighting thanks to wide light distribution
- Supports circadian lighting solutions with tunable white luminaires and integrated lighting controls

Applications

- Offices
- Retail
- Hospitals and Care Centers
- Hospitality
- Airports

- Municipal Buildings
- Atriums

Features

- Mini (DN560B/DN561B), Compact (DN610B) and Square (DN572B) types for recessed applications
- Surface-mounted round (DN570C/DN571C) versions
- Choice of five optics: high gloss, faded lines, matte, white and black

- UGR19 is standard for Compact and optional for other versions
- White (RAL9003), gray (RAL9006), and black (RAL9004) are standard, with any other RAL color possible upon request
- Compliant for central emergency lighting with DC (PSED driver type)
- Multiple additional options: PG and PGO (IP54 front face), emergency lighting (single battery 3 hours), through-wiring, Eca and B2ca cable and connector options
- Extended useful lifetime of 50,000 hours at L90

Versions



LuxSpace Compact, Recessed
- Faded lines reflector, Black
Rim



LuxSpace Compact, Recessed
- Matt reflector, White Rim



LuxSpace Compact, Recessed
- Faded lines reflector, White
Rim



LuxSpace Compact, Recessed
- Matt reflector, Silver Rim



LuxSpace Compact, Recessed
- Protection Glass



LuxSpace Compact, Recessed
- Matt reflector, Black Rim

LuxSpace Compact, Recessed
- Clear reflector, Black Rim



LuxSpace Compact, Recessed
- Clear reflector, Silver Rim



LuxSpace Compact, Recessed
- Clear reflector, White Rim, 240mm cut-out



LuxSpace Compact, Recessed
- Black reflector, Black Rim



LuxSpace Compact, Recessed
- Clear reflector, White Rim, 225mm cut-out



LuxSpace Compact, Recessed
- Faded lines reflector, White Rim



LuxSpace Compact, Recessed
- Matt reflector, Rimless



LuxSpace Compact, Recessed
- Faded lines reflector, Silver Rim



LuxSpace Compact, Recessed
- Black reflector, White Rim



LuxSpace Compact, Recessed
- Protection Glass Opal






LuxSpace Compact, Recessed
- Clear reflector, White Rim,
240mm cut-out



LuxSpace Compact, Recessed
- White reflector, White Rim

Dimensional drawing



DN610B 20S/840UE PSU-E C RAD225 WH

Product details



LuxSpace Compact, Recessed
- Black reflector, Black Rim



LuxSpace Compact, Recessed
- Matt reflector, Rimless



LuxSpace Compact, Recessed
- Rimless accessory



LuxSpace Compact, Recessed
- Black reflector, White Rim



LuxSpace Compact, Recessed
- White adaptor ring 240mm cut-out



LuxSpace Compact, Recessed
- Silver adaptor ring 240mm cut-out



LuxSpace Compact, Recessed
- White adaptor ring 225mm cut-out



LuxSpace Compact, Recessed
- Black reflector, Black Rim



LuxSpace Compact, Recessed
- Faded lines reflector, White Rim, Tunable-white



LuxSpace Compact, Recessed
- Black adaptor ring 240mm cut-out



LuxSpace Compact, Recessed
- Clear reflector, White Rim



LuxSpace Compact, Recessed
- Matt reflector, Silver Rim

General Information

Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Optic type	-
------------	---

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No
Protection class IEC	Safety class II

Emergency Operation

Central Emergency	No
Emergency lighting	Emergency lighting 3 hours duration Pro version

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
Ambient temperature range	+10 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
-------------------------	-------------

Product Data

Product family code	DN610B [LuxSpace Compact, recessed]
---------------------	-------------------------------------

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)
910505104698	DN610B 20S/840UE PSU-E FLR BK	2,000 lm	4000 K	185 lm/W	>80
910505104680	DN610B 20S/840 PSU-E M WH	2,100 lm	4000 K	117 lm/W	>80
910505104685	DN610B 24S/840 PSU-E M WH	2,300 lm	4000 K	116 lm/W	>80
910505104757	DN610B 40S/TWH DIA-E C WH	4,000 lm	Tunable white 2700-6500 K	121 lm/W	80
910505104704	DN610B 20S/840 PSU-E M SI	2,100 lm	4000 K	117 lm/W	>80
910505104693	DN610B 20S/840UE PSU-E C WH PG	2,000 lm	4000 K	185 lm/W	>80
910505104695	DN610B 24S/840UE PSU-E C WH PG	2,500 lm	4000 K	187 lm/W	>80
910505104699	DN610B 20S/840 PSU-E M BK	2,100 lm	4000 K	117 lm/W	>80
910505104697	DN610B 20S/840UE PSU-E C BK	2,000 lm	4000 K	185 lm/W	>80
910505104702	DN610B 20S/840UE PSU-E C SI	2,000 lm	4000 K	185 lm/W	>80
910505104753	DN610B 20S/840UE PSU-E C RAD240 WH	2,000 lm	4000 K	185 lm/W	>80
910505104701	DN610B 20S/840 PSU-E BKR BK	2,200 lm	4000 K	96 lm/W	>80
910505104752	DN610B 20S/840UE PSU-E C RAD225 WH	2,000 lm	4000 K	185 lm/W	>80

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)
910505104678	DN610B 20S/840UE PSU-E FLR WH	2,000 lm	4000 K	185 lm/W	>80
910505104683	DN610B 24S/840UE PSU-E FLR WH	2,500 lm	4000 K	187 lm/W	>80
910505104706	DN610B 20S/830UE PSU-E FLR WH	1,950 lm	3000 K	181 lm/W	>80
910505104709	DN610B 24S/830UE PSU-E FLR WH	2,400 lm	3000 K	179 lm/W	>80
910505104755	DN610B 20S/940UE PSU-E FLR WH	1,900 lm	4000 K	176 lm/W	>90
910505104751	DN610B 20S/840UE PSU-E C RML	2,000 lm	4000 K	185 lm/W	>80
910505104703	DN610B 20S/840UE PSU-E FLR SI	2,000 lm	4000 K	185 lm/W	>80
910505104681	DN610B 20S/840 PSU-E BKR WH	2,300 lm	4000 K	98 lm/W	>80
910505104686	DN610B 24S/840 PSU-E BKR WH	2,700 lm	4000 K	95 lm/W	>80
910505104694	DN610B 20S/840UE PSU-E C WH PGO	2,000 lm	4000 K	185 lm/W	>80
910505104696	DN610B 24S/840UE PSU-E C WH PGO	2,500 lm	4000 K	187 lm/W	>80
910505104677	DN610B 20S/840UE PSU-E C WH	2,000 lm	4000 K	185 lm/W	>80
910505104682	DN610B 24S/840UE PSU-E C WH	2,500 lm	4000 K	187 lm/W	>80
910505104687	DN610B 40S/840UE PSU-E C WH	4,200 lm	4000 K	168 lm/W	>80
910505104691	DN610B 60S/840UE PSU-E C WH	5,900 lm	4000 K	159 lm/W	>80
910505104705	DN610B 20S/830UE PSU-E C WH	1,950 lm	3000 K	181 lm/W	>80
910505104708	DN610B 24S/830UE PSU-E C WH	2,400 lm	3000 K	179 lm/W	>80
910505104716	DN610B 20S/840UE PSD-E C WH	2,100 lm	4000 K	162 lm/W	>80
910505104719	DN610B 24S/840UE PSD-E C WH	2,500 lm	4000 K	169 lm/W	>80
910505104722	DN610B 40S/840UE PSD-E C WH	4,200 lm	4000 K	162 lm/W	>80
910505104725	DN610B 20S/840UE DIA-E C WH	2,200 lm	4000 K	169 lm/W	>80
910505104728	DN610B 20S/840UE DIA-VLC-E C WH	2,200 lm	4000 K	169 lm/W	>80
910505104731	DN610B 60S/840UE PSD-E C WH	5,900 lm	4000 K	157 lm/W	>80
910505104733	DN610B 20S/840UE PSU-E C ELP3 WH	2,000 lm	4000 K	185 lm/W	>80
910505104736	DN610B 24S/840UE PSU-E C ELP3 WH	2,400 lm	4000 K	179 lm/W	>80
910505104739	DN610B 40S/840UE PSU-E C ELP3 WH	4,200 lm	4000 K	168 lm/W	>80
910505104742	DN610B 20S/840UE WIA-E C WH	2,200 lm	4000 K	159 lm/W	>80
910505104745	DN610B 24S/840UE WIA-E C WH	2,500 lm	4000 K	158 lm/W	>80
910505104748	DN610B 40S/840UE WIA-E C WH	4,200 lm	4000 K	142 lm/W	>80
910505104754	DN610B 20S/940UE PSU-E C WH	1,900 lm	4000 K	176 lm/W	>90
910505104679	DN610B 20S/840UE PSU-E WR WH	2,000 lm	4000 K	185 lm/W	>80
910505104684	DN610B 24S/840UE PSU-E WR WH	2,300 lm	4000 K	172 lm/W	>80
910505104707	DN610B 20S/830UE PSU-E WR WH	1,950 lm	3000 K	181 lm/W	>80
910505104710	DN610B 24S/830UE PSU-E WR WH	2,200 lm	3000 K	164 lm/W	>80

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910505104698	DN610B 20S/840UE PSU-E FLR BK	10.8 W
910505104680	DN610B 20S/840 PSU-E M WH	18 W
910505104685	DN610B 24S/840 PSU-E M WH	19.8 W

Order Code	Full Product Name	Power Consumption
910505104757	DN610B 40S/TWH DIA-E C WH	33 W
910505104704	DN610B 20S/840 PSU-E M SI	18 W
910505104693	DN610B 20S/840UE PSU-E C WH PG	10.8 W
910505104695	DN610B 24S/840UE PSU-E C WH PG	13.4 W
910505104699	DN610B 20S/840 PSU-E M BK	18 W
910505104697	DN610B 20S/840UE PSU-E C BK	10.8 W
910505104702	DN610B 20S/840UE PSU-E C SI	10.8 W
910505104753	DN610B 20S/840UE PSU-E C RAD240 WH	10.8 W
910505104701	DN610B 20S/840 PSU-E BKR BK	23 W
910505104752	DN610B 20S/840UE PSU-E C RAD225 WH	10.8 W
910505104678	DN610B 20S/840UE PSU-E FLR WH	10.8 W
910505104683	DN610B 24S/840UE PSU-E FLR WH	13.4 W
910505104706	DN610B 20S/830UE PSU-E FLR WH	10.8 W
910505104709	DN610B 24S/830UE PSU-E FLR WH	13.4 W
910505104755	DN610B 20S/940UE PSU-E FLR WH	10.8 W
910505104751	DN610B 20S/840UE PSU-E C RML	10.8 W
910505104703	DN610B 20S/840UE PSU-E FLR SI	10.8 W
910505104681	DN610B 20S/840 PSU-E BKR WH	23.5 W
910505104686	DN610B 24S/840 PSU-E BKR WH	28.5 W
910505104694	DN610B 20S/840UE PSU-E C WH PGO	10.8 W
910505104696	DN610B 24S/840UE PSU-E C WH PGO	13.4 W
910505104677	DN610B 20S/840UE PSU-E C WH	10.8 W
910505104682	DN610B 24S/840UE PSU-E C WH	13.4 W
910505104687	DN610B 40S/840UE PSU-E C WH	25 W
910505104691	DN610B 60S/840UE PSU-E C WH	37 W
910505104705	DN610B 20S/830UE PSU-E C WH	10.8 W
910505104708	DN610B 24S/830UE PSU-E C WH	13.4 W
910505104716	DN610B 20S/840UE PSD-E C WH	13 W
910505104719	DN610B 24S/840UE PSD-E C WH	14.8 W
910505104722	DN610B 40S/840UE PSD-E C WH	26 W
910505104725	DN610B 20S/840UE DIA-E C WH	13 W
910505104728	DN610B 20S/840UE DIA-VLC-E C WH	13 W
910505104731	DN610B 60S/840UE PSD-E C WH	37.5 W
910505104733	DN610B 20S/840UE PSU-E C ELP3 WH	10.8 W
910505104736	DN610B 24S/840UE PSU-E C ELP3 WH	13.4 W
910505104739	DN610B 40S/840UE PSU-E C ELP3 WH	25 W
910505104742	DN610B 20S/840UE WIA-E C WH	13.8 W
910505104745	DN610B 24S/840UE WIA-E C WH	15.8 W
910505104748	DN610B 40S/840UE WIA-E C WH	29.5 W
910505104754	DN610B 20S/940UE PSU-E C WH	10.8 W
910505104679	DN610B 20S/840UE PSU-E WR WH	10.8 W
910505104684	DN610B 24S/840UE PSU-E WR WH	13.4 W
910505104707	DN610B 20S/830UE PSU-E WR WH	10.8 W
910505104710	DN610B 24S/830UE PSU-E WR WH	13.4 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
910505104698	DN610B 20S/840UE PSU-E FLR BK	No
910505104680	DN610B 20S/840 PSU-E M WH	No
910505104685	DN610B 24S/840 PSU-E M WH	No
910505104757	DN610B 40S/TWH DIA-E C WH	Yes
910505104704	DN610B 20S/840 PSU-E M SI	No
910505104693	DN610B 20S/840UE PSU-E C WH PG	No
910505104695	DN610B 24S/840UE PSU-E C WH PG	No
910505104699	DN610B 20S/840 PSU-E M BK	No
910505104697	DN610B 20S/840UE PSU-E C BK	No
910505104702	DN610B 20S/840UE PSU-E C SI	No
910505104753	DN610B 20S/840UE PSU-E C RAD240 WH	No
910505104701	DN610B 20S/840 PSU-E BKR BK	No
910505104752	DN610B 20S/840UE PSU-E C RAD225 WH	No
910505104678	DN610B 20S/840UE PSU-E FLR WH	No
910505104683	DN610B 24S/840UE PSU-E FLR WH	No
910505104706	DN610B 20S/830UE PSU-E FLR WH	No
910505104709	DN610B 24S/830UE PSU-E FLR WH	No
910505104755	DN610B 20S/940UE PSU-E FLR WH	No
910505104751	DN610B 20S/840UE PSU-E C RML	No
910505104703	DN610B 20S/840UE PSU-E FLR SI	No
910505104681	DN610B 20S/840 PSU-E BKR WH	No
910505104686	DN610B 24S/840 PSU-E BKR WH	No
910505104694	DN610B 20S/840UE PSU-E C WH PGO	No
910505104696	DN610B 24S/840UE PSU-E C WH PGO	No
910505104677	DN610B 20S/840UE PSU-E C WH	No
910505104682	DN610B 24S/840UE PSU-E C WH	No
910505104687	DN610B 40S/840UE PSU-E C WH	No
910505104691	DN610B 60S/840UE PSU-E C WH	No
910505104705	DN610B 20S/830UE PSU-E C WH	No
910505104708	DN610B 24S/830UE PSU-E C WH	No
910505104716	DN610B 20S/840UE PSD-E C WH	Yes
910505104719	DN610B 24S/840UE PSD-E C WH	Yes
910505104722	DN610B 40S/840UE PSD-E C WH	Yes
910505104725	DN610B 20S/840UE DIA-E C WH	Yes
910505104728	DN610B 20S/840UE DIA-VLC-E C WH	Yes
910505104731	DN610B 60S/840UE PSD-E C WH	Yes
910505104733	DN610B 20S/840UE PSU-E C ELP3 WH	No
910505104736	DN610B 24S/840UE PSU-E C ELP3 WH	No
910505104739	DN610B 40S/840UE PSU-E C ELP3 WH	No
910505104742	DN610B 20S/840UE WIA-E C WH	Yes
910505104745	DN610B 24S/840UE WIA-E C WH	Yes

Order Code	Full Product Name	Dimmable
910505104748	DN610B 40S/840UE WIA-E C WH	Yes
910505104754	DN610B 20S/940UE PSU-E C WH	No
910505104679	DN610B 20S/840UE PSU-E WR WH	No
910505104684	DN610B 24S/840UE PSU-E WR WH	No
910505104707	DN610B 20S/830UE PSU-E WR WH	No
910505104710	DN610B 24S/830UE PSU-E WR WH	No

Mechanical and Housing

Order Code	Full Product Name	Housing Color	Ingress protection code	Mech. impact protection code
910505104698	DN610B 20S/840UE PSU-E FLR BK	Black	IP20	IK03
910505104680	DN610B 20S/840 PSU-E M WH	White	IP20	IK03
910505104685	DN610B 24S/840 PSU-E M WH	White	IP20	IK03
910505104757	DN610B 40S/TWH DIA-E C WH	White	IP20	IK02
910505104704	DN610B 20S/840 PSU-E M SI	Silver	IP20	IK03
910505104693	DN610B 20S/840UE PSU-E C WH PG	White	IP20/54	IK03
910505104695	DN610B 24S/840UE PSU-E C WH PG	White	IP20/54	IK03
910505104699	DN610B 20S/840 PSU-E M BK	Black	IP20	IK03
910505104697	DN610B 20S/840UE PSU-E C BK	Black	IP20	IK03
910505104702	DN610B 20S/840UE PSU-E C SI	Silver	IP20	IK03
910505104753	DN610B 20S/840UE PSU-E C RAD240 WH	White	IP20	IK03
910505104701	DN610B 20S/840 PSU-E BKR BK	Black	IP20	IK03
910505104752	DN610B 20S/840UE PSU-E C RAD225 WH	White	IP20	IK03
910505104678	DN610B 20S/840UE PSU-E FLR WH	White	IP20	IK03
910505104683	DN610B 24S/840UE PSU-E FLR WH	White	IP20	IK03
910505104706	DN610B 20S/830UE PSU-E FLR WH	White	IP20	IK03
910505104709	DN610B 24S/830UE PSU-E FLR WH	White	IP20	IK03
910505104755	DN610B 20S/940UE PSU-E FLR WH	White	IP20	IK03
910505104751	DN610B 20S/840UE PSU-E C RML	White	IP20	IK03
910505104703	DN610B 20S/840UE PSU-E FLR SI	Silver	IP20	IK03
910505104681	DN610B 20S/840 PSU-E BKR WH	White	IP20	IK03
910505104686	DN610B 24S/840 PSU-E BKR WH	White	IP20	IK03
910505104694	DN610B 20S/840UE PSU-E C WH PGO	White	IP20/54	IK03
910505104696	DN610B 24S/840UE PSU-E C WH PGO	White	IP20/54	IK03
910505104677	DN610B 20S/840UE PSU-E C WH	White	IP20	IK03
910505104682	DN610B 24S/840UE PSU-E C WH	White	IP20	IK03
910505104687	DN610B 40S/840UE PSU-E C WH	White	IP20	IK02
910505104691	DN610B 60S/840UE PSU-E C WH	White	IP20	IK02
910505104705	DN610B 20S/830UE PSU-E C WH	White	IP20	IK03
910505104708	DN610B 24S/830UE PSU-E C WH	White	IP20	IK03
910505104716	DN610B 20S/840UE PSD-E C WH	White	IP20	IK02
910505104719	DN610B 24S/840UE PSD-E C WH	White	IP20	IK02
910505104722	DN610B 40S/840UE PSD-E C WH	White	IP20	IK02

Order Code	Full Product Name	Housing Color	Ingress protection code	Mech. impact protection code
910505104725	DN610B 20S/840UE DIA-E C WH	White	IP20	IK02
910505104728	DN610B 20S/840UE DIA-VLC-E C WH	White	IP20	IK02
910505104731	DN610B 60S/840UE PSD-E C WH	White	IP20	IK02
910505104733	DN610B 20S/840UE PSU-E C ELP3 WH	White	IP20	IK03
910505104736	DN610B 24S/840UE PSU-E C ELP3 WH	White	IP20	IK03
910505104739	DN610B 40S/840UE PSU-E C ELP3 WH	White	IP20	IK03
910505104742	DN610B 20S/840UE WIA-E C WH	White	IP20	IK02
910505104745	DN610B 24S/840UE WIA-E C WH	White	IP20	IK02
910505104748	DN610B 40S/840UE WIA-E C WH	White	IP20	IK02
910505104754	DN610B 20S/940UE PSU-E C WH	White	IP20	IK03
910505104679	DN610B 20S/840UE PSU-E WR WH	White	IP20	IK03
910505104684	DN610B 24S/840UE PSU-E WR WH	White	IP20	IK03
910505104707	DN610B 20S/830UE PSU-E WR WH	White	IP20	IK03
910505104710	DN610B 24S/830UE PSU-E WR WH	White	IP20	IK03

Approval and Application

Order Code	Full Product Name	ENEC mark
910505104698	DN610B 20S/840UE PSU-E FLR BK	ENEC mark
910505104680	DN610B 20S/840 PSU-E M WH	ENEC mark
910505104685	DN610B 24S/840 PSU-E M WH	ENEC mark
910505104757	DN610B 40S/TWH DIA-E C WH	-
910505104704	DN610B 20S/840 PSU-E M SI	ENEC mark
910505104693	DN610B 20S/840UE PSU-E C WH PG	ENEC mark
910505104695	DN610B 24S/840UE PSU-E C WH PG	ENEC mark
910505104699	DN610B 20S/840 PSU-E M BK	ENEC mark
910505104697	DN610B 20S/840UE PSU-E C BK	ENEC mark
910505104702	DN610B 20S/840UE PSU-E C SI	ENEC mark
910505104753	DN610B 20S/840UE PSU-E C RAD240 WH	ENEC mark
910505104701	DN610B 20S/840 PSU-E BKR BK	ENEC mark
910505104752	DN610B 20S/840UE PSU-E C RAD225 WH	ENEC mark
910505104678	DN610B 20S/840UE PSU-E FLR WH	ENEC mark
910505104683	DN610B 24S/840UE PSU-E FLR WH	ENEC mark
910505104706	DN610B 20S/830UE PSU-E FLR WH	ENEC mark
910505104709	DN610B 24S/830UE PSU-E FLR WH	ENEC mark
910505104755	DN610B 20S/940UE PSU-E FLR WH	ENEC mark
910505104751	DN610B 20S/840UE PSU-E C RML	ENEC mark
910505104703	DN610B 20S/840UE PSU-E FLR SI	ENEC mark
910505104681	DN610B 20S/840 PSU-E BKR WH	ENEC mark
910505104686	DN610B 24S/840 PSU-E BKR WH	ENEC mark
910505104694	DN610B 20S/840UE PSU-E C WH PGO	ENEC mark
910505104696	DN610B 24S/840UE PSU-E C WH PGO	ENEC mark
910505104677	DN610B 20S/840UE PSU-E C WH	ENEC mark


Order Code	Full Product Name	ENEC mark
910505104682	DN610B 24S/840UE PSU-E C WH	ENEC mark
910505104687	DN610B 40S/840UE PSU-E C WH	ENEC mark
910505104691	DN610B 60S/840UE PSU-E C WH	ENEC mark
910505104705	DN610B 20S/830UE PSU-E C WH	ENEC mark
910505104708	DN610B 24S/830UE PSU-E C WH	ENEC mark
910505104716	DN610B 20S/840UE PSD-E C WH	ENEC mark
910505104719	DN610B 24S/840UE PSD-E C WH	ENEC mark
910505104722	DN610B 40S/840UE PSD-E C WH	ENEC mark
910505104725	DN610B 20S/840UE DIA-E C WH	ENEC mark
910505104728	DN610B 20S/840UE DIA-VLC-E C WH	ENEC mark
910505104731	DN610B 60S/840UE PSD-E C WH	ENEC mark
910505104733	DN610B 20S/840UE PSU-E C ELP3 WH	ENEC mark
910505104736	DN610B 24S/840UE PSU-E C ELP3 WH	ENEC mark
910505104739	DN610B 40S/840UE PSU-E C ELP3 WH	ENEC mark
910505104742	DN610B 20S/840UE WIA-E C WH	ENEC mark
910505104745	DN610B 24S/840UE WIA-E C WH	ENEC mark
910505104748	DN610B 40S/840UE WIA-E C WH	ENEC mark
910505104754	DN610B 20S/940UE PSU-E C WH	ENEC mark
910505104679	DN610B 20S/840UE PSU-E WR WH	ENEC mark
910505104684	DN610B 24S/840UE PSU-E WR WH	ENEC mark
910505104707	DN610B 20S/830UE PSU-E WR WH	ENEC mark
910505104710	DN610B 24S/830UE PSU-E WR WH	ENEC mark

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505104698	DN610B 20S/840UE PSU-E FLR BK	(0.38,0.38)
910505104680	DN610B 20S/840 PSU-E M WH	(0.38,0.38)
910505104685	DN610B 24S/840 PSU-E M WH	(0.38,0.38)
910505104757	DN610B 40S/TWH DIA-E C WH	-
910505104704	DN610B 20S/840 PSU-E M SI	(0.38,0.38)
910505104693	DN610B 20S/840UE PSU-E C WH PG	(0.38,0.38)
910505104695	DN610B 24S/840UE PSU-E C WH PG	(0.38,0.38)
910505104699	DN610B 20S/840 PSU-E M BK	(0.38,0.38)
910505104697	DN610B 20S/840UE PSU-E C BK	(0.38,0.38)
910505104702	DN610B 20S/840UE PSU-E C SI	(0.38,0.38)
910505104753	DN610B 20S/840UE PSU-E C RAD240 WH	(0.38,0.38)
910505104701	DN610B 20S/840 PSU-E BKR BK	(0.38,0.38)
910505104752	DN610B 20S/840UE PSU-E C RAD225 WH	(0.38,0.38)
910505104678	DN610B 20S/840UE PSU-E FLR WH	(0.38,0.38)
910505104683	DN610B 24S/840UE PSU-E FLR WH	(0.38,0.38)
910505104706	DN610B 20S/830UE PSU-E FLR WH	(0.44,0.40)
910505104709	DN610B 24S/830UE PSU-E FLR WH	(0.44,0.40)

Order Code	Full Product Name	Initial chromaticity
910505104755	DN610B 20S/940UE PSU-E FLR WH	(0.38,0.38)
910505104751	DN610B 20S/840UE PSU-E C RML	(0.38,0.38)
910505104703	DN610B 20S/840UE PSU-E FLR SI	(0.38,0.38)
910505104681	DN610B 20S/840 PSU-E BKR WH	(0.38,0.38)
910505104686	DN610B 24S/840 PSU-E BKR WH	(0.38,0.38)
910505104694	DN610B 20S/840UE PSU-E C WH PGO	(0.38,0.38)
910505104696	DN610B 24S/840UE PSU-E C WH PGO	(0.38,0.38)
910505104677	DN610B 20S/840UE PSU-E C WH	(0.38,0.38)
910505104682	DN610B 24S/840UE PSU-E C WH	(0.38,0.38)
910505104687	DN610B 40S/840UE PSU-E C WH	(0.38,0.38)
910505104691	DN610B 60S/840UE PSU-E C WH	(0.38,0.38)
910505104705	DN610B 20S/830UE PSU-E C WH	(0.44,0.40)
910505104708	DN610B 24S/830UE PSU-E C WH	(0.44,0.40)
910505104716	DN610B 20S/840UE PSD-E C WH	(0.38,0.38)
910505104719	DN610B 24S/840UE PSD-E C WH	(0.38,0.38)
910505104722	DN610B 40S/840UE PSD-E C WH	(0.38,0.38)
910505104725	DN610B 20S/840UE DIA-E C WH	(0.38,0.38)
910505104728	DN610B 20S/840UE DIA-VLC-E C WH	(0.38,0.38)
910505104731	DN610B 60S/840UE PSD-E C WH	(0.38,0.38)
910505104733	DN610B 20S/840UE PSU-E C ELP3 WH	(0.38,0.38)
910505104736	DN610B 24S/840UE PSU-E C ELP3 WH	(0.38,0.38)
910505104739	DN610B 40S/840UE PSU-E C ELP3 WH	(0.38,0.38)
910505104742	DN610B 20S/840UE WIA-E C WH	(0.38,0.38)
910505104745	DN610B 24S/840UE WIA-E C WH	(0.38,0.38)
910505104748	DN610B 40S/840UE WIA-E C WH	(0.38,0.38)
910505104754	DN610B 20S/940UE PSU-E C WH	(0.38,0.38)
910505104679	DN610B 20S/840UE PSU-E WR WH	(0.38,0.38)
910505104684	DN610B 24S/840UE PSU-E WR WH	(0.38,0.38)
910505104707	DN610B 20S/830UE PSU-E WR WH	(0.44,0.40)
910505104710	DN610B 24S/830UE PSU-E WR WH	(0.44,0.40)


Polar normal diagrams



DN610BI - 910505104691

DN610BI - 910505104678


DN610BI - 910505104693



DN610BI - 910505104696

DN610BI - 910505104757


DN610BI - 910505104677




DN610BI - 910505104753

DN610BI - 910505104728


DN610BI - 910505104736




DN610BI - 910505104708




DN610BI - 910505104751




DN610BI - 910505104704




DN610BI - 910505104701




DN610BI - 910505104733




DN610BI - 910505104695




DN610BI - 910505104686




DN610BI - 910505104698




DN610BI - 910505104680




DN610BI - 910505104697




DN610BI - 910505104682




DN610BI - 910505104687




DN610BI - 910505104694




DN610BI - 910505104683




DN610BI - 910505104681




DN610BI - 910505104685




DN610BI - 910505104679




DN610BI - 910505104684




DN610BI - 910505104722




DN610BI - 910505104719




DN610BI - 910505104706




DN610BI - 910505104754




DN610BI - 910505104739




DN610BI - 910505104707




DN610BI - 910505104752




DN610BI - 910505104703




DN610BI - 910505104731




DN610BI - 910505104755




DN610BI - 910505104716




DN610BI - 910505104748




DN610BI - 910505104702




DN610BI - 910505104745




DN610BI - 910505104705




DN610BI - 910505104709




DN610BI - 910505104699



DN610BI - 910505104742



DN610BI - 910505104725



DN610BI - 910505104710