



# LuxSpace Compact, recessed: UltraEfficient , stylish, and designed for circularity

## LuxSpace Compact, recessed

Philips LuxSpace is designed to provide the perfect combination of efficiency, high visual comfort, and stylish design without compromising on lighting performance. LuxSpace offers a long lifetime and efficacy of up to 185 lm/W, along with excellent color rendering and light distribution which have a major influence on the visual and non-visual effects of light on human health and well-being. The LuxSpace downlight family offers a wide choice of options for creating the desired ambience and supporting user comfort, no matter what the application is. For office applications, LuxSpace offers dedicated tunable white luminaires with lighting controls for circadian lighting solutions and office-compliant versions (UGR19).

### Benefits

- Best-in-class efficacy of up to 185 lm/ W
- Gentle, natural light ensures visual comfort
- Extensive design options with mounting types, rim colors, and reflectors
- Perfect ceiling integration with narrow rim or rimless versions for plaster ceilings
- Improved glare control complies with office lighting standards
- High color rendering up to CRI 90 (R9>50)
- Provides uniform lighting thanks to wide light distribution
- Supports circadian lighting solutions with tunable white luminaires and integrated lighting controls

## LuxSpace Compact, recessed

### Features

- Mini (DN560B/DN561B), Compact (DN610B) and Square (DN572B) types for recessed applications
- Surface-mounted round (DN570C/DN571C) versions
- Choice of five optics: high gloss, faded lines, matte, white and black
- UGR19 is standard for Compact and optional for other versions
- White (RAL9003), gray (RAL9006), and black (RAL9004) are standard, with any other RAL color possible upon request
- Compliant for central emergency lighting with DC (PSED driver type)
- Multiple additional options: PG and PGO (IP54 front face), emergency lighting (single battery 3 hours), through-wiring, Eca and B2ca cable and connector options
- Extended useful lifetime of 50,000 hours at L90

### Application

- Offices
- Retail
- Hospitals and Care Centers
- Hospitality
- Airports
- Municipal Buildings
- Atriums

### Versions

LuxSpace Compact, Recessed -  
Faded lines reflector, Black Rim



LuxSpace Compact, Recessed -  
Matt reflector, White Rim



LuxSpace Compact, Recessed -  
Faded lines reflector, White Rim



LuxSpace Compact, Recessed -  
Matt reflector, Silver Rim



# LuxSpace Compact, recessed

## Versions

LuxSpace Compact, Recessed -  
Matt reflector, Black Rim



LuxSpace Compact, Recessed -  
Clear reflector, Black Rim



LuxSpace Compact, Recessed -  
Clear reflector, Silver Rim



LuxSpace Compact, Recessed -  
Clear reflector, White Rim, 240mm  
cut-out



LuxSpace Compact, Recessed -  
Black reflector, Black Rim



LuxSpace Compact, Recessed -  
Clear reflector, White Rim, 225mm  
cut-out



LuxSpace Compact, Recessed -  
Matt reflector, Rimless



LuxSpace Compact, Recessed -  
Faded lines reflector, Silver Rim




# LuxSpace Compact, recessed

## Versions

LuxSpace Compact, Recessed -  
Black reflector, White Rim



## Dimensional drawing



## Product details

LuxSpace Compact, Recessed -  
Black reflector, Black Rim



LuxSpace Compact, Recessed -  
Matt reflector, Rimless



LuxSpace Compact, Recessed -  
Rimless accessory



LuxSpace Compact, Recessed -  
Black reflector, White Rim



# LuxSpace Compact, recessed

## Product details

LuxSpace Compact, Recessed -  
White adaptor ring 240mm cut-out



LuxSpace Compact, Recessed -  
Silver adaptor ring 240mm cut-out



LuxSpace Compact, Recessed -  
White adaptor ring 225mm cut-out



LuxSpace Compact, Recessed -  
Black reflector, Black Rim



LuxSpace Compact, Recessed -  
Faded lines reflector, White Rim,  
Tunable-white



LuxSpace Compact, Recessed -  
Black adaptor ring 240mm cut-out



LuxSpace Compact, Recessed -  
Clear reflector, White Rim



# LuxSpace Compact, recessed

## Product details

LuxSpace Compact, Recessed -  
Matt reflector, Silver Rim



### General Information

Driver included	Yes
Number of gear units	1 unit

### Light Technical

Optic type	-
------------	---

### Operating and Electrical

Protection class IEC	Safety class II
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No

### Approval and Application

Ambient temperature range	+10 to +35 °C
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s

### Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
-------------------------	-------------

### Product Data

Product family code	DN610B
---------------------	--------

### Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505104698	DN610B 20S/840UE PSU-E FLR BK	4000 K	>80	185 lm/W	2,000 lm
910505104680	DN610B 20S/840 PSU-E M WH	4000 K	>80	117 lm/W	2,100 lm
910505104685	DN610B 24S/840 PSU-E M WH	4000 K	>80	116 lm/W	2,300 lm
910505104757	DN610B 40S/TWH DIA-E C WH	Tunable white 2700-6500 K	80	121 lm/W	4,000 lm
910505104704	DN610B 20S/840 PSU-E M SI	4000 K	>80	117 lm/W	2,100 lm
910505104693	DN610B 20S/840UE PSU-E C WH PG	4000 K	>80	185 lm/W	2,000 lm
910505104695	DN610B 24S/840UE PSU-E C WH PG	4000 K	>80	187 lm/W	2,500 lm
910505104699	DN610B 20S/840 PSU-E M BK	4000 K	>80	117 lm/W	2,100 lm
910505104697	DN610B 20S/840UE PSU-E C BK	4000 K	>80	185 lm/W	2,000 lm
910505104702	DN610B 20S/840UE PSU-E C SI	4000 K	>80	185 lm/W	2,000 lm
910505104753	DN610B 20S/840UE PSU-E C RAD240 WH	4000 K	>80	185 lm/W	2,000 lm
910505104701	DN610B 20S/840 PSU-E BKR BK	4000 K	>80	96 lm/W	2,200 lm
910505104752	DN610B 20S/840UE PSU-E C RAD225 WH	4000 K	>80	185 lm/W	2,000 lm
910505104678	DN610B 20S/840UE PSU-E FLR WH	4000 K	>80	185 lm/W	2,000 lm
910505104683	DN610B 24S/840UE PSU-E FLR WH	4000 K	>80	187 lm/W	2,500 lm
910505104706	DN610B 20S/830UE PSU-E FLR WH	3000 K	>80	181 lm/W	1,950 lm
910505104709	DN610B 24S/830UE PSU-E FLR WH	3000 K	>80	179 lm/W	2,400 lm

## LuxSpace Compact, recessed

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505104755	DN610B 20S/940UE PSU-E FLR WH	4000 K	>90	176 lm/W	1,900 lm
910505104751	DN610B 20S/840UE PSU-E C RML	4000 K	>80	185 lm/W	2,000 lm
910505104703	DN610B 20S/840UE PSU-E FLR SI	4000 K	>80	185 lm/W	2,000 lm
910505104681	DN610B 20S/840 PSU-E BKR WH	4000 K	>80	98 lm/W	2,300 lm
910505104686	DN610B 24S/840 PSU-E BKR WH	4000 K	>80	95 lm/W	2,700 lm
910505104694	DN610B 20S/840UE PSU-E C WH PGO	4000 K	>80	185 lm/W	2,000 lm
910505104696	DN610B 24S/840UE PSU-E C WH PGO	4000 K	>80	187 lm/W	2,500 lm
910505104677	DN610B 20S/840UE PSU-E C WH	4000 K	>80	185 lm/W	2,000 lm
910505104682	DN610B 24S/840UE PSU-E C WH	4000 K	>80	187 lm/W	2,500 lm
910505104687	DN610B 40S/840UE PSU-E C WH	4000 K	>80	168 lm/W	4,200 lm
910505104691	DN610B 60S/840UE PSU-E C WH	4000 K	>80	159 lm/W	5,900 lm
910505104705	DN610B 20S/830UE PSU-E C WH	3000 K	>80	181 lm/W	1,950 lm
910505104708	DN610B 24S/830UE PSU-E C WH	3000 K	>80	179 lm/W	2,400 lm
910505104716	DN610B 20S/840UE PSD-E C WH	4000 K	>80	162 lm/W	2,100 lm
910505104719	DN610B 24S/840UE PSD-E C WH	4000 K	>80	169 lm/W	2,500 lm
910505104722	DN610B 40S/840UE PSD-E C WH	4000 K	>80	162 lm/W	4,200 lm
910505104725	DN610B 20S/840UE DIA-E C WH	4000 K	>80	169 lm/W	2,200 lm
910505104728	DN610B 20S/840UE DIA-VLC-E C WH	4000 K	>80	169 lm/W	2,200 lm
910505104731	DN610B 60S/840UE PSD-E C WH	4000 K	>80	157 lm/W	5,900 lm
910505104733	DN610B 20S/840UE PSU-E C ELP3 WH	4000 K	>80	185 lm/W	2,000 lm
910505104736	DN610B 24S/840UE PSU-E C ELP3 WH	4000 K	>80	179 lm/W	2,400 lm
910505104739	DN610B 40S/840UE PSU-E C ELP3 WH	4000 K	>80	168 lm/W	4,200 lm
910505104742	DN610B 20S/840UE WIA-E C WH	4000 K	>80	159 lm/W	2,200 lm
910505104745	DN610B 24S/840UE WIA-E C WH	4000 K	>80	158 lm/W	2,500 lm
910505104748	DN610B 40S/840UE WIA-E C WH	4000 K	>80	142 lm/W	4,200 lm

## LuxSpace Compact, recessed

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505104754	DN610B 20S/940UE PSU-E C WH	4000 K	>90	176 lm/W	1,900 lm
910505104679	DN610B 20S/840UE PSU-E WR WH	4000 K	>80	185 lm/W	2,000 lm
910505104684	DN610B 24S/840UE PSU-E WR WH	4000 K	>80	172 lm/W	2,300 lm
910505104707	DN610B 20S/830UE PSU-E WR WH	3000 K	>80	181 lm/W	1,950 lm
910505104710	DN610B 24S/830UE PSU-E WR WH	3000 K	>80	164 lm/W	2,200 lm

### Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
910505104698	DN610B 20S/840UE PSU-E FLR BK	10.8 W	910505104677	DN610B 20S/840UE PSU-E C WH	10.8 W
910505104680	DN610B 20S/840 PSU-E M WH	18 W	910505104682	DN610B 24S/840UE PSU-E C WH	13.4 W
910505104685	DN610B 24S/840 PSU-E M WH	19.8 W	910505104687	DN610B 40S/840UE PSU-E C WH	25 W
910505104757	DN610B 40S/TWH DIA-E C WH	33 W	910505104691	DN610B 60S/840UE PSU-E C WH	37 W
910505104704	DN610B 20S/840 PSU-E M SI	18 W	910505104705	DN610B 20S/830UE PSU-E C WH	10.8 W
910505104693	DN610B 20S/840UE PSU-E C WH PG	10.8 W	910505104708	DN610B 24S/830UE PSU-E C WH	13.4 W
910505104695	DN610B 24S/840UE PSU-E C WH PG	13.4 W	910505104716	DN610B 20S/840UE PSD-E C WH	13 W
910505104699	DN610B 20S/840 PSU-E M BK	18 W	910505104719	DN610B 24S/840UE PSD-E C WH	14.8 W
910505104697	DN610B 20S/840UE PSU-E C BK	10.8 W	910505104722	DN610B 40S/840UE PSD-E C WH	26 W
910505104702	DN610B 20S/840UE PSU-E C SI	10.8 W	910505104725	DN610B 20S/840UE DIA-E C WH	13 W
910505104753	DN610B 20S/840UE PSU-E C RAD240 WH	10.8 W	910505104728	DN610B 20S/840UE DIA-VLC-E C WH	13 W
910505104701	DN610B 20S/840 PSU-E BKR BK	23 W	910505104731	DN610B 60S/840UE PSD-E C WH	37.5 W
910505104752	DN610B 20S/840UE PSU-E C RAD225 WH	10.8 W	910505104733	DN610B 20S/840UE PSU-E C ELP3 WH	10.8 W
910505104678	DN610B 20S/840UE PSU-E FLR WH	10.8 W	910505104736	DN610B 24S/840UE PSU-E C ELP3 WH	13.4 W
910505104683	DN610B 24S/840UE PSU-E FLR WH	13.4 W	910505104739	DN610B 40S/840UE PSU-E C ELP3 WH	25 W
910505104706	DN610B 20S/830UE PSU-E FLR WH	10.8 W	910505104742	DN610B 20S/840UE WIA-E C WH	13.8 W
910505104709	DN610B 24S/830UE PSU-E FLR WH	13.4 W	910505104745	DN610B 24S/840UE WIA-E C WH	15.8 W
910505104755	DN610B 20S/940UE PSU-E FLR WH	10.8 W	910505104748	DN610B 40S/840UE WIA-E C WH	29.5 W
910505104751	DN610B 20S/840UE PSU-E C RML	10.8 W	910505104754	DN610B 20S/940UE PSU-E C WH	10.8 W
910505104703	DN610B 20S/840UE PSU-E FLR SI	10.8 W	910505104679	DN610B 20S/840UE PSU-E WR WH	10.8 W
910505104681	DN610B 20S/840 PSU-E BKR WH	23.5 W	910505104684	DN610B 24S/840UE PSU-E WR WH	13.4 W
910505104686	DN610B 24S/840 PSU-E BKR WH	28.5 W	910505104707	DN610B 20S/830UE PSU-E WR WH	10.8 W
910505104694	DN610B 20S/840UE PSU-E C WH PGO	10.8 W	910505104710	DN610B 24S/830UE PSU-E WR WH	13.4 W
910505104696	DN610B 24S/840UE PSU-E C WH PGO	13.4 W			

### Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
910505104698	DN610B 20S/840UE PSU-E FLR BK	No	910505104699	DN610B 20S/840 PSU-E M BK	No
910505104680	DN610B 20S/840 PSU-E M WH	No	910505104697	DN610B 20S/840UE PSU-E C BK	No
910505104685	DN610B 24S/840 PSU-E M WH	No	910505104702	DN610B 20S/840UE PSU-E C SI	No
910505104757	DN610B 40S/TWH DIA-E C WH	Yes	910505104753	DN610B 20S/840UE PSU-E C RAD240 WH	No
910505104704	DN610B 20S/840 PSU-E M SI	No	910505104701	DN610B 20S/840 PSU-E BKR BK	No
910505104693	DN610B 20S/840UE PSU-E C WH PG	No	910505104752	DN610B 20S/840UE PSU-E C RAD225 WH	No
910505104695	DN610B 24S/840UE PSU-E C WH PG	No	910505104678	DN610B 20S/840UE PSU-E FLR WH	No

## LuxSpace Compact, recessed

Order Code	Full Product Name	Dimmable
910505104683	DN610B 24S/840UE PSU-E FLR WH	No
910505104706	DN610B 20S/830UE PSU-E FLR WH	No
910505104709	DN610B 24S/830UE PSU-E FLR WH	No
910505104755	DN610B 20S/940UE PSU-E FLR WH	No
910505104751	DN610B 20S/840UE PSU-E C RML	No
910505104703	DN610B 20S/840UE PSU-E FLR SI	No
910505104681	DN610B 20S/840 PSU-E BKR WH	No
910505104686	DN610B 24S/840 PSU-E BKR WH	No
910505104694	DN610B 20S/840UE PSU-E C WH PGO	No
910505104696	DN610B 24S/840UE PSU-E C WH PGO	No
910505104677	DN610B 20S/840UE PSU-E C WH	No
910505104682	DN610B 24S/840UE PSU-E C WH	No
910505104687	DN610B 40S/840UE PSU-E C WH	No
910505104691	DN610B 60S/840UE PSU-E C WH	No
910505104705	DN610B 20S/830UE PSU-E C WH	No
910505104708	DN610B 24S/830UE PSU-E C WH	No
910505104716	DN610B 20S/840UE PSD-E C WH	Yes

Order Code	Full Product Name	Dimmable
910505104719	DN610B 24S/840UE PSD-E C WH	Yes
910505104722	DN610B 40S/840UE PSD-E C WH	Yes
910505104725	DN610B 20S/840UE DIA-E C WH	Yes
910505104728	DN610B 20S/840UE DIA-VLC-E C WH	Yes
910505104731	DN610B 60S/840UE PSD-E C WH	Yes
910505104733	DN610B 20S/840UE PSU-E C ELP3 WH	No
910505104736	DN610B 24S/840UE PSU-E C ELP3 WH	No
910505104739	DN610B 40S/840UE PSU-E C ELP3 WH	No
910505104742	DN610B 20S/840UE WIA-E C WH	Yes
910505104745	DN610B 24S/840UE WIA-E C WH	Yes
910505104748	DN610B 40S/840UE WIA-E C WH	Yes
910505104754	DN610B 20S/940UE PSU-E C WH	No
910505104679	DN610B 20S/840UE PSU-E WR WH	No
910505104684	DN610B 24S/840UE PSU-E WR WH	No
910505104707	DN610B 20S/830UE PSU-E WR WH	No
910505104710	DN610B 24S/830UE PSU-E WR WH	No

### Mechanical and Housing

Order Code	Full Product Name	Housing Color	Mech. impact protection code	Ingress protection code
910505104698	DN610B 20S/840UE PSU-E FLR BK	Black	IK03	IP20
910505104680	DN610B 20S/840 PSU-E M WH	White	IK03	IP20
910505104685	DN610B 24S/840 PSU-E M WH	White	IK03	IP20
910505104757	DN610B 40S/TWH DIA-E C WH	White	IK02	IP20
910505104704	DN610B 20S/840 PSU-E M SI	Silver	IK03	IP20
910505104693	DN610B 20S/840UE PSU-E C WH PG	White	IK03	IP20/54
910505104695	DN610B 24S/840UE PSU-E C WH PG	White	IK03	IP20/54
910505104699	DN610B 20S/840 PSU-E M BK	Black	IK03	IP20
910505104697	DN610B 20S/840UE PSU-E C BK	Black	IK03	IP20
910505104702	DN610B 20S/840UE PSU-E C SI	Silver	IK03	IP20
910505104753	DN610B 20S/840UE PSU-E C RAD240 WH	White	IK03	IP20
910505104701	DN610B 20S/840 PSU-E BKR BK	Black	IK03	IP20
910505104752	DN610B 20S/840UE PSU-E C RAD225 WH	White	IK03	IP20
910505104678	DN610B 20S/840UE PSU-E FLR WH	White	IK03	IP20

Order Code	Full Product Name	Housing Color	Mech. impact protection code	Ingress protection code
910505104683	DN610B 24S/840UE PSU-E FLR WH	White	IK03	IP20
910505104706	DN610B 20S/830UE PSU-E FLR WH	White	IK03	IP20
910505104709	DN610B 24S/830UE PSU-E FLR WH	White	IK03	IP20
910505104755	DN610B 20S/940UE PSU-E FLR WH	White	IK03	IP20
910505104751	DN610B 20S/840UE PSU-E C RML	White	IK03	IP20
910505104703	DN610B 20S/840UE PSU-E FLR SI	Silver	IK03	IP20
910505104681	DN610B 20S/840 PSU-E BKR WH	White	IK03	IP20
910505104686	DN610B 24S/840 PSU-E BKR WH	White	IK03	IP20
910505104694	DN610B 20S/840UE PSU-E C WH PGO	White	IK03	IP20/54
910505104696	DN610B 24S/840UE PSU-E C WH PGO	White	IK03	IP20/54
910505104677	DN610B 20S/840UE PSU-E C WH	White	IK03	IP20
910505104682	DN610B 24S/840UE PSU-E C WH	White	IK03	IP20
910505104687	DN610B 40S/840UE PSU-E C WH	White	IK02	IP20
910505104691	DN610B 60S/840UE PSU-E C WH	White	IK02	IP20

## LuxSpace Compact, recessed

Order Code	Full Product Name	Housing Color	Mech. impact protection code	Ingress protection code
910505104705	DN610B 20S/830UE PSU-E C WH	White	IK03	IP20
910505104708	DN610B 24S/830UE PSU-E C WH	White	IK03	IP20
910505104716	DN610B 20S/840UE PSD-E C WH	White	IK02	IP20
910505104719	DN610B 24S/840UE PSD-E C WH	White	IK02	IP20
910505104722	DN610B 40S/840UE PSD-E C WH	White	IK02	IP20
910505104725	DN610B 20S/840UE DIA-E C WH	White	IK02	IP20
910505104728	DN610B 20S/840UE DIA-VLC-E C WH	White	IK02	IP20
910505104731	DN610B 60S/840UE PSD-E C WH	White	IK02	IP20
910505104733	DN610B 20S/840UE PSU-E C ELP3 WH	White	IK03	IP20
910505104736	DN610B 24S/840UE PSU-E C ELP3 WH	White	IK03	IP20

Order Code	Full Product Name	Housing Color	Mech. impact protection code	Ingress protection code
910505104739	DN610B 40S/840UE PSU-E C ELP3 WH	White	IK03	IP20
910505104742	DN610B 20S/840UE WIA-E C WH	White	IK02	IP20
910505104745	DN610B 24S/840UE WIA-E C WH	White	IK02	IP20
910505104748	DN610B 40S/840UE WIA-E C WH	White	IK02	IP20
910505104754	DN610B 20S/940UE PSU-E C WH	White	IK03	IP20
910505104679	DN610B 20S/840UE PSU-E WR WH	White	IK03	IP20
910505104684	DN610B 24S/840UE PSU-E WR WH	White	IK03	IP20
910505104707	DN610B 20S/830UE PSU-E WR WH	White	IK03	IP20
910505104710	DN610B 24S/830UE PSU-E WR WH	White	IK03	IP20

### Emergency Operation

Order Code	Full Product Name	Central Emergency	Emergency lighting
910505104698	DN610B 20S/840UE PSU-E FLR BK	-	-
910505104680	DN610B 20S/840 PSU-E M WH	-	-
910505104685	DN610B 24S/840 PSU-E M WH	-	-
910505104757	DN610B 40S/TWH DIA-E C WH	-	-
910505104704	DN610B 20S/840 PSU-E M SI	-	-
910505104693	DN610B 20S/840UE PSU-E C WH PG	-	-
910505104695	DN610B 24S/840UE PSU-E C WH PG	-	-
910505104699	DN610B 20S/840 PSU-E M BK	-	-
910505104697	DN610B 20S/840UE PSU-E C BK	-	-
910505104702	DN610B 20S/840UE PSU-E C SI	-	-
910505104753	DN610B 20S/840UE PSU-E C RAD240 WH	-	-
910505104701	DN610B 20S/840 PSU-E BKR BK	-	-
910505104752	DN610B 20S/840UE PSU-E C RAD225 WH	-	-
910505104678	DN610B 20S/840UE PSU-E FLR WH	-	-
910505104683	DN610B 24S/840UE PSU-E FLR WH	-	-
910505104706	DN610B 20S/830UE PSU-E FLR WH	-	-
910505104709	DN610B 24S/830UE PSU-E FLR WH	-	-
910505104755	DN610B 20S/940UE PSU-E FLR WH	-	-
910505104751	DN610B 20S/840UE PSU-E C RML	-	-
910505104703	DN610B 20S/840UE PSU-E FLR SI	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting
910505104681	DN610B 20S/840 PSU-E BKR WH	-	-
910505104686	DN610B 24S/840 PSU-E BKR WH	-	-
910505104694	DN610B 20S/840UE PSU-E C WH PGO	-	-
910505104696	DN610B 24S/840UE PSU-E C WH PGO	-	-
910505104677	DN610B 20S/840UE PSU-E C WH	-	-
910505104682	DN610B 24S/840UE PSU-E C WH	-	-
910505104687	DN610B 40S/840UE PSU-E C WH	-	-
910505104691	DN610B 60S/840UE PSU-E C WH	-	-
910505104705	DN610B 20S/830UE PSU-E C WH	-	-
910505104708	DN610B 24S/830UE PSU-E C WH	-	-
910505104716	DN610B 20S/840UE PSD-E C WH	-	-
910505104719	DN610B 24S/840UE PSD-E C WH	-	-
910505104722	DN610B 40S/840UE PSD-E C WH	-	-
910505104725	DN610B 20S/840UE DIA-E C WH	-	-
910505104728	DN610B 20S/840UE DIA-VLC-E C WH	-	-
910505104731	DN610B 60S/840UE PSD-E C WH	-	-
910505104733	DN610B 20S/840UE PSU-E C ELP3 WH	No	Emergency lighting 3 hours duration Pro version

## LuxSpace Compact, recessed

Order Code	Full Product Name	Central Emergency	Emergency lighting
910505104736	DN610B 24S/840UE PSU-E C ELP3 WH	No	Emergency lighting 3 hours duration Pro version
910505104739	DN610B 40S/840UE PSU-E C ELP3 WH	No	Emergency lighting 3 hours duration Pro version

Order Code	Full Product Name	Central Emergency	Emergency lighting
910505104742	DN610B 20S/840UE WIA-E C WH	-	-
910505104745	DN610B 24S/840UE WIA-E C WH	-	-
910505104748	DN610B 40S/840UE WIA-E C WH	-	-
910505104754	DN610B 20S/940UE PSU-E C WH	-	-
910505104679	DN610B 20S/840UE PSU-E WR WH	-	-
910505104684	DN610B 24S/840UE PSU-E WR WH	-	-
910505104707	DN610B 20S/830UE PSU-E WR WH	-	-
910505104710	DN610B 24S/830UE PSU-E WR WH	-	-

### Approval and Application

Order Code	Full Product Name	ENEC mark
910505104698	DN610B 20S/840UE PSU-E FLR BK	ENEC mark
910505104680	DN610B 20S/840 PSU-E M WH	ENEC mark
910505104685	DN610B 24S/840 PSU-E M WH	ENEC mark
910505104757	DN610B 40S/TWH DIA-E C WH	-
910505104704	DN610B 20S/840 PSU-E M SI	ENEC mark
910505104693	DN610B 20S/840UE PSU-E C WH PG	ENEC mark
910505104695	DN610B 24S/840UE PSU-E C WH PG	ENEC mark
910505104699	DN610B 20S/840 PSU-E M BK	ENEC mark
910505104697	DN610B 20S/840UE PSU-E C BK	ENEC mark
910505104702	DN610B 20S/840UE PSU-E C SI	ENEC mark
910505104753	DN610B 20S/840UE PSU-E C RAD240 WH	ENEC mark
910505104701	DN610B 20S/840 PSU-E BKR BK	ENEC mark
910505104752	DN610B 20S/840UE PSU-E C RAD225 WH	ENEC mark
910505104678	DN610B 20S/840UE PSU-E FLR WH	ENEC mark
910505104683	DN610B 24S/840UE PSU-E FLR WH	ENEC mark
910505104706	DN610B 20S/830UE PSU-E FLR WH	ENEC mark
910505104709	DN610B 24S/830UE PSU-E FLR WH	ENEC mark
910505104755	DN610B 20S/940UE PSU-E FLR WH	ENEC mark
910505104751	DN610B 20S/840UE PSU-E C RML	ENEC mark
910505104703	DN610B 20S/840UE PSU-E FLR SI	ENEC mark
910505104681	DN610B 20S/840 PSU-E BKR WH	ENEC mark
910505104686	DN610B 24S/840 PSU-E BKR WH	ENEC mark
910505104694	DN610B 20S/840UE PSU-E C WH PGO	ENEC mark
910505104696	DN610B 24S/840UE PSU-E C WH PGO	ENEC mark

Order Code	Full Product Name	ENEC mark
910505104677	DN610B 20S/840UE PSU-E C WH	ENEC mark
910505104682	DN610B 24S/840UE PSU-E C WH	ENEC mark
910505104687	DN610B 40S/840UE PSU-E C WH	ENEC mark
910505104691	DN610B 60S/840UE PSU-E C WH	ENEC mark
910505104705	DN610B 20S/830UE PSU-E C WH	ENEC mark
910505104708	DN610B 24S/830UE PSU-E C WH	ENEC mark
910505104716	DN610B 20S/840UE PSD-E C WH	ENEC mark
910505104719	DN610B 24S/840UE PSD-E C WH	ENEC mark
910505104722	DN610B 40S/840UE PSD-E C WH	ENEC mark
910505104725	DN610B 20S/840UE DIA-E C WH	ENEC mark
910505104728	DN610B 20S/840UE DIA-VLC-E C WH	ENEC mark
910505104731	DN610B 60S/840UE PSD-E C WH	ENEC mark
910505104733	DN610B 20S/840UE PSU-E C ELP3 WH	ENEC mark
910505104736	DN610B 24S/840UE PSU-E C ELP3 WH	ENEC mark
910505104739	DN610B 40S/840UE PSU-E C ELP3 WH	ENEC mark
910505104742	DN610B 20S/840UE WIA-E C WH	ENEC mark
910505104745	DN610B 24S/840UE WIA-E C WH	ENEC mark
910505104748	DN610B 40S/840UE WIA-E C WH	ENEC mark
910505104754	DN610B 20S/940UE PSU-E C WH	ENEC mark
910505104679	DN610B 20S/840UE PSU-E WR WH	ENEC mark
910505104684	DN610B 24S/840UE PSU-E WR WH	ENEC mark
910505104707	DN610B 20S/830UE PSU-E WR WH	ENEC mark
910505104710	DN610B 24S/830UE PSU-E WR WH	ENEC mark

### Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505104698	DN610B 20S/840UE PSU-E FLR BK	(0.38,0.38)
910505104680	DN610B 20S/840 PSU-E M WH	(0.38,0.38)
910505104685	DN610B 24S/840 PSU-E M WH	(0.38,0.38)
910505104757	DN610B 40S/TWH DIA-E C WH	-
910505104704	DN610B 20S/840 PSU-E M SI	(0.38,0.38)
910505104693	DN610B 20S/840UE PSU-E C WH PG	(0.38,0.38)
910505104695	DN610B 24S/840UE PSU-E C WH PG	(0.38,0.38)
910505104699	DN610B 20S/840 PSU-E M BK	(0.38,0.38)
910505104697	DN610B 20S/840UE PSU-E C BK	(0.38,0.38)
910505104702	DN610B 20S/840UE PSU-E C SI	(0.38,0.38)


Order Code	Full Product Name	Initial chromaticity
910505104753	DN610B 20S/840UE PSU-E C RAD240 WH	(0.38,0.38)
910505104701	DN610B 20S/840 PSU-E BKR BK	(0.38,0.38)
910505104752	DN610B 20S/840UE PSU-E C RAD225 WH	(0.38,0.38)
910505104678	DN610B 20S/840UE PSU-E FLR WH	(0.38,0.38)
910505104683	DN610B 24S/840UE PSU-E FLR WH	(0.38,0.38)
910505104706	DN610B 20S/830UE PSU-E FLR WH	(0.44,0.40)
910505104709	DN610B 24S/830UE PSU-E FLR WH	(0.44,0.40)
910505104755	DN610B 20S/940UE PSU-E FLR WH	(0.38,0.38)
910505104751	DN610B 20S/840UE PSU-E C RML	(0.38,0.38)
910505104703	DN610B 20S/840UE PSU-E FLR SI	(0.38,0.38)

# LuxSpace Compact, recessed


Order Code	Full Product Name	Initial chromaticity
910505104681	DN610B 20S/840 PSU-E BKR WH	(0.38,0.38)
910505104686	DN610B 24S/840 PSU-E BKR WH	(0.38,0.38)
910505104694	DN610B 20S/840UE PSU-E C WH PGO	(0.38,0.38)
910505104696	DN610B 24S/840UE PSU-E C WH PGO	(0.38,0.38)
910505104677	DN610B 20S/840UE PSU-E C WH	(0.38,0.38)
910505104682	DN610B 24S/840UE PSU-E C WH	(0.38,0.38)
910505104687	DN610B 40S/840UE PSU-E C WH	(0.38,0.38)
910505104691	DN610B 60S/840UE PSU-E C WH	(0.38,0.38)
910505104705	DN610B 20S/830UE PSU-E C WH	(0.44,0.40)
910505104708	DN610B 24S/830UE PSU-E C WH	(0.44,0.40)
910505104716	DN610B 20S/840UE PSD-E C WH	(0.38,0.38)
910505104719	DN610B 24S/840UE PSD-E C WH	(0.38,0.38)
910505104722	DN610B 40S/840UE PSD-E C WH	(0.38,0.38)
910505104725	DN610B 20S/840UE DIA-E C WH	(0.38,0.38)

Order Code	Full Product Name	Initial chromaticity
910505104728	DN610B 20S/840UE DIA-VLC-E C WH	(0.38,0.38)
910505104731	DN610B 60S/840UE PSD-E C WH	(0.38,0.38)
910505104733	DN610B 20S/840UE PSU-E C ELP3 WH	(0.38,0.38)
910505104736	DN610B 24S/840UE PSU-E C ELP3 WH	(0.38,0.38)
910505104739	DN610B 40S/840UE PSU-E C ELP3 WH	(0.38,0.38)
910505104742	DN610B 20S/840UE WIA-E C WH	(0.38,0.38)
910505104745	DN610B 24S/840UE WIA-E C WH	(0.38,0.38)
910505104748	DN610B 40S/840UE WIA-E C WH	(0.38,0.38)
910505104754	DN610B 20S/940UE PSU-E C WH	(0.38,0.38)
910505104679	DN610B 20S/840UE PSU-E WR WH	(0.38,0.38)
910505104684	DN610B 24S/840UE PSU-E WR WH	(0.38,0.38)
910505104707	DN610B 20S/830UE PSU-E WR WH	(0.44,0.40)
910505104710	DN610B 24S/830UE PSU-E WR WH	(0.44,0.40)


## Polar Wide Diagrams




Polar Normal (separate) - DN610BI - 910505104691




Polar Normal (separate) - DN610BI - 910505104678




Polar Normal (separate) - DN610BI - 910505104693



Polar Normal (separate) - DN610BI - 910505104696




Polar Normal (separate) - DN610BI - 910505104757




Polar Normal (separate) - DN610BI - 910505104677

# LuxSpace Compact, recessed


## Polar Wide Diagrams




**Polar Normal (separate) - DN610BI - 910505104753**




**Polar Normal (separate) - DN610BI - 910505104728**




**Polar Normal (separate) - DN610BI - 910505104736**




**Polar Normal (separate) - DN610BI - 910505104708**




**Polar Normal (separate) - DN610BI - 910505104751**




**Polar Normal (separate) - DN610BI - 910505104704**



**Polar Normal (separate) - DN610BI - 910505104701**




**Polar Normal (separate) - DN610BI - 910505104733**




**Polar Normal (separate) - DN610BI - 910505104695**

# LuxSpace Compact, recessed


## Polar Wide Diagrams




Polar Normal (separate) - DN610BI - 910505104686




Polar Normal (separate) - DN610BI - 910505104698




Polar Normal (separate) - DN610BI - 910505104680




Polar Normal (separate) - DN610BI - 910505104697




Polar Normal (separate) - DN610BI - 910505104682




Polar Normal (separate) - DN610BI - 910505104687



Polar Normal (separate) - DN610BI - 910505104694




Polar Normal (separate) - DN610BI - 910505104683




Polar Normal (separate) - DN610BI - 910505104681

# LuxSpace Compact, recessed


## Polar Wide Diagrams




**Polar Normal (separate) - DN610BI - 910505104685**




**Polar Normal (separate) - DN610BI - 910505104679**




**Polar Normal (separate) - DN610BI - 910505104684**




**Polar Normal (separate) - DN610BI - 910505104722**




**Polar Normal (separate) - DN610BI - 910505104719**




**Polar Normal (separate) - DN610BI - 910505104706**



**Polar Normal (separate) - DN610BI - 910505104754**




**Polar Normal (separate) - DN610BI - 910505104739**




**Polar Normal (separate) - DN610BI - 910505104707**

# LuxSpace Compact, recessed


## Polar Wide Diagrams




Polar Normal (separate) - DN610BI - 910505104752




Polar Normal (separate) - DN610BI - 910505104703




Polar Normal (separate) - DN610BI - 910505104731




Polar Normal (separate) - DN610BI - 910505104755




Polar Normal (separate) - DN610BI - 910505104716




Polar Normal (separate) - DN610BI - 910505104748



Polar Normal (separate) - DN610BI - 910505104702




Polar Normal (separate) - DN610BI - 910505104745




Polar Normal (separate) - DN610BI - 910505104705

# LuxSpace Compact, recessed


## Polar Wide Diagrams




**Polar Normal (separate) - DN610BI - 910505104709**




**Polar Normal (separate) - DN610BI - 910505104699**



**Polar Normal (separate) - DN610BI - 910505104742**



**Polar Normal (separate) - DN610BI - 910505104725**



**Polar Normal (separate) - DN610BI - 910505104710**

