



Product Description

MASTER SDW-TG Mini

Range of high-efficiency, discharge lamps with warm colour to be used in small, open luminaires designed around MASTERColour CDM-T lamps

Benefits

- Exceptional brightness and colour rendering especially of warm colours, e.g. red and gold
- High lamp efficacy results in low operating costs and low heat generation
- Long lamp life compared with incandescent and halogen lamps

Features

- Warm white colour impression, very good colour rendering, especially superb red rendition
- Lamp design is well-suited to be used in luminaires for MASTER Colour CDM-T power-spots
- UV-block glass

Application

- Shop lighting (create cosy atmosphere e.g. in furniture shops), excellent display of fresh goods (at butchers, bakeries, flower-shops)

Warnings and Safety

- Use only with dedicated Philips control gear
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


MASTER SDW-TG Mini

Versions



LPPR_SDW-TG_50W_GX12-1-Product photo

Dimensional drawing



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MST SDW-TG Mini	20 mm	0.75	14.5	53.5 mm	56.5 mm	55 mm	103 mm
50W/825 GX12-1		inch	mm				
1CT/12							

