

PHILIPS

Lighting



Product Description

SON-T

High Pressure Sodium lamp with clear tubular outer bulb

Benefits

- SON-T is a cost-efficient and reliable solution in High Pressure Sodium

Features

- Clear tubular outer bulb
- High luminous efficacy
- Robust construction is vibration- and shock-resistant leading to a reliable life
- Dimming possible with dedicated gear

Application


- Road and residential lighting
- Decorative floodlighting
- Commercial and industrial applications
- Recreational sports facilities indoor and outdoor

Warnings and Safety

- Control gear must include end-of-life protection (IEC60662, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

SON-T

Dimensional drawing



Product	D (max)	O	L	C (max)
SON-T 1000W E E40 1SL/4	66 mm	145 mm	240 mm	390 mm
SON-T 1000W E E40 1SL/4	66 mm	153 mm	240 mm	390 mm
SON-T 100W E E40 SL/12	47 mm	44 mm	132 mm	209 mm
SON-T 150W E E40 SL/12	47 mm	58 mm	132 mm	209 mm
SON-T 250W E E40 SL/12	47 mm	66 mm	158 mm	255 mm
SON-T 400W E E40 SL/12	47 mm	82 mm	175 mm	286 mm

General Information	
Cap-Base	E40
Operating Position	UNIVERSAL
Light Technical	
Correlated Color Temperature (Nom)	2000 K
Color rendering index (CRI)	-
Operating and Electrical	
Voltage (Nom)	100 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear

Light Technical

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)
18412245	SON-T 1000W E40 1SL/4	130 lm/W
21264500	SON-T 100W E E40 SL/12	90 lm/W
21270600	SON-T 150W E E40 SL/12	98 lm/W

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)
21288100	SON-T 250W E E40 SL/12	110 lm/W
21292800	SON-T 400W E E40 1SL/12	123 lm/W
21060945	SON-T 1000W E E40 1SL/4	130 lm/W

Operating and Electrical

Order Code	Full Product Name	Power Consumption
18412245	SON-T 1000W E40 1SL/4	960.0 W
21264500	SON-T 100W E E40 SL/12	100.0 W
21270600	SON-T 150W E E40 SL/12	153 W

Order Code	Full Product Name	Power Consumption
21288100	SON-T 250W E E40 SL/12	255 W
21292800	SON-T 400W E E40 1SL/12	392.0 W
21060945	SON-T 1000W E E40 1SL/4	960.0 W

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
18412245	SON-T 1000W E40 1SL/4	T65
21264500	SON-T 100W E E40 SL/12	T46
21270600	SON-T 150W E E40 SL/12	T46

Order Code	Full Product Name	Bulb Shape
21288100	SON-T 250W E E40 SL/12	T46
21292800	SON-T 400W E E40 1SL/12	T46
21060945	SON-T 1000W E E40 1SL/4	T65

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Mercury (Hg) Content (Nom)
18412245	SON-T 1000W E40 1SL/4	1,056 kWh	23 mg
21264500	SON-T 100W E E40 SL/12	110 kWh	18.36 mg
21270600	SON-T 150W E E40 SL/12	162 kWh	20.4 mg
21288100	SON-T 250W E E40 SL/12	275 kWh	20.4 mg
21292800	SON-T 400W E E40 1SL/12	431 kWh	24.5 mg
21060945	SON-T 1000W E E40 1SL/4	1,056 kWh	22.65 mg

