



Product Description

High Pressure Sodium lamp with clear tubular outer bulb

Benefits

- SON-T Pro is a cost-efficient and reliable solution in High Pressure Sodium

Applications

- Road and residential lighting
- Decorative floodlighting
- Commercial and industrial applications
- Recreational sports facilities Outdoor and Indoor

Features

- Clear tubular outer bulb
- High luminous efficacy


- Robust construction is vibration- and shock-resistant leading to a reliable life
- Dimming possible with dedicated gear
- Control gear must include end-of-life protection (IEC60662, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



LPPR SON-T E40

Dimensional drawing



Product	D (max)	O	L	C (max)
SON-T 1000W E40 1SL/4	66 mm	153 mm	240 mm	390 mm

General Information

Cap base	E40
Operating position	UNIVERSAL [Any or Universal (U)]

Light Technical

Correlated Colour Temperature (Nom)	2000 K
Luminous efficacy (rated) (nom.)	130 lm/W
Colour rendering index (CRI)	-

Operating and Electrical

Power Consumption	960.0 W
Voltage (nom.)	100 V

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Lamp Finish	Clear
Bulb shape	T65

Approval and Application

Mercury (Hg) content (nom.)	23 mg
Energy consumption kWh/1,000 hours	1,056 kWh