

PHILIPS

SON

DSO



Product Description

High Pressure Sodium lamp with opalized ovoid outer bulb

Benefits

- SON is a cost-efficient and reliable solution in High Pressure Sodium
- SON Pro is a cost-efficient and reliable solution in High Pressure Sodium


Applications

- Road and residential lighting
- Road and residential lighting
- Decorative floodlighting
- Decorative floodlighting
- Commercial and industrial applications
- Commercial and industrial applications

Features

- Ovoid, internally white coated outer bulb
- Ovoid, internally white coated outer bulb
- High luminous efficacy
- High luminous efficacy
- Robust construction is vibration- and shock-resistant leading to a reliable life
- Robust construction is vibration- and shock-resistant leading to a reliable life
- Dimming possible with dedicated gear
- Dimming possible with dedicated gear

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.



Controls and Dimming

Dimmable Yes

Mechanical and Housing

Bulb Finish Coated glass

Approval and Application

Mercury (Hg) Content (Max) 14.3 mg

General Information

Order Code	Full Product Name	Cap-Base
928486800091	SON 150W E E40 CO 1SL/12	E40
928150108828	SON 70W/220 I E27 1CT/24	E27

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
928486800091	SON 150W E E40 CO 1SL/12	2000 K	93 lm/W
928150108828	SON 70W/220 I E27 1CT/24	1900 K	78 lm/W

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Voltage (Nom)
928486800091	SON 150W E E40 CO 1SL/12	147.0 W	100 V
928150108828	SON 70W/220 I E27 1CT/24	71.5 W	90 V

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
928486800091	SON 150W E E40 CO 1SL/12	ED90
928150108828	SON 70W/220 I E27 1CT/24	B70

Approval and Application

Order Code	Full Product Name	Mercury (Hg) Content (Nom)	Energy Consumption kWh/1000 h
928486800091	SON 150W E E40 CO 1SL/12	20.4 mg	162 kWh
928150108828	SON 70W/220 I E27 1CT/24	14.3 mg	72 kWh