



# Product Description

## SON

High Pressure Sodium lamp with opalized ovoid outer bulb

### Benefits

- SON is a cost-efficient and reliable solution in High Pressure Sodium

### Features

- Ovoid, internally white coated outer bulb
- High luminous efficacy
- Robust construction is vibration- and shock-resistant leading to a reliable life
- Dimming possible with dedicated gear

### Application


- Road and residential lighting
- Decorative floodlighting
- Commercial and industrial applications

### Warnings and Safety

- Control gear must include end-of-life protection (IEC60662, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

**Versions**

LPPR SON-I CO

**Dimensional drawing**

Product	D (max)	C (max)
SON 70W/220 I E27 1CT/24	71 mm	155 mm

