



Stand-alone 3 hours Interact ready emergency lighting bulkhead

Emergency Bulkhead Wireless

New wireless emergency lighting bulkheads and monitoring system, enabling building managers to control, monitor and test emergency lighting and produce compliance reports, through a secure cloud-based dashboard.

Benefits

- Achieve compliance through proof testing
- Save time and money on installation and maintenance
- Effortlessly monitor and manage general and/or emergency lighting in one dashboard

Features

- Emergency wireless bulkheads and Interact Building Manager system regulate and offer insights into emergency lighting testing with a secure cloud-based dashboard
- Allows building managers to maintain emergency lighting, automate testing and ensure regulatory compliance
- Having general and emergency lighting under one dashboard enables cost savings and efficient maintenance and monitoring of an entire lighting system

Application

- Exit & Emergency
- Offices
- Retails
- Hospitality

Emergency Bulkhead Wireless

Warnings and Safety

- The battery is designed with a rated average battery design life of 50,000 hours in standby mode. The battery is supported with a standard 5year warranty; conditional of the product being maintained and operated in accordance with the manufacturer's guidelines and tested in accordance with EN50272

Dimensional drawing



Product details



Emergency Bulkhead Wireless,
knock-out holes on the side



Emergency Bulkhead Wireless,
BESA mounting holes on back side



Emergency Bulkhead Wireless, no
sticker, lights off

Emergency Bulkhead Wireless, set
of exit legends



Emergency Bulkhead Wireless

General Information	
Driver included	Yes
Number of gear units	1 unit
Light Technical	
Correlated Color Temperature (Nom)	5000 K
Color rendering index (CRI)	≥70
Optic type	-
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220-240 V
Line Frequency	50 Hz
Power Consumption	5 W
Suitable for random switching	Not applicable
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Color	White
Mech. impact protection code	IK08
Ingress protection code	IP65
Emergency Operation	
Central Emergency	No
Emergency lighting	Emergency lighting 3 hours duration with Wireless Interface
Type of emergency lighting battery	Lithium
Rated duration of the emergency lighting (when fully charged)	3 hour(s)
Approval and Application	
Ambient temperature range	+5 to +45 °C
CE mark	Yes
ENEC mark	-
Flammability mark	-
Glow-wire test	-
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Initial Performance (IEC Compliant)	
Initial chromaticity	(0.346, 0.356) SDCM<5
Luminous flux tolerance	+/-5%

General Information

Order Code	Full Product Name	Light source replaceable
912401483626	EM253C SM BKD EXIT SIGN NM3 ELW IP65 WH	No
912401483627	EM254C HO BKD 7S NM3 ELW IP65 WH	-

Light Technical

Emergency Bulkhead Wireless

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux
912401483626	EM253C SM BKD EXIT SIGN NM3 ELW IP65 WH	120 lm/W	220 lm

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux
912401483627	EM254C HO BKD 7S NM3 ELW IP65 WH	105 lm/W	700 lm

Emergency Operation

Order Code	Full Product Name	Emergency flux
912401483626	EM253C SM BKD EXIT SIGN NM3 ELW IP65 WH	220 lm

Order Code	Full Product Name	Emergency flux
912401483627	EM254C HO BKD 7S NM3 ELW IP65 WH	700 lm

