

PHILIPS

Lighting



Product Description

HORTI

High Pressure Sodium lamp with clear outer bulb, optimized growthlight output and maintenance

Benefits

- Optimized performance for horticultural applications
- High growthlight maintenance safeguards a constant crop quality and quantity over life

Features

- Clear tubular outer bulb
- Ceramic discharge tube with Philips Integrated Antenna (PIA) for a long and reliable lifetime
- Advanced getter ensures high growthlight maintenance and few early failures
- "GreenPower" concept with optimized micromol output (growth light)
- "Plus" concept with high efficacy translated into high light output
- "Agro" concept with optimized light spectrum

Application


- Horticultural applications, plant irradiation, assimilation lighting

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions

LPPR SONTHORT 0001

Dimensional drawing

Product	D (max)	O	L	C (max)	A
MASTER GreenPower CG T 600W E40	47 mm	151 mm	166 mm	279 mm	205 mm

1SL/12

