



The new classic light bulb

Halogen Classic A-shape

Philips Halogen Classic light bulbs offer the classical shapes you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.

Benefits

- Identical look and feel to standard lamp, with bright, sparkling halogen light
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Double the lifetime of a standard bulb and immediate light when switching on

Features


- Superior quality of light with excellent colour rendering ($R_{a} \geq 100$)
- Mains-voltage lamp, no transformer needed
- Universal burning position
- Instant start

Application

- Accent and general lighting applications in homes, offices, shops, hotels and restaurants. Replacement for traditional bulb in classical luminaires

Halogen Classic A-shape

Dimensional drawing



Product	D (max)	C (max)
EcoClassic 105W B22 240V A55 FR 1CT/10	56 mm	95.5 mm
EcoClassic 140W B22 240V A55 FR 1CT/10	56 mm	95.5 mm

General Information	
Cap-Base	B22
Rated Lifetime (Hours)	2,000 hour(s)
Switching Cycle	8,000
Nominal lifetime	2,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Correlated Color Temperature (Nom)	2800 K
Color rendering index (CRI)	100
Operating and Electrical	
Warm-up time to 60% light	instant full light s
Voltage (Nom)	240 V
Starting Time (Nom)	0.0 s
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A55

Light Technical

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux
925702745503	EcoClassic 105W B22 240V A55 FR 1CT/10	18.9 lm/W	1,980 lm
925702845503	EcoClassic 140W B22 240V A55 FR 1CT/10	20.3 lm/W	2,840 lm

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
925702745503	EcoClassic 105W B22 240V A55 FR 1CT/10	0.44 A	105 W

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
925702845503	EcoClassic 140W B22 240V A55 FR 1CT/10	0.58 A	140 W

Halogen Classic A-shape

