

PHILIPS

Lighting



Product Description

Plusline Compact

Mains-voltage linear lamp giving white halogen light

Benefits

- Bright halogen light
- Long lifetime

Features

- Clear tubular quartz bulb
- Reinforced filament supports for maximum safety and shock resistance resulting in longer lifetime
- Two arc-preventing fuses for greater safety
- Excellent colour rendering
- Constant light output during life

Application

- Typically used in shop lighting applications
- Indoor: homes, offices, shops and museums
- Outdoor: billboards, car parks, security lighting and construction sites

Plusline Compact

Versions




8711500885388 - RFT



LPPR HDECOMP R7s 10

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
100 W R7s cap Clear Halogen linear lamp	15 mm	76.5 mm	74.9 mm	73.3 mm	78.3 mm
Plusline C 150W R7s 240V 1BC/12	15 mm	76.5 mm	74.9 mm	73.3 mm	78.3 mm

General Information	
Cap-Base	R7s
Rated Lifetime (Hours)	2,000 hour(s)
Nominal lifetime	2,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Voltage (Nom)	240 V
Starting Time (Nom)	0.0 s
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T3

Light Technical

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux
923920045792	100 W R7s cap Clear Halogen linear lamp	15.5 lm/W	1,550 lm
923919945709	Plusline C 150W R7s 240V 1BC/12	16 lm/W	2,400 lm

Operating and Electrical

Plusline Compact

Lamp Current			
Order Code	Full Product Name	(Nom)	Power Consumption
923920045792	100 W R7s cap Clear Halogen linear lamp	0.42 A	100 W

Lamp Current			
Order Code	Full Product Name	(Nom)	Power Consumption
923919945709	Plusline C 150W R7s 240V	0.63 A	150 W

