



Product Description

Plusline Small

Mains-voltage linear lamp giving white halogen light

Benefits

- Bright halogen light
- Long lifetime

Features

- Clear tubular quartz bulb
- Reinforced filament supports for maximum safety and shock resistance resulting in longer lifetime
- Two arc-preventing fuses for greater safety
- Excellent colour rendering
- Constant light output during life

Application

- Typically used in shop lighting applications
- Indoor: homes, offices, shops and museums
- Outdoor: billboards, car parks, security lighting and construction sites

Plusline Small



Versions



LPPR_HDESMALL_R7s-Product photo

LPPR_HLINEAR_0001

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
200 W R7s cap Clear Halogen linear lamp	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm
300 W R7s cap Clear Halogen linear lamp	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm
500 W R7s cap 220-240 V Warm white Halogen linear lamp	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm
Plusline S 500W R7s 240V 1BC/12	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm

Product	D (max)	C (max)
PLUS PRO S 1000W 240-250V CL 1SL	12.75 mm	114.2 mm

General Information

Cap-Base	R7s
Rated Lifetime (Hours)	2,000 hour(s)
Operating Position	UNIVERSAL

Mechanical and Housing

Bulb Finish	Clear
-------------	-------

General Information

Plusline Small

Order Code	Full Product Name	Nominal lifetime
924735545501	Plusline S 500W R7s 240V 1BC/12	2,000 hour(s)
923880045799	PLUS PRO S 1000W 240-250V CL 1SL	-
924735445597	300 W R7s cap Clear Halogen linear lamp	2,000 hour(s)

Order Code	Full Product Name	Nominal lifetime
924735544280	500 W R7s cap 220-240 V Warm white Halogen linear lamp	2,000 hour(s)
924735745597	200 W R7s cap Clear Halogen linear lamp	2,000 hour(s)

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
		(K)		(lm/W)	(lm)
924735545501	Plusline S 500W R7s 240V 1BC/12	2900 K	100	19.3 lm/W	9,660 lm
923880045799	PLUS PRO S 1000W 240-250V CL 1SL	-	-	-	22,000 lm
924735445597	300 W R7s cap Clear Halogen linear lamp	-	100	17 lm/W	5,114 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
		(K)		(lm/W)	(lm)
924735544280	500 W R7s cap 220-240 V Warm white Halogen linear lamp	2900 K	100	19.3 lm/W	9,660 lm
924735745597	200 W R7s cap Clear Halogen linear lamp	2900 K	100	15 lm/W	3,000 lm

Operating and Electrical

Order Code	Full Product Name	Lamp			Starting Time (Nom)
		Current (Nom)	Voltage (Nom)	Power Consumption	(s)
924735545501	Plusline S 500W R7s 240V 1BC/12	2.08 A	240 V	500 W	0.0 s
923880045799	PLUS PRO S 1000W 240-250V CL 1SL	-	240-250 V	1,000 W	-
924735445597	300 W R7s cap Clear Halogen linear lamp	1.25 A	240 V	300 W	0.0 s

Order Code	Full Product Name	Lamp			Starting Time (Nom)
		Current (Nom)	Voltage (Nom)	Power Consumption	(s)
924735544280	500 W R7s cap 220-240 V Warm white Halogen linear lamp	2.17 A	230 V	500 W	0.0 s
924735745597	200 W R7s cap Clear Halogen linear lamp	0.83 A	240 V	200 W	0.0 s

Controls and Dimming

Order Code	Full Product Name	Dimmable
924735545501	Plusline S 500W R7s 240V 1BC/12	Yes
923880045799	PLUS PRO S 1000W 240-250V CL 1SL	-
924735445597	300 W R7s cap Clear Halogen linear lamp	Yes

Order Code	Full Product Name	Dimmable
924735544280	500 W R7s cap 220-240 V Warm white Halogen linear lamp	Yes
924735745597	200 W R7s cap Clear Halogen linear lamp	Yes

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
924735545501	Plusline S 500W R7s 240V 1BC/12	T3
923880045799	PLUS PRO S 1000W 240-250V CL 1SL	T37
924735445597	300 W R7s cap Clear Halogen linear lamp	T3

Order Code	Full Product Name	Bulb Shape
924735544280	500 W R7s cap 220-240 V Warm white Halogen linear lamp	T3
924735745597	200 W R7s cap Clear Halogen linear lamp	T3

Plusline Small

