



Product Description

CLASSICTONE Superlux

Mushroom-shaped (E-shaped) lamps in various diameters

Benefits

- Gives up to 35% more light on the working plane with no extra energy consumption


Features

- Partial white bulb finish with a white window in a mushroom shape
- Shields the filament and directs light to where it is needed
- Universal burning Position

Application

- Wherever higher local lighting levels are required, e.g. for reading or task lighting

Dimensional drawing



Product	D	C (max)
CLAS 100W E27 220-240V E60 W-W 1CT/5X10F	60 mm	104 mm
CLAS 40W E27 220-240V E50 W-W 1CT/5X10F	50 mm	91 mm

CLASSICTONE Superlux

General Information	
Cap-Base	E27
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL

Light Technical	
Color rendering index (CRI)	100

Operating and Electrical	
Voltage (Nom)	220-240 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	White window

Light Technical

Order Code	Full Product Name	Luminous Flux
920226243301	CLAS 40W E27 220-240V E50 W-W 1CT/5X10F	400 lm

Order Code	Full Product Name	Luminous Flux
920246243301	CLAS 100W E27 220-240V E60 W-W 1CT/5X10F	1,280 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
920226243301	CLAS 40W E27 220-240V E50 W-W 1CT/5X10F	40 W

Order Code	Full Product Name	Power Consumption
920246243301	CLAS 100W E27 220-240V E60 W-W 1CT/5X10F	100 W

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
920226243301	CLAS 40W E27 220-240V E50 W-W 1CT/5X10F	E50

Order Code	Full Product Name	Bulb Shape
920246243301	CLAS 100W E27 220-240V E60 W-W 1CT/5X10F	E60

