

PHILIPS

Lighting



Product Description

CLASSICTONE Superlux

Mushroom-shaped (E-shaped) lamps in various diameters

Benefits

- Gives up to 35% more light on the working plane with no extra energy consumption

Features

- Partial white bulb finish with a white window in a mushroom shape
- Shields the filament and directs light to where it is needed
- Universal burning Position

Application

- Wherever higher local lighting levels are required, e.g. for reading or task lighting


Versions



LPPR_ISUPERLX_W-W-Product photo

CLASSICTONE Superlux

Dimensional drawing



Product	D	C (max)
CLAS 100W E27 220-240V E60 W-W 1CT/5X10F	60 mm	104 mm
CLAS 40W E27 220-240V E50 W-W 1CT/5X10F	50 mm	91 mm

General Information	
Cap-Base	E27
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	White window

Light Technical

Order Code	Full Product Name	Luminous Flux	Order Code	Full Product Name	Luminous Flux
920226243301	CLAS 40W E27 220-240V E50 W-W 1CT/5X10F	400 lm	920246243301	CLAS 100W E27 220-240V E60 W-W 1CT/5X10F	1,280 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
920226243301	CLAS 40W E27 220-240V E50 W-W 1CT/5X10F	40 W



CLASSICTONE Superlux

Order Code	Full Product Name	Power Consumption
920246243301	CLAS 100W E27 220-240V E60 W-W 1CT/5X10F	100 W

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
920226243301	CLAS 40W E27 220-240V E50 W-W 1CT/5X10F	E50

Order Code	Full Product Name	Bulb Shape
920246243301	CLAS 100W E27 220-240V E60 W-W 1CT/5X10F	E60

