



# Product Description

## Party Lustre P45

Colored incandescent lamp with P45 shape and superior ESC coating

### Benefits

- Environment-friendly due to ESC coating and cadmium-free lamp
- Energy savings thanks to much higher color brilliance and lumen output than conventional colored lamps with higher wattages
- Weather-resistant bulbs are perfectly suitable for outdoor use

### Features


- Choice of attractive colours
- Superior quality thanks to the Electro Static Coated (ESC) internal coating (instead of the conventional wet-flushed inside paint process)

### Application

- All kinds of indoor and outdoor decorative lighting and special effects
- Outdoor: streets, facades, shopping centres, amusement parks, garden parties, carnivals, restaurants, bars, beaches, Christmas and other decorations
- Indoor: parties, special celebrations and decorative effects
- Multi-color versions and printing of special graphics available on project basis

# Party Lustre P45

## Dimensional drawing



Product	D	C (max)
230V 15W DECORATION BLUE	45 mm	71.5 mm
230V 15W DECORATION GREEN	45 mm	71.5 mm
230V 15W DECORATION ORANGE	45 mm	71.5 mm

General Information	
Cap-Base	B22
Rated Lifetime (Hours)	1,000 hour(s)
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL
Operating and Electrical	
Voltage (Nom)	230 V
Power Consumption	15 W
Starting Time (Nom)	0.0 s
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	P45

## Light Technical

Order Code	Full Product Name	Luminous Flux
921560044299	230V 15W DECORATION BLUE	120 lm
921560144298	230V 15W DECORATION GREEN	100 lm
921560344299	230V 15W DECORATION ORANGE	110 lm

## Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Order Code	Full Product Name	Bulb Finish
921560044299	230V 15W DECORATION BLUE	Blue	921560344299	230V 15W DECORATION ORANGE	Orange
921560144298	230V 15W DECORATION GREEN	Yellow			

