



# Product Description

## Standard Lustre P45 clear

Spherical vacuum- or gas-filled incandescent lamps with a clear glass bulb and E- or B-base

### Benefits

- Brilliant, visible filament adds small points of brightness for an enriched lighting effect

### Features

- Small, crystal-clear lamps designed for sparkling highlights
- At their best in decorative small luminaires such as table models and wall brackets with clear glass bowls
- Creates a sparkling atmosphere

### Application

- Home use in living and dining rooms, bedrooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Shops, boutiques and department stores
- Other similar areas

# Standard Lustre P45 clear

## Versions





LPPR ILUSBSTD B22 P45 CL



7894400001841 - RFT

## Dimensional drawing



Product	D	C (max)
40 W E27 cap 110-127 V Incandescent luster bulb	45 mm	73 mm

Product	D	C (max)
230V 15W GLS CLEAR BAYONET CAP	45 mm	71.5 mm

### General Information

Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL

### Light Technical

Color rendering index (CRI)	100
-----------------------------	-----

### Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	P45

## General Information

## Standard Lustre P45 clear

Order Code	Full Product Name	Cap-Base
921400544299	230V 15W GLS CLEAR BAYONET CAP	B22

Order Code	Full Product Name	Cap-Base
923268735892	40 W E27 cap 110-127 V Incandescent luster bulb	E27

### Light Technical

Order Code	Full Product Name	Luminous Flux
921400544299	230V 15W GLS CLEAR BAYONET CAP	110 lm

Order Code	Full Product Name	Luminous Flux
923268735892	40 W E27 cap 110-127 V Incandescent luster bulb	455 lm

### Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power Consumption	Starting Time (Nom)
921400544299	230V 15W GLS CLEAR BAYONET CAP	230 V	15 W	-

Order Code	Full Product Name	Voltage (Nom)	Power Consumption	Starting Time (Nom)
923268735892	40 W E27 cap 110-127 V Incandescent luster bulb	127 V	40 W	0.0 s

### Controls and Dimming

Order Code	Full Product Name	Dimmable
921400544299	230V 15W GLS CLEAR BAYONET CAP	Yes

Order Code	Full Product Name	Dimmable
923268735892	40 W E27 cap 110-127 V Incandescent luster bulb	-

