



# Product Description

## Standard Lustre P45 frosted

Spherical vacuum- or gas-filled incandescent lamps with white or inside-frosted glass bulb and E- or B-base

### Benefits

- Softly diffused light sets the scene for cosiness and comfort, and meets both aesthetic and functional requirements

### Features

- Lamps with reduced size and neat shape
- Extremely popular for use around mirrors or in chandeliers, candelabras, floor lamps and wall brackets, fitted with small, decorative shades
- Creates a pleasant low glare atmosphere

### Application

- Home use in living and dining rooms, bedrooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Shops, boutiques and department stores
- Other similar areas


# Standard Lustre P45 frosted

## Versions




GreenSpace Linear Accent

## Dimensional drawing



Product	D	C (max)
Stan 40W E14 230V P45 FR 1CT/10X10F	45 mm	78 mm
Stan 60W E14 230V P45 FR 1CT/10X10F	45 mm	78 mm



Product	D	C (max)
Stan 40W E27 230V P45 FR 1CT/10X10F	45 mm	73 mm
Stan 60W E27 230V P45 FR 1CT/10X10F	45 mm	73 mm

# Standard Lustre P45 frosted

General Information	
Rated Lifetime (Hours)	1,000 hour(s)
Nominal lifetime	1,000 hour(s)
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	P45

## General Information

Order Code	Full Product Name	Cap-Base	Operating Position
926000003568	Stan 60W E27 230V P45 FR 1CT/10X10F	E27	S90
926000003857	Stan 60W E14 230V P45 FR 1CT/10X10F	E14	UNIVERSAL

Order Code	Full Product Name	Cap-Base	Operating Position
926000007010	Stan 40W E14 230V P45 FR 1CT/10X10F	E14	UNIVERSAL
926000007412	Stan 40W E27 230V P45 FR 1CT/10X10F	E27	UNIVERSAL

## Light Technical

Order Code	Full Product Name	Luminous Flux
926000003568	Stan 60W E27 230V P45 FR 1CT/10X10F	640 lm
926000003857	Stan 60W E14 230V P45 FR 1CT/10X10F	650 lm

Order Code	Full Product Name	Luminous Flux
926000007010	Stan 40W E14 230V P45 FR 1CT/10X10F	405 lm
926000007412	Stan 40W E27 230V P45 FR 1CT/10X10F	390 lm

## Operating and Electrical

Order Code	Full Product Name	Power Consumption
926000003568	Stan 60W E27 230V P45 FR 1CT/10X10F	60 W
926000003857	Stan 60W E14 230V P45 FR 1CT/10X10F	60 W

Order Code	Full Product Name	Power Consumption
926000007010	Stan 40W E14 230V P45 FR 1CT/10X10F	40 W
926000007412	Stan 40W E27 230V P45 FR 1CT/10X10F	40 W

## Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
926000003568	Stan 60W E27 230V P45 FR 1CT/10X10F	60 kWh
926000003857	Stan 60W E14 230V P45 FR 1CT/10X10F	60 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
926000007010	Stan 40W E14 230V P45 FR 1CT/10X10F	-
926000007412	Stan 40W E27 230V P45 FR 1CT/10X10F	-

## Standard Lustre P45 frosted

