

PHILIPS

Lighting



Product Description

Standard A-shape frosted

Conventional pear-shaped incandescent lamps

Benefits

- Vacuum-filled (15W) or gas-filled (25W and above)
- Choice of pearl lamp
- Universal burning position


Features

- Vacuum-filled (15W) or gas-filled (25W and above)

Application

- Frosted lamps give low glare and diffused lighting for universal applicability

Dimensional drawing



Product	D (max)	D	C (max)
Stan 60W E27 120V A55 FR U 1CT/10X10F	56 mm	55 mm	97 mm
Stan 75W E27 120V A55 FR U 1CT/10X10F	56 mm	55 mm	97 mm

Standard A-shape frosted

General Information	
Cap-Base	E27
Operating Position	UNIVERSAL
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Voltage (Nom)	120 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A55

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
920054736379	Stan 60W E27 120V A55 FR U 1CT/10X10F	60 W	920055636379	Stan 75W E27 120V A55 FR U 1CT/10X10F	75 W

