



# Product Description

## Standard A-shape frosted

Conventional pear-shaped incandescent lamps

### Benefits

- Vacuum-filled (15W) or gas-filled (25W and above)
- Choice of pearl lamp
- Universal burning position


### Features

- Vacuum-filled (15W) or gas-filled (25W and above)

### Application

- Frosted lamps give low glare and diffused lighting for universal applicability

### Dimensional drawing



Product	D (max)	D	C (max)
Stan 60W E27 120V A55 FR U 1CT/10X10F	56 mm	55 mm	97 mm
Stan 75W E27 120V A55 FR U 1CT/10X10F	56 mm	55 mm	97 mm

## Standard A-shape frosted

General Information	
Cap-Base	E27
Operating Position	UNIVERSAL
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Voltage (Nom)	120 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A55

### Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
920054736379	Stan 60W E27 120V A55 FR U 1CT/10X10F	60 W	920055636379	Stan 75W E27 120V A55 FR U 1CT/10X10F	75 W

