



Product Description

Standard A-shape clear

Conventional pear-shaped incandescent lamps

Benefits

- Brilliant, visible filament adds friendly points of brightness for an enriched lighting effect


Features

- Vacuum-filled (15W) or gas-filled (25W and above)

Application

- Clear lamps are ideal for indirect lighting in closed luminaires, and where brilliance and sparkling effects are more important than reduction of glare

Dimensional drawing



Product	D (max)	D	C (max)
Stan 100W E27 220V A55 CL U 1CT/10X10F	56 mm	55 mm	97 mm
Stan 60W E27 220-240V A55 CL 1CT/5X10F	56 mm	55 mm	97 mm
Stan 60W E27 230V A55 CL 1CT/12X10F	56 mm	55 mm	97 mm

Standard A-shape clear

General Information	
Cap-Base	E27
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL

Light Technical	
Color rendering index (CRI)	100

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A55

General Information

Order Code	Full Product Name	Rated Lifetime (Hours)
920054643302	Stan 60W E27 220-240V A55 CL 1CT/5X10F	-
920056542905	Stan 100W E27 220V A55 CL U 1CT/10X10F	-

Order Code	Full Product Name	Rated Lifetime (Hours)
926000006627	Stan 60W E27 230V A55 CL 1CT/12X10F	1,000 hour(s)

Light Technical

Order Code	Full Product Name	Luminous Flux
920054643302	Stan 60W E27 220-240V A55 CL 1CT/5X10F	710 lm
920056542905	Stan 100W E27 220V A55 CL U 1CT/10X10F	1,340 lm

Order Code	Full Product Name	Luminous Flux
926000006627	Stan 60W E27 230V A55 CL 1CT/12X10F	710 lm

Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power
			Consumption
920054643302	Stan 60W E27 220-240V A55 CL 1CT/5X10F	220-240 V	60 W
920056542905	Stan 100W E27 220V A55 CL U 1CT/10X10F	220 V	100 W

Order Code	Full Product Name	Voltage (Nom)	Power
			Consumption
926000006627	Stan 60W E27 230V A55 CL 1CT/12X10F	230 V	60 W

