



Product Description

Softone Standard T-shape

T-shaped gas-filled lamps with a modern appearance

Benefits

- Enhances colours in the home and adds a new dimension to interior decoration
- Creates a pleasant, relaxed atmosphere with a high degree of visual comfort

Features

- Gives a delicate, glare-free light in a subtle white or pastel colour
- Glare free and soft white or soft pastel lighting effect

Application

- Home use in living and dining rooms, halls and studies
- Offices
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs, social areas and public accommodation
- Shops and boutiques
- Other similar areas


Versions




LPPR ISTDESOF 0001

Softone Standard T-shape

Dimensional drawing



Product	D	C (max)
Soft 100W B22 230V T55 WH U 1CT/100	55 mm	93.5 mm
Soft 100W B22 240V T55 WH 1CT/5X20FT	55 mm	93.5 mm
Soft 40W B22 230V T55 WH U 1CT/100	55 mm	93.5 mm
Soft 60W B22 230V T55 WH U 1CT/100	55 mm	93.5 mm
Soft 60W B22 240V T55 WH 1CT/5X20FT	55 mm	93.5 mm
Soft 75W B22 240V T55 WH 1CT/5X20FT	55 mm	96.5 mm



Product	D	C (max)
Soft 60W E27 240V T55 WH 1CT/5X20FT	55 mm	95 mm
Soft 75W E27 240V T55 WH 1CT/5X20FT	55 mm	98 mm

General Information

Rated Lifetime (Hours)	1,000 hour(s)
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL

Light Technical

Color rendering index (CRI)	100
-----------------------------	-----

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Finish	Soft White
Bulb Shape	T55

General Information

Order Code	Full Product Name	Cap-Base
922801245537	Soft 60W B22 240V T55 WH 1CT/5X20FT	B22
922801345537	Soft 75W B22 240V T55 WH 1CT/5X20FT	B22
922801445537	Soft 100W B22 240V T55 WH 1CT/5X20FT	B22
926000205012	Soft 60W B22 230V T55 WH U 1CT/100	B22

Order Code	Full Product Name	Cap-Base
926000205013	Soft 40W B22 230V T55 WH U 1CT/100	B22
926000205014	Soft 100W B22 230V T55 WH U 1CT/100	B22
922800345537	Soft 60W E27 240V T55 WH 1CT/5X20FT	E27
922800445537	Soft 75W E27 240V T55 WH 1CT/5X20FT	E27

Light Technical

Softone Standard T-shape

Order Code	Full Product Name	Luminous Flux
922801245537	Soft 60W B22 240V T55 WH 1CT/5X20FT	630 lm
922801345537	Soft 75W B22 240V T55 WH 1CT/5X20FT	830 lm
922801445537	Soft 100W B22 240V T55 WH 1CT/5X20FT	1,200 lm
926000205012	Soft 60W B22 230V T55 WH U 1CT/100	630 lm

Order Code	Full Product Name	Luminous Flux
926000205013	Soft 40W B22 230V T55 WH U 1CT/100	370 lm
926000205014	Soft 100W B22 230V T55 WH U 1CT/100	1,200 lm
922800345537	Soft 60W E27 240V T55 WH 1CT/5X20FT	630 lm
922800445537	Soft 75W E27 240V T55 WH 1CT/5X20FT	830 lm

Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
922801245537	Soft 60W B22 240V T55 WH 1CT/5X20FT	240 V	60 W
922801345537	Soft 75W B22 240V T55 WH 1CT/5X20FT	240 V	75 W
922801445537	Soft 100W B22 240V T55 WH 1CT/5X20FT	240 V	100 W
926000205012	Soft 60W B22 230V T55 WH U 1CT/100	230 V	60 W

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
926000205013	Soft 40W B22 230V T55 WH U 1CT/100	230 V	40 W
926000205014	Soft 100W B22 230V T55 WH U 1CT/100	230 V	100 W
922800345537	Soft 60W E27 240V T55 WH 1CT/5X20FT	240 V	60 W
922800445537	Soft 75W E27 240V T55 WH 1CT/5X20FT	240 V	75 W

