

PHILIPS

Lighting



Product Description

Deco Tubular

Tubular lamps with single- and coiled-coil filaments and clear, inside frosted or internally coated white bulbs with B- or E-base

Benefits

- Give brilliant and decorative lighting effects
- Ideal for creating a comfortable and relaxing ambience

Features

- Internal coating cannot chip, fade, become scratched or weathered

Application

- General lighting: switchboards, cupboards, piano and painting lighting
- Clear lamps are suitable for use in industrial and professional lighting applications, such as sign boards, elevator sign systems and fair and festive lighting
- Lamps with inside-frosted bulbs are ideal for use in a wide range of domestic and industrial applications


Versions




LPPR_ITUBE_E14_T25_CL-Product photo

Deco Tubular

Dimensional drawing



Product	D	C (max)
40W E14 240V T25L CL CH 1CT/10x10F	25 mm	81 mm



Product	D (max)	C (max)
10 W E14 cap Clear Incandescent tubular bulb	17 mm	54 mm
7 W E14 cap Clear Incandescent tubular bulb	17 mm	54 mm

General Information	
Cap-Base	E14
Rated Lifetime (Hours)	1,000 hour(s)
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL
Operating and Electrical	
Starting Time (Nom)	0.0 s
Mechanical and Housing	
Bulb Finish	Clear

General Information

Order Code	Full Product Name	Switching Cycle
924151144441	7 W E14 cap Clear Incandescent tubular bulb	4,000
924151445740	10 W E14 cap Clear Incandescent tubular bulb	4,000

Order Code	Full Product Name	Switching Cycle
925350444480	40W E14 240V T25L CL CH 1CT/10x10F	-

Light Technical

Order Code	Full Product Name	Correlated Color			Luminous Flux
		Temperature (Nom)	rendering index (CRI)	Luminous Flux	
924151144441	7 W E14 cap Clear Incandescent tubular bulb	2700 K	100	21 lm	

Order Code	Full Product Name	Correlated Color			Luminous Flux
		Temperature (Nom)	rendering index (CRI)	Luminous Flux	
924151445740	10 W E14 cap Clear Incandescent tubular bulb	2700 K	100	37 lm	

Deco Tubular

Order Code	Full Product Name	Correlated Color	Color	Luminous Flux
		Temperature (Nom)	rendering index (CRI)	
925350444480	40W E14 240V T25L CL CH 1CT/10x10F	-	-	424 lm

Operating and Electrical

Order Code	Full Product Name	Warm-up time to 60% light	Lamp	Power Consumption
		Current (Nom)	Voltage (Nom)	
924151144441	7 W E14 cap Clear Incandescent tubular bulb	instant full light s	230-240 V	7 W
924151445740	10 W E14 cap Clear Incandescent tubular bulb	instant full light s	240-250 V	10.0 W

Order Code	Full Product Name	Warm-up time to 60% light	Lamp	Power Consumption
		Current (Nom)	Voltage (Nom)	
925350444480	40W E14 240V T25L CL CH 1CT/10x10F	-	-	230-240 V 40 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
924151144441	7 W E14 cap Clear Incandescent tubular bulb	Yes
924151445740	10 W E14 cap Clear Incandescent tubular bulb	Yes

Order Code	Full Product Name	Dimmable
925350444480	40W E14 240V T25L CL CH 1CT/10x10F	-

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
924151144441	7 W E14 cap Clear Incandescent tubular bulb	T17
924151445740	10 W E14 cap Clear Incandescent tubular bulb	T17

Order Code	Full Product Name	Bulb Shape
925350444480	40W E14 240V T25L CL CH 1CT/10x10F	T25

Approval and Application

Order Code	Full Product Name	Energy Consumption	
		kWh/1000 h	
924151144441	7 W E14 cap Clear Incandescent tubular bulb	7 kWh	
924151445740	10 W E14 cap Clear Incandescent tubular bulb	10 kWh	

Order Code	Full Product Name	Energy Consumption	
		kWh/1000 h	
925350444480	40W E14 240V T25L CL CH 1CT/10x10F	-	

