

Deco Tubular

ITUBEB



Product Description

Tubular lamps with single- and coiled-coil filaments and clear, inside frosted or internally coated white bulbs with B- or E-base

Benefits

- Give brilliant and decorative lighting effects
- Ideal for creating a comfortable and relaxing ambience

Applications

- General lighting: switchboards, cupboards, piano and painting lighting
- Clear lamps:

- industrial/professional lighting: sign boards, elevator sign systems, fair and festive lighting
- Lamps with inside-frosted bulb:
- ideal for a wide range of domestic and industrial applications

Features


- Internal coating cannot chip, fade, become scratched or weathered

Versions



10 W E14 cap Incandescent
tubular bulb - RFT

Dimensional drawing



Product	D (max)	C (max)
7 W E14 cap Clear Incandescent tubular bulb	17 mm	54 mm

General Information

Cap-Base	E14
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Switching Cycle	4,000
Rated Lifetime (Hours)	1,000 hour(s)

Light Technical

Luminous Flux	21 lm
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100

Operating and Electrical

Power Consumption	7 W
Lamp Current (Nom)	0.03 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Voltage (Nom)	230-240 V

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	T17

Approval and Application

Energy Consumption kWh/1000 h	7 kWh
-------------------------------	-------