



Product Description

Tubular vacuum lamps with clear glass (T-bulb)

Benefits

- Reliable operation when used in special lampholders at high oven temperatures (up to 300°C)

Applications

- Electrical and standard ovens, rotisseries and similar places subject to high operating temperatures

- Available for specific oven luminaires fitted in different positions such as downlighter, side-light and backlight

Features

- Coiled-coil filament
- Manufactured with heat-resistant solder, getter and lamp-base cement

Versions



LPPR_ITUBAPE_E14_T22_CL-
Product photo




LPPR_ITUBAPE_E14_T25_CL-
Product photo




15 W E14 cap Incandescent
appliance bulb - RFT

Dimensional drawing




Product	D (max)	C (max)
App 15.4W E14 230-240V T22 CL OV 1CT	22 mm	49 mm

Product	D (max)	C (max)
App 26.0W E14 230-240V T25 CL OV 1CT	25 mm	57 mm
App 26.0W E14 230-240V T25CL OV 1CT/20F	25 mm	57 mm



Product	D (max)	C (max)
10 W E14 cap Clear Incandescent tubular bulb	26 mm	59 mm



General Information

Cap-Base	E14
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Switching Cycle	4,000
Rated Lifetime (Hours)	1,000 hour(s)

Light Technical

Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100

Operating and Electrical

Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Voltage (Nom)	230-240 V

Controls and Dimming

Dimmable Yes

Mechanical and Housing

Bulb Finish Clear

Light Technical

Order Code	Full Product Name	Luminous Flux
924196244441	App 15.4W E14 230-240V T22 CL OV 1CT	90 lm
924198244441	App 26.0W E14 230-240V T25 CL OV 1CT	172 lm
924198244443	App 26.0W E14 230-240V T25CL OV 1CT/20F	172 lm
924198344441	10 W E14 cap Clear Incandescent tubular bulb	34 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Lamp Current (Nom)
924196244441	App 15.4W E14 230-240V T22 CL OV 1CT	15.0 W	0.06 A
924198244441	App 26.0W E14 230-240V T25 CL OV 1CT	25.0 W	0.11 A
924198244443	App 26.0W E14 230-240V T25CL OV 1CT/20F	25.0 W	0.11 A
924198344441	10 W E14 cap Clear Incandescent tubular bulb	10.0 W	0.04 A

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
924196244441	App 15.4W E14 230-240V T22 CL OV 1CT	T22
924198244441	App 26.0W E14 230-240V T25 CL OV 1CT	T25
924198244443	App 26.0W E14 230-240V T25CL OV 1CT/20F	T25
924198344441	10 W E14 cap Clear Incandescent tubular bulb	T25

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
924196244441	App 15.4W E14 230-240V T22 CL OV 1CT	15 kWh
924198244441	App 26.0W E14 230-240V T25 CL OV 1CT	25 kWh
924198244443	App 26.0W E14 230-240V T25CL OV 1CT/20F	25 kWh
924198344441	10 W E14 cap Clear Incandescent tubular bulb	10 kWh