



Product Description

Tubular vacuum lamps with clear glass (T-bulb)

Benefits

- Reliable operation when used in special lampholders at high oven temperatures (up to 300°C)

Applications

- Electrical and standard ovens, rotisseries and similar places subject to high operating temperatures

- Available for specific oven luminaires fitted in different positions such as downlighter, side-light and backlight

Features

- Coiled-coil filament
- Manufactured with heat-resistant solder, getter and lamp-base cement

Versions




LPPR_ITUBAPE_E14_T22_CL-
 Product photo




LPPR_ITUBAPE_E14_T25_CL-
 Product photo

Dimensional drawing



Product	D (max)	C (max)
App 15.4W E14 230-240V T22 CL OV 1CT	22 mm	49 mm



Product	D (max)	C (max)
App 26.0W E14 230-240V T25 CL OV 1CT	25 mm	57 mm

General Information

Cap-Base	E14
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Switching Cycle	4,000
Rated Lifetime (Hours)	1,000 hour(s)

Light Technical

Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100

Operating and Electrical

Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Voltage (Nom)	230-240 V

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Finish	Clear
-------------	-------

Light Technical

Order Code	Full Product Name	Luminous Flux
03659950	Appliance 15.4W E14 230-240V T22 CL OV 1CT	90 lm
03871550	Appliance 26.0W E14 230-240V T25 CL OV 1CT	172 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Lamp Current (Nom)
03659950	Appliance 15.4W E14 230-240V T22 CL OV 1CT	15.0 W	0.06 A
03871550	Appliance 26.0W E14 230-240V T25 CL OV 1CT	25.0 W	0.11 A

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
03659950	Appliance 15.4W E14 230-240V T22 CL OV 1CT	T22
03871550	Appliance 26.0W E14 230-240V T25 CL OV 1CT	T25

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
03659950	Appliance 15.4W E14 230-240V T22 CL OV 1CT	15 kWh
03871550	Appliance 26.0W E14 230-240V T25 CL OV 1CT	25 kWh

