

# LED Lamps – ideal for general lighting applications

## LED Lamps

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

### Benefits

- Color temperature suitable for both functional lighting and to enhance atmosphere
- Up to 80% energy savings compared with incandescent bulbs
- Suitable for retrofit
- Lower maintenance costs

### Features

- Long lifetime
- UV- and IR-free light for less heat and protection of heat-sensitive objects
- Instant start

### Application

- Homes, hotels, restaurants, cafes
- Bedroom, dining room, living room, study room

# LED Lamps

## Versions



LEDGlobe 10 75W G120 B22 WW 230V AU



LED Sensor A60 E27 WW POS1



27W E27 A67 FR



LEDGlobe 7 60W G95 B22 WW 230V AU



LEDGlobe 10 75W G120 E27 WW 230V AU





LEDStick B22 AU



LEDGlobe 7 60W G95 E27 WW 230V AU

## Dimensional drawing





Product	D	C
LEDBulb 19W E27 3000K 230VA80 1CT/6APR	80 mm	155 mm
LEDBulb 19W E27 6500K 230VA80 1CT/6APR	80 mm	155 mm


Product	D	C
LEDGlobe 10W G120 B22 WW 230V_AU	120 mm	168 mm

# LED Lamps


## Dimensional drawing



Product	D	C
LEDBulb 14.5W E27 3000K 230VA67 1CT/6APR	68 mm	132 mm
LEDBulb 14.5W E27 6500K 230VA67 1CT/6APR	68 mm	132 mm






Product	D	C
LEDBulb 10W E27 930 230V 1CT/12 CN	60 mm	110 mm
LEDBulb 10W E27 930 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 10W E27 930 230V 2PF/3 AU	60 mm	110 mm
LEDBulb 10W E27 965 230V 1CT/12 CN	60 mm	110 mm
LEDBulb 10W E27 965 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 10W E27 965 230V 2PF/3 AU	60 mm	110 mm
LEDBulb 12W E27 930 230V 1CT/12 CN	60 mm	110 mm
LEDBulb 12W E27 930 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 12W E27 930 230V 2PF/3 AU	60 mm	110 mm
LEDBulb 12W E27 965 230V 1CT/12 CN	60 mm	110 mm
LEDBulb 12W E27 965 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 12W E27 965 230V 2PF/3 AU	60 mm	110 mm
LEDBulb 6W E27 930 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 6W E27 930 230V 2PF/3 AU	60 mm	110 mm
LEDBulb 6W E27 965 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 6W E27 965 230V 2PF/3 AU	60 mm	110 mm
LEDBulb 8W E27 930 230V 1CT/12 CN	60 mm	110 mm
LEDBulb 8W E27 930 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 8W E27 930 230V 2PF/3 AU	60 mm	110 mm
LEDBulb 8W E27 965 230V 1CT/12 CN	60 mm	110 mm
LEDBulb 8W E27 965 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 8W E27 965 230V 2PF/3 AU	60 mm	110 mm



Product	D	C
LEDGlobe 7W G95 E27 WW 230V_AU	95 mm	137 mm

# LED Lamps

## Dimensional drawing



### Product

LEDBulb 10W B22 930 230V 1PF/6 AU  
 LEDBulb 10W B22 930 230V 2PF/3 AU  
 LEDBulb 10W B22 965 230V 1PF/6 AU  
 LEDBulb 10W B22 965 230V 2PF/3 AU  
 LEDBulb 12W B22 930 230V 1PF/6 AU  
 LEDBulb 12W B22 930 230V 2PF/3 AU  
 LEDBulb 12W B22 965 230V 1PF/6 AU  
 LEDBulb 12W B22 965 230V 2PF/3 AU  
 LEDBulb 6W B22 930 230V 1PF/6 AU  
 LEDBulb 6W B22 930 230V 2PF/3 AU  
 LEDBulb 6W B22 965 230V 1PF/6 AU  
 LEDBulb 6W B22 965 230V 2PF/3 AU  
 LEDBulb 8W B22 930 230V 1PF/6 AU  
 LEDBulb 8W B22 930 230V 2PF/3 AU  
 LEDBulb 8W B22 965 230V 1PF/6 AU  
 LEDBulb 8W B22 965 230V 2PF/3 AU

### Product

LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6

### D

62.5 mm

### C

122 mm

### Product

LEDGlobe 7W G95 B22 WW 230V\_AU

### D


95 mm

### C


135 mm

# LED Lamps


## Dimensional drawing




Product	D	C
LEDStick 9.5W B22 3000K 1PF/6 AU	37.2 mm	113 mm
LEDStick 9.5W B22 6500K 1PF/6 AU	37.2 mm	113 mm



Product	D	C
LED Sensor 8W B22 CDL FR 1PF/6 APR	62.5 mm	120 mm
LED Sensor 8W B22 WH FR 1PF/6 APR	62.5 mm	120 mm



Product	D	C
LEDStick 9.5W E27 3000K 1PF/6 AU	37.2 mm	114.3 mm
LEDStick 9.5W E27 6500K 1PF/6 AU	37.2 mm	114.3 mm



Product	D	C
LEDGlobe 10W G120 E27 WW 230V_AU	120 mm	170 mm

# LED Lamps

General Information	
Switching Cycle	50,000
Light Technical	
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted

## General Information

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)	Nominal lifetime
929003006319	LEDBulb 6W E27 930 230V 2PF/3 AU	E27	15,000 hour(s)	25,000 hour(s)
929003006399	LEDBulb 6W E27 930 230V 1PF/6 AU	E27	15,000 hour(s)	25,000 hour(s)
929003006719	LEDBulb 6W E27 965 230V 2PF/3 AU	E27	15,000 hour(s)	25,000 hour(s)
929003006799	LEDBulb 6W E27 965 230V 1PF/6 AU	E27	15,000 hour(s)	25,000 hour(s)
929003006909	LEDBulb 8W E27 930 230V 1CT/12 CN	E27	15,000 hour(s)	25,000 hour(s)
929003006919	LEDBulb 8W E27 930 230V 2PF/3 AU	E27	15,000 hour(s)	25,000 hour(s)
929003006999	LEDBulb 8W E27 930 230V 1PF/6 AU	E27	15,000 hour(s)	25,000 hour(s)
929003007309	LEDBulb 8W E27 965 230V 1CT/12 CN	E27	15,000 hour(s)	25,000 hour(s)
929003007319	LEDBulb 8W E27 965 230V 2PF/3 AU	E27	15,000 hour(s)	25,000 hour(s)
929003007399	LEDBulb 8W E27 965 230V 1PF/6 AU	E27	15,000 hour(s)	25,000 hour(s)
929002004049	LEDBulb 19W E27 3000K 230VA80 1CT/6APR	E27	12,000 hour(s)	15,000 hour(s)
929002004149	LEDBulb 19W E27 6500K 230VA80 1CT/6APR	E27	12,000 hour(s)	25,000 hour(s)
929002400119	LED Sensor 8W B22 WH FR 1PF/6 APR	B22	15,000 hour(s)	15,000 hour(s)
929002400219	LED Sensor 8W B22 CDL FR 1PF/6 APR	B22	15,000 hour(s)	15,000 hour(s)
929002442369	LEDGlobe 10W G120 B22 WW 230V_AU	B22	15,000 hour(s)	15,000 hour(s)

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)	Nominal lifetime
929003007509	LEDBulb 10W E27 930 230V 1CT/12 CN	E27	15,000 hour(s)	25,000 hour(s)
929003007519	LEDBulb 10W E27 930 230V 2PF/3 AU	E27	15,000 hour(s)	25,000 hour(s)
929003007599	LEDBulb 10W E27 930 230V 1PF/6 AU	E27	15,000 hour(s)	25,000 hour(s)
929003007909	LEDBulb 10W E27 965 230V 1CT/12 CN	E27	15,000 hour(s)	25,000 hour(s)
929003007919	LEDBulb 10W E27 965 230V 2PF/3 AU	E27	15,000 hour(s)	25,000 hour(s)
929003007999	LEDBulb 10W E27 965 230V 1PF/6 AU	E27	15,000 hour(s)	25,000 hour(s)
929003008109	LEDBulb 12W E27 930 230V 1CT/12 CN	E27	15,000 hour(s)	25,000 hour(s)
929003008119	LEDBulb 12W E27 930 230V 2PF/3 AU	E27	15,000 hour(s)	25,000 hour(s)
929003008199	LEDBulb 12W E27 930 230V 1PF/6 AU	E27	15,000 hour(s)	25,000 hour(s)
929003008509	LEDBulb 12W E27 965 230V 1CT/12 CN	E27	15,000 hour(s)	25,000 hour(s)
929003008519	LEDBulb 12W E27 965 230V 2PF/3 AU	E27	15,000 hour(s)	25,000 hour(s)
929003008599	LEDBulb 12W E27 965 230V 1PF/6 AU	E27	15,000 hour(s)	25,000 hour(s)
929002058619	LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6	E27	15,000 hour(s)	15,000 hour(s)
929001901469	LEDStick 9.5W E27 3000K 1PF/6 AU	E27	15,000 hour(s)	15,000 hour(s)
929001901669	LEDStick 9.5W E27 6500K 1PF/6 AU	E27	15,000 hour(s)	15,000 hour(s)

## LED Lamps

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)	Nominal lifetime	Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)	Nominal lifetime
929003006419	LEDBulb 6W B22 930 230V 2PF/3 AU	B22	15,000 hour(s)	25,000 hour(s)	929001927069	LEDStick 9.5W B22 3000K 1PF/6 AU	B22	15,000 hour(s)	15,000 hour(s)
929003006499	LEDBulb 6W B22 930 230V 1PF/6 AU	B22	15,000 hour(s)	25,000 hour(s)	929001927269	LEDStick 9.5W B22 6500K 1PF/6 AU	B22	15,000 hour(s)	15,000 hour(s)
929003006819	LEDBulb 6W B22 965 230V 2PF/3 AU	B22	15,000 hour(s)	25,000 hour(s)	929002441669	LEDGlobe 7W G95 E27 WW 230V_AU	E27	15,000 hour(s)	15,000 hour(s)
929003006899	LEDBulb 6W B22 965 230V 1PF/6 AU	B22	15,000 hour(s)	25,000 hour(s)	929003007619	LEDBulb 10W B22 930 230V 2PF/3 AU	B22	15,000 hour(s)	25,000 hour(s)
929003007019	LEDBulb 8W B22 930 230V 2PF/3 AU	B22	15,000 hour(s)	25,000 hour(s)	929003007699	LEDBulb 10W B22 930 230V 1PF/6 AU	B22	15,000 hour(s)	25,000 hour(s)
929003007099	LEDBulb 8W B22 930 230V 1PF/6 AU	B22	15,000 hour(s)	25,000 hour(s)	929003008019	LEDBulb 10W B22 965 230V 2PF/3 AU	B22	15,000 hour(s)	25,000 hour(s)
929003007419	LEDBulb 8W B22 965 230V 2PF/3 AU	B22	15,000 hour(s)	25,000 hour(s)	929003008099	LEDBulb 10W B22 965 230V 1PF/6 AU	B22	15,000 hour(s)	25,000 hour(s)
929003007499	LEDBulb 8W B22 965 230V 1PF/6 AU	B22	15,000 hour(s)	25,000 hour(s)	929003008219	LEDBulb 12W B22 930 230V 2PF/3 AU	B22	15,000 hour(s)	25,000 hour(s)
929002003849	LEDBulb 14.5W E27 3000K 230VA67 1CT/6APR	E27	12,000 hour(s)	25,000 hour(s)	929003008299	LEDBulb 12W B22 930 230V 1PF/6 AU	B22	15,000 hour(s)	25,000 hour(s)
929002003949	LEDBulb 14.5W E27 6500K 230VA67 1CT/6APR	E27	12,000 hour(s)	25,000 hour(s)	929003008619	LEDBulb 12W B22 965 230V 2PF/3 AU	B22	15,000 hour(s)	25,000 hour(s)
929002442069	LEDGlobe 7W G95 B22 WW 230V_AU	B22	15,000 hour(s)	15,000 hour(s)	929003008699	LEDBulb 12W B22 965 230V 1PF/6 AU	B22	15,000 hour(s)	25,000 hour(s)
929002442169	LEDGlobe 10W G120 E27 WW 230V_AU	E27	15,000 hour(s)	15,000 hour(s)					

### Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code	Luminous Flux
929003006319	LEDBulb 6W E27 930 230V 2PF/3 AU	200 degree(s)	3000 K	90	930	700 lm
929003006399	LEDBulb 6W E27 930 230V 1PF/6 AU	200 degree(s)	3000 K	90	930	700 lm
929003006719	LEDBulb 6W E27 965 230V 2PF/3 AU	200 degree(s)	6500 K	90	965	700 lm
929003006799	LEDBulb 6W E27 965 230V 1PF/6 AU	200 degree(s)	6500 K	90	965	700 lm
929003006909	LEDBulb 8W E27 930 230V 1CT/12 CN	200 degree(s)	3000 K	90	930	800 lm
929003006919	LEDBulb 8W E27 930 230V 2PF/3 AU	200 degree(s)	3000 K	90	930	910 lm
929003006999	LEDBulb 8W E27 930 230V 1PF/6 AU	200 degree(s)	3000 K	90	930	910 lm
929003007309	LEDBulb 8W E27 965 230V 1CT/12 CN	200 degree(s)	6500 K	90	965	800 lm
929003007319	LEDBulb 8W E27 965 230V 2PF/3 AU	200 degree(s)	6500 K	90	965	910 lm
929003007399	LEDBulb 8W E27 965 230V 1PF/6 AU	200 degree(s)	6500 K	90	965	910 lm
929002004049	LEDBulb 19W E27 3000K 230VA80 1CT/6APR	150 degree(s)	3000 K	80	830	2,150 lm
929002004149	LEDBulb 19W E27 6500K 230VA80 1CT/6APR	150 degree(s)	6500 K	80	865	2,300 lm
929002400119	LED Sensor 8W B22 WH FR 1PF/6 APR	280 degree(s)	3000 K	80	830	806 lm
929002400219	LED Sensor 8W B22 CDL FR 1PF/6 APR	280 degree(s)	6500 K	80	865	850 lm
929002442369	LEDGlobe 10W G120 B22 WW 230V_AU	150 degree(s)	2700 K	80	827	1,055 lm
929003007509	LEDBulb 10W E27 930 230V 1CT/12 CN	150 degree(s)	3000 K	90	930	1,000 lm
929003007519	LEDBulb 10W E27 930 230V 2PF/3 AU	150 degree(s)	3000 K	90	930	1,150 lm
929003007599	LEDBulb 10W E27 930 230V 1PF/6 AU	150 degree(s)	3000 K	90	930	1,150 lm
929003007909	LEDBulb 10W E27 965 230V 1CT/12 CN	150 degree(s)	6500 K	90	965	1,100 lm
929003007919	LEDBulb 10W E27 965 230V 2PF/3 AU	150 degree(s)	6500 K	90	965	1,150 lm
929003007999	LEDBulb 10W E27 965 230V 1PF/6 AU	150 degree(s)	6500 K	90	965	1,150 lm
929003008109	LEDBulb 12W E27 930 230V 1CT/12 CN	150 degree(s)	3000 K	90	930	1,300 lm

## LED Lamps

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code	Luminous Flux
929003008119	LEDBulb 12W E27 930 230V 2PF/3 AU	150 degree(s)	3000 K	90	930	1,360 lm
929003008199	LEDBulb 12W E27 930 230V 1PF/6 AU	150 degree(s)	3000 K	90	930	1,360 lm
929003008509	LEDBulb 12W E27 965 230V 1CT/12 CN	150 degree(s)	6500 K	90	965	1,300 lm
929003008519	LEDBulb 12W E27 965 230V 2PF/3 AU	150 degree(s)	6500 K	90	965	1,360 lm
929003008599	LEDBulb 12W E27 965 230V 1PF/6 AU	150 degree(s)	6500 K	90	965	1,360 lm
929002058619	LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6	280 degree(s)	6500 K	80	865	850 lm
929001901469	LEDStick 9.5W E27 3000K 1PF/6 AU	200 degree(s)	3000 K	80	830	950 lm
929001901669	LEDStick 9.5W E27 6500K 1PF/6 AU	200 degree(s)	6500 K	80	865	1,050 lm
929003006419	LEDBulb 6W B22 930 230V 2PF/3 AU	200 degree(s)	3000 K	90	930	700 lm
929003006499	LEDBulb 6W B22 930 230V 1PF/6 AU	200 degree(s)	3000 K	90	930	700 lm
929003006819	LEDBulb 6W B22 965 230V 2PF/3 AU	200 degree(s)	6500 K	90	965	700 lm
929003006899	LEDBulb 6W B22 965 230V 1PF/6 AU	200 degree(s)	6500 K	90	965	700 lm
929003007019	LEDBulb 8W B22 930 230V 2PF/3 AU	200 degree(s)	3000 K	90	930	910 lm
929003007099	LEDBulb 8W B22 930 230V 1PF/6 AU	200 degree(s)	3000 K	90	930	910 lm
929003007419	LEDBulb 8W B22 965 230V 2PF/3 AU	200 degree(s)	6500 K	90	965	910 lm
929003007499	LEDBulb 8W B22 965 230V 1PF/6 AU	200 degree(s)	6500 K	90	965	910 lm
929002003849	LEDBulb 14.5W E27 3000K 230VA67 1CT/6APR	150 degree(s)	3000 K	80	830	1,650 lm
929002003949	LEDBulb 14.5W E27 6500K 230VA67 1CT/6APR	150 degree(s)	6500 K	80	865	1,800 lm
929002442069	LEDGlobe 7W G95 B22 WW 230V_AU	150 degree(s)	2700 K	80	827	806 lm
929002442169	LEDGlobe 10W G120 E27 WW 230V_AU	150 degree(s)	2700 K	80	827	1,055 lm
929001927069	LEDStick 9.5W B22 3000K 1PF/6 AU	200 degree(s)	3000 K	80	830	950 lm
929001927269	LEDStick 9.5W B22 6500K 1PF/6 AU	200 degree(s)	6500 K	80	865	1,050 lm
929002441669	LEDGlobe 7W G95 E27 WW 230V_AU	150 degree(s)	2700 K	80	827	806 lm
929003007619	LEDBulb 10W B22 930 230V 2PF/3 AU	150 degree(s)	3000 K	90	930	1,150 lm
929003007699	LEDBulb 10W B22 930 230V 1PF/6 AU	150 degree(s)	3000 K	90	930	1,150 lm
929003008019	LEDBulb 10W B22 965 230V 2PF/3 AU	150 degree(s)	6500 K	90	965	1,150 lm
929003008099	LEDBulb 10W B22 965 230V 1PF/6 AU	150 degree(s)	6500 K	90	965	1,150 lm
929003008219	LEDBulb 12W B22 930 230V 2PF/3 AU	150 degree(s)	3000 K	90	930	1,360 lm
929003008299	LEDBulb 12W B22 930 230V 1PF/6 AU	150 degree(s)	3000 K	90	930	1,360 lm
929003008619	LEDBulb 12W B22 965 230V 2PF/3 AU	150 degree(s)	6500 K	90	965	1,360 lm
929003008699	LEDBulb 12W B22 965 230V 1PF/6 AU	150 degree(s)	6500 K	90	965	1,360 lm

### Operating and Electrical

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent	Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent
929003006319	LEDBulb 6W E27 930 230V 2PF/3 AU	-	6 W	65 W	929003007319	LEDBulb 8W E27 965 230V 2PF/3 AU	-	8 W	76 W
929003006399	LEDBulb 6W E27 930 230V 1PF/6 AU	-	6 W	65 W	929003007399	LEDBulb 8W E27 965 230V 1PF/6 AU	-	8 W	76 W
929003006719	LEDBulb 6W E27 965 230V 2PF/3 AU	-	6 W	65 W	929002004049	LEDBulb 19W E27 3000K 230VA80 1CT/6APR	-	19 W	155 W
929003006799	LEDBulb 6W E27 965 230V 1PF/6 AU	-	6 W	65 W	929002004149	LEDBulb 19W E27 6500K 230VA80 1CT/6APR	-	19 W	160 W
929003006909	LEDBulb 8W E27 930 230V 1CT/12 CN	50 to 60 Hz	8 W	60 W	929002400119	LED Sensor 8W B22 WH FR 1PF/6 APR	-	8 W	60 W
929003006919	LEDBulb 8W E27 930 230V 2PF/3 AU	-	8 W	76 W	929002400219	LED Sensor 8W B22 CDL FR 1PF/6 APR	-	8 W	60 W
929003006999	LEDBulb 8W E27 930 230V 1PF/6 AU	-	8 W	76 W	929002442369	LEDGlobe 10W G120 B22 WW 230V_AU	-	10 W	75 W
929003007309	LEDBulb 8W E27 965 230V 1CT/12 CN	50 to 60 Hz	8 W	60 W					

## LED Lamps

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent
929003007509	LEDBulb 10W E27 930 230V 1CT/12 CN	50 to 60 Hz	10 W	75 W
929003007519	LEDBulb 10W E27 930 230V 2PF/3 AU	-	10 W	89 W
929003007599	LEDBulb 10W E27 930 230V 1PF/6 AU	-	10 W	89 W
929003007909	LEDBulb 10W E27 965 230V 1CT/12 CN	50 to 60 Hz	10 W	80 W
929003007919	LEDBulb 10W E27 965 230V 2PF/3 AU	-	10 W	89 W
929003007999	LEDBulb 10W E27 965 230V 1PF/6 AU	-	10 W	89 W
929003008109	LEDBulb 12W E27 930 230V 1CT/12 CN	50 to 60 Hz	12 W	90 W
929003008119	LEDBulb 12W E27 930 230V 2PF/3 AU	-	12 W	98 W
929003008199	LEDBulb 12W E27 930 230V 1PF/6 AU	-	12 W	98 W
929003008509	LEDBulb 12W E27 965 230V 1CT/12 CN	50 to 60 Hz	12 W	90 W
929003008519	LEDBulb 12W E27 965 230V 2PF/3 AU	-	12 W	98 W
929003008599	LEDBulb 12W E27 965 230V 1PF/6 AU	-	12 W	98 W
929002058619	LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6	-	8 W	60 W
929001901469	LEDStick 9.5W E27 3000K 1PF/6 AU	-	9.5 W	68 W
929001901669	LEDStick 9.5W E27 6500K 1PF/6 AU	-	9.5 W	75 W
929003006419	LEDBulb 6W B22 930 230V 2PF/3 AU	-	6 W	65 W
929003006499	LEDBulb 6W B22 930 230V 1PF/6 AU	-	6 W	65 W
929003006819	LEDBulb 6W B22 965 230V 2PF/3 AU	-	6 W	65 W
929003006899	LEDBulb 6W B22 965 230V 1PF/6 AU	-	6 W	65 W
929003007019	LEDBulb 8W B22 930 230V 2PF/3 AU	-	8 W	76 W

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent
929003007099	LEDBulb 8W B22 930 230V 1PF/6 AU	-	8 W	76 W
929003007419	LEDBulb 8W B22 965 230V 2PF/3 AU	-	8 W	76 W
929003007499	LEDBulb 8W B22 965 230V 1PF/6 AU	-	8 W	76 W
929002003849	LEDBulb 14.5W E27 3000K 230VA67 1CT/6APR	-	14.5 W	120 W
929002003949	LEDBulb 14.5W E27 6500K 230VA67 1CT/6APR	-	14.5 W	120 W
929002442069	LEDGlobe 7W G95 B22 WW 230V_AU	-	7 W	60 W
929002442169	LEDGlobe 10W G120 E27 WW 230V_AU	-	10 W	75 W
929001927069	LEDStick 9.5W B22 3000K 1PF/6 AU	-	9.5 W	68 W
929001927269	LEDStick 9.5W B22 6500K 1PF/6 AU	-	9.5 W	75 W
929002441669	LEDGlobe 7W G95 E27 WW 230V_AU	-	7 W	60 W
929003007619	LEDBulb 10W B22 930 230V 2PF/3 AU	-	10 W	89 W
929003007699	LEDBulb 10W B22 930 230V 1PF/6 AU	-	10 W	89 W
929003008019	LEDBulb 10W B22 965 230V 2PF/3 AU	-	10 W	89 W
929003008099	LEDBulb 10W B22 965 230V 1PF/6 AU	-	10 W	89 W
929003008219	LEDBulb 12W B22 930 230V 2PF/3 AU	-	12 W	98 W
929003008299	LEDBulb 12W B22 930 230V 1PF/6 AU	-	12 W	98 W
929003008619	LEDBulb 12W B22 965 230V 2PF/3 AU	-	12 W	98 W
929003008699	LEDBulb 12W B22 965 230V 1PF/6 AU	-	12 W	98 W

## Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929003006319	LEDBulb 6W E27 930 230V 2PF/3 AU	85 °C
929003006399	LEDBulb 6W E27 930 230V 1PF/6 AU	85 °C
929003006719	LEDBulb 6W E27 965 230V 2PF/3 AU	85 °C
929003006799	LEDBulb 6W E27 965 230V 1PF/6 AU	85 °C
929003006909	LEDBulb 8W E27 930 230V 1CT/12 CN	95 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929003006919	LEDBulb 8W E27 930 230V 2PF/3 AU	95 °C
929003006999	LEDBulb 8W E27 930 230V 1PF/6 AU	95 °C
929003007309	LEDBulb 8W E27 965 230V 1CT/12 CN	95 °C
929003007319	LEDBulb 8W E27 965 230V 2PF/3 AU	95 °C
929003007399	LEDBulb 8W E27 965 230V 1PF/6 AU	95 °C

# LED Lamps

Order Code	Full Product Name	T-Case Maximum (Nom)
929002004049	LEDBulb 19W E27 3000K 230VA80 1CT/6APR	90 °C
929002004149	LEDBulb 19W E27 6500K 230VA80 1CT/6APR	90 °C
929002400119	LED Sensor 8W B22 WH FR 1PF/6 APR	75 °C
929002400219	LED Sensor 8W B22 CDL FR 1PF/6 APR	75 °C
929002442369	LEDGlobe 10W G120 B22 WW 230V_AU	50 °C
929003007509	LEDBulb 10W E27 930 230V 1CT/12 CN	90 °C
929003007519	LEDBulb 10W E27 930 230V 2PF/3 AU	90 °C
929003007599	LEDBulb 10W E27 930 230V 1PF/6 AU	90 °C
929003007909	LEDBulb 10W E27 965 230V 1CT/12 CN	90 °C
929003007919	LEDBulb 10W E27 965 230V 2PF/3 AU	90 °C
929003007999	LEDBulb 10W E27 965 230V 1PF/6 AU	90 °C
929003008109	LEDBulb 12W E27 930 230V 1CT/12 CN	95 °C
929003008119	LEDBulb 12W E27 930 230V 2PF/3 AU	95 °C
929003008199	LEDBulb 12W E27 930 230V 1PF/6 AU	95 °C
929003008509	LEDBulb 12W E27 965 230V 1CT/12 CN	95 °C
929003008519	LEDBulb 12W E27 965 230V 2PF/3 AU	95 °C
929003008599	LEDBulb 12W E27 965 230V 1PF/6 AU	95 °C
929002058619	LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6	75 °C
929001901469	LEDStick 9.5W E27 3000K 1PF/6 AU	85 °C
929001901669	LEDStick 9.5W E27 6500K 1PF/6 AU	85 °C
929003006419	LEDBulb 6W B22 930 230V 2PF/3 AU	85 °C
929003006499	LEDBulb 6W B22 930 230V 1PF/6 AU	85 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929003006819	LEDBulb 6W B22 965 230V 2PF/3 AU	85 °C
929003006899	LEDBulb 6W B22 965 230V 1PF/6 AU	85 °C
929003007019	LEDBulb 8W B22 930 230V 2PF/3 AU	95 °C
929003007099	LEDBulb 8W B22 930 230V 1PF/6 AU	95 °C
929003007419	LEDBulb 8W B22 965 230V 2PF/3 AU	95 °C
929003007499	LEDBulb 8W B22 965 230V 1PF/6 AU	95 °C
929002003849	LEDBulb 14.5W E27 3000K 230VA67 1CT/6APR	90 °C
929002003949	LEDBulb 14.5W E27 6500K 230VA67 1CT/6APR	90 °C
929002442069	LEDGlobe 7W G95 B22 WW 230V_AU	45 °C
929002442169	LEDGlobe 10W G120 E27 WW 230V_AU	50 °C
929001927069	LEDStick 9.5W B22 3000K 1PF/6 AU	85 °C
929001927269	LEDStick 9.5W B22 6500K 1PF/6 AU	85 °C
929002441669	LEDGlobe 7W G95 E27 WW 230V_AU	45 °C
929003007619	LEDBulb 10W B22 930 230V 2PF/3 AU	90 °C
929003007699	LEDBulb 10W B22 930 230V 1PF/6 AU	90 °C
929003008019	LEDBulb 10W B22 965 230V 2PF/3 AU	90 °C
929003008099	LEDBulb 10W B22 965 230V 1PF/6 AU	90 °C
929003008219	LEDBulb 12W B22 930 230V 2PF/3 AU	95 °C
929003008299	LEDBulb 12W B22 930 230V 1PF/6 AU	95 °C
929003008619	LEDBulb 12W B22 965 230V 2PF/3 AU	95 °C
929003008699	LEDBulb 12W B22 965 230V 1PF/6 AU	95 °C

## Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
929003006319	LEDBulb 6W E27 930 230V 2PF/3 AU	A60S
929003006399	LEDBulb 6W E27 930 230V 1PF/6 AU	A60S
929003006719	LEDBulb 6W E27 965 230V 2PF/3 AU	A60S
929003006799	LEDBulb 6W E27 965 230V 1PF/6 AU	A60S
929003006909	LEDBulb 8W E27 930 230V 1CT/12 CN	A60S
929003006919	LEDBulb 8W E27 930 230V 2PF/3 AU	A60S
929003006999	LEDBulb 8W E27 930 230V 1PF/6 AU	A60S
929003007309	LEDBulb 8W E27 965 230V 1CT/12 CN	A60S
929003007319	LEDBulb 8W E27 965 230V 2PF/3 AU	A60S
929003007399	LEDBulb 8W E27 965 230V 1PF/6 AU	A60S
929002004049	LEDBulb 19W E27 3000K 230VA80 1CT/6APR	A80
929002004149	LEDBulb 19W E27 6500K 230VA80 1CT/6APR	A80
929002400119	LED Sensor 8W B22 WH FR 1PF/6 APR	A60
929002400219	LED Sensor 8W B22 CDL FR 1PF/6 APR	A60
929002442369	LEDGlobe 10W G120 B22 WW 230V_AU	G120
929003007509	LEDBulb 10W E27 930 230V 1CT/12 CN	A60M
929003007519	LEDBulb 10W E27 930 230V 2PF/3 AU	A60M
929003007599	LEDBulb 10W E27 930 230V 1PF/6 AU	A60M
929003007909	LEDBulb 10W E27 965 230V 1CT/12 CN	A60M
929003007919	LEDBulb 10W E27 965 230V 2PF/3 AU	A60M
929003007999	LEDBulb 10W E27 965 230V 1PF/6 AU	A60M
929003008109	LEDBulb 12W E27 930 230V 1CT/12 CN	A60M
929003008119	LEDBulb 12W E27 930 230V 2PF/3 AU	A60M
929003008199	LEDBulb 12W E27 930 230V 1PF/6 AU	A60M
929003008509	LEDBulb 12W E27 965 230V 1CT/12 CN	A60M

Order Code	Full Product Name	Bulb Shape
929003008519	LEDBulb 12W E27 965 230V 2PF/3 AU	A60M
929003008599	LEDBulb 12W E27 965 230V 1PF/6 AU	A60M
929002058619	LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6	A60
929001901469	LEDStick 9.5W E27 3000K 1PF/6 AU	Stick
929001901669	LEDStick 9.5W E27 6500K 1PF/6 AU	Stick
929003006419	LEDBulb 6W B22 930 230V 2PF/3 AU	A60S
929003006499	LEDBulb 6W B22 930 230V 1PF/6 AU	A60S
929003006819	LEDBulb 6W B22 965 230V 2PF/3 AU	A60S
929003006899	LEDBulb 6W B22 965 230V 1PF/6 AU	A60S
929003007019	LEDBulb 8W B22 930 230V 2PF/3 AU	A60S
929003007099	LEDBulb 8W B22 930 230V 1PF/6 AU	A60S
929003007419	LEDBulb 8W B22 965 230V 2PF/3 AU	A60S
929003007499	LEDBulb 8W B22 965 230V 1PF/6 AU	A60S
929002003849	LEDBulb 14.5W E27 3000K 230VA67 1CT/6APR	A67
929002003949	LEDBulb 14.5W E27 6500K 230VA67 1CT/6APR	A67
929002442069	LEDGlobe 7W G95 B22 WW 230V_AU	G95
929002442169	LEDGlobe 10W G120 E27 WW 230V_AU	G120
929001927069	LEDStick 9.5W B22 3000K 1PF/6 AU	Stick
929001927269	LEDStick 9.5W B22 6500K 1PF/6 AU	Stick
929002441669	LEDGlobe 7W G95 E27 WW 230V_AU	G95
929003007619	LEDBulb 10W B22 930 230V 2PF/3 AU	A60M
929003007699	LEDBulb 10W B22 930 230V 1PF/6 AU	A60M
929003008019	LEDBulb 10W B22 965 230V 2PF/3 AU	A60M
929003008099	LEDBulb 10W B22 965 230V 1PF/6 AU	A60M
929003008219	LEDBulb 12W B22 930 230V 2PF/3 AU	A60M

## LED Lamps

Order Code	Full Product Name	Bulb Shape
929003008299	LEDBulb 12W B22 930 230V 1PF/6 AU	A60M
929003008619	LEDBulb 12W B22 965 230V 2PF/3 AU	A60M

Order Code	Full Product Name	Bulb Shape
929003008699	LEDBulb 12W B22 965 230V 1PF/6 AU	A60M









### Approval and Application

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929003006319	LEDBulb 6W E27 930 230V 2PF/3 AU	-20 to +45 °C	-
929003006399	LEDBulb 6W E27 930 230V 1PF/6 AU	-20 to +45 °C	-
929003006719	LEDBulb 6W E27 965 230V 2PF/3 AU	-20 to +45 °C	-
929003006799	LEDBulb 6W E27 965 230V 1PF/6 AU	-20 to +45 °C	-
929003006909	LEDBulb 8W E27 930 230V 1CT/12 CN	-	-
929003006919	LEDBulb 8W E27 930 230V 2PF/3 AU	-20 to +45 °C	-
929003006999	LEDBulb 8W E27 930 230V 1PF/6 AU	-20 to +45 °C	-
929003007309	LEDBulb 8W E27 965 230V 1CT/12 CN	-	-
929003007319	LEDBulb 8W E27 965 230V 2PF/3 AU	-20 to +45 °C	-
929003007399	LEDBulb 8W E27 965 230V 1PF/6 AU	-20 to +45 °C	-
929002004049	LEDBulb 19W E27 3000K 230VA80 1CT/6APR	-20 to +45 °C	19 kWh
929002004149	LEDBulb 19W E27 6500K 230VA80 1CT/6APR	-20 to +45 °C	19 kWh
929002400119	LED Sensor 8W B22 WH FR 1PF/6 APR	-20 to +30 °C	8 kWh
929002400219	LED Sensor 8W B22 CDL FR 1PF/6 APR	-20 to +30 °C	8 kWh
929002442369	LEDGlobe 10W G120 B22 WW 230V_AU	-20 to +45 °C	10 kWh
929003007509	LEDBulb 10W E27 930 230V 1CT/12 CN	-	-
929003007519	LEDBulb 10W E27 930 230V 2PF/3 AU	-20 to +45 °C	-
929003007599	LEDBulb 10W E27 930 230V 1PF/6 AU	-20 to +45 °C	-
929003007909	LEDBulb 10W E27 965 230V 1CT/12 CN	-	-
929003007919	LEDBulb 10W E27 965 230V 2PF/3 AU	-20 to +45 °C	-
929003007999	LEDBulb 10W E27 965 230V 1PF/6 AU	-20 to +45 °C	-
929003008109	LEDBulb 12W E27 930 230V 1CT/12 CN	-	-











Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929003008119	LEDBulb 12W E27 930 230V 2PF/3 AU	-20 to +45 °C	-
929003008199	LEDBulb 12W E27 930 230V 1PF/6 AU	-20 to +45 °C	-
929003008509	LEDBulb 12W E27 965 230V 1CT/12 CN	-	-
929003008519	LEDBulb 12W E27 965 230V 2PF/3 AU	-20 to +45 °C	-
929003008599	LEDBulb 12W E27 965 230V 1PF/6 AU	-20 to +45 °C	-
929002058619	LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6	-20 to +30 °C	8 kWh
929001901469	LEDStick 9.5W E27 3000K 1PF/6 AU	-20 to +45 °C	10 kWh
929001901669	LEDStick 9.5W E27 6500K 1PF/6 AU	-20 to +45 °C	10 kWh
929003006419	LEDBulb 6W B22 930 230V 2PF/3 AU	-20 to +45 °C	-
929003006499	LEDBulb 6W B22 930 230V 1PF/6 AU	-20 to +45 °C	-
929003006819	LEDBulb 6W B22 965 230V 2PF/3 AU	-20 to +45 °C	-
929003006899	LEDBulb 6W B22 965 230V 1PF/6 AU	-20 to +45 °C	-
929003007019	LEDBulb 8W B22 930 230V 2PF/3 AU	-20 to +45 °C	-
929003007099	LEDBulb 8W B22 930 230V 1PF/6 AU	-20 to +45 °C	-
929003007419	LEDBulb 8W B22 965 230V 2PF/3 AU	-20 to +45 °C	-
929003007499	LEDBulb 8W B22 965 230V 1PF/6 AU	-20 to +45 °C	-
929002003849	LEDBulb 14.5W E27 3000K 230VA67 1CT/6APR	-20 to +45 °C	15 kWh
929002003949	LEDBulb 14.5W E27 6500K 230VA67 1CT/6APR	-20 to +45 °C	15 kWh
929002442069	LEDGlobe 7W G95 B22 WW 230V_AU	-20 to +45 °C	7 kWh
929002442169	LEDGlobe 10W G120 E27 WW 230V_AU	-20 to +45 °C	10 kWh
929001927069	LEDStick 9.5W B22 3000K 1PF/6 AU	-20 to +45 °C	10 kWh
929001927269	LEDStick 9.5W B22 6500K 1PF/6 AU	-20 to +45 °C	10 kWh

# LED Lamps

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929002441669	LEDGlobe 7W G95 E27 WW 230V_AU	-20 to +45 °C	7 kWh
929003007619	LEDBulb 10W B22 930 230V 2PF/3 AU	-20 to +45 °C	-
929003007699	LEDBulb 10W B22 930 230V 1PF/6 AU	-20 to +45 °C	-
929003008019	LEDBulb 10W B22 965 230V 2PF/3 AU	-20 to +45 °C	-
929003008099	LEDBulb 10W B22 965 230V 1PF/6 AU	-20 to +45 °C	-
929003008219	LEDBulb 12W B22 930 230V 2PF/3 AU	-20 to +45 °C	-
929003008299	LEDBulb 12W B22 930 230V 1PF/6 AU	-20 to +45 °C	-
929003008619	LEDBulb 12W B22 965 230V 2PF/3 AU	-20 to +45 °C	-
929003008699	LEDBulb 12W B22 965 230V 1PF/6 AU	-20 to +45 °C	-



# LED Lamps



# LED Lamps

