



LED Lamps – ideal for general lighting applications

LED Lamps

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

Benefits

- Color temperature suitable for both functional lighting and to enhance atmosphere
- Up to 80% energy savings compared with incandescent bulbs
- Suitable for retrofit
- Lower maintenance costs

Features

- Long lifetime
- UV- and IR-free light for less heat and protection of heat-sensitive objects
- Instant start

Application

- Homes, hotels, restaurants, cafes
- Bedroom, dining room, living room, study room

LED Lamps

Versions



LED Sensor 8 60W B22 WH FR



LED Sensor A60 E27 WW POS1





LEDGlobe 7 60W G95 B22 WW 230V AU



LEDBulb 10W B22 AU




Dimensional drawing



Product	D	C
LEDBulb 10W E27 930 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 10W E27 930 230V 2PF/3 AU	60 mm	110 mm
LEDBulb 10W E27 965 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 10W E27 965 230V 2PF/3 AU	60 mm	110 mm
LEDBulb 12W E27 930 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 12W E27 930 230V 2PF/3 AU	60 mm	110 mm
LEDBulb 12W E27 965 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 12W E27 965 230V 2PF/3 AU	60 mm	110 mm
LEDBulb 6W E27 930 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 6W E27 930 230V 2PF/3 AU	60 mm	110 mm
LEDBulb 6W E27 965 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 6W E27 965 230V 2PF/3 AU	60 mm	110 mm
LEDBulb 8W E27 930 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 8W E27 930 230V 2PF/3 AU	60 mm	110 mm
LEDBulb 8W E27 965 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 8W E27 965 230V 2PF/3 AU	60 mm	110 mm

LED Lamps

Dimensional drawing




Product
LEDBulb 10W B22 930 230V 1PF/6 AU
LEDBulb 10W B22 930 230V 2PF/3 AU
LEDBulb 10W B22 965 230V 1PF/6 AU
LEDBulb 10W B22 965 230V 2PF/3 AU
LEDBulb 12W B22 930 230V 1PF/6 AU
LEDBulb 12W B22 930 230V 2PF/3 AU
LEDBulb 12W B22 965 230V 1PF/6 AU
LEDBulb 12W B22 965 230V 2PF/3 AU
LEDBulb 6W B22 930 230V 1PF/6 AU
LEDBulb 6W B22 930 230V 2PF/3 AU
LEDBulb 6W B22 965 230V 1PF/6 AU
LEDBulb 6W B22 965 230V 2PF/3 AU
LEDBulb 8W B22 930 230V 1PF/6 AU
LEDBulb 8W B22 930 230V 2PF/3 AU
LEDBulb 8W B22 965 230V 1PF/6 AU
LEDBulb 8W B22 965 230V 2PF/3 AU

Product	D	C
LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6	62.5 mm	122 mm

Product	D	C
LEDGlobe 7W G95 B22 WW 230V_AU	95 mm	135 mm

LED Lamps

Dimensional drawing



Product	D	C
LED Sensor 8W B22 CDL FR 1PF/6 APR	62.5 mm	120 mm

General Information	
Rated Lifetime (Hours)	15,000 h
Switching Cycle	50,000
Light Technical	
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted

General Information

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929003006319	LEDBulb 6W E27 930 230V 2PF/3 AU	E27	25,000 h
929003006399	LEDBulb 6W E27 930 230V 1PF/6 AU	E27	25,000 h
929003006719	LEDBulb 6W E27 965 230V 2PF/3 AU	E27	25,000 h
929003006799	LEDBulb 6W E27 965 230V 1PF/6 AU	E27	25,000 h
929003006919	LEDBulb 8W E27 930 230V 2PF/3 AU	E27	25,000 h
929003006999	LEDBulb 8W E27 930 230V 1PF/6 AU	E27	25,000 h
929003007319	LEDBulb 8W E27 965 230V 2PF/3 AU	E27	25,000 h
929003007399	LEDBulb 8W E27 965 230V 1PF/6 AU	E27	25,000 h
929002400219	LED Sensor 8W B22 CDL FR 1PF/6 APR	B22	15,000 h
929003007519	LEDBulb 10W E27 930 230V 2PF/3 AU	E27	25,000 h
929003007599	LEDBulb 10W E27 930 230V 1PF/6 AU	E27	25,000 h
929003007919	LEDBulb 10W E27 965 230V 2PF/3 AU	E27	25,000 h
929003007999	LEDBulb 10W E27 965 230V 1PF/6 AU	E27	25,000 h
929003008119	LEDBulb 12W E27 930 230V 2PF/3 AU	E27	25,000 h
929003008199	LEDBulb 12W E27 930 230V 1PF/6 AU	E27	25,000 h
929003008519	LEDBulb 12W E27 965 230V 2PF/3 AU	E27	25,000 h

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929003008599	LEDBulb 12W E27 965 230V 1PF/6 AU	E27	25,000 h
929002058619	LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6	E27	15,000 h
929003006419	LEDBulb 6W B22 930 230V 2PF/3 AU	B22	25,000 h
929003006499	LEDBulb 6W B22 930 230V 1PF/6 AU	B22	25,000 h
929003006819	LEDBulb 6W B22 965 230V 2PF/3 AU	B22	25,000 h
929003006899	LEDBulb 6W B22 965 230V 1PF/6 AU	B22	25,000 h
929003007019	LEDBulb 8W B22 930 230V 2PF/3 AU	B22	25,000 h
929003007099	LEDBulb 8W B22 930 230V 1PF/6 AU	B22	25,000 h
929003007419	LEDBulb 8W B22 965 230V 2PF/3 AU	B22	25,000 h
929003007499	LEDBulb 8W B22 965 230V 1PF/6 AU	B22	25,000 h
929002442069	LEDGlobe 7W G95 B22 WW 230V_AU	B22	15,000 h
929003007619	LEDBulb 10W B22 930 230V 2PF/3 AU	B22	25,000 h
929003007699	LEDBulb 10W B22 930 230V 1PF/6 AU	B22	25,000 h
929003008019	LEDBulb 10W B22 965 230V 2PF/3 AU	B22	25,000 h
929003008099	LEDBulb 10W B22 965 230V 1PF/6 AU	B22	25,000 h

LED Lamps

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929003008219	LEDBulb 12W B22 930 230V 2PF/3 AU	B22	25,000 h
929003008299	LEDBulb 12W B22 930 230V 1PF/6 AU	B22	25,000 h

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929003008619	LEDBulb 12W B22 965 230V 2PF/3 AU	B22	25,000 h
929003008699	LEDBulb 12W B22 965 230V 1PF/6 AU	B22	25,000 h

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code	Luminous Flux
929003006319	LEDBulb 6W E27 930 230V 2PF/3 AU	200 degree(s)	3000 K	90	930	700 lm
929003006399	LEDBulb 6W E27 930 230V 1PF/6 AU	200 degree(s)	3000 K	90	930	700 lm
929003006719	LEDBulb 6W E27 965 230V 2PF/3 AU	200 degree(s)	6500 K	90	965	700 lm
929003006799	LEDBulb 6W E27 965 230V 1PF/6 AU	200 degree(s)	6500 K	90	965	700 lm
929003006919	LEDBulb 8W E27 930 230V 2PF/3 AU	200 degree(s)	3000 K	90	930	910 lm
929003006999	LEDBulb 8W E27 930 230V 1PF/6 AU	200 degree(s)	3000 K	90	930	910 lm
929003007319	LEDBulb 8W E27 965 230V 2PF/3 AU	200 degree(s)	6500 K	90	965	910 lm
929003007399	LEDBulb 8W E27 965 230V 1PF/6 AU	200 degree(s)	6500 K	90	965	910 lm
929002400219	LED Sensor 8W B22 CDL FR 1PF/6 APR	280 degree(s)	6500 K	80	865	850 lm
929003007519	LEDBulb 10W E27 930 230V 2PF/3 AU	150 degree(s)	3000 K	90	930	1,150 lm
929003007599	LEDBulb 10W E27 930 230V 1PF/6 AU	150 degree(s)	3000 K	90	930	1,150 lm
929003007919	LEDBulb 10W E27 965 230V 2PF/3 AU	150 degree(s)	6500 K	90	965	1,150 lm
929003007999	LEDBulb 10W E27 965 230V 1PF/6 AU	150 degree(s)	6500 K	90	965	1,150 lm
929003008119	LEDBulb 12W E27 930 230V 2PF/3 AU	150 degree(s)	3000 K	90	930	1,360 lm
929003008199	LEDBulb 12W E27 930 230V 1PF/6 AU	150 degree(s)	3000 K	90	930	1,360 lm
929003008519	LEDBulb 12W E27 965 230V 2PF/3 AU	150 degree(s)	6500 K	90	965	1,360 lm
929003008599	LEDBulb 12W E27 965 230V 1PF/6 AU	150 degree(s)	6500 K	90	965	1,360 lm
929002058619	LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6	280 degree(s)	6500 K	80	865	850 lm
929003006419	LEDBulb 6W B22 930 230V 2PF/3 AU	200 degree(s)	3000 K	90	930	700 lm
929003006499	LEDBulb 6W B22 930 230V 1PF/6 AU	200 degree(s)	3000 K	90	930	700 lm
929003006819	LEDBulb 6W B22 965 230V 2PF/3 AU	200 degree(s)	6500 K	90	965	700 lm
929003006899	LEDBulb 6W B22 965 230V 1PF/6 AU	200 degree(s)	6500 K	90	965	700 lm
929003007019	LEDBulb 8W B22 930 230V 2PF/3 AU	200 degree(s)	3000 K	90	930	910 lm
929003007099	LEDBulb 8W B22 930 230V 1PF/6 AU	200 degree(s)	3000 K	90	930	910 lm
929003007419	LEDBulb 8W B22 965 230V 2PF/3 AU	200 degree(s)	6500 K	90	965	910 lm
929003007499	LEDBulb 8W B22 965 230V 1PF/6 AU	200 degree(s)	6500 K	90	965	910 lm
929002442069	LEDGlobe 7W G95 B22 WW 230V_AU	150 degree(s)	2700 K	80	827	806 lm
929003007619	LEDBulb 10W B22 930 230V 2PF/3 AU	150 degree(s)	3000 K	90	930	1,150 lm
929003007699	LEDBulb 10W B22 930 230V 1PF/6 AU	150 degree(s)	3000 K	90	930	1,150 lm
929003008019	LEDBulb 10W B22 965 230V 2PF/3 AU	150 degree(s)	6500 K	90	965	1,150 lm
929003008099	LEDBulb 10W B22 965 230V 1PF/6 AU	150 degree(s)	6500 K	90	965	1,150 lm
929003008219	LEDBulb 12W B22 930 230V 2PF/3 AU	150 degree(s)	3000 K	90	930	1,360 lm
929003008299	LEDBulb 12W B22 930 230V 1PF/6 AU	150 degree(s)	3000 K	90	930	1,360 lm
929003008619	LEDBulb 12W B22 965 230V 2PF/3 AU	150 degree(s)	6500 K	90	965	1,360 lm
929003008699	LEDBulb 12W B22 965 230V 1PF/6 AU	150 degree(s)	6500 K	90	965	1,360 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
929003006319	LEDBulb 6W E27 930 230V 2PF/3 AU	6 W	65 W
929003006399	LEDBulb 6W E27 930 230V 1PF/6 AU	6 W	65 W

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
929003006719	LEDBulb 6W E27 965 230V 2PF/3 AU	6 W	65 W
929003006799	LEDBulb 6W E27 965 230V 1PF/6 AU	6 W	65 W

LED Lamps

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
929003006919	LEDBulb 8W E27 930 230V 2PF/3 AU	8 W	76 W
929003006999	LEDBulb 8W E27 930 230V 1PF/6 AU	8 W	76 W
929003007319	LEDBulb 8W E27 965 230V 2PF/3 AU	8 W	76 W
929003007399	LEDBulb 8W E27 965 230V 1PF/6 AU	8 W	76 W
929002400219	LED Sensor 8W B22 CDL FR 1PF/6 APR	8 W	60 W
929003007519	LEDBulb 10W E27 930 230V 2PF/3 AU	10 W	89 W
929003007599	LEDBulb 10W E27 930 230V 1PF/6 AU	10 W	89 W
929003007919	LEDBulb 10W E27 965 230V 2PF/3 AU	10 W	89 W
929003007999	LEDBulb 10W E27 965 230V 1PF/6 AU	10 W	89 W
929003008119	LEDBulb 12W E27 930 230V 2PF/3 AU	12 W	98 W
929003008199	LEDBulb 12W E27 930 230V 1PF/6 AU	12 W	98 W
929003008519	LEDBulb 12W E27 965 230V 2PF/3 AU	12 W	98 W
929003008599	LEDBulb 12W E27 965 230V 1PF/6 AU	12 W	98 W
929002058619	LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6	8 W	60 W
929003006419	LEDBulb 6W B22 930 230V 2PF/3 AU	6 W	65 W
929003006499	LEDBulb 6W B22 930 230V 1PF/6 AU	6 W	65 W

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
929003006819	LEDBulb 6W B22 965 230V 2PF/3 AU	6 W	65 W
929003006899	LEDBulb 6W B22 965 230V 1PF/6 AU	6 W	65 W
929003007019	LEDBulb 8W B22 930 230V 2PF/3 AU	8 W	76 W
929003007099	LEDBulb 8W B22 930 230V 1PF/6 AU	8 W	76 W
929003007419	LEDBulb 8W B22 965 230V 2PF/3 AU	8 W	76 W
929003007499	LEDBulb 8W B22 965 230V 1PF/6 AU	8 W	76 W
929002442069	LEDGlobe 7W G95 B22 WW 230V_AU	7 W	60 W
929003007619	LEDBulb 10W B22 930 230V 2PF/3 AU	10 W	89 W
929003007699	LEDBulb 10W B22 930 230V 1PF/6 AU	10 W	89 W
929003008019	LEDBulb 10W B22 965 230V 2PF/3 AU	10 W	89 W
929003008099	LEDBulb 10W B22 965 230V 1PF/6 AU	10 W	89 W
929003008219	LEDBulb 12W B22 930 230V 2PF/3 AU	12 W	98 W
929003008299	LEDBulb 12W B22 930 230V 1PF/6 AU	12 W	98 W
929003008619	LEDBulb 12W B22 965 230V 2PF/3 AU	12 W	98 W
929003008699	LEDBulb 12W B22 965 230V 1PF/6 AU	12 W	98 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929003006319	LEDBulb 6W E27 930 230V 2PF/3 AU	85 °C
929003006399	LEDBulb 6W E27 930 230V 1PF/6 AU	85 °C
929003006719	LEDBulb 6W E27 965 230V 2PF/3 AU	85 °C
929003006799	LEDBulb 6W E27 965 230V 1PF/6 AU	85 °C
929003006919	LEDBulb 8W E27 930 230V 2PF/3 AU	95 °C
929003006999	LEDBulb 8W E27 930 230V 1PF/6 AU	95 °C
929003007319	LEDBulb 8W E27 965 230V 2PF/3 AU	95 °C
929003007399	LEDBulb 8W E27 965 230V 1PF/6 AU	95 °C
929002400219	LED Sensor 8W B22 CDL FR 1PF/6 APR	75 °C
929003007519	LEDBulb 10W E27 930 230V 2PF/3 AU	90 °C
929003007599	LEDBulb 10W E27 930 230V 1PF/6 AU	90 °C
929003007919	LEDBulb 10W E27 965 230V 2PF/3 AU	90 °C
929003007999	LEDBulb 10W E27 965 230V 1PF/6 AU	90 °C
929003008119	LEDBulb 12W E27 930 230V 2PF/3 AU	95 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929003008199	LEDBulb 12W E27 930 230V 1PF/6 AU	95 °C
929003008519	LEDBulb 12W E27 965 230V 2PF/3 AU	95 °C
929003008599	LEDBulb 12W E27 965 230V 1PF/6 AU	95 °C
929002058619	LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6	75 °C
929003006419	LEDBulb 6W B22 930 230V 2PF/3 AU	85 °C
929003006499	LEDBulb 6W B22 930 230V 1PF/6 AU	85 °C
929003006819	LEDBulb 6W B22 965 230V 2PF/3 AU	85 °C
929003006899	LEDBulb 6W B22 965 230V 1PF/6 AU	85 °C
929003007019	LEDBulb 8W B22 930 230V 2PF/3 AU	95 °C
929003007099	LEDBulb 8W B22 930 230V 1PF/6 AU	95 °C
929003007419	LEDBulb 8W B22 965 230V 2PF/3 AU	95 °C
929003007499	LEDBulb 8W B22 965 230V 1PF/6 AU	95 °C
929002442069	LEDGlobe 7W G95 B22 WW 230V_AU	45 °C
929003007619	LEDBulb 10W B22 930 230V 2PF/3 AU	90 °C

LED Lamps

Order Code	Full Product Name	T-Case Maximum (Nom)
929003007699	LEDBulb 10W B22 930 230V 1PF/6 AU	90 °C
929003008019	LEDBulb 10W B22 965 230V 2PF/3 AU	90 °C
929003008099	LEDBulb 10W B22 965 230V 1PF/6 AU	90 °C
929003008219	LEDBulb 12W B22 930 230V 2PF/3 AU	95 °C

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
929003006319	LEDBulb 6W E27 930 230V 2PF/3 AU	A60S
929003006399	LEDBulb 6W E27 930 230V 1PF/6 AU	A60S
929003006719	LEDBulb 6W E27 965 230V 2PF/3 AU	A60S
929003006799	LEDBulb 6W E27 965 230V 1PF/6 AU	A60S
929003006919	LEDBulb 8W E27 930 230V 2PF/3 AU	A60S
929003006999	LEDBulb 8W E27 930 230V 1PF/6 AU	A60S
929003007319	LEDBulb 8W E27 965 230V 2PF/3 AU	A60S
929003007399	LEDBulb 8W E27 965 230V 1PF/6 AU	A60S
929002400219	LED Sensor 8W B22 CDL FR 1PF/6 APR	A60
929003007519	LEDBulb 10W E27 930 230V 2PF/3 AU	A60M
929003007599	LEDBulb 10W E27 930 230V 1PF/6 AU	A60M
929003007919	LEDBulb 10W E27 965 230V 2PF/3 AU	A60M
929003007999	LEDBulb 10W E27 965 230V 1PF/6 AU	A60M
929003008119	LEDBulb 12W E27 930 230V 2PF/3 AU	A60M
929003008199	LEDBulb 12W E27 930 230V 1PF/6 AU	A60M
929003008519	LEDBulb 12W E27 965 230V 2PF/3 AU	A60M
929003008599	LEDBulb 12W E27 965 230V 1PF/6 AU	A60M
929002058619	LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6	A60

Approval and Application

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929003006319	LEDBulb 6W E27 930 230V 2PF/3 AU	-20 to +45 °C	-
929003006399	LEDBulb 6W E27 930 230V 1PF/6 AU	-20 to +45 °C	-
929003006719	LEDBulb 6W E27 965 230V 2PF/3 AU	-20 to +45 °C	-
929003006799	LEDBulb 6W E27 965 230V 1PF/6 AU	-20 to +45 °C	-
929003006919	LEDBulb 8W E27 930 230V 2PF/3 AU	-20 to +45 °C	-
929003006999	LEDBulb 8W E27 930 230V 1PF/6 AU	-20 to +45 °C	-
929003007319	LEDBulb 8W E27 965 230V 2PF/3 AU	-20 to +45 °C	-
929003007399	LEDBulb 8W E27 965 230V 1PF/6 AU	-20 to +45 °C	-
929002400219	LED Sensor 8W B22 CDL FR 1PF/6 APR	-20 to +30 °C	8 kWh








Order Code	Full Product Name	T-Case Maximum (Nom)
929003008299	LEDBulb 12W B22 930 230V 1PF/6 AU	95 °C
929003008619	LEDBulb 12W B22 965 230V 2PF/3 AU	95 °C
929003008699	LEDBulb 12W B22 965 230V 1PF/6 AU	95 °C

Order Code	Full Product Name	Bulb Shape
929003006419	LEDBulb 6W B22 930 230V 2PF/3 AU	A60S
929003006499	LEDBulb 6W B22 930 230V 1PF/6 AU	A60S
929003006819	LEDBulb 6W B22 965 230V 2PF/3 AU	A60S
929003006899	LEDBulb 6W B22 965 230V 1PF/6 AU	A60S
929003007019	LEDBulb 8W B22 930 230V 2PF/3 AU	A60S
929003007099	LEDBulb 8W B22 930 230V 1PF/6 AU	A60S
929003007419	LEDBulb 8W B22 965 230V 2PF/3 AU	A60S
929003007499	LEDBulb 8W B22 965 230V 1PF/6 AU	A60S
929002442069	LEDGlobe 7W G95 B22 WW 230V_AU	G95
929003007619	LEDBulb 10W B22 930 230V 2PF/3 AU	A60M
929003007699	LEDBulb 10W B22 930 230V 1PF/6 AU	A60M
929003008019	LEDBulb 10W B22 965 230V 2PF/3 AU	A60M
929003008099	LEDBulb 10W B22 965 230V 1PF/6 AU	A60M
929003008219	LEDBulb 12W B22 930 230V 2PF/3 AU	A60M
929003008299	LEDBulb 12W B22 930 230V 1PF/6 AU	A60M
929003008619	LEDBulb 12W B22 965 230V 2PF/3 AU	A60M
929003008699	LEDBulb 12W B22 965 230V 1PF/6 AU	A60M











Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929003007519	LEDBulb 10W E27 930 230V 2PF/3 AU	-20 to +45 °C	-
929003007599	LEDBulb 10W E27 930 230V 1PF/6 AU	-20 to +45 °C	-
929003007919	LEDBulb 10W E27 965 230V 2PF/3 AU	-20 to +45 °C	-
929003007999	LEDBulb 10W E27 965 230V 1PF/6 AU	-20 to +45 °C	-
929003008119	LEDBulb 12W E27 930 230V 2PF/3 AU	-20 to +45 °C	-
929003008199	LEDBulb 12W E27 930 230V 1PF/6 AU	-20 to +45 °C	-
929003008519	LEDBulb 12W E27 965 230V 2PF/3 AU	-20 to +45 °C	-
929003008599	LEDBulb 12W E27 965 230V 1PF/6 AU	-20 to +45 °C	-
929002058619	LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6	-20 to +30 °C	8 kWh

LED Lamps

Order Code	Full Product Name	Ambient temperature range	Energy	
			Consumption kWh/1000 h	
929003006419	LEDBulb 6W B22 930 230V 2PF/3 AU	-20 to +45 °C	-	
929003006499	LEDBulb 6W B22 930 230V 1PF/6 AU	-20 to +45 °C	-	
929003006819	LEDBulb 6W B22 965 230V 2PF/3 AU	-20 to +45 °C	-	
929003006899	LEDBulb 6W B22 965 230V 1PF/6 AU	-20 to +45 °C	-	
929003007019	LEDBulb 8W B22 930 230V 2PF/3 AU	-20 to +45 °C	-	
929003007099	LEDBulb 8W B22 930 230V 1PF/6 AU	-20 to +45 °C	-	
929003007419	LEDBulb 8W B22 965 230V 2PF/3 AU	-20 to +45 °C	-	
929003007499	LEDBulb 8W B22 965 230V 1PF/6 AU	-20 to +45 °C	-	
929002442069	LEDGlobe 7W G95 B22 WW 230V_AU	-20 to +45 °C	7 kWh	
929003007619	LEDBulb 10W B22 930 230V 2PF/3 AU	-20 to +45 °C	-	
929003007699	LEDBulb 10W B22 930 230V 1PF/6 AU	-20 to +45 °C	-	
929003008019	LEDBulb 10W B22 965 230V 2PF/3 AU	-20 to +45 °C	-	
929003008099	LEDBulb 10W B22 965 230V 1PF/6 AU	-20 to +45 °C	-	
929003008219	LEDBulb 12W B22 930 230V 2PF/3 AU	-20 to +45 °C	-	
929003008299	LEDBulb 12W B22 930 230V 1PF/6 AU	-20 to +45 °C	-	
929003008619	LEDBulb 12W B22 965 230V 2PF/3 AU	-20 to +45 °C	-	
929003008699	LEDBulb 12W B22 965 230V 1PF/6 AU	-20 to +45 °C	-	



LED Lamps



LED Lamps

