


LED Lamps

LEDBULB



LED Lamps – ideal for general lighting applications

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

Benefits

- Color temperature suitable for both functional lighting and to enhance atmosphere
- Up to 80% energy savings compared with incandescent bulbs
- Suitable for retrofit
- Lower maintenance costs

Features

- Long lifetime
- UV- and IR-free light for less heat and protection of heat-sensitive objects
- Instant start

Applications

- Homes, hotels, restaurants, cafes
- Bedroom, dining room, living room, study room

Versions



LEDbulb Entry A60 E27 FR



LED Sensor 8 60W B22 WH FR



LEDGlobe 10 75W G120 B22 WW 230V AU



LEDbulb Entry A60 E27 FR 1



LED Sensor A60 E27 WW POS1



LEDBulb 6W B22 AU



LEDGlobe 7 60W G95 B22 WW 230V AU



LEDGlobe 10 75W G120 E27 WW 230V AU





LEDGlobe 7 60W G95 E27 WW
230V AU




LEDBulb 10W B22 AU

Dimensional drawing




Product	D	C
LEDGlobe 10W G120 B22 WW 230V_AU	120 mm	168 mm


Product	D	C
LEDBulb 10W E27 930 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 10W E27 930 230V 2PF/3 AU	60 mm	110 mm
LEDBulb 10W E27 965 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 10W E27 965 230V 2PF/3 AU	60 mm	110 mm
LEDBulb 12W E27 930 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 12W E27 965 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 12W E27 965 230V 2PF/3 AU	60 mm	110 mm
LEDBulb 6W E27 930 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 6W E27 930 230V 2PF/3 AU	60 mm	110 mm
LEDBulb 6W E27 965 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 6W E27 965 230V 2PF/3 AU	60 mm	110 mm
LEDBulb 8W E27 930 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 8W E27 930 230V 2PF/3 AU	60 mm	110 mm
LEDBulb 8W E27 965 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 8W E27 965 230V 2PF/3 AU	60 mm	110 mm




Product	D	C
LEDGlobe 7W G95 E27 WW 230V_AU	95 mm	137 mm




Product
LEDBulb 10W B22 930 230V 1PF/6 AU
LEDBulb 10W B22 930 230V 2PF/3 AU
LEDBulb 10W B22 965 230V 1PF/6 AU
LEDBulb 10W B22 965 230V 2PF/3 AU
LEDBulb 12W B22 930 230V 1PF/6 AU
LEDBulb 12W B22 965 230V 1PF/6 AU
LEDBulb 12W B22 965 230V 2PF/3 AU
LEDBulb 6W B22 930 230V 1PF/6 AU
LEDBulb 6W B22 965 230V 1PF/6 AU
LEDBulb 6W B22 965 230V 2PF/3 AU
LEDBulb 8W B22 930 230V 1PF/6 AU
LEDBulb 8W B22 930 230V 2PF/3 AU
LEDBulb 8W B22 965 230V 1PF/6 AU
LEDBulb 8W B22 965 230V 2PF/3 AU




Product	D	C
LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6	62.5 mm	122 mm




Product	D	C
LEDGlobe 7W G95 B22 WW 230V_AU	95 mm	135 mm



Product	D	C
LED Sensor 8W B22 CDL FR 1PF/6 APR	62.5 mm	120 mm
LED Sensor 8W B22 WH FR 1PF/6 APR	62.5 mm	120 mm



Product	D	C
LEDGlobe 10W G120 E27 WW 230V_AU	120 mm	170 mm



LED Sensor 8W B22 CDL FR 1PF/6 APR

General Information	
Switching Cycle	50,000
Rated Lifetime (Hours)	15,000 hour(s)
Light Technical	
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted

General Information

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929003006319	LEDBulb 6W E27 930 230V 2PF/3 AU	E27	25,000 hour(s)

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929003006399	LEDBulb 6W E27 930 230V 1PF/6 AU	E27	25,000 hour(s)
929003006719	LEDBulb 6W E27 965 230V 2PF/3 AU	E27	25,000 hour(s)
929003006799	LEDBulb 6W E27 965 230V 1PF/6 AU	E27	25,000 hour(s)
929003006919	LEDBulb 8W E27 930 230V 2PF/3 AU	E27	25,000 hour(s)
929003006999	LEDBulb 8W E27 930 230V 1PF/6 AU	E27	25,000 hour(s)
929003007319	LEDBulb 8W E27 965 230V 2PF/3 AU	E27	25,000 hour(s)
929003007399	LEDBulb 8W E27 965 230V 1PF/6 AU	E27	25,000 hour(s)
929002400119	LED Sensor 8W B22 WH FR 1PF/6 APR	B22	15,000 hour(s)
929002400219	LED Sensor 8W B22 CDL FR 1PF/6 APR	B22	15,000 hour(s)
929002442369	LEDGlobe 10W G120 B22 WW 230V_AU	B22	15,000 hour(s)
929003007519	LEDBulb 10W E27 930 230V 2PF/3 AU	E27	25,000 hour(s)
929003007599	LEDBulb 10W E27 930 230V 1PF/6 AU	E27	25,000 hour(s)
929003007919	LEDBulb 10W E27 965 230V 2PF/3 AU	E27	25,000 hour(s)
929003007999	LEDBulb 10W E27 965 230V 1PF/6 AU	E27	25,000 hour(s)
929003008199	LEDBulb 12W E27 930 230V 1PF/6 AU	E27	25,000 hour(s)
929003008519	LEDBulb 12W E27 965 230V 2PF/3 AU	E27	25,000 hour(s)
929003008599	LEDBulb 12W E27 965 230V 1PF/6 AU	E27	25,000 hour(s)
929002058619	LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6	E27	15,000 hour(s)
929003006499	LEDBulb 6W B22 930 230V 1PF/6 AU	B22	25,000 hour(s)
929003006819	LEDBulb 6W B22 965 230V 2PF/3 AU	B22	25,000 hour(s)
929003006899	LEDBulb 6W B22 965 230V 1PF/6 AU	B22	25,000 hour(s)
929003007019	LEDBulb 8W B22 930 230V 2PF/3 AU	B22	25,000 hour(s)
929003007099	LEDBulb 8W B22 930 230V 1PF/6 AU	B22	25,000 hour(s)
929003007419	LEDBulb 8W B22 965 230V 2PF/3 AU	B22	25,000 hour(s)
929003007499	LEDBulb 8W B22 965 230V 1PF/6 AU	B22	25,000 hour(s)
929002442069	LEDGlobe 7W G95 B22 WW 230V_AU	B22	15,000 hour(s)
929002442169	LEDGlobe 10W G120 E27 WW 230V_AU	E27	15,000 hour(s)
929002441669	LEDGlobe 7W G95 E27 WW 230V_AU	E27	15,000 hour(s)
929003007619	LEDBulb 10W B22 930 230V 2PF/3 AU	B22	25,000 hour(s)
929003007699	LEDBulb 10W B22 930 230V 1PF/6 AU	B22	25,000 hour(s)
929003008019	LEDBulb 10W B22 965 230V 2PF/3 AU	B22	25,000 hour(s)
929003008099	LEDBulb 10W B22 965 230V 1PF/6 AU	B22	25,000 hour(s)
929003008299	LEDBulb 12W B22 930 230V 1PF/6 AU	B22	25,000 hour(s)
929003008619	LEDBulb 12W B22 965 230V 2PF/3 AU	B22	25,000 hour(s)
929003008699	LEDBulb 12W B22 965 230V 1PF/6 AU	B22	25,000 hour(s)

Light Technical

Order Code	Full Product Name	Color Code	Beam Angle (Nom)	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)
929003006319	LEDBulb 6W E27 930 230V 2PF/3 AU	930	200 degree(s)	700 lm	3000 K	90
929003006399	LEDBulb 6W E27 930 230V 1PF/6 AU	930	200 degree(s)	700 lm	3000 K	90
929003006719	LEDBulb 6W E27 965 230V 2PF/3 AU	965	200 degree(s)	700 lm	6500 K	90

Order Code	Full Product Name	Color Code	Beam Angle (Nom)	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)
929003006799	LEDBulb 6W E27 965 230V 1PF/6 AU	965	200 degree(s)	700 lm	6500 K	90
929003006919	LEDBulb 8W E27 930 230V 2PF/3 AU	930	200 degree(s)	910 lm	3000 K	90
929003006999	LEDBulb 8W E27 930 230V 1PF/6 AU	930	200 degree(s)	910 lm	3000 K	90
929003007319	LEDBulb 8W E27 965 230V 2PF/3 AU	965	200 degree(s)	910 lm	6500 K	90
929003007399	LEDBulb 8W E27 965 230V 1PF/6 AU	965	200 degree(s)	910 lm	6500 K	90
929002400119	LED Sensor 8W B22 WH FR 1PF/6 APR	830	280 degree(s)	806 lm	3000 K	80
929002400219	LED Sensor 8W B22 CDL FR 1PF/6 APR	865	280 degree(s)	850 lm	6500 K	80
929002442369	LEDGlobe 10W G120 B22 WW 230V_AU	827	150 degree(s)	1,055 lm	2700 K	80
929003007519	LEDBulb 10W E27 930 230V 2PF/3 AU	930	150 degree(s)	1,150 lm	3000 K	90
929003007599	LEDBulb 10W E27 930 230V 1PF/6 AU	930	150 degree(s)	1,150 lm	3000 K	90
929003007919	LEDBulb 10W E27 965 230V 2PF/3 AU	965	150 degree(s)	1,150 lm	6500 K	90
929003007999	LEDBulb 10W E27 965 230V 1PF/6 AU	965	150 degree(s)	1,150 lm	6500 K	90
929003008199	LEDBulb 12W E27 930 230V 1PF/6 AU	930	150 degree(s)	1,360 lm	3000 K	90
929003008519	LEDBulb 12W E27 965 230V 2PF/3 AU	965	150 degree(s)	1,360 lm	6500 K	90
929003008599	LEDBulb 12W E27 965 230V 1PF/6 AU	965	150 degree(s)	1,360 lm	6500 K	90
929002058619	LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6	865	280 degree(s)	850 lm	6500 K	80
929003006499	LEDBulb 6W B22 930 230V 1PF/6 AU	930	200 degree(s)	700 lm	3000 K	90
929003006819	LEDBulb 6W B22 965 230V 2PF/3 AU	965	200 degree(s)	700 lm	6500 K	90
929003006899	LEDBulb 6W B22 965 230V 1PF/6 AU	965	200 degree(s)	700 lm	6500 K	90
929003007019	LEDBulb 8W B22 930 230V 2PF/3 AU	930	200 degree(s)	910 lm	3000 K	90
929003007099	LEDBulb 8W B22 930 230V 1PF/6 AU	930	200 degree(s)	910 lm	3000 K	90
929003007419	LEDBulb 8W B22 965 230V 2PF/3 AU	965	200 degree(s)	910 lm	6500 K	90
929003007499	LEDBulb 8W B22 965 230V 1PF/6 AU	965	200 degree(s)	910 lm	6500 K	90
929002442069	LEDGlobe 7W G95 B22 WW 230V_AU	827	150 degree(s)	806 lm	2700 K	80
929002442169	LEDGlobe 10W G120 E27 WW 230V_AU	827	150 degree(s)	1,055 lm	2700 K	80
929002441669	LEDGlobe 7W G95 E27 WW 230V_AU	827	150 degree(s)	806 lm	2700 K	80
929003007619	LEDBulb 10W B22 930 230V 2PF/3 AU	930	150 degree(s)	1,150 lm	3000 K	90
929003007699	LEDBulb 10W B22 930 230V 1PF/6 AU	930	150 degree(s)	1,150 lm	3000 K	90
929003008019	LEDBulb 10W B22 965 230V 2PF/3 AU	965	150 degree(s)	1,150 lm	6500 K	90
929003008099	LEDBulb 10W B22 965 230V 1PF/6 AU	965	150 degree(s)	1,150 lm	6500 K	90
929003008299	LEDBulb 12W B22 930 230V 1PF/6 AU	930	150 degree(s)	1,360 lm	3000 K	90
929003008619	LEDBulb 12W B22 965 230V 2PF/3 AU	965	150 degree(s)	1,360 lm	6500 K	90
929003008699	LEDBulb 12W B22 965 230V 1PF/6 AU	965	150 degree(s)	1,360 lm	6500 K	90

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
929003006319	LEDBulb 6W E27 930 230V 2PF/3 AU	6 W	65 W
929003006399	LEDBulb 6W E27 930 230V 1PF/6 AU	6 W	65 W
929003006719	LEDBulb 6W E27 965 230V 2PF/3 AU	6 W	65 W
929003006799	LEDBulb 6W E27 965 230V 1PF/6 AU	6 W	65 W
929003006919	LEDBulb 8W E27 930 230V 2PF/3 AU	8 W	76 W

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
929003006999	LED Bulb 8W E27 930 230V 1PF/6 AU	8 W	76 W
929003007319	LED Bulb 8W E27 965 230V 2PF/3 AU	8 W	76 W
929003007399	LED Bulb 8W E27 965 230V 1PF/6 AU	8 W	76 W
929002400119	LED Sensor 8W B22 WH FR 1PF/6 APR	8 W	60 W
929002400219	LED Sensor 8W B22 CDL FR 1PF/6 APR	8 W	60 W
929002442369	LED Globe 10W G120 B22 WW 230V_AU	10 W	75 W
929003007519	LED Bulb 10W E27 930 230V 2PF/3 AU	10 W	89 W
929003007599	LED Bulb 10W E27 930 230V 1PF/6 AU	10 W	89 W
929003007919	LED Bulb 10W E27 965 230V 2PF/3 AU	10 W	89 W
929003007999	LED Bulb 10W E27 965 230V 1PF/6 AU	10 W	89 W
929003008199	LED Bulb 12W E27 930 230V 1PF/6 AU	12 W	98 W
929003008519	LED Bulb 12W E27 965 230V 2PF/3 AU	12 W	98 W
929003008599	LED Bulb 12W E27 965 230V 1PF/6 AU	12 W	98 W
929002058619	LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6	8 W	60 W
929003006499	LED Bulb 6W B22 930 230V 1PF/6 AU	6 W	65 W
929003006819	LED Bulb 6W B22 965 230V 2PF/3 AU	6 W	65 W
929003006899	LED Bulb 6W B22 965 230V 1PF/6 AU	6 W	65 W
929003007019	LED Bulb 8W B22 930 230V 2PF/3 AU	8 W	76 W
929003007099	LED Bulb 8W B22 930 230V 1PF/6 AU	8 W	76 W
929003007419	LED Bulb 8W B22 965 230V 2PF/3 AU	8 W	76 W
929003007499	LED Bulb 8W B22 965 230V 1PF/6 AU	8 W	76 W
929002442069	LED Globe 7W G95 B22 WW 230V_AU	7 W	60 W
929002442169	LED Globe 10W G120 E27 WW 230V_AU	10 W	75 W
929002441669	LED Globe 7W G95 E27 WW 230V_AU	7 W	60 W
929003007619	LED Bulb 10W B22 930 230V 2PF/3 AU	10 W	89 W
929003007699	LED Bulb 10W B22 930 230V 1PF/6 AU	10 W	89 W
929003008019	LED Bulb 10W B22 965 230V 2PF/3 AU	10 W	89 W
929003008099	LED Bulb 10W B22 965 230V 1PF/6 AU	10 W	89 W
929003008299	LED Bulb 12W B22 930 230V 1PF/6 AU	12 W	98 W
929003008619	LED Bulb 12W B22 965 230V 2PF/3 AU	12 W	98 W
929003008699	LED Bulb 12W B22 965 230V 1PF/6 AU	12 W	98 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929003006319	LED Bulb 6W E27 930 230V 2PF/3 AU	85 °C
929003006399	LED Bulb 6W E27 930 230V 1PF/6 AU	85 °C
929003006719	LED Bulb 6W E27 965 230V 2PF/3 AU	85 °C
929003006799	LED Bulb 6W E27 965 230V 1PF/6 AU	85 °C
929003006919	LED Bulb 8W E27 930 230V 2PF/3 AU	95 °C
929003006999	LED Bulb 8W E27 930 230V 1PF/6 AU	95 °C
929003007319	LED Bulb 8W E27 965 230V 2PF/3 AU	95 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929003007399	LEDBulb 8W E27 965 230V 1PF/6 AU	95 °C
929002400119	LED Sensor 8W B22 WH FR 1PF/6 APR	75 °C
929002400219	LED Sensor 8W B22 CDL FR 1PF/6 APR	75 °C
929002442369	LEDGlobe 10W G120 B22 WW 230V_AU	50 °C
929003007519	LEDBulb 10W E27 930 230V 2PF/3 AU	90 °C
929003007599	LEDBulb 10W E27 930 230V 1PF/6 AU	90 °C
929003007919	LEDBulb 10W E27 965 230V 2PF/3 AU	90 °C
929003007999	LEDBulb 10W E27 965 230V 1PF/6 AU	90 °C
929003008199	LEDBulb 12W E27 930 230V 1PF/6 AU	95 °C
929003008519	LEDBulb 12W E27 965 230V 2PF/3 AU	95 °C
929003008599	LEDBulb 12W E27 965 230V 1PF/6 AU	95 °C
929002058619	LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6	75 °C
929003006499	LEDBulb 6W B22 930 230V 1PF/6 AU	85 °C
929003006819	LEDBulb 6W B22 965 230V 2PF/3 AU	85 °C
929003006899	LEDBulb 6W B22 965 230V 1PF/6 AU	85 °C
929003007019	LEDBulb 8W B22 930 230V 2PF/3 AU	95 °C
929003007099	LEDBulb 8W B22 930 230V 1PF/6 AU	95 °C
929003007419	LEDBulb 8W B22 965 230V 2PF/3 AU	95 °C
929003007499	LEDBulb 8W B22 965 230V 1PF/6 AU	95 °C
929002442069	LEDGlobe 7W G95 B22 WW 230V_AU	45 °C
929002442169	LEDGlobe 10W G120 E27 WW 230V_AU	50 °C
929002441669	LEDGlobe 7W G95 E27 WW 230V_AU	45 °C
929003007619	LEDBulb 10W B22 930 230V 2PF/3 AU	90 °C
929003007699	LEDBulb 10W B22 930 230V 1PF/6 AU	90 °C
929003008019	LEDBulb 10W B22 965 230V 2PF/3 AU	90 °C
929003008099	LEDBulb 10W B22 965 230V 1PF/6 AU	90 °C
929003008299	LEDBulb 12W B22 930 230V 1PF/6 AU	95 °C
929003008619	LEDBulb 12W B22 965 230V 2PF/3 AU	95 °C
929003008699	LEDBulb 12W B22 965 230V 1PF/6 AU	95 °C

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
929003006319	LEDBulb 6W E27 930 230V 2PF/3 AU	A60S
929003006399	LEDBulb 6W E27 930 230V 1PF/6 AU	A60S
929003006719	LEDBulb 6W E27 965 230V 2PF/3 AU	A60S
929003006799	LEDBulb 6W E27 965 230V 1PF/6 AU	A60S
929003006919	LEDBulb 8W E27 930 230V 2PF/3 AU	A60S
929003006999	LEDBulb 8W E27 930 230V 1PF/6 AU	A60S
929003007319	LEDBulb 8W E27 965 230V 2PF/3 AU	A60S
929003007399	LEDBulb 8W E27 965 230V 1PF/6 AU	A60S
929002400119	LED Sensor 8W B22 WH FR 1PF/6 APR	A60

Order Code	Full Product Name	Bulb Shape
929002400219	LED Sensor 8W B22 CDL FR 1PF/6 APR	A60
929002442369	LEDGlobe 10W G120 B22 WW 230V_AU	G120
929003007519	LEDBulb 10W E27 930 230V 2PF/3 AU	A60M
929003007599	LEDBulb 10W E27 930 230V 1PF/6 AU	A60M
929003007919	LEDBulb 10W E27 965 230V 2PF/3 AU	A60M
929003007999	LEDBulb 10W E27 965 230V 1PF/6 AU	A60M
929003008199	LEDBulb 12W E27 930 230V 1PF/6 AU	A60M
929003008519	LEDBulb 12W E27 965 230V 2PF/3 AU	A60M
929003008599	LEDBulb 12W E27 965 230V 1PF/6 AU	A60M
929002058619	LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6	A60
929003006499	LEDBulb 6W B22 930 230V 1PF/6 AU	A60S
929003006819	LEDBulb 6W B22 965 230V 2PF/3 AU	A60S
929003006899	LEDBulb 6W B22 965 230V 1PF/6 AU	A60S
929003007019	LEDBulb 8W B22 930 230V 2PF/3 AU	A60S
929003007099	LEDBulb 8W B22 930 230V 1PF/6 AU	A60S
929003007419	LEDBulb 8W B22 965 230V 2PF/3 AU	A60S
929003007499	LEDBulb 8W B22 965 230V 1PF/6 AU	A60S
929002442069	LEDGlobe 7W G95 B22 WW 230V_AU	G95
929002442169	LEDGlobe 10W G120 E27 WW 230V_AU	G120
929002441669	LEDGlobe 7W G95 E27 WW 230V_AU	G95
929003007619	LEDBulb 10W B22 930 230V 2PF/3 AU	A60M
929003007699	LEDBulb 10W B22 930 230V 1PF/6 AU	A60M
929003008019	LEDBulb 10W B22 965 230V 2PF/3 AU	A60M
929003008099	LEDBulb 10W B22 965 230V 1PF/6 AU	A60M
929003008299	LEDBulb 12W B22 930 230V 1PF/6 AU	A60M
929003008619	LEDBulb 12W B22 965 230V 2PF/3 AU	A60M
929003008699	LEDBulb 12W B22 965 230V 1PF/6 AU	A60M

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Ambient temperature range
929003006319	LEDBulb 6W E27 930 230V 2PF/3 AU	-	-20 to +45 °C
929003006399	LEDBulb 6W E27 930 230V 1PF/6 AU	-	-20 to +45 °C
929003006719	LEDBulb 6W E27 965 230V 2PF/3 AU	-	-20 to +45 °C
929003006799	LEDBulb 6W E27 965 230V 1PF/6 AU	-	-20 to +45 °C
929003006919	LEDBulb 8W E27 930 230V 2PF/3 AU	-	-20 to +45 °C
929003006999	LEDBulb 8W E27 930 230V 1PF/6 AU	-	-20 to +45 °C
929003007319	LEDBulb 8W E27 965 230V 2PF/3 AU	-	-20 to +45 °C
929003007399	LEDBulb 8W E27 965 230V 1PF/6 AU	-	-20 to +45 °C
929002400119	LED Sensor 8W B22 WH FR 1PF/6 APR	8 kWh	-20 to +30 °C
929002400219	LED Sensor 8W B22 CDL FR 1PF/6 APR	8 kWh	-20 to +30 °C
929002442369	LEDGlobe 10W G120 B22 WW 230V_AU	10 kWh	-20 to +45 °C

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Ambient temperature range
929003007519	LEDBulb 10W E27 930 230V 2PF/3 AU	-	-20 to +45 °C
929003007599	LEDBulb 10W E27 930 230V 1PF/6 AU	-	-20 to +45 °C
929003007919	LEDBulb 10W E27 965 230V 2PF/3 AU	-	-20 to +45 °C
929003007999	LEDBulb 10W E27 965 230V 1PF/6 AU	-	-20 to +45 °C
929003008199	LEDBulb 12W E27 930 230V 1PF/6 AU	-	-20 to +45 °C
929003008519	LEDBulb 12W E27 965 230V 2PF/3 AU	-	-20 to +45 °C
929003008599	LEDBulb 12W E27 965 230V 1PF/6 AU	-	-20 to +45 °C
929002058619	LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6	8 kWh	-20 to +30 °C
929003006499	LEDBulb 6W B22 930 230V 1PF/6 AU	-	-20 to +45 °C
929003006819	LEDBulb 6W B22 965 230V 2PF/3 AU	-	-20 to +45 °C
929003006899	LEDBulb 6W B22 965 230V 1PF/6 AU	-	-20 to +45 °C
929003007019	LEDBulb 8W B22 930 230V 2PF/3 AU	-	-20 to +45 °C
929003007099	LEDBulb 8W B22 930 230V 1PF/6 AU	-	-20 to +45 °C
929003007419	LEDBulb 8W B22 965 230V 2PF/3 AU	-	-20 to +45 °C
929003007499	LEDBulb 8W B22 965 230V 1PF/6 AU	-	-20 to +45 °C
929002442069	LEDGlobe 7W G95 B22 WW 230V_AU	7 kWh	-20 to +45 °C
929002442169	LEDGlobe 10W G120 E27 WW 230V_AU	10 kWh	-20 to +45 °C
929002441669	LEDGlobe 7W G95 E27 WW 230V_AU	7 kWh	-20 to +45 °C
929003007619	LEDBulb 10W B22 930 230V 2PF/3 AU	-	-20 to +45 °C
929003007699	LEDBulb 10W B22 930 230V 1PF/6 AU	-	-20 to +45 °C
929003008019	LEDBulb 10W B22 965 230V 2PF/3 AU	-	-20 to +45 °C
929003008099	LEDBulb 10W B22 965 230V 1PF/6 AU	-	-20 to +45 °C
929003008299	LEDBulb 12W B22 930 230V 1PF/6 AU	-	-20 to +45 °C
929003008619	LEDBulb 12W B22 965 230V 2PF/3 AU	-	-20 to +45 °C
929003008699	LEDBulb 12W B22 965 230V 1PF/6 AU	-	-20 to +45 °C