

Classic LEDbulbs lamps for decorative lighting

Classic filament LED bulbs

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Benefits

- Around 90% energy saving
- Very long lifetime that reduces the need for replacement
- Easy replacement of classic conventional lamps

Features

- Heritage design with classic shape
- Designed to be seen, they look good on and off
- Perfect fit and high quality finishing
- High color rendering (CRI> 80) for vivid colors
- Environmentally friendly: contains no mercury or other hazardous substances

Application

- Perfect for decorative installations
- Domestic applications
- Hospitality: restaurants and hotels

Classic filament LED bulbs


Versions



LEDclassic G93 G95 E27 POS2



CLA LEDbulb 60W E27 827 CL G93



LEDbulb classic-giant 40W E27
G200 GOLD DIM



LEDbulb classic-giant 40W E27
T65 GOLD DIM



LEDclassic ST64 E27 smoky POS2







LEDbulb classic-giant 40W E27
A160 GOLD DIM



LEDclassic giant 28W E27 A160
GOLD ND

Classic filament LED bulbs

Dimensional drawing



Product	D	C
LED classic 60W G93 E27 WW CL ND RF 1PF4	95 mm	140 mm





Product	D	C
LED classic-giant 28W E27 A160 GOLD ND	162 mm	293 mm
LED classic-giant 40W E27 A160 GOLD DIM	162 mm	293 mm

Product	D	C
LED classic-giant 40W E27 G200 GOLD DIM	202 mm	286 mm

Product	D	C
LED classic 120W A67 E27 CDL FR ND 1SRT4	70 mm	121 mm
LED classic 120W A67 E27 CW FR NDRF1SRT4	70 mm	121 mm
LED classic 120W A67 E27 WW FR NDRFSRT4	70 mm	121 mm
LED classic 150W A67 E27 CDL FR ND 1SRT4	70 mm	121 mm
LED classic 150W A67 E27 CW FR ND 1SRT4	70 mm	121 mm
LED classic 150W A67 E27 WW FR NDRFSRT4	70 mm	121 mm

Classic filament LED bulbs

Dimensional drawing



Product	D	C
LED classic-giant 40W E27 T65 GOLD DIM	66 mm	273 mm



Product	D	C
LED classic 60W G95 E27 WW FR ND RFSRT4	95 mm	140 mm

Product	D	C
LED classic 100W A60 CW FR ND 1CT/10	60 mm	104 mm
LED classic 100W A60 WW FR ND 1CT/10	60 mm	104 mm
LED classic 75W E27 CW A60 FR ND 1CT/10	60 mm	104 mm
LED classic 75W E27 WW A60 FR ND 1CT10	60 mm	104 mm

Product	D	C
LED classic 200W A95 E27 CDL FR ND 1PF/4	95 mm	165 mm
LED classic 200W A95 E27 CW FR ND 1PF/4	95 mm	165 mm
LED classic 200W A95 E27 WW FR ND 1PF	95 mm	165 mm

Classic filament LED bulbs

Dimensional drawing



Product	D	C
LED cla 120W G120 E27 WW FR ND RFSRT4	124 mm	177 mm
LED classic 75W G120 E27 WW FR ND SRT4	125 mm	177 mm

Product	D	C
LEDclassic 11W ST64 E27 smoky ND RFSRT4	64 mm	143 mm

General Information

Cap-Base	E27
Rated Lifetime (Hours)	15,000 hour(s)
Switching Cycle	20,000
Nominal lifetime	15,000 hour(s)

Light Technical

Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical

Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color			Luminous Flux
			Temperature (Nom)	Color Code		
76451700	LED classic 120W A67 E27 WW FR ND RFSRT4	300 degree(s)	2700 K	827	2,000 lm	
76453100	LED classic 120W A67 E27 CW FR ND RFSRT4	300 degree(s)	4000 K	840	2,000 lm	
76455500	LED classic 120W A67 E27 CDL FR ND 1SRT4	300 degree(s)	6500 K	865	2,000 lm	
76457900	LED classic 150W A67 E27 WW FR ND RFSRT4	300 degree(s)	2700 K	827	2,452 lm	
76459300	LED classic 150W A67 E27 CW FR ND 1SRT4	300 degree(s)	4000 K	840	2,452 lm	
76461600	LED classic 150W A67 E27 CDL FR ND 1SRT4	300 degree(s)	6500 K	865	2,452 lm	
76469200	LED classic 60W G95 E27 WW FR ND RFSRT4	-	2700 K	827	806 lm	
74245700	LED classic 60W G95 E27 WW CL ND 1PF	300 degree(s)	2700 K	827	806 lm	
70416200	LED classic 100W A60 WW FR ND 1CT/10	-	2700 K	827	1,521 lm	
70414800	LED classic 100W A60 CW FR ND 1CT/10	-	4000 K	840	1,521 lm	
31378100	LED classic-giant 40W E27 G200 GOLD DIM	330 degree(s)	1800 K	818	470 lm	

Classic filament LED bulbs

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color		
			Temperature (Nom)	Color Code	Luminous Flux
76463000	LED classic 200W A95 E27 WW FR ND 1PF	300 degree(s)	2700 K	827	3,452 lm
76465400	LED classic 200W A95 E27 CW FR ND 1PF/4	300 degree(s)	4000 K	840	3,452 lm
76467800	LED classic 200W A95 E27 CDL FR ND 1PF/4	300 degree(s)	6500 K	865	3,452 lm
76475300	LED classic 75W G120 E27 WW FR ND SRT4	-	2700 K	827	1,055 lm
76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	300 degree(s)	2700 K	827	2,000 lm
31380400	LED classic-giant 40W E27 T65 GOLD DIM	330 degree(s)	1800 K	818	470 lm
75965000	LEDclassic 11W ST64 E27 smoky ND RFSRT4	-	1800 K	818	100 lm
31376700	LED classic-giant 40W E27 A160 GOLD DIM	330 degree(s)	1800 K	818	470 lm
70555100	LED classic 75W E27 WW A60 FR ND 1CT10	300 degree(s)	2700 K	827	1,055 lm
70561200	LED classic 75W E27 CW A60 FR ND 1CT/10	-	4000 K	840	1,055 lm
31382800	LED classic-giant 28W E27 A160 GOLD ND	330 degree(s)	1800 K	818	300 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Wattage Equivalent	Order Code	Full Product Name	Power Consumption	Wattage Equivalent
76451700	LED classic 120W A67 E27 WW FR NDRFSRT4	13 W	120 W	76463000	LED classic 200W A95 E27 WW FR ND 1PF	23 W	200 W
76453100	LED classic 120W A67 E27 CW FR NDRFISRT4	13 W	120 W	76465400	LED classic 200W A95 E27 CW FR ND 1PF/4	23 W	200 W
76455500	LED classic 120W A67 E27 CDL FR ND 1SRT4	13 W	120 W	76467800	LED classic 200W A95 E27 CDL FR ND 1PF/4	23 W	200 W
76457900	LED classic 150W A67 E27 WW FR NDRFSRT4	17.5 W	150 W	76475300	LED classic 75W G120 E27 WW FR ND SRT4	8.5 W	75 W
76459300	LED classic 150W A67 E27 CW FR ND 1SRT4	17.5 W	150 W	76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	13 W	120 W
76461600	LED classic 150W A67 E27 CDL FR ND 1SRT4	17.5 W	150 W	31380400	LED classic-giant 40W E27 T65 GOLD DIM	7 W	40 W
76469200	LED classic 60W G95 E27 WW FR ND RFSRT4	7 W	60 W	75965000	LEDclassic 11W ST64 E27 smoky ND RFSRT4	2.3 W	11 W
74245700	LED classic 60W G95 E27 WW CL ND 1PF	7 W	60 W	31376700	LED classic-giant 40W E27 A160 GOLD DIM	7 W	40 W
70416200	LED classic 100W A60 WW FR ND 1CT/10	10.5 W	100 W	70555100	LED classic 75W E27 WW A60 FR ND 1CT10	8.5 W	75 W
70414800	LED classic 100W A60 CW FR ND 1CT/10	10.5 W	100 W	70561200	LED classic 75W E27 CW A60 FR ND 1CT/10	8.5 W	75 W
31378100	LED classic-giant 40W E27 G200 GOLD DIM	7 W	40 W	31382800	LED classic-giant 28W E27 A160 GOLD ND	4.5 W	28 W

Classic filament LED bulbs

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
76451700	LED classic 120W A67 E27 WW FR NDRFSRT4	60 °C
76453100	LED classic 120W A67 E27 CW FR NDRFISRT4	60 °C
76455500	LED classic 120W A67 E27 CDL FR ND 1SRT4	60 °C
76457900	LED classic 150W A67 E27 WW FR NDRFSRT4	60 °C
76459300	LED classic 150W A67 E27 CW FR ND 1SRT4	60 °C
76461600	LED classic 150W A67 E27 CDL FR ND 1SRT4	60 °C
76469200	LED classic 60W G95 E27 WW FR ND RFSRT4	45 °C
74245700	LED classic 60W G95 E27 WW CL ND 1PF	45 °C
70416200	LED classic 100W A60 WW FR ND 1CT/10	55 °C
70414800	LED classic 100W A60 CW FR ND 1CT/10	55 °C
31378100	LED classic-giant 40W E27 G200 GOLD DIM	45 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
76463000	LED classic 200W A95 E27 WW FR ND 1PF	55 °C
76465400	LED classic 200W A95 E27 CW FR ND 1PF/4	55 °C
76467800	LED classic 200W A95 E27 CDL FR ND 1PF/4	55 °C
76475300	LED classic 75W G120 E27 WW FR ND SRT4	50 °C
76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	55 °C
31380400	LED classic-giant 40W E27 T65 GOLD DIM	45 °C
75965000	LEDclassic 11W ST64 E27 smoky ND RFSRT4	40 °C
31376700	LED classic-giant 40W E27 A160 GOLD DIM	45 °C
70555100	LED classic 75W E27 WW A60 FR ND 1CT10	50 °C
70561200	LED classic 75W E27 CW A60 FR ND 1CT/10	50 °C
31382800	LED classic-giant 28W E27 A160 GOLD ND	45 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
76451700	LED classic 120W A67 E27 WW FR NDRFSRT4	No
76453100	LED classic 120W A67 E27 CW FR NDRFISRT4	No
76455500	LED classic 120W A67 E27 CDL FR ND 1SRT4	No
76457900	LED classic 150W A67 E27 WW FR NDRFSRT4	No
76459300	LED classic 150W A67 E27 CW FR ND 1SRT4	No
76461600	LED classic 150W A67 E27 CDL FR ND 1SRT4	No
76469200	LED classic 60W G95 E27 WW FR ND RFSRT4	No
74245700	LED classic 60W G95 E27 WW CL ND 1PF	No
70416200	LED classic 100W A60 WW FR ND 1CT/10	No
70414800	LED classic 100W A60 CW FR ND 1CT/10	No
31378100	LED classic-giant 40W E27 G200 GOLD DIM	Only with specific dimmers

Order Code	Full Product Name	Dimmable
76463000	LED classic 200W A95 E27 WW FR ND 1PF	No
76465400	LED classic 200W A95 E27 CW FR ND 1PF/4	No
76467800	LED classic 200W A95 E27 CDL FR ND 1PF/4	No
76475300	LED classic 75W G120 E27 WW FR ND SRT4	No
76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	No
31380400	LED classic-giant 40W E27 T65 GOLD DIM	Only with specific dimmers
75965000	LEDclassic 11W ST64 E27 smoky ND RFSRT4	No
31376700	LED classic-giant 40W E27 A160 GOLD DIM	Only with specific dimmers
70555100	LED classic 75W E27 WW A60 FR ND 1CT10	No
70561200	LED classic 75W E27 CW A60 FR ND 1CT/10	No
31382800	LED classic-giant 28W E27 A160 GOLD ND	No

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
76451700	LED classic 120W A67 E27 WW FR NDRFSRT4	Frosted	A67
76453100	LED classic 120W A67 E27 CW FR NDRFISRT4	Frosted	A67
76455500	LED classic 120W A67 E27 CDL FR ND 1SRT4	Frosted	A67
76457900	LED classic 150W A67 E27 WW FR NDRFSRT4	Frosted	A67
76459300	LED classic 150W A67 E27 CW FR ND 1SRT4	Frosted	A67
76461600	LED classic 150W A67 E27 CDL FR ND 1SRT4	Frosted	A67
76469200	LED classic 60W G95 E27 WW FR ND RFSRT4	Frosted	G95
74245700	LED classic 60W G95 E27 WW CL ND 1PF	Clear	G95
70416200	LED classic 100W A60 WW FR ND 1CT/10	Frosted	A60
70414800	LED classic 100W A60 CW FR ND 1CT/10	Frosted	A60
31378100	LED classic-giant 40W E27 G200 GOLD DIM	Amber	G200

Order Code	Full Product Name	Bulb Finish	Bulb Shape
76463000	LED classic 200W A95 E27 WW FR ND 1PF	Frosted	A95
76465400	LED classic 200W A95 E27 CW FR ND 1PF/4	Frosted	A95
76467800	LED classic 200W A95 E27 CDL FR ND 1PF/4	Frosted	A95
76475300	LED classic 75W G120 E27 WW FR ND SRT4	Frosted	G120
76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	Frosted	G120
31380400	LED classic-giant 40W E27 T65 GOLD DIM	Amber	T65
75965000	LEDclassic 11W ST64 E27 smoky ND RFSRT4	Smoky	ST64
31376700	LED classic-giant 40W E27 A160 GOLD DIM	Amber	A160
70555100	LED classic 75W E27 WW A60 FR ND 1CT10	Frosted	A60
70561200	LED classic 75W E27 CW A60 FR ND 1CT/10	Frosted	A60
31382800	LED classic-giant 28W E27 A160 GOLD ND	Amber	A160



Approval and Application

Order Code	Full Product Name	Energy	
		Ambient temperature range	Consumption kWh/1000 h
76451700	LED classic 120W A67 E27 WW FR NDRFSRT4	-20 to +45 °C	13 kWh

Order Code	Full Product Name	Energy	
		Ambient temperature range	Consumption kWh/1000 h
76453100	LED classic 120W A67 E27 CW FR NDRFISRT4	-20 to +45 °C	13 kWh


Classic filament LED bulbs

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
76455500	LED classic 120W A67 E27 CDL FR ND 1SRT4	-20 to +45 °C	13 kWh
76457900	LED classic 150W A67 E27 WW FR NDRFSRT4	-20 to +45 °C	18 kWh
76459300	LED classic 150W A67 E27 CW FR ND 1SRT4	-20 to +45 °C	18 kWh
76461600	LED classic 150W A67 E27 CDL FR ND 1SRT4	-20 to +45 °C	18 kWh
76469200	LED classic 60W G95 E27 WW FR ND RFSRT4	-20 to +45 °C	7 kWh
74245700	LED classic 60W G95 E27 WW CL ND 1PF	-20 to +45 °C	7 kWh
70416200	LED classic 100W A60 WW FR ND 1CT/10	-20 to +45 °C	11 kWh
70414800	LED classic 100W A60 CW FR ND 1CT/10	-20 to +45 °C	11 kWh
31378100	LED classic-giant 40W E27 G200 GOLD DIM	-20 to +45 °C	7 kWh
76463000	LED classic 200W A95 E27 WW FR ND 1PF	-20 to +45 °C	23 kWh
76465400	LED classic 200W A95 E27 CW FR ND 1PF/4	-20 to +45 °C	23 kWh
76467800	LED classic 200W A95 E27 CDL FR ND 1PF/4	-20 to +45 °C	23 kWh
76475300	LED classic 75W G120 E27 WW FR ND SRT4	-20 to +45 °C	9 kWh
76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	-20 to +45 °C	13 kWh
31380400	LED classic-giant 40W E27 T65 GOLD DIM	-20 to +45 °C	7 kWh
75965000	LEDclassic 11W ST64 E27 smoky ND RFSRT4	-20 to +40 °C	3 kWh
31376700	LED classic-giant 40W E27 A160 GOLD DIM	-20 to +45 °C	7 kWh
70555100	LED classic 75W E27 WW A60 FR ND 1CT10	-20 to +45 °C	9 kWh
70561200	LED classic 75W E27 CW A60 FR ND 1CT/10	-20 to +45 °C	9 kWh
31382800	LED classic-giant 28W E27 A160 GOLD ND	-20 to +45 °C	5 kWh




Classic filament LED bulbs

Classic filament LED bulbs



Classic filament LED bulbs



Classic filament LED bulbs

