



# Lampade Classic LEDbulbs per illuminazioni decorative

## Lampadine LED a filamento classico

Con un design ispirato allo stile classico, le lampade Classic LEDbulbs con filamento combinano le forme familiari delle classiche lampadine a incandescenza ai vantaggi in termini di durata della tecnologia LED. Producono una piacevole luce bianca calda decorativa consentendo un risparmio di circa il 90% sui costi energetici rispetto alle lampadine tradizionali.

### Vantaggi

- Circa il 90% di risparmio energetico
- Durata molto lunga che riduce l'esigenza di sostituzione
- Sostituzione semplice delle lampade tradizionali classiche

### Caratteristiche

- Design tradizionale con forma classica
- Progettate per la visibilità, sia accese che spente
- Idoneità perfetta e finiture di alta qualità
- Elevata resa cromatica (CRI > 80) per colori naturali
- Rispetto dell'ambiente: non contiene mercurio o altre sostanze nocive

### Applicazione

- Perfette per le installazioni decorative
- Applicazioni domestiche
- Hotel, ristoranti e bar




# Lampadine LED a filamento classico

## Versions



LEDclassic G93 G95 E27 POS2

## Disegno tecnico



Product	D	C
LED classic 60W G95 E27 CW FR ND 1PF/4	95 mm	140 mm
LED classic 60W G95 E27 WW FR ND RFSRT4	95 mm	140 mm

Product	D	C
Classic LED 100 W E27 WW G120 FR ND SRT4	125 mm	177 mm
LED classic 100W E27 CW G120 FR ND 1PF/6	125 mm	177 mm

Product	D	C
LED cla 120W G120 E27 WW FR ND RFSRT4	124 mm	177 mm
LED classic 120W G120 E27 CDL FRND 1PF/4	124 mm	177 mm
LED classic 120W G120 E27 CW FR ND 1PF/4	124 mm	177 mm
LED classic 75W G120 E27 WW FR ND SRT4	125 mm	177 mm

# Lampadine LED a filamento classico

## Informazioni generali

Attacco	E27
Durata specificata (ore)	15.000 ore
Ciclo di commutazione on/off	20.000
Durata nominale	15.000 ore

## Dati tecnici di illuminazione

Indice di resa cromatica (CRI)	80
LLMF a fine durata vita nominale (Nom)	70 %

## Funzionamento e parte elettrica

Frequenza di ingresso	Da 50 a 60 Hz
Frequenza di linea	50 to 60 Hz
Tempo di avvio (Nom)	0,5 s

## Controlli e dimmerazione

Dimmerabile	No
-------------	----

## Meccanica e corpo

Finitura lampadina	Smerigliata
--------------------	-------------

## Approvazione e applicazione

Intervallo temperatura ambiente	Da -20 a +45 °C
---------------------------------	-----------------

## Dati tecnici di illuminazione

Order Code	Full Product Name	Angolo del fascio (Nom)	Temperatura di colore correlata (Nom)	Codice colore	Flusso luminoso
76469200	LED classic 60W G95 E27 WW FR ND RFSRT4	-	2700 K	827	806 lm
76471500	LED classic 60W G95 E27 CW FR ND 1PF/4	-	4000 K	840	806 lm
66514200	LED classic 100W E27 WW G120 FRNDRFSRT4	-	2700 K	827	1.521 lm
66516600	LED classic 100W E27 CW G120 FR ND 1PF/6	-	4000 K	840	1.521 lm
76475300	LED classic 75W G120 E27 WW FR ND SRT4	-	2700 K	827	1.055 lm
76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	300 °	2700 K	827	2.000 lm
76483800	LED classic 120W G120 E27 CW FR ND 1PF/4	300 °	4000 K	840	2.000 lm
76497500	LED classic 120W G120 E27 CDL FRND 1PF/4	300 °	6500 K	865	2.000 lm

## Funzionamento e parte elettrica

Order Code	Full Product Name	Consumo energetico	Potenza equivalente
76469200	LED classic 60W G95 E27 WW FR ND RFSRT4	7 W	60 W
76471500	LED classic 60W G95 E27 CW FR ND 1PF/4	7 W	60 W
66514200	LED classic 100W E27 WW G120 FRNDRFSRT4	10,5 W	100 W
66516600	LED classic 100W E27 CW G120 FR ND 1PF/6	10,5 W	100 W

Order Code	Full Product Name	Consumo energetico	Potenza equivalente
76475300	LED classic 75W G120 E27 WW FR ND SRT4	8,5 W	75 W
76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	13 W	120 W
76483800	LED classic 120W G120 E27 CW FR ND 1PF/4	13 W	120 W
76497500	LED classic 120W G120 E27 CDL FRND 1PF/4	13 W	120 W

## Temperatura

Order Code	Full Product Name	Temp. massima involucro (Nom)
76469200	LED classic 60W G95 E27 WW FR ND RFSRT4	45 °C
76471500	LED classic 60W G95 E27 CW FR ND 1PF/4	45 °C
66514200	LED classic 100W E27 WW G120 FRNDRFSRT4	50 °C
66516600	LED classic 100W E27 CW G120 FR ND 1PF/6	50 °C

Order Code	Full Product Name	Temp. massima involucro (Nom)
76475300	LED classic 75W G120 E27 WW FR ND SRT4	50 °C
76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	55 °C
76483800	LED classic 120W G120 E27 CW FR ND 1PF/4	55 °C
76497500	LED classic 120W G120 E27 CDL FRND 1PF/4	55 °C

## Meccanica e corpo

Order Code	Full Product Name	Forma lampadina
76469200	LED classic 60W G95 E27 WW FR ND RFSRT4	G95
76471500	LED classic 60W G95 E27 CW FR ND 1PF/4	G95

Order Code	Full Product Name	Forma lampadina
66514200	LED classic 100W E27 WW G120 FRNDRFSRT4	G120
66516600	LED classic 100W E27 CW G120 FR ND 1PF/6	G120

## Lampadine LED a filamento classico

Order Code	Full Product Name	Forma lampadina
76475300	LED classic 75W G120 E27 WW FR ND SRT4	G120
76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	G120

Order Code	Full Product Name	Forma lampadina
76483800	LED classic 120W G120 E27 CW FR ND 1PF/4	G120
76497500	LED classic 120W G120 E27 CDL FRND 1PF/4	G120

### Approvazione e applicazione

Order Code	Full Product Name	Consumo energetico kWh/ 1000 h
76469200	LED classic 60W G95 E27 WW FR ND RFSRT4	7 kWh
76471500	LED classic 60W G95 E27 CW FR ND 1PF/4	7 kWh
66514200	LED classic 100W E27 WW G120 FRNDRFSRT4	11 kWh
66516600	LED classic 100W E27 CW G120 FR ND 1PF/6	11 kWh
76475300	LED classic 75W G120 E27 WW FR ND SRT4	9 kWh
76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	13 kWh
76483800	LED classic 120W G120 E27 CW FR ND 1PF/4	13 kWh
76497500	LED classic 120W G120 E27 CDL FRND 1PF/4	13 kWh

