



Classic LEDbulbs- ljuskällor för dekorativ belysning

Classic filament LEDbulbs

Classic filament LEDbulbs har en klassisk kulturdesign och kombinerar de välkända formerna hos klassiska glödlampor med fördelarna hos LED-tekniken med lång livslängd. De ger ett vackert och dekorativt varmt ljus och bidrar till energibesparingar på 90 % jämfört med traditionella glödlampor.

Fördelar

- Energibesparing på runt 90 %
- Mycket lång livslängd som minskar behovet av lampbyten
- Enkel ersättning av konventionella ljuskällor

Funktioner

- Klassisk design och formgivning
- Designad för att synas - lika vacker tänd som släckt
- Perfekt passform och ytbehandling av hög kvalitet
- God färgåtergivning (CRI > 80) för klara färger
- Miljövänlig: fri från kvicksilver och andra skadliga ämnen

Användning

- Perfekt för dekorativ belysning
- Kan användas i hemmet
- Hotell- och restaurangbranschen

Classic filament LEDbulbs

Versions



LEDclassic G93 G95 E27 POS2



LED classic E27 G120



LEDbulb classic-giant 40W E27
G200 GOLD DIM



LEDclassic A95 E27 FR-POS2A



LEDclassic G120 E27 FR POS2



25W E27 G200



LEDbulb classic-giant 40W E27
T65 GOLD DIM



LEDclassic CM A60 E27 CL POS2

Classic filament LEDbulbs

Versions



LEDbulb classic-giant 40W E27
A160 GOLD DIM



LED classic 60W E27 WW G120 FR
ND SRT4-SPP





LEDclassic giant 28W E27 A160
GOLD ND



25W E27 A160

Måttskiss







Product	D	C
LED classic CM 50W A60 E27 WW CL D SRT4	60 mm	106 mm

Product	D	C
LED classic-giant 28W E27 A160 GOLD ND	162 mm	293 mm
LED classic-giant 40W E27 A160 GOLD DIM	162 mm	293 mm
LED giant 20W E27 A160 1800K smoky D	162 mm	293 mm

Classic filament LEDbulbs

Måttskiss



Product	D	C
LED classic-giant 40W E27 G200 GOLD DIM	202 mm	286 mm
LED giant 20W E27 G200 1800K smoky D	202 mm	286 mm




Product	D	C
LED classic 120W A67 E27 CW FR NDRF1SRT4	70 mm	121 mm
LED classic 120W A67 E27 WW FR NDRFSRT4	70 mm	121 mm
LED classic 150W A67 E27 CDL FR ND 1SRT4	70 mm	121 mm
LED classic 150W A67 E27 CW FR ND 1SRT4	70 mm	121 mm
LED classic 150W A67 E27 WW FR NDRFSRT4	70 mm	121 mm

Product	D	C
LED classic-giant 40W E27 T65 GOLD DIM	66 mm	273 mm

Product	D	C
LED classic 60W G95 E27 WW FR ND RFSRT4	95 mm	140 mm

Classic filament LEDbulbs

Måttskiss



Product	D	C
LED classic 200W A95 E27 CW FR ND 1PF/4	95 mm	165 mm
LED classic 200W A95 E27 WW FR ND 1PF	95 mm	165 mm

Product	D	C
LED Classic 100 W E27 WW G120 FR ND SRT4	125 mm	177 mm
LED Classic 60 W E27 WW G120 FR ND SRT4	125 mm	177 mm

Product	D	C
LED cla 120W G120 E27 WW FR ND RFSRT4	124 mm	177 mm

Classic filament LEDbulbs

Allmän information

Socket	E27
Specificerad livslängd (timmar)	15 000 h
Driftcykel	20 000
Nominell livslängd	15 000 h

Ljusteknik

Färgåtergivningsindex	80
LLMF vid slutet av nominell livslängd (nom)	70 %

Drift och elektricitet

Ingångsfrekvens	50–60 Hz
Line Frequency	50 to 60 Hz
Tändningstid (nom)	0,5 s

Användning och godkännande

Omgivningstemperatur	-20 till +45 °C
----------------------	-----------------

Ljusteknik

Order Code	Full Product Name	Spridningsvinkel (nom)	Korrelerad färgtemperatur (Nom)	Färgkod	Ljusflöde
929002371801	LED classic 120W A67 E27 WW FR NDRFSRT4	300 °	2700 K	827	2 000 lm
929002371901	LED classic 120W A67 E27 CW FR NDRFISRT4	300 °	4000 K	840	2 000 lm
929002372601	LED classic 150W A67 E27 WW FR NDRFSRT4	300 °	2700 K	827	2 452 lm
929002372701	LED classic 150W A67 E27 CW FR ND 1SRT4	300 °	4000 K	840	2 452 lm
929002372801	LED classic 150W A67 E27 CDL FR ND 1SRT4	300 °	6500 K	865	2 452 lm
929002370801	LED classic 60W G95 E27 WW FR ND RFSRT4	-	2700 K	827	806 lm
929002067801	LED Classic 100 W E27 WW G120 FR ND SRT4	-	2700 K	827	1 521 lm
929002983601	LED classic-giant 40W E27 G200 GOLD DIM	330 °	1800 K	818	470 lm
929002372901	LED classic 200W A95 E27 WW FR ND 1PF	300 °	2700 K	827	3 452 lm
929002373001	LED classic 200W A95 E27 CW FR ND 1PF/4	300 °	4000 K	840	3 452 lm
929002372101	LED cla 120W G120 E27 WW FR ND RFSRT4	300 °	2700 K	827	2 000 lm
929002982601	LED giant 20W E27 G200 1800K smoky D	300 °	1800 K	818	200 lm
929002983701	LED classic-giant 40W E27 T65 GOLD DIM	330 °	1800 K	818	470 lm
929002412801	LED classic CM 50W A60 E27 WW CL D SRT4	270 °	2700 K	827	650 lm
929002983501	LED classic-giant 40W E27 A160 GOLD DIM	330 °	1800 K	818	470 lm
929002025201	LED Classic 60 W E27 WW G120 FR ND SRT4	-	2700 K	827	806 lm
929002983801	LED classic-giant 28W E27 A160 GOLD ND	330 °	1800 K	818	300 lm
929002982501	LED giant 20W E27 A160 1800K smoky D	-	1800 K	818	200 lm

Drift och elektricitet

Order Code	Full Product Name	Effektförbrukning	Motsvarande effekt	Order Code	Full Product Name	Effektförbrukning	Motsvarande effekt
929002371801	LED classic 120W A67 E27 WW FR NDRFSRT4	13 W	120 W	929002372701	LED classic 150W A67 E27 CW FR ND 1SRT4	17,5 W	150 W
929002371901	LED classic 120W A67 E27 CW FR NDRFISRT4	13 W	120 W	929002372801	LED classic 150W A67 E27 CDL FR ND 1SRT4	17,5 W	150 W
929002372601	LED classic 150W A67 E27 WW FR NDRFSRT4	17,5 W	150 W	929002370801	LED classic 60W G95 E27 WW FR ND RFSRT4	7 W	60 W

Classic filament LEDbulbs

Order Code	Full Product Name	Motsvarande	
		Effektförbrukning	effekt
929002067801	LED Classic 100 W E27 WW G120 FR ND SRT4	10,5 W	100 W
929002983601	LED classic-giant 40W E27 G200 GOLD DIM	7 W	40 W
929002372901	LED classic 200W A95 E27 WW FR ND 1PF	23 W	200 W
929002373001	LED classic 200W A95 E27 CW FR ND 1PF/4	23 W	200 W
929002372101	LED cla 120W G120 E27 WW FR ND RFSRT4	13 W	120 W
929002982601	LED giant 20W E27 G200 1800K smoky D	6,5 W	20 W

Order Code	Full Product Name	Motsvarande	
		Effektförbrukning	effekt
929002983701	LED classic-giant 40W E27 T65 GOLD DIM	7 W	40 W
929002412801	LED classic CM 50W A60 E27 WW CL D SRT4	7,2 W	50 W
929002983501	LED classic-giant 40W E27 A160 GOLD DIM	7 W	40 W
929002025201	LED Classic 60 W E27 WW G120 FR ND SRT4	7 W	60 W
929002983801	LED classic-giant 28W E27 A160 GOLD ND	4,5 W	28 W
929002982501	LED giant 20W E27 A160 1800K smoky D	6,5 W	20 W

Temperatur

Order Code	Full Product Name	T-Case max. (nom)
929002371801	LED classic 120W A67 E27 WW FR NDRFSRT4	60 °C
929002371901	LED classic 120W A67 E27 CW FR NDRFSRT4	60 °C
929002372601	LED classic 150W A67 E27 WW FR NDRFSRT4	60 °C
929002372701	LED classic 150W A67 E27 CW FR ND 1SRT4	60 °C
929002372801	LED classic 150W A67 E27 CDL FR ND 1SRT4	60 °C
929002370801	LED classic 60W G95 E27 WW FR ND RFSRT4	45 °C
929002067801	LED Classic 100 W E27 WW G120 FR ND SRT4	50 °C
929002983601	LED classic-giant 40W E27 G200 GOLD DIM	45 °C
929002372901	LED classic 200W A95 E27 WW FR ND 1PF	55 °C

Order Code	Full Product Name	T-Case max. (nom)
929002373001	LED classic 200W A95 E27 CW FR ND 1PF/4	55 °C
929002372101	LED cla 120W G120 E27 WW FR ND RFSRT4	55 °C
929002982601	LED giant 20W E27 G200 1800K smoky D	45 °C
929002983701	LED classic-giant 40W E27 T65 GOLD DIM	45 °C
929002412801	LED classic CM 50W A60 E27 WW CL D SRT4	55 °C
929002983501	LED classic-giant 40W E27 A160 GOLD DIM	45 °C
929002025201	LED Classic 60 W E27 WW G120 FR ND SRT4	45 °C
929002983801	LED classic-giant 28W E27 A160 GOLD ND	45 °C
929002982501	LED giant 20W E27 A160 1800K smoky D	45 °C

Styrenheter och dimring

Order Code	Full Product Name	Dimbar
929002371801	LED classic 120W A67 E27 WW FR NDRFSRT4	Nej
929002371901	LED classic 120W A67 E27 CW FR NDRFSRT4	Nej
929002372601	LED classic 150W A67 E27 WW FR NDRFSRT4	Nej
929002372701	LED classic 150W A67 E27 CW FR ND 1SRT4	Nej
929002372801	LED classic 150W A67 E27 CDL FR ND 1SRT4	Nej
929002370801	LED classic 60W G95 E27 WW FR ND RFSRT4	Nej
929002067801	LED Classic 100 W E27 WW G120 FR ND SRT4	Nej
929002983601	LED classic-giant 40W E27 G200 GOLD DIM	Endast med särskilda dimmers
929002372901	LED classic 200W A95 E27 WW FR ND 1PF	Nej
929002373001	LED classic 200W A95 E27 CW FR ND 1PF/4	Nej
929002372101	LED cla 120W G120 E27 WW FR ND RFSRT4	Nej

Order Code	Full Product Name	Dimbar
929002982601	LED giant 20W E27 G200 1800K smoky D	Endast med särskilda dimmers
929002983701	LED classic-giant 40W E27 T65 GOLD DIM	Endast med särskilda dimmers
929002412801	LED classic CM 50W A60 E27 WW CL D SRT4	Endast med särskilda dimmers
929002983501	LED classic-giant 40W E27 A160 GOLD DIM	Endast med särskilda dimmers
929002025201	LED Classic 60 W E27 WW G120 FR ND SRT4	Nej
929002983801	LED classic-giant 28W E27 A160 GOLD ND	Nej
929002982501	LED giant 20W E27 A160 1800K smoky D	Endast med särskilda dimmers

Mekanik och armaturhus

Order Code	Full Product Name	Ljuskällans	
		ytbehandling	Lampform
929002371801	LED classic 120W A67 E27 WW FR NDRFSRT4	Frostad	A67
929002371901	LED classic 120W A67 E27 CW FR NDRFSRT4	Frostad	A67

Order Code	Full Product Name	Ljuskällans	
		ytbehandling	Lampform
929002372601	LED classic 150W A67 E27 WW FR NDRFSRT4	Frostad	A67
929002372701	LED classic 150W A67 E27 CW FR ND 1SRT4	Frostad	A67


Classic filament LEDbulbs

Order Code	Full Product Name	Ljuskällans ytbehandling	Lampform
929002372801	LED classic 150W A67 E27 CDL FR ND 1SRT4	Frostad	A67
929002370801	LED classic 60W G95 E27 WW FR ND RFSRT4	Frostad	G95
929002067801	LED Classic 100 W E27 WW G120 FR ND SRT4	Frostad	G120
929002983601	LED classic-giant 40W E27 G200 GOLD DIM	Amber	G200
929002372901	LED classic 200W A95 E27 WW FR ND 1PF	Frostad	A95
929002373001	LED classic 200W A95 E27 CW FR ND 1PF/4	Frostad	A95
929002372101	LED cla 120W G120 E27 WW FR ND RFSRT4	Frostad	G120


Order Code	Full Product Name	Ljuskällans ytbehandling	Lampform
929002982601	LED giant 20W E27 G200 1800K smoky D	rökig	G200
929002983701	LED classic-giant 40W E27 T65 GOLD DIM	Amber	T65
929002412801	LED classic CM 50W A60 E27 WW CL D SRT4	Spegelkrona	A60
929002983501	LED classic-giant 40W E27 A160 GOLD DIM	Amber	A160
929002025201	LED Classic 60 W E27 WW G120 FR ND SRT4	Frostad	G120
929002983801	LED classic-giant 28W E27 A160 GOLD ND	Amber	A160
929002982501	LED giant 20W E27 A160 1800K smoky D	rökig	A160

Användning och godkännande

Order Code	Full Product Name	Energiförbrukning kWh/ 1 000 tim
929002371801	LED classic 120W A67 E27 WW FR NDRFSRT4	13 kWh
929002371901	LED classic 120W A67 E27 CW FR NDRFISRT4	13 kWh
929002372601	LED classic 150W A67 E27 WW FR NDRFSRT4	18 kWh
929002372701	LED classic 150W A67 E27 CW FR ND 1SRT4	18 kWh
929002372801	LED classic 150W A67 E27 CDL FR ND 1SRT4	18 kWh
929002370801	LED classic 60W G95 E27 WW FR ND RFSRT4	7 kWh
929002067801	LED Classic 100 W E27 WW G120 FR ND SRT4	11 kWh
929002983601	LED classic-giant 40W E27 G200 GOLD DIM	7 kWh
929002372901	LED classic 200W A95 E27 WW FR ND 1PF	23 kWh
929002373001	LED classic 200W A95 E27 CW FR ND 1PF/4	23 kWh
929002372101	LED cla 120W G120 E27 WW FR ND RFSRT4	13 kWh
929002982601	LED giant 20W E27 G200 1800K smoky D	7 kWh
929002983701	LED classic-giant 40W E27 T65 GOLD DIM	7 kWh
929002412801	LED classic CM 50W A60 E27 WW CL D SRT4	8 kWh
929002983501	LED classic-giant 40W E27 A160 GOLD DIM	7 kWh
929002025201	LED Classic 60 W E27 WW G120 FR ND SRT4	7 kWh
929002983801	LED classic-giant 28W E27 A160 GOLD ND	5 kWh
929002982501	LED giant 20W E27 A160 1800K smoky D	7 kWh





Classic filament LEDbulbs




Classic filament LEDbulbs

Classic filament LEDbulbs



Classic filament LEDbulbs



Classic filament LEDbulbs

