



# The LEDlamps are ideal for general lighting applications

## CorePro LEDbulb

LEDbulbs are compatible with existing fixtures with an E27 holder and are designed for retrofit replacement of incandescent bulbs.

### Benefits

- Up to 80% energy saving compared with halogen lamps
- Retrofittable
- Lower maintenance costs

### Features

- Non dimmable
- Warm white light
- Lifetime of 15,000 hours
- UV- and IR-free light for less heat and protection for heat-sensitive objects

### Application

- Hotels, restaurants, bars, cafés
- Lobbies, corridors, stairwells, washrooms, reception areas

# CorePro LEDbulb

## Versions



CorePro LEDbulb 75W B22 827 FR A60



LED Bulb 9W B22 AU






LEDbulb A65 E27 FR P1



LEDbulb CorePro B22 A60 5W

## Dimensional drawing







Product	D	C
CorePro LEDbulb ND 11-75W A60 B22 927 UK	60 mm	107 mm
CorePro LEDbulb ND 7.5-60W A60 B22 930	60 mm	105 mm
CorePro LEDbulb ND 8-60W A60 B22 927 UK	60 mm	105 mm
CoreProLEDbulb ND 4.9-40W A60 B22 927 UK	60 mm	105 mm
CoreProLEDbulb ND 7.5-60W A60 B22 930 UK	60 mm	105 mm

Product	D	C
CorePro LEDbulb ND 10-75W A60 E27 830	60 mm	108 mm
CorePro LEDbulb ND 10-75W A60 E27 840	60 mm	108 mm
CorePro LEDbulb ND 10-75W A60 E27 940	60 mm	109 mm
CorePro LEDbulb ND 11-75W A60 E27 927	60 mm	109 mm

Product	D	C
CorePro LEDbulb ND 13-100W A60 B22 930	60 mm	110 mm
CoreProLEDbulb ND 13-100W A60 B22 927 UK	60 mm	118 mm

# CorePro LEDbulb

## Dimensional drawing



Product	D	C
CorePro LEDbulb ND 13-100W A60 E27 827	60 mm	120 mm
CorePro LEDbulb ND 13-100W A60 E27 830	60 mm	120 mm
CorePro LEDbulb ND 13-100W A60 E27 840	60 mm	120 mm


Product	D	C
CorePro LEDbulb ND 11-75W A60 B22 827	60 mm	110 mm
CorePro LEDbulb ND 13-100W A60 B22 827	60 mm	110 mm

Product	D	C
CorePro LEDbulb ND 12.5-100W A60 E27 940	60 mm	110 mm
CoreProLEDbulb ND 13-100W A60 E27 927 UK	60 mm	120 mm
CoreProLEDbulb ND 13-100W A60 E27 930 UK	60 mm	110 mm

Product	D	C
CorePro LEDbulb ND 4.9-40W A60 B22 827	60 mm	110 mm

# CorePro LEDbulb

## Dimensional drawing



Product	D	C
CorePro LEDbulb ND 4.9-40W A60 E27 827	60 mm	107 mm
CorePro LEDbulb ND 4.9-40W A60 E27 840	60 mm	108 mm
CorePro LEDbulb ND 4.9-40W A60 E27 940UK	60 mm	107 mm
CorePro LEDbulb ND 7.5-60W A60 E27 930UK	60 mm	107 mm
CorePro LEDbulb ND 7.5-60W A60 E27 940UK	60 mm	107 mm
CorePro LEDbulb ND 8-60W A60 E27 827	60 mm	108 mm
CorePro LEDbulb ND 8-60W A60 E27 830	60 mm	108 mm
CorePro LEDbulb ND 8-60W A60 E27 840	60 mm	108 mm
CorePro LEDbulb ND 8-60W A60 E27 927 UK	60 mm	107 mm
CoreProLEDbulb ND 4.9-40W A60 E27 927 UK	60 mm	107 mm
LEDbulb ND 8-60W A60 E27 827 12CT	60 mm	107 mm
LEDbulb ND 8-60W A60 E27 840 12CT	60 mm	107 mm

General Information	
Switching Cycle	50,000
Nominal lifetime	15,000 h
Light Technical	
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Starting time (nom.)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Frosted

## General Information

Order Code	Full Product Name	Cap base
929003003799	CoreProLEDbulb ND 13-100W A60 E27 927 UK	E27
929003003999	CoreProLEDbulb ND 13-100W A60 E27 930 UK	E27
929003004102	CorePro LEDbulb ND 12.5-100W A60 E27 940	E27
929003003899	CoreProLEDbulb ND 13-100W A60 B22 927 UK	B22
929003004002	CorePro LEDbulb ND 13-100W A60 B22 930	B22
929003544599	CorePro LEDbulb ND 11-75W A60 B22 927 UK	B22
929002306808	CorePro LEDbulb ND 13-100W A60 E27 827	E27
929002306908	CorePro LEDbulb ND 13-100W A60 E27 840	E27
929003607608	CorePro LEDbulb ND 13-100W A60 E27 830	E27
929002306608	CorePro LEDbulb ND 10-75W A60 E27 840	E27
929003544102	CorePro LEDbulb ND 11-75W A60 E27 927	E27
929003544302	CorePro LEDbulb ND 10-75W A60 E27 940	E27
929003607508	CorePro LEDbulb ND 10-75W A60 E27 830	E27
929003542999	CoreProLEDbulb ND 4.9-40W A60 B22 927 UK	B22
929003543799	CorePro LEDbulb ND 8-60W A60 B22 927 UK	B22
929003543802	CorePro LEDbulb ND 7.5-60W A60 B22 930	B22

Order Code	Full Product Name	Cap base
929003543899	CoreProLEDbulb ND 7.5-60W A60 B22 930 UK	B22
929003603102	CorePro LEDbulb ND 4.9-40W A60 B22 827	B22
929002306208	CorePro LEDbulb ND 8-60W A60 E27 827	E27
929002306308	CorePro LEDbulb ND 8-60W A60 E27 840	E27
929002306309	LEDbulb ND 8-60W A60 E27 840 12CT	E27
929003540208	CorePro LEDbulb ND 4.9-40W A60 E27 827	E27
929003542599	CoreProLEDbulb ND 4.9-40W A60 E27 927 UK	E27
929003542799	CorePro LEDbulb ND 4.9-40W A60 E27 940UK	E27
929003543385	CorePro LEDbulb ND 8-60W A60 E27 927 UK	E27
929003543499	CorePro LEDbulb ND 7.5-60W A60 E27 930UK	E27
929003543599	CorePro LEDbulb ND 7.5-60W A60 E27 940UK	E27
929003564108	CorePro LEDbulb ND 4.9-40W A60 E27 840	E27
929003607408	CorePro LEDbulb ND 8-60W A60 E27 830	E27
929003774009	LEDbulb ND 8-60W A60 E27 827 12CT	E27
929001234002	CorePro LEDbulb ND 11-75W A60 B22 827	B22
929001234102	CorePro LEDbulb ND 13-100W A60 B22 827	B22

# CorePro LEDbulb

## Light Technical

Order Code	Full Product Name	Beam angle (nom.)	Correlated Colour Temperature (Nom)	Colour rendering index		Luminous Flux
				(CRI)	Colour Code	
929003003799	CoreProLEDbulb ND 13-100W A60 E27 927 UK	200 degree(s)	2700 K	90	927	1,521 lm
929003003999	CoreProLEDbulb ND 13-100W A60 E27 930 UK	200 degree(s)	3000 K	90	930	1,521 lm
929003004102	CorePro LEDbulb ND 12.5-100W A60 E27 940	200 degree(s)	4000 K	90	940	1,521 lm
929003003899	CoreProLEDbulb ND 13-100W A60 B22 927 UK	200 degree(s)	2700 K	90	927	1,521 lm
929003004002	CorePro LEDbulb ND 13-100W A60 B22 930	200 degree(s)	3000 K	90	930	1,521 lm
929003544599	CorePro LEDbulb ND 11-75W A60 B22 927 UK	180 degree(s)	2700 K	90	927	1,055 lm
929002306808	CorePro LEDbulb ND 13-100W A60 E27 827	180 degree(s)	2700 K	80	827	1,521 lm
929002306908	CorePro LEDbulb ND 13-100W A60 E27 840	180 degree(s)	4000 K	80	840	1,521 lm
929003607608	CorePro LEDbulb ND 13-100W A60 E27 830	180 degree(s)	3000 K	80	830	1,521 lm
929002306608	CorePro LEDbulb ND 10-75W A60 E27 840	180 degree(s)	4000 K	80	840	1,055 lm
929003544102	CorePro LEDbulb ND 11-75W A60 E27 927	180 degree(s)	2700 K	90	927	1,055 lm
929003544302	CorePro LEDbulb ND 10-75W A60 E27 940	180 degree(s)	4000 K	90	940	1,055 lm
929003607508	CorePro LEDbulb ND 10-75W A60 E27 830	180 degree(s)	3000 K	80	830	1,055 lm
929003542999	CoreProLEDbulb ND 4.9-40W A60 B22 927 UK	180 degree(s)	2700 K	90	927	470 lm
929003543799	CorePro LEDbulb ND 8-60W A60 B22 927 UK	180 degree(s)	2700 K	90	927	806 lm
929003543802	CorePro LEDbulb ND 7.5-60W A60 B22 930	180 degree(s)	3000 K	90	930	806 lm
929003543899	CoreProLEDbulb ND 7.5-60W A60 B22 930 UK	180 degree(s)	3000 K	90	930	806 lm
929003603102	CorePro LEDbulb ND 4.9-40W A60 B22 827	200 degree(s)	2700 K	80	827	470 lm
929002306208	CorePro LEDbulb ND 8-60W A60 E27 827	180 degree(s)	2700 K	80	827	806 lm
929002306308	CorePro LEDbulb ND 8-60W A60 E27 840	180 degree(s)	4000 K	80	840	806 lm
929002306309	LEDbulb ND 8-60W A60 E27 840 12CT	150 degree(s)	4000 K	80	840	806 lm
929003540208	CorePro LEDbulb ND 4.9-40W A60 E27 827	180 degree(s)	2700 K	80	827	470 lm
929003542599	CoreProLEDbulb ND 4.9-40W A60 E27 927 UK	180 degree(s)	2700 K	90	927	470 lm
929003542799	CorePro LEDbulb ND 4.9-40W A60 E27 940UK	180 degree(s)	4000 K	90	940	470 lm
929003543385	CorePro LEDbulb ND 8-60W A60 E27 927 UK	180 degree(s)	2700 K	90	927	806 lm
929003543499	CorePro LEDbulb ND 7.5-60W A60 E27 930UK	180 degree(s)	3000 K	90	930	806 lm
929003543599	CorePro LEDbulb ND 7.5-60W A60 E27 940UK	180 degree(s)	4000 K	90	940	806 lm
929003564108	CorePro LEDbulb ND 4.9-40W A60 E27 840	180 degree(s)	4000 K	80	840	470 lm
929003607408	CorePro LEDbulb ND 8-60W A60 E27 830	180 degree(s)	3000 K	80	830	806 lm
929003774009	LEDbulb ND 8-60W A60 E27 827 12CT	150 degree(s)	2700 K	80	827	806 lm
929001234002	CorePro LEDbulb ND 11-75W A60 B22 827	200 degree(s)	2700 K	80	827	1,055 lm
929001234102	CorePro LEDbulb ND 13-100W A60 B22 827	200 degree(s)	2700 K	80	827	1,521 lm

## Operating and Electrical

Order Code	Full Product Name	Input frequency	Line Frequency	Power Consumption	Wattage equivalent	Order Code	Full Product Name	Input frequency	Line Frequency	Power Consumption	Wattage equivalent
929003003799	CoreProLEDbulb ND 13-100W A60 E27 927 UK	50 Hz	50 Hz	13 W	100 W	929003004002	CorePro LEDbulb ND 13-100W A60 B22 930	50 to 60 Hz	50 to 60 Hz	13 W	100 W
929003003999	CoreProLEDbulb ND 13-100W A60 E27 930 UK	50 to 60 Hz	50 to 60 Hz	13 W	100 W	929003544599	CorePro LEDbulb ND 11-75W A60 B22 927 UK	50 Hz	50 Hz	11 W	75 W
929003004102	CorePro LEDbulb ND 12.5-100W A60 E27 940	50 to 60 Hz	50 to 60 Hz	12.5 W	100 W	929002306808	CorePro LEDbulb ND 13-100W A60 E27 827	50 to 60 Hz	50 to 60 Hz	13 W	100 W
929003003899	CoreProLEDbulb ND 13-100W A60 B22 927 UK	50 Hz	50 Hz	13 W	100 W	929002306908	CorePro LEDbulb ND 13-100W A60 E27 840	50 to 60 Hz	50 to 60 Hz	13 W	100 W

## CorePro LEDbulb

Order Code	Full Product Name	Input frequency	Line Frequency	Power Consumption	Wattage equivalent
929003607608	CorePro LEDbulb ND 13-100W A60 E27 830	50 to 60 Hz	50 to 60 Hz	13 W	100 W
929002306608	CorePro LEDbulb ND 10-75W A60 E27 840	50 to 60 Hz	50 to 60 Hz	10 W	75 W
929003544102	CorePro LEDbulb ND 11-75W A60 E27 927	50 Hz	50 Hz	11 W	75 W
929003544302	CorePro LEDbulb ND 10-75W A60 E27 940	50 Hz	50 Hz	10 W	75 W
929003607508	CorePro LEDbulb ND 10-75W A60 E27 830	50 to 60 Hz	50 to 60 Hz	10 W	75 W
929003542999	CorePro LEDbulb ND 4.9-40W A60 B22 927 UK	50 Hz	50 Hz	4.9 W	40 W
929003543799	CorePro LEDbulb ND 8-60W A60 B22 927 UK	50 Hz	50 Hz	8 W	60 W
929003543802	CorePro LEDbulb ND 7.5-60W A60 B22 930	50 Hz	50 Hz	7.5 W	60 W
929003543899	CorePro LEDbulb ND 7.5-60W A60 B22 930 UK	50 Hz	50 Hz	7.5 W	60 W
929003603102	CorePro LEDbulb ND 4.9-40W A60 B22 827	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W
929002306208	CorePro LEDbulb ND 8-60W A60 E27 827	50 to 60 Hz	50 to 60 Hz	8 W	60 W
929002306308	CorePro LEDbulb ND 8-60W A60 E27 840	50 to 60 Hz	50 to 60 Hz	8 W	60 W

Order Code	Full Product Name	Input frequency	Line Frequency	Power Consumption	Wattage equivalent
929002306309	LEDbulb ND 8-60W A60 E27 840 12CT	50 to 60 Hz	-	8 W	60 W
929003540208	CorePro LEDbulb ND 4.9-40W A60 E27 827	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W
929003542599	CorePro LEDbulb ND 4.9-40W A60 E27 927 UK	50 Hz	50 Hz	4.9 W	40 W
929003542799	CorePro LEDbulb ND 4.9-40W A60 E27 940UK	50 Hz	50 Hz	4.9 W	40 W
929003543385	CorePro LEDbulb ND 8-60W A60 E27 927 UK	50 Hz	50 Hz	8 W	60 W
929003543499	CorePro LEDbulb ND 7.5-60W A60 E27 930UK	50 Hz	50 Hz	7.5 W	60 W
929003543599	CorePro LEDbulb ND 7.5-60W A60 E27 940UK	50 Hz	50 Hz	7.5 W	60 W
929003564108	CorePro LEDbulb ND 4.9-40W A60 E27 840	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W
929003607408	CorePro LEDbulb ND 8-60W A60 E27 830	50 to 60 Hz	50 to 60 Hz	8 W	60 W
929003774009	LEDbulb ND 8-60W A60 E27 827 12CT	50 to 60 Hz	-	8 W	60 W
929001234002	CorePro LEDbulb ND 11-75W A60 B22 827	50 to 60 Hz	50 to 60 Hz	11 W	75 W
929001234102	CorePro LEDbulb ND 13-100W A60 B22 827	50 to 60 Hz	50 to 60 Hz	13 W	100 W

## Temperature

Order Code	Full Product Name	T-Case maximum (nom.)
929003003799	CorePro LEDbulb ND 13-100W A60 E27 927 UK	105 °C
929003003999	CorePro LEDbulb ND 13-100W A60 E27 930 UK	95 °C
929003004102	CorePro LEDbulb ND 12.5-100W A60 E27 940	95 °C
929003003899	CorePro LEDbulb ND 13-100W A60 B22 927 UK	105 °C
929003004002	CorePro LEDbulb ND 13-100W A60 B22 930	95 °C
929003544599	CorePro LEDbulb ND 11-75W A60 B22 927 UK	105 °C
929002306808	CorePro LEDbulb ND 13-100W A60 E27 827	95 °C
929002306908	CorePro LEDbulb ND 13-100W A60 E27 840	95 °C
929003607608	CorePro LEDbulb ND 13-100W A60 E27 830	95 °C
929002306608	CorePro LEDbulb ND 10-75W A60 E27 840	85 °C

Order Code	Full Product Name	T-Case maximum (nom.)
929003544102	CorePro LEDbulb ND 11-75W A60 E27 927	105 °C
929003544302	CorePro LEDbulb ND 10-75W A60 E27 940	105 °C
929003607508	CorePro LEDbulb ND 10-75W A60 E27 830	85 °C
929003542999	CorePro LEDbulb ND 4.9-40W A60 B22 927 UK	80 °C
929003543799	CorePro LEDbulb ND 8-60W A60 B22 927 UK	95 °C
929003543802	CorePro LEDbulb ND 7.5-60W A60 B22 930	95 °C
929003543899	CorePro LEDbulb ND 7.5-60W A60 B22 930 UK	95 °C
929003603102	CorePro LEDbulb ND 4.9-40W A60 B22 827	80 °C
929002306208	CorePro LEDbulb ND 8-60W A60 E27 827	75 °C
929002306308	CorePro LEDbulb ND 8-60W A60 E27 840	75 °C

# CorePro LEDbulb

Order Code	Full Product Name	T-Case maximum (nom.)
929002306309	LEDbulb ND 8-60W A60 E27 840 12CT	90 °C
929003540208	CorePro LEDbulb ND 4.9-40W A60 E27 827	75 °C
929003542599	CoreProLEDbulb ND 4.9-40W A60 E27 927 UK	80 °C
929003542799	CorePro LEDbulb ND 4.9-40W A60 E27 940UK	80 °C
929003543385	CorePro LEDbulb ND 8-60W A60 E27 927 UK	95 °C
929003543499	CorePro LEDbulb ND 7.5-60W A60 E27 930UK	95 °C

Order Code	Full Product Name	T-Case maximum (nom.)
929003543599	CorePro LEDbulb ND 7.5-60W A60 E27 940UK	95 °C
929003564108	CorePro LEDbulb ND 4.9-40W A60 E27 840	75 °C
929003607408	CorePro LEDbulb ND 8-60W A60 E27 830	75 °C
929003774009	LEDbulb ND 8-60W A60 E27 827 12CT	90 °C
929001234002	CorePro LEDbulb ND 11-75W A60 B22 827	80 °C
929001234102	CorePro LEDbulb ND 13-100W A60 B22 827	85 °C

## Mechanical and Housing

Order Code	Full Product Name	Bulb shape
929003003799	CoreProLEDbulb ND 13-100W A60 E27 927 UK	A60M
929003003999	CoreProLEDbulb ND 13-100W A60 E27 930 UK	A60M
929003004102	CorePro LEDbulb ND 12.5-100W A60 E27 940	A60M
929003003899	CoreProLEDbulb ND 13-100W A60 B22 927 UK	A60M
929003004002	CorePro LEDbulb ND 13-100W A60 B22 930	A60M
929003544599	CorePro LEDbulb ND 11-75W A60 B22 927 UK	A60
929002306808	CorePro LEDbulb ND 13-100W A60 E27 827	A60
929002306908	CorePro LEDbulb ND 13-100W A60 E27 840	A60
929003607608	CorePro LEDbulb ND 13-100W A60 E27 830	A60
929002306608	CorePro LEDbulb ND 10-75W A60 E27 840	A60
929003544102	CorePro LEDbulb ND 11-75W A60 E27 927	A60
929003544302	CorePro LEDbulb ND 10-75W A60 E27 940	A60
929003607508	CorePro LEDbulb ND 10-75W A60 E27 830	A60
929003542999	CoreProLEDbulb ND 4.9-40W A60 B22 927 UK	A60
929003543799	CorePro LEDbulb ND 8-60W A60 B22 927 UK	A60
929003543802	CorePro LEDbulb ND 7.5-60W A60 B22 930	A60

Order Code	Full Product Name	Bulb shape
929003543899	CoreProLEDbulb ND 7.5-60W A60 B22 930 UK	A60
929003603102	CorePro LEDbulb ND 4.9-40W A60 B22 827	A60S
929002306208	CorePro LEDbulb ND 8-60W A60 E27 827	A60
929002306308	CorePro LEDbulb ND 8-60W A60 E27 840	A60
929002306309	LEDbulb ND 8-60W A60 E27 840 12CT	A60
929003540208	CorePro LEDbulb ND 4.9-40W A60 E27 827	A60
929003542599	CoreProLEDbulb ND 4.9-40W A60 E27 927 UK	A60
929003542799	CorePro LEDbulb ND 4.9-40W A60 E27 940UK	A60
929003543385	CorePro LEDbulb ND 8-60W A60 E27 927 UK	A60
929003543499	CorePro LEDbulb ND 7.5-60W A60 E27 930UK	A60
929003543599	CorePro LEDbulb ND 7.5-60W A60 E27 940UK	A60
929003564108	CorePro LEDbulb ND 4.9-40W A60 E27 840	A60
929003607408	CorePro LEDbulb ND 8-60W A60 E27 830	A60
929003774009	LEDbulb ND 8-60W A60 E27 827 12CT	A60
929001234002	CorePro LEDbulb ND 11-75W A60 B22 827	A60
929001234102	CorePro LEDbulb ND 13-100W A60 B22 827	A60







## Approval and Application

Order Code	Full Product Name	Energy consumption	
		Ambient temperature range	kWh/1,000 hours
929003003799	CoreProLEDbulb ND 13-100W A60 E27 927 UK	-20°C to 45°C	13 kWh
929003003999	CoreProLEDbulb ND 13-100W A60 E27 930 UK	-20 to +45 °C	13 kWh
929003004102	CorePro LEDbulb ND 12.5-100W A60 E27 940	-20 to +45 °C	13 kWh
929003003899	CoreProLEDbulb ND 13-100W A60 B22 927 UK	-20°C to 45°C	13 kWh
929003004002	CorePro LEDbulb ND 13-100W A60 B22 930	-20 to +45 °C	13 kWh
929003544599	CorePro LEDbulb ND 11-75W A60 B22 927 UK	-20°C to 45°C	11 kWh
929002306808	CorePro LEDbulb ND 13-100W A60 E27 827	-20°C to 45°C	13 kWh
929002306908	CorePro LEDbulb ND 13-100W A60 E27 840	-20°C to 45°C	13 kWh











Order Code	Full Product Name	Energy consumption	
		Ambient temperature range	kWh/1,000 hours
929003607608	CorePro LEDbulb ND 13-100W A60 E27 830	-20°C to 45°C	13 kWh
929002306608	CorePro LEDbulb ND 10-75W A60 E27 840	-20°C to 45°C	10 kWh
929003544102	CorePro LEDbulb ND 11-75W A60 E27 927	-20°C to 45°C	11 kWh
929003544302	CorePro LEDbulb ND 10-75W A60 E27 940	-20°C to 45°C	10 kWh
929003607508	CorePro LEDbulb ND 10-75W A60 E27 830	-20°C to 45°C	10 kWh
929003542999	CoreProLEDbulb ND 4.9-40W A60 B22 927 UK	-20°C to 45°C	5 kWh
929003543799	CorePro LEDbulb ND 8-60W A60 B22 927 UK	-20°C to 45°C	8 kWh
929003543802	CorePro LEDbulb ND 7.5-60W A60 B22 930	-20°C to 45°C	8 kWh

# CorePro LEDbulb

Order Code	Full Product Name	Ambient temperature range	Energy consumption kWh/1,000 hours
929003543899	CoreProLEDbulb ND 7.5-60W A60 B22 930 UK	-20°C to 45°C	8 kWh
929003603102	CorePro LEDbulb ND 4.9-40W A60 B22 827	-20°C to 45°C	5 kWh
929002306208	CorePro LEDbulb ND 8-60W A60 E27 827	-20°C to 45°C	8 kWh
929002306308	CorePro LEDbulb ND 8-60W A60 E27 840	-20°C to 45°C	8 kWh
929002306309	LEDbulb ND 8-60W A60 E27 840 12CT	-20 to +45 °C	8 kWh
929003540208	CorePro LEDbulb ND 4.9-40W A60 E27 827	-20°C to 45°C	5 kWh
929003542599	CoreProLEDbulb ND 4.9-40W A60 E27 927 UK	-20°C to 45°C	5 kWh
929003542799	CorePro LEDbulb ND 4.9-40W A60 E27 940UK	-20°C to 45°C	5 kWh
929003543385	CorePro LEDbulb ND 8-60W A60 E27 927 UK	-20°C to 45°C	8 kWh
929003543499	CorePro LEDbulb ND 7.5-60W A60 E27 930UK	-20°C to 45°C	8 kWh
929003543599	CorePro LEDbulb ND 7.5-60W A60 E27 940UK	-20°C to 45°C	8 kWh
929003564108	CorePro LEDbulb ND 4.9-40W A60 E27 840	-20°C to 45°C	5 kWh
929003607408	CorePro LEDbulb ND 8-60W A60 E27 830	-20°C to 45°C	8 kWh
929003774009	LEDbulb ND 8-60W A60 E27 827 12CT	-20 to +45 °C	8 kWh
929001234002	CorePro LEDbulb ND 11-75W A60 B22 827	-20°C to 45°C	11 kWh
929001234102	CorePro LEDbulb ND 13-100W A60 B22 827	-20°C to 45°C	13 kWh



# CorePro LEDbulb



# CorePro LEDbulb

