



# Innovative LED light lines have never been so simple

## CoreLine trunking gen2.5

CoreLine Trunking gen2 is a light-line system that is designed for simplicity. It comes in a choice of lengths, flux packages and beam shapes to suit every project and application. Easy to use and integrate with spots and sensors, CoreLine Trunking gen2 provides consistent, high-quality lighting with added protection against accidental water ingress. The innovative system is also easy to assemble and install for faster retrofits and refurbishments

### Benefits

- Simplicity – easy to understand architecture
- Wide portfolio offer including emergency lighting options
- Consistent, high-quality light without color or striping artefacts
- Easy to order, fast to assemble and install
- InterAct ready for enhanced use in Retail and Industry applications
- Fully compliant with relevant norms

### Features

- Intuitive, single layer architecture – only #2 12NCs needed to create a line
- Choice of 3 lengths, each with 3 flux packages
- 8 different optics with consistent light quality
- Dedicated sensor units to upgrade to Interact system propositions
- Lumen maintenance @ 50,000 hours - L85
- Available as trunking and standalone versions

### Application

- Food and Large Retailers
- Manufacturing
- Warehouses






# CoreLine trunking gen2.5

## Versions



LL217X

## Dimensional drawing



# CoreLine trunking gen2.5

## Product details



Coreline trunking gen2.5 coupling

General Information	
Driver included	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	>80
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Not applicable
Mechanical and Housing	
Housing Color	White
Mech. impact protection code	IK02
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 to +35 °C
CE mark	Yes
ENEC mark	ENEC plus mark
Flammability mark	-
Glow-wire test	Temperature 850 °C, duration 30 s
Initial Performance (IEC Compliant)	
Initial chromaticity	(0.38, 0.38) SDCM <3
Luminous flux tolerance	+/-10%

## General Information

Order Code	Full Product Name	Number of gear units
910925870146	LL243X 160S/840 UE PSU WB BV WH	1 unit
910925870147	LL243X 160S/840 UE DIA WB BV WH	1 unit
910925870148	LL243X 160S/840 UE PSU NB BV WH	1 unit
910925870149	LL243X 160S/840 UE DIA NB BV WH	1 unit
910925870150	LL243X 240S/840 HE PSU NB BV WH	2 units
910925870151	LL243X 240S/840 UE DIA NB BV WH	2 units
910925870152	LL243X 160S/840 NE PSU WB BV WH	1 unit
910925870153	LL243X 160S/840 NE DIA WB BV WH	1 unit
910925870154	LL243X 160S/840 NE PSU NB BV WH	1 unit
910925870155	LL243X 160S/840 NE DIA NB BV WH	1 unit
910925870120	LL241X 53S/840 PSU NE WB 5x1.5 WH	1 unit
910925870121	LL241X 80S/840 HE PSU WB 5x1.5 WH	1 unit
910925870122	LL242X 80S/840 NE DIA WB 7x1.5 WH	1 unit
910925870123	LL242X 45S/840 UE DIA WB 7x1.5 WH	1 unit
910925870124	LL242X 45S/840 UE PSU WB 5x1.5 WH	1 unit
910925870125	LL242X 80S/840 UE DIA WB 7x1.5 WH	1 unit
910925870126	LL242X 80S/840 HE PSU WB 5x1.5 WH	1 unit
910925870127	LL242X 120S/840 UE DIA WB 7x1.5 WH	1 unit
910925870128	LL242X 120S/840 UE PSU WB 5x1.5 WH	1 unit
910925870129	LL242X 120S/840 HE DIA O 7x1.5 WH	1 unit
910925870130	LL242X 120S/840 HE PSU O 5x1.5 WH	1 unit
910925870131	LL243X 160S/840 NE DIA WB 7x1.5 WH	1 unit
910925870132	LL243X 90S/840 UE DIA WB 7x1.5 WH	1 unit
910925870133	LL243X 90S/840 UE PSU WB 5x1.5 WH	1 unit
910925870134	LL243X 160S/840 UE DIA WB 7x1.5 WH	1 unit
910925870135	LL243X 160S/840 UE PSU WB 5x1.5 WH	1 unit
910925870136	LL243X 240S/840 UE DIA WB 7x1.5 WH	2 units
910925870137	LL243X 240S/840 HE PSU WB 5x1.5 WH	2 units
910925870138	LL243X 160S/840 UE DIA NB 7x1.5 WH	1 unit
910925870139	LL243X 160S/840 UE PSU NB 5x1.5 WH	1 unit
910925870140	LL243X 240S/840 UE DIA NB 7x1.5 WH	2 units
910925870141	LL243X 240S/840 HE PSU NB 5x1.5 WH	2 units
910925870143	LL243X 160S/840 HE PSU O 5x1.5 WH	1 unit
910925870144	LL243X 240S/840 HE DIA O 7x1.5 WH	2 units
910925870145	LL243X 240S/840 HE PSU O 5x1.5 WH	2 units

## Light Technical

## CoreLine trunking gen2.5

Order Code	Full Product Name	Luminous		Optic type
		Efficacy (rated) (Nom)	Luminous Flux	
910925870146	LL243X 160S/840 UE PSU WB BV WH	195 lm/W	16,000 lm	Wide beam
910925870147	LL243X 160S/840 UE DIA WB BV WH	200 lm/W	16,000 lm	Wide beam
910925870148	LL243X 160S/840 UE PSU NB BV WH	195 lm/W	16,000 lm	Narrow beam
910925870149	LL243X 160S/840 UE DIA NB BV WH	200 lm/W	16,000 lm	Narrow beam
910925870150	LL243X 240S/840 HE PSU NB BV WH	182 lm/W	24,000 lm	Narrow beam
910925870151	LL243X 240S/840 UE DIA NB BV WH	188 lm/W	24,000 lm	Narrow beam
910925870152	LL243X 160S/840 NE PSU WB BV WH	160 lm/W	16,000 lm	Wide beam
910925870153	LL243X 160S/840 NE DIA WB BV WH	160 lm/W	16,000 lm	Wide beam
910925870154	LL243X 160S/840 NE PSU NB BV WH	160 lm/W	16,000 lm	Narrow beam
910925870155	LL243X 160S/840 NE DIA NB BV WH	160 lm/W	16,000 lm	Narrow beam
910925870120	LL241X 53S/840 PSU NE WB 5x1.5 WH	156 lm/W	5,300 lm	Wide beam
910925870121	LL241X 80S/840 HE PSU WB 5x1.5 WH	180 lm/W	8,000 lm	Wide beam
910925870122	LL242X 80S/840 NE DIA WB 7x1.5 WH	160 lm/W	8,000 lm	Wide beam
910925870123	LL242X 45S/840 UE DIA WB 7x1.5 WH	188 lm/W	4,500 lm	Wide beam
910925870124	LL242X 45S/840 UE PSU WB 5x1.5 WH	191 lm/W	4,500 lm	Wide beam
910925870125	LL242X 80S/840 UE DIA WB 7x1.5 WH	186 lm/W	8,000 lm	Wide beam
910925870126	LL242X 80S/840 HE PSU WB 5x1.5 WH	182 lm/W	8,000 lm	Wide beam
910925870127	LL242X 120S/840 UE DIA WB 7x1.5 WH	185 lm/W	12,000 lm	Wide beam

Order Code	Full Product Name	Luminous		Optic type
		Efficacy (rated) (Nom)	Luminous Flux	
910925870128	LL242X 120S/840 UE PSU WB 5x1.5 WH	185 lm/W	12,000 lm	Wide beam
910925870129	LL242X 120S/840 HE DIA O 7x1.5 WH	169 lm/W	11,000 lm	Opal
910925870130	LL242X 120S/840 HE PSU O 5x1.5 WH	169 lm/W	11,000 lm	Opal
910925870131	LL243X 160S/840 NE DIA WB 7x1.5 WH	160 lm/W	16,000 lm	Wide beam
910925870132	LL243X 90S/840 UE DIA WB 7x1.5 WH	198 lm/W	9,000 lm	Wide beam
910925870133	LL243X 90S/840 UE PSU WB 5x1.5 WH	200 lm/W	9,000 lm	Wide beam
910925870134	LL243X 160S/840 UE DIA WB 7x1.5 WH	200 lm/W	16,000 lm	Wide beam
910925870135	LL243X 160S/840 UE PSU WB 5x1.5 WH	195 lm/W	16,000 lm	Wide beam
910925870136	LL243X 240S/840 UE DIA WB 7x1.5 WH	188 lm/W	24,000 lm	Wide beam
910925870137	LL243X 240S/840 HE PSU WB 5x1.5 WH	182 lm/W	24,000 lm	Wide beam
910925870138	LL243X 160S/840 UE DIA NB 7x1.5 WH	200 lm/W	16,000 lm	Narrow beam
910925870139	LL243X 160S/840 UE PSU NB 5x1.5 WH	195 lm/W	16,000 lm	Narrow beam
910925870140	LL243X 240S/840 UE DIA NB 7x1.5 WH	188 lm/W	24,000 lm	Narrow beam
910925870141	LL243X 240S/840 HE PSU NB 5x1.5 WH	182 lm/W	24,000 lm	Narrow beam
910925870143	LL243X 160S/840 HE PSU O 5x1.5 WH	183 lm/W	15,000 lm	Opal
910925870144	LL243X 240S/840 HE DIA O 7x1.5 WH	176 lm/W	22,500 lm	Opal
910925870145	LL243X 240S/840 HE PSU O 5x1.5 WH	170 lm/W	22,500 lm	Opal

### Operating and Electrical

Order Code	Full Product Name	Power Consumption
910925870146	LL243X 160S/840 UE PSU WB BV WH	82 W
910925870147	LL243X 160S/840 UE DIA WB BV WH	80 W
910925870148	LL243X 160S/840 UE PSU NB BV WH	82 W
910925870149	LL243X 160S/840 UE DIA NB BV WH	80 W
910925870150	LL243X 240S/840 HE PSU NB BV WH	132 W
910925870151	LL243X 240S/840 UE DIA NB BV WH	128 W
910925870152	LL243X 160S/840 NE PSU WB BV WH	100 W
910925870153	LL243X 160S/840 NE DIA WB BV WH	100 W
910925870154	LL243X 160S/840 NE PSU NB BV WH	100 W
910925870155	LL243X 160S/840 NE DIA NB BV WH	100 W

Order Code	Full Product Name	Power Consumption
910925870120	LL241X 53S/840 PSU NE WB 5x1.5 WH	34 W
910925870121	LL241X 80S/840 HE PSU WB 5x1.5 WH	44.5 W
910925870122	LL242X 80S/840 NE DIA WB 7x1.5 WH	50 W
910925870123	LL242X 45S/840 UE DIA WB 7x1.5 WH	24 W
910925870124	LL242X 45S/840 UE PSU WB 5x1.5 WH	23.5 W
910925870125	LL242X 80S/840 UE DIA WB 7x1.5 WH	43 W
910925870126	LL242X 80S/840 HE PSU WB 5x1.5 WH	44 W
910925870127	LL242X 120S/840 UE DIA WB 7x1.5 WH	65 W
910925870128	LL242X 120S/840 UE PSU WB 5x1.5 WH	65 W
910925870129	LL242X 120S/840 HE DIA O 7x1.5 WH	65 W

## CoreLine trunking gen2.5

Order Code	Full Product Name	Power Consumption
910925870130	LL242X 120S/840 HE PSU O 5x1.5 WH	65 W
910925870131	LL243X 160S/840 NE DIA WB 7x1.5 WH	100 W
910925870132	LL243X 90S/840 UE DIA WB 7x1.5 WH	45.5 W
910925870133	LL243X 90S/840 UE PSU WB 5x1.5 WH	45 W
910925870134	LL243X 160S/840 UE DIA WB 7x1.5 WH	80 W
910925870135	LL243X 160S/840 UE PSU WB 5x1.5 WH	82 W
910925870136	LL243X 240S/840 UE DIA WB 7x1.5 WH	128 W
910925870137	LL243X 240S/840 HE PSU WB 5x1.5 WH	132 W

Order Code	Full Product Name	Power Consumption
910925870138	LL243X 160S/840 UE DIA NB 7x1.5 WH	80 W
910925870139	LL243X 160S/840 UE PSU NB 5x1.5 WH	82 W
910925870140	LL243X 240S/840 UE DIA NB 7x1.5 WH	128 W
910925870141	LL243X 240S/840 HE PSU NB 5x1.5 WH	132 W
910925870143	LL243X 160S/840 HE PSU O 5x1.5 WH	82 W
910925870144	LL243X 240S/840 HE DIA O 7x1.5 WH	128 W
910925870145	LL243X 240S/840 HE PSU O 5x1.5 WH	132 W

### Controls and Dimming

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
910925870146	LL243X 160S/840 UE PSU WB BV WH	No	Not applicable
910925870147	LL243X 160S/840 UE DIA WB BV WH	Yes	1%
910925870148	LL243X 160S/840 UE PSU NB BV WH	No	Not applicable
910925870149	LL243X 160S/840 UE DIA NB BV WH	Yes	1%
910925870150	LL243X 240S/840 HE PSU NB BV WH	No	Not applicable
910925870151	LL243X 240S/840 UE DIA NB BV WH	Yes	1%
910925870152	LL243X 160S/840 NE PSU WB BV WH	No	Not applicable
910925870153	LL243X 160S/840 NE DIA WB BV WH	Yes	1%
910925870154	LL243X 160S/840 NE PSU NB BV WH	No	Not applicable
910925870155	LL243X 160S/840 NE DIA NB BV WH	Yes	1%
910925870120	LL241X 53S/840 PSU NE WB 5x1.5 WH	No	Not applicable
910925870121	LL241X 80S/840 HE PSU WB 5x1.5 WH	No	Not applicable
910925870122	LL242X 80S/840 NE DIA WB 7x1.5 WH	Yes	1%
910925870123	LL242X 45S/840 UE DIA WB 7x1.5 WH	Yes	1%
910925870124	LL242X 45S/840 UE PSU WB 5x1.5 WH	No	Not applicable
910925870125	LL242X 80S/840 UE DIA WB 7x1.5 WH	Yes	1%
910925870126	LL242X 80S/840 HE PSU WB 5x1.5 WH	No	Not applicable
910925870127	LL242X 120S/840 UE DIA WB 7x1.5 WH	Yes	1%

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
910925870128	LL242X 120S/840 UE PSU WB 5x1.5 WH	No	Not applicable
910925870129	LL242X 120S/840 HE DIA O 7x1.5 WH	Yes	1%
910925870130	LL242X 120S/840 HE PSU O 5x1.5 WH	No	Not applicable
910925870131	LL243X 160S/840 NE DIA WB 7x1.5 WH	Yes	1%
910925870132	LL243X 90S/840 UE DIA WB 7x1.5 WH	Yes	1%
910925870133	LL243X 90S/840 UE PSU WB 5x1.5 WH	No	Not applicable
910925870134	LL243X 160S/840 UE DIA WB 7x1.5 WH	Yes	1%
910925870135	LL243X 160S/840 UE PSU WB 5x1.5 WH	No	Not applicable
910925870136	LL243X 240S/840 UE DIA WB 7x1.5 WH	Yes	1%
910925870137	LL243X 240S/840 HE PSU WB 5x1.5 WH	No	Not applicable
910925870138	LL243X 160S/840 UE DIA NB 7x1.5 WH	Yes	1%
910925870139	LL243X 160S/840 UE PSU NB 5x1.5 WH	No	Not applicable
910925870140	LL243X 240S/840 UE DIA NB 7x1.5 WH	Yes	1%
910925870141	LL243X 240S/840 HE PSU NB 5x1.5 WH	No	Not applicable
910925870143	LL243X 160S/840 HE PSU O 5x1.5 WH	No	Not applicable
910925870144	LL243X 240S/840 HE DIA O 7x1.5 WH	Yes	1%
910925870145	LL243X 240S/840 HE PSU O 5x1.5 WH	No	Not applicable

### Product Data


Order Code	Full Product Name	Product family code
910925870146	LL243X 160S/840 UE PSU WB BV WH	LL243X
910925870147	LL243X 160S/840 UE DIA WB BV WH	LL243X
910925870148	LL243X 160S/840 UE PSU NB BV WH	LL243X
910925870149	LL243X 160S/840 UE DIA NB BV WH	LL243X
910925870150	LL243X 240S/840 HE PSU NB BV WH	LL243X
910925870151	LL243X 240S/840 UE DIA NB BV WH	LL243X
910925870152	LL243X 160S/840 NE PSU WB BV WH	LL243X
910925870153	LL243X 160S/840 NE DIA WB BV WH	LL243X
910925870154	LL243X 160S/840 NE PSU NB BV WH	LL243X
910925870155	LL243X 160S/840 NE DIA NB BV WH	LL243X
910925870120	LL241X 53S/840 PSU NE WB 5x1.5 WH	LL241X
910925870121	LL241X 80S/840 HE PSU WB 5x1.5 WH	LL241X
910925870122	LL242X 80S/840 NE DIA WB 7x1.5 WH	LL242X
910925870123	LL242X 45S/840 UE DIA WB 7x1.5 WH	LL242X
910925870124	LL242X 45S/840 UE PSU WB 5x1.5 WH	LL242X
910925870125	LL242X 80S/840 UE DIA WB 7x1.5 WH	LL242X

Order Code	Full Product Name	Product family code
910925870126	LL242X 80S/840 HE PSU WB 5x1.5 WH	LL242X
910925870127	LL242X 120S/840 UE DIA WB 7x1.5 WH	LL242X
910925870128	LL242X 120S/840 UE PSU WB 5x1.5 WH	LL242X
910925870129	LL242X 120S/840 HE DIA O 7x1.5 WH	LL242X
910925870130	LL242X 120S/840 HE PSU O 5x1.5 WH	LL242X
910925870131	LL243X 160S/840 NE DIA WB 7x1.5 WH	LL243X
910925870132	LL243X 90S/840 UE DIA WB 7x1.5 WH	LL243X
910925870133	LL243X 90S/840 UE PSU WB 5x1.5 WH	LL243X
910925870134	LL243X 160S/840 UE DIA WB 7x1.5 WH	LL243X
910925870135	LL243X 160S/840 UE PSU WB 5x1.5 WH	LL243X
910925870136	LL243X 240S/840 UE DIA WB 7x1.5 WH	LL243X
910925870137	LL243X 240S/840 HE PSU WB 5x1.5 WH	LL243X
910925870138	LL243X 160S/840 UE DIA NB 7x1.5 WH	LL243X
910925870139	LL243X 160S/840 UE PSU NB 5x1.5 WH	LL243X
910925870140	LL243X 240S/840 UE DIA NB 7x1.5 WH	LL243X
910925870141	LL243X 240S/840 HE PSU NB 5x1.5 WH	LL243X


# CoreLine trunking gen2.5

Order Code	Full Product Name	Product family code	Order Code	Full Product Name	Product family code
910925870143	LL243X 160S/840 HE PSU O 5x1.5 WH	LL243X	910925870145	LL243X 240S/840 HE PSU O 5x1.5 WH	LL243X
910925870144	LL243X 240S/840 HE DIA O 7x1.5 WH	LL243X			


## Polar Wide Diagrams




Polar Normal (separate) - LL240XI - 910925870134




Polar Normal (separate) - LL240XI - 910925870138




Polar Normal (separate) - LL240XI - 910925870140




Polar Normal (separate) - LL240XI - 910925870144




Polar Normal (separate) - LL240XI - 910925870136




Polar Normal (separate) - LL240XI - 910925870129



Polar Normal (separate) - LL240XI - 910925870131




Polar Normal (separate) - LL240XI - 910925870132




Polar Normal (separate) - LL240XI - 910925870124

# CoreLine trunking gen2.5


## Polar Wide Diagrams




Polar Normal (separate) - LL240XI -  
910925870128




Polar Normal (separate) - LL240XI -  
910925870126




Polar Normal (separate) - LL240XI -  
910925870125




Polar Normal (separate) - LL240XI -  
910925870122




Polar Normal (separate) - LL240XI -  
910925870123




Polar Normal (separate) - LL240XI -  
910925870127



Polar Normal (separate) - LL240XI -  
910925870130




Polar Normal (separate) - LL240XI -  
910925870146




Polar Normal (separate) - LL240XI -  
910925870121

# CoreLine trunking gen2.5


## Polar Wide Diagrams




Polar Normal (separate) - LL240XI -  
910925870137




Polar Normal (separate) - LL240XI -  
910925870145




Polar Normal (separate) - LL240XI -  
910925870148




Polar Normal (separate) - LL240XI -  
910925870149




Polar Normal (separate) - LL240XI -  
910925870150




Polar Normal (separate) - LL240XI -  
910925870153



Polar Normal (separate) - LL240XI -  
910925870154




Polar Normal (separate) - LL240XI -  
910925870141




Polar Normal (separate) - LL240XI -  
910925870143

# CoreLine trunking gen2.5


## Polar Wide Diagrams




Polar Normal (separate) - LL240XI -  
910925870139




Polar Normal (separate) - LL240XI -  
910925870135




Polar Normal (separate) - LL240XI -  
910925870147




Polar Normal (separate) - LL240XI -  
910925870133




Polar Normal (separate) - LL240XI -  
910925870151



Polar Normal (separate) - LL240XI -  
910925870155



Polar Normal (separate) - LL240XI -  
910925870152



Polar Normal (separate) - LL240XI -  
910925870120

## CoreLine trunking gen2.5

