



Guaranteed performance, thinking ahead

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

Benefits

- Freedom of (re-)positioning enables you to direct the light where needed
- Family of fixtures to create the desired atmosphere; wide variety of beam shapes to suit diversity of applications
- With up to 13-wire track, emergency lighting and third-party hardware can be integrated to declutter ceilings

Applications

- (Food) retail
- Industrial halls/areas
- Warehouses/distribution centers

Features

- Track system inside the trunk with up to 13 wires
- High uniformity and artefact-free light distributions
- Linear fixtures, non-linear fixtures and spots can be easily installed onto the trunk
- Eight optics, including (double) asymmetric distributions and a frosted cover
- IP54 optional, silicone-free
- StoreWise, Indoor Positioning and GreenWarehouse-ready

Versions

Maxos Fusion Panel-LL512X
PCO WH



Maxos Fusion Panel-LL512X
WB WH



Maxos Fusion Panel-LL523X
WB WH



Maxos Fusion Panel-LL612X




Maxos Fusion Panel-LL623X




Maxos fusion panel 1,5m




Dimensional drawing




Maxos fusion Panel




LL512X LED80S/840 DIA WB 7 WH HE




LL523X LED123S/840 PSD DA35W 7 WH HE




LL523X LED62S/840 DIA O-PC 7 WH HE



LL612X LED61S/840 DIA MB 7 WH HE



LL623X LED123S/840 PSD WB 7 WH HE



MAXOS FUSION PANEL - 840 neutral white - Power supply unit with DALI interface - Medium beam - White

General Information

Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Color rendering index (CRI)	>80
Beam angle of light source	120 degree(s)

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Not applicable
Protection class IEC	Safety class I

Controls and Dimming

Dimmable	Yes
Maximum dim level	1%

Emergency Operation

Emergency flux	600 lm
Power consumption during Central DC emergency mode	3.7 W

Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
CE mark	Yes
ENEC mark	ENEC mark
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.34. 0.35) SDCM <3

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Optic type
910925870051	LL512X LED61S/840 PSD O-PC 7 VLC WH XA	5,200 lm	4000 K	151 lm/W	Opal
910925870052	LL523X LED123S/840 PSD O-PC 7 VLC WH XA	10,400 lm	4000 K	158 lm/W	Opal
910925870055	LL523X LED123S/840 SIA O-PC 7 WH HE	10,400 lm	4000 K	146 lm/W	Opal
910925870056	LL523X LED100S/840 SIA O-PC 7 WH HE	8,500 lm	4000 K	144 lm/W	Opal
910925870057	LL523X LED62S/840 SIA O-PC 7 WH HE	5,300 lm	4000 K	154 lm/W	Opal
910925870058	LL512X LED61S/840 SIA O-PC 7 WH HE	5,200 lm	4000 K	141 lm/W	Opal
910925870059	LL512X LED31S/840 SIA O-PC 7 WH HE	2,650 lm	4000 K	143 lm/W	Opal
910925870061	LL523X LED62S/840 DIA O-PC 7 WH HE	5,300 lm	4000 K	147 lm/W	Opal
910925870062	LL523X LED62S/840 DIA O-PC 13 ELP3 WH HE	5,300 lm	4000 K	147 lm/W	Opal
910925870063	LL523X LED100S/840 DIA O-PC 7 WH HE	8,500 lm	4000 K	144 lm/W	Opal
910925870064	LL523X LED123S/840 DIA O-PC 7 WH HE	10,400 lm	4000 K	149 lm/W	Opal
910925870065	LL512X LED31S/840 DIA O-PC 7 WH HE	2,650 lm	4000 K	143 lm/W	Opal
910925870066	LL512X LED50S/840 DIA O-PC 7 WH HE	4,250 lm	4000 K	142 lm/W	Opal
910925870067	LL512X LED61S/840 DIA O-PC 7 WH HE	5,200 lm	4000 K	141 lm/W	Opal
910925868139	LL512X LED31S/840 PSD WB-OC 7 WH XA	3,100 lm	4000 K	175 lm/W	Wide beam
910925868958	LL512X LED31S/840 PSD MB 7 WH HE	3,150 lm	4000 K	175 lm/W	Medium beam
910925868959	LL512X LED31S/840 PSD WB 7 WH HE	3,150 lm	4000 K	175 lm/W	Wide beam
910925868960	LL512X LED50S/840 PSD MB 7 WH HE	5,000 lm	4000 K	172 lm/W	Medium beam
910925868961	LL512X LED50S/840 PSD WB 7 WH HE	5,000 lm	4000 K	172 lm/W	Wide beam
910925868963	LL512X LED61S/840 PSD MB 7 WH HE	6,100 lm	4000 K	165 lm/W	Medium beam
910925868964	LL512X LED61S/840 PSD WB 7 WH HE	6,100 lm	4000 K	165 lm/W	Wide beam
910925868965	LL512X LED80S/840 PSD NB 7 WH HE	8,000 lm	4000 K	160 lm/W	Narrow beam
910925868966	LL512X LED80S/840 PSD MB 7 WH HE	8,000 lm	4000 K	160 lm/W	Medium beam
910925868981	LL512X LED61S/840 SIA MB 7 WH HE	6,100 lm	4000 K	165 lm/W	Medium beam
910925868982	LL512X LED61S/840 SIA WB 7 WH HE	6,100 lm	4000 K	165 lm/W	Wide beam

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Optic type
910925868984	LL512X LED80S/840 SIA MB 7 WH HE	8,000 lm	4000 K	160 lm/W	Medium beam
910925868986	LL512X LED31S/840 SIA WB 7 WH HE	3,150 lm	4000 K	175 lm/W	Wide beam
910925869743	LL512X LED80S/840 PSD WB 7 WH HE	8,000 lm	4000 K	160 lm/W	Wide beam
910925870173	LL512X LED31S/840 DIA WB 7 WH UE	3,150 lm	4000 K	194 lm/W	Wide beam
910925870174	LL512X LED50S/840 DIA WB 7 WH UE	5,050 lm	4000 K	192 lm/W	Wide beam
910925870175	LL512X LED61S/840 DIA WB 7 WH UE	6,150 lm	4000 K	191 lm/W	Wide beam
910925870176	LL512X LED80S/840 DIA WB 7 WH UE	8,000 lm	4000 K	195 lm/W	Wide beam
910925870773	LL512X LED31S/830 DIA WB 7 WH HE	3,100 lm	3000 K	175 lm/W	Wide beam
910925870775	LL512X LED31S/840 DEIA WB-OC 13 WH HE	3,100 lm	4000 K	175 lm/W	Wide beam
910925870777	LL512X LED50S/840 DIA DA35W 7 WH HE	5,000 lm	4000 K	172 lm/W	Double asymmetric optic 35° wide beam
910925870779	LL512X LED80S/840 DIA WB 7 WH HE	8,000 lm	4000 K	160 lm/W	Wide beam
910925870801	LL512X LED50S/840 PSD WB 7 BK HE	5,000 lm	4000 K	172 lm/W	Wide beam
910925870804	LL512X LED50S/840 PSED WB 7 WH HE	5,000 lm	4000 K	172 lm/W	Wide beam
910925870806	LL512X LED31S/840 PSD DA35W 7 WH HE	3,100 lm	4000 K	175 lm/W	Double asymmetric optic 35° wide beam
910925870807	LL512X LED31S/840 PSD WB 7 BK HE	3,100 lm	4000 K	175 lm/W	Wide beam
910925870808	LL512X LED61S/840 PSD WB 7 BK HE	6,100 lm	4000 K	165 lm/W	Wide beam
910925867812	LL523X LED123S/830 PSD DA45W 7 WH XA	12,300 lm	3000 K	172 lm/W	Double asymmetric optic 45°
910925867813	LL523X LED123S/840 PSD DA45W 7 WH XA	12,300 lm	4000 K	181 lm/W	Double asymmetric optic 45°
910925867816	LL523X LED123S/840 PSD WB 7 WH XA	12,300 lm	4000 K	181 lm/W	Wide beam
910925867820	LL523X LED160S/840 PSD MB 7 WH XA	16,000 lm	4000 K	176 lm/W	Medium beam
910925867839	LL523X LED160S/840 PSD MB 7 WH XA	16,000 lm	4000 K	176 lm/W	Medium beam
910925867854	LL523X LED123S/840 PSD NB 7 VLC WH XA	12,300 lm	4000 K	181 lm/W	Narrow beam
910925867855	LL523X LED160S/840 PSD NB 7 WH XA	16,000 lm	4000 K	176 lm/W	Narrow beam
910925868138	LL523X LED62S/840 PSD WB-OC 7 WH XA	6,200 lm	4000 K	185 lm/W	Wide beam
910925868949	LL523X LED62S/840 PSD MB 7 WH HE	6,200 lm	4000 K	180 lm/W	Medium beam
910925868950	LL523X LED62S/840 PSD WB 7 WH HE	6,200 lm	4000 K	180 lm/W	Wide beam
910925868951	LL523X LED100S/840 PSD MB 7 WH HE	10,100 lm	4000 K	177 lm/W	Medium beam
910925868952	LL523X LED100S/840 PSD WB 7 WH HE	10,100 lm	4000 K	177 lm/W	Wide beam
910925868953	LL523X LED123S/840 PSD NB 7 WH HE	12,300 lm	4000 K	171 lm/W	Narrow beam
910925868954	LL523X LED123S/840 PSD MB 7 WH HE	12,300 lm	4000 K	171 lm/W	Medium beam
910925868955	LL523X LED123S/840 PSD WB 7 WH HE	12,300 lm	4000 K	171 lm/W	Wide beam
910925868956	LL523X LED160S/840 PSD NB 7 WH HE	16,000 lm	4000 K	165 lm/W	Narrow beam
910925868957	LL523X LED160S/840 PSD MB 7 WH HE	16,000 lm	4000 K	165 lm/W	Medium beam
910925868967	LL523X LED100S/840 SIA MB 7 WH HE	10,100 lm	4000 K	177 lm/W	Medium beam
910925868968	LL523X LED100S/840 SIA WB 7 WH HE	10,100 lm	4000 K	177 lm/W	Wide beam
910925868969	LL523X LED123S/840 SIA NB 7 WH HE	12,300 lm	4000 K	171 lm/W	Narrow beam
910925868970	LL523X LED123S/840 SIA MB 7 WH HE	12,300 lm	4000 K	171 lm/W	Medium beam
910925868971	LL523X LED123S/840 SIA WB 7 WH HE	12,300 lm	4000 K	171 lm/W	Wide beam
910925868972	LL523X LED160S/840 SIA NB 7 WH HE	16,000 lm	4000 K	165 lm/W	Narrow beam
910925868973	LL523X LED160S/840 SIA MB 7 WH HE	16,000 lm	4000 K	165 lm/W	Medium beam

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Optic type
910925868974	LL523X LED62S/840 SIA WB 7 WH HE	6,200 lm	4000 K	180 lm/W	Wide beam
910925869742	LL523X LED160S/840 PSD WB 7 WH HE	16,000 lm	4000 K	165 lm/W	Wide beam
910925870169	LL523X LED62S/840 DIA WB 7 WH UE	6,136 lm	4000 K	200 lm/W	Wide beam
910925870170	LL523X LED100S/840 DIA WB 7 WH UE	10,100 lm	4000 K	194 lm/W	Wide beam
910925870171	LL523X LED123S/840 DIA WB 7 WH UE	12,300 lm	4000 K	195 lm/W	Wide beam
910925870172	LL523X LED160S/840 DIA WB 7 WH UE	16,000 lm	4000 K	195 lm/W	Wide beam
910925870371	LL523X LED62S/840 DIA MB 7 WH HE	6,200 lm	4000 K	180 lm/W	Medium beam
910925870372	LL523X LED62S/840 DIA WB 7 WH HE	6,200 lm	4000 K	180 lm/W	Wide beam
910925870373	LL523X LED100S/840 DIA MB 7 WH HE	10,100 lm	4000 K	177 lm/W	Medium beam
910925870374	LL523X LED123S/840 DIA MB 7 WH HE	12,300 lm	4000 K	171 lm/W	Medium beam
910925870375	LL523X LED100S/840 DIA WB 7 WH HE	10,100 lm	4000 K	177 lm/W	Wide beam
910925870376	LL523X LED123S/840 DIA NB 7 WH HE	12,300 lm	4000 K	171 lm/W	Narrow beam
910925870377	LL523X LED123S/840 DIA WB 7 WH HE	12,300 lm	4000 K	171 lm/W	Wide beam
910925870378	LL523X LED160S/840 DIA NB 7 WH HE	16,000 lm	4000 K	165 lm/W	Narrow beam
910925870379	LL523X LED160S/840 DIA MB 7 WH HE	16,000 lm	4000 K	165 lm/W	Medium beam
910925870380	LL512X LED31S/840 DIA MB 7 WH HE	3,150 lm	4000 K	175 lm/W	Medium beam
910925870381	LL512X LED31S/840 DIA WB 7 WH HE	3,150 lm	4000 K	175 lm/W	Wide beam
910925870382	LL512X LED50S/840 DIA MB 7 WH HE	5,000 lm	4000 K	172 lm/W	Medium beam
910925870383	LL512X LED50S/840 DIA WB 7 WH HE	5,000 lm	4000 K	172 lm/W	Wide beam
910925870384	LL512X LED61S/840 DIA NB 7 WH HE	6,100 lm	4000 K	165 lm/W	Narrow beam
910925870385	LL512X LED61S/840 DIA MB 7 WH HE	6,100 lm	4000 K	165 lm/W	Medium beam
910925870386	LL512X LED61S/840 DIA WB 7 WH HE	6,100 lm	4000 K	165 lm/W	Wide beam
910925870387	LL512X LED80S/840 DIA NB 7 WH HE	8,000 lm	4000 K	160 lm/W	Narrow beam
910925870388	LL512X LED80S/840 DIA MB 7 WH HE	8,000 lm	4000 K	160 lm/W	Medium beam
910925870756	LL523X LED62S/840 DEIA WB-OC 13 WH HE	6,200 lm	4000 K	180 lm/W	Wide beam
910925870758	LL523X LED62S/840 DIA DA25N 7 WH HE	6,200 lm	4000 K	180 lm/W	Double asymmetric optic 25° narrow beam
910925870759	LL523X LED62S/840 DIA DA25W 7 WH HE	6,200 lm	4000 K	180 lm/W	Double asymmetric optic 25° narrow beam
910925870760	LL523X LED62S/840 DIA DA35W 7 WH HE	6,200 lm	4000 K	180 lm/W	Double asymmetric optic 35° wide beam
910925870761	LL523X LED100S/840 DIA NB 7 WH HE	10,000 lm	4000 K	177 lm/W	Narrow beam
910925870763	LL523X LED100S/840 DIA A20 7 WH HE	10,000 lm	4000 K	177 lm/W	Asymmetrical mirror
910925870764	LL523X LED100S/840 DIA DA35W 7 WH HE	10,000 lm	4000 K	177 lm/W	Double asymmetric optic 35° wide beam
910925870766	LL523X LED123S/840 DIA A20 7 WH HE	12,300 lm	4000 K	171 lm/W	Asymmetrical mirror
910925870767	LL523X LED123S/840 DIA DA25W 7 WH HE	12,300 lm	4000 K	171 lm/W	Double asymmetric optic 25° narrow beam
910925870768	LL523X LED123S/840 DIA DA35W 7 WH HE	12,300 lm	4000 K	171 lm/W	Double asymmetric optic 35° wide beam
910925870769	LL523X LED160S/840 DIA WB 7 WH HE	16,000 lm	4000 K	165 lm/W	Wide beam
910925870796	LL523X LED123S/840 PSD A20 7 WH HE	12,300 lm	4000 K	171 lm/W	Asymmetrical mirror
910925870797	LL523X LED160S/840 PSD XNB 7 WH HE	16,000 lm	4000 K	165 lm/W	Extra narrow beam
910925870798	LL523X LED100S/840 PSD WB 7 SI HE	10,000 lm	4000 K	177 lm/W	Wide beam

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Optic type
910925870799	LL523X LED123S/840 PSD WB 7 BK HE	12,300 lm	4000 K	171 lm/W	Wide beam
910925870802	LL523X LED62S/840 PSD WB 7 SI HE	6,200 lm	4000 K	180 lm/W	Wide beam
910925870809	LL523X LED100S/840 PSD DA35W 7 WH HE	10,000 lm	4000 K	177 lm/W	Double asymmetric optic 35° wide beam
910925870810	LL523X LED100S/840 PSD WB 7 BK HE	10,000 lm	4000 K	177 lm/W	Wide beam
910925870811	LL523X LED123S/840 PSD DA35W 7 WH HE	12,300 lm	4000 K	171 lm/W	Double asymmetric optic 35° wide beam
910925870812	LL523X LED62S/840 PSD DA35W 7 WH HE	6,200 lm	4000 K	180 lm/W	Double asymmetric optic 35° wide beam
910925870819	LL523X LED123S/840 DIA WB 13 ELP3 WH HE	12,300 lm	4000 K	162 lm/W	Wide beam
910925870780	LL612X LED61S/840 DIA WB 7 WH HE	6,100 lm	4000 K	165 lm/W	Wide beam
910925870794	LL612X LED61S/840 DIA MB 7 WH HE	6,100 lm	4000 K	165 lm/W	Medium beam
910925870795	LL612X LED61S/840 DIA NB 7 WH HE	6,100 lm	4000 K	165 lm/W	Narrow beam
910925870803	LL612X LED61S/840 PSD NB 7 WH HE	6,100 lm	4000 K	165 lm/W	Narrow beam
910925870770	LL623X LED123S/840 DIA MB 7 WH HE	12,300 lm	4000 K	171 lm/W	Medium beam
910925870771	LL623X LED123S/840 DIA WB 7 WH HE	12,300 lm	4000 K	171 lm/W	Wide beam
910925870772	LL623X LED123S/840 DIA NB 7 WH HE	12,300 lm	4000 K	171 lm/W	Narrow beam
910925870805	LL623X LED123S/840 PSD WB 7 WH HE	12,300 lm	4000 K	171 lm/W	Wide beam
910925868648	LL515X 61S/840 PSD WB 7 HE WH	6,100 lm	4000 K	165 lm/W	Wide beam
910925868649	LL515X 80S/840 PSD WB 7 HE WH	8,000 lm	4000 K	160 lm/W	Wide beam
910925868651	LL515X 80S/840 PSD MB 7 HE WH	8,000 lm	4000 K	160 lm/W	Medium beam
910925868653	LL515X 80S/840 PSD NB 7 HE WH	8,000 lm	4000 K	160 lm/W	Narrow beam

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910925870051	LL512X LED61S/840 PSD O-PC 7 VLC WH XA	34.5 W
910925870052	LL523X LED123S/840 PSD O-PC 7 VLC WH XA	66 W
910925870055	LL523X LED123S/840 SIA O-PC 7 WH HE	71 W
910925870056	LL523X LED100S/840 SIA O-PC 7 WH HE	59 W
910925870057	LL523X LED62S/840 SIA O-PC 7 WH HE	34.5 W
910925870058	LL512X LED61S/840 SIA O-PC 7 WH HE	37 W
910925870059	LL512X LED31S/840 SIA O-PC 7 WH HE	18.5 W
910925870061	LL523X LED62S/840 DIA O-PC 7 WH HE	36 W
910925870062	LL523X LED62S/840 DIA O-PC 13 ELP3 WH HE	36 W
910925870063	LL523X LED100S/840 DIA O-PC 7 WH HE	59 W
910925870064	LL523X LED123S/840 DIA O-PC 7 WH HE	70 W
910925870065	LL512X LED31S/840 DIA O-PC 7 WH HE	18.5 W
910925870066	LL512X LED50S/840 DIA O-PC 7 WH HE	30 W
910925870067	LL512X LED61S/840 DIA O-PC 7 WH HE	37 W
910925868139	LL512X LED31S/840 PSD WB-OC 7 WH XA	18 W
910925868958	LL512X LED31S/840 PSD MB 7 WH HE	18 W
910925868959	LL512X LED31S/840 PSD WB 7 WH HE	18 W

Order Code	Full Product Name	Power Consumption
910925868960	LL512X LED50S/840 PSD MB 7 WH HE	29 W
910925868961	LL512X LED50S/840 PSD WB 7 WH HE	29 W
910925868963	LL512X LED61S/840 PSD MB 7 WH HE	37 W
910925868964	LL512X LED61S/840 PSD WB 7 WH HE	37 W
910925868965	LL512X LED80S/840 PSD NB 7 WH HE	50 W
910925868966	LL512X LED80S/840 PSD MB 7 WH HE	50 W
910925868981	LL512X LED61S/840 SIA MB 7 WH HE	37 W
910925868982	LL512X LED61S/840 SIA WB 7 WH HE	37 W
910925868984	LL512X LED80S/840 SIA MB 7 WH HE	50 W
910925868986	LL512X LED31S/840 SIA WB 7 WH HE	18 W
910925869743	LL512X LED80S/840 PSD WB 7 WH HE	50 W
910925870173	LL512X LED31S/840 DIA WB 7 WH UE	16 W
910925870174	LL512X LED50S/840 DIA WB 7 WH UE	26 W
910925870175	LL512X LED61S/840 DIA WB 7 WH UE	32 W
910925870176	LL512X LED80S/840 DIA WB 7 WH UE	41 W
910925870773	LL512X LED31S/830 DIA WB 7 WH HE	18 W
910925870775	LL512X LED31S/840 DEIA WB-OC 13 WH HE	18 W
910925870777	LL512X LED50S/840 DIA DA35W 7 WH HE	29 W
910925870779	LL512X LED80S/840 DIA WB 7 WH HE	50 W
910925870801	LL512X LED50S/840 PSD WB 7 BK HE	29 W
910925870804	LL512X LED50S/840 PSED WB 7 WH HE	29 W
910925870806	LL512X LED31S/840 PSD DA35W 7 WH HE	18 W
910925870807	LL512X LED31S/840 PSD WB 7 BK HE	18 W
910925870808	LL512X LED61S/840 PSD WB 7 BK HE	37 W
910925867812	LL523X LED123S/830 PSD DA45W 7 WH XA	68 W
910925867813	LL523X LED123S/840 PSD DA45W 7 WH XA	68 W
910925867816	LL523X LED123S/840 PSD WB 7 WH XA	68 W
910925867820	LL523X LED160S/840 PSD MB 7 WH XA	91 W
910925867839	LL523X LED160S/840 PSD MB 7 WH XA	91 W
910925867854	LL523X LED123S/840 PSD NB 7 VLC WH XA	68 W
910925867855	LL523X LED160S/840 PSD NB 7 WH XA	91 W
910925868138	LL523X LED62S/840 PSD WB-OC 7 WH XA	35 W
910925868949	LL523X LED62S/840 PSD MB 7 WH HE	34.5 W
910925868950	LL523X LED62S/840 PSD WB 7 WH HE	34.5 W
910925868951	LL523X LED100S/840 PSD MB 7 WH HE	57 W
910925868952	LL523X LED100S/840 PSD WB 7 WH HE	57 W
910925868953	LL523X LED123S/840 PSD NB 7 WH HE	72 W
910925868954	LL523X LED123S/840 PSD MB 7 WH HE	72 W
910925868955	LL523X LED123S/840 PSD WB 7 WH HE	72 W
910925868956	LL523X LED160S/840 PSD NB 7 WH HE	97 W
910925868957	LL523X LED160S/840 PSD MB 7 WH HE	97 W
910925868967	LL523X LED100S/840 SIA MB 7 WH HE	57 W

Order Code	Full Product Name	Power Consumption
910925868968	LL523X LED100S/840 SIA WB 7 WH HE	57 W
910925868969	LL523X LED123S/840 SIA NB 7 WH HE	72 W
910925868970	LL523X LED123S/840 SIA MB 7 WH HE	72 W
910925868971	LL523X LED123S/840 SIA WB 7 WH HE	72 W
910925868972	LL523X LED160S/840 SIA NB 7 WH HE	97 W
910925868973	LL523X LED160S/840 SIA MB 7 WH HE	97 W
910925868974	LL523X LED62S/840 SIA WB 7 WH HE	34.5 W
910925869742	LL523X LED160S/840 PSD WB 7 WH HE	97 W
910925870169	LL523X LED62S/840 DIA WB 7 WH UE	31 W
910925870170	LL523X LED100S/840 DIA WB 7 WH UE	51.5 W
910925870171	LL523X LED123S/840 DIA WB 7 WH UE	63 W
910925870172	LL523X LED160S/840 DIA WB 7 WH UE	82 W
910925870371	LL523X LED62S/840 DIA MB 7 WH HE	34.5 W
910925870372	LL523X LED62S/840 DIA WB 7 WH HE	34.5 W
910925870373	LL523X LED100S/840 DIA MB 7 WH HE	57 W
910925870374	LL523X LED123S/840 DIA MB 7 WH HE	72 W
910925870375	LL523X LED100S/840 DIA WB 7 WH HE	57 W
910925870376	LL523X LED123S/840 DIA NB 7 WH HE	72 W
910925870377	LL523X LED123S/840 DIA WB 7 WH HE	72 W
910925870378	LL523X LED160S/840 DIA NB 7 WH HE	97 W
910925870379	LL523X LED160S/840 DIA MB 7 WH HE	97 W
910925870380	LL512X LED31S/840 DIA MB 7 WH HE	18 W
910925870381	LL512X LED31S/840 DIA WB 7 WH HE	18 W
910925870382	LL512X LED50S/840 DIA MB 7 WH HE	29 W
910925870383	LL512X LED50S/840 DIA WB 7 WH HE	29 W
910925870384	LL512X LED61S/840 DIA NB 7 WH HE	37 W
910925870385	LL512X LED61S/840 DIA MB 7 WH HE	37 W
910925870386	LL512X LED61S/840 DIA WB 7 WH HE	37 W
910925870387	LL512X LED80S/840 DIA NB 7 WH HE	50 W
910925870388	LL512X LED80S/840 DIA MB 7 WH HE	50 W
910925870756	LL523X LED62S/840 DEIA WB-OC 13 WH HE	34.5 W
910925870758	LL523X LED62S/840 DIA DA25N 7 WH HE	34.5 W
910925870759	LL523X LED62S/840 DIA DA25W 7 WH HE	34.5 W
910925870760	LL523X LED62S/840 DIA DA35W 7 WH HE	34.5 W
910925870761	LL523X LED100S/840 DIA NB 7 WH HE	57 W
910925870763	LL523X LED100S/840 DIA A20 7 WH HE	57 W
910925870764	LL523X LED100S/840 DIA DA35W 7 WH HE	57 W
910925870766	LL523X LED123S/840 DIA A20 7 WH HE	72 W
910925870767	LL523X LED123S/840 DIA DA25W 7 WH HE	72 W
910925870768	LL523X LED123S/840 DIA DA35W 7 WH HE	72 W
910925870769	LL523X LED160S/840 DIA WB 7 WH HE	97 W
910925870796	LL523X LED123S/840 PSD A20 7 WH HE	72 W

Order Code	Full Product Name	Power Consumption
910925870797	LL523X LED160S/840 PSD XNB 7 WH HE	97 W
910925870798	LL523X LED100S/840 PSD WB 7 SI HE	57 W
910925870799	LL523X LED123S/840 PSD WB 7 BK HE	72 W
910925870802	LL523X LED62S/840 PSD WB 7 SI HE	34.5 W
910925870809	LL523X LED100S/840 PSD DA35W 7 WH HE	57 W
910925870810	LL523X LED100S/840 PSD WB 7 BK HE	57 W
910925870811	LL523X LED123S/840 PSD DA35W 7 WH HE	72 W
910925870812	LL523X LED62S/840 PSD DA35W 7 WH HE	34.5 W
910925870819	LL523X LED123S/840 DIA WB 13 ELP3 WH HE	76 W
910925870780	LL612X LED61S/840 DIA WB 7 WH HE	37 W
910925870794	LL612X LED61S/840 DIA MB 7 WH HE	37 W
910925870795	LL612X LED61S/840 DIA NB 7 WH HE	37 W
910925870803	LL612X LED61S/840 PSD NB 7 WH HE	37 W
910925870770	LL623X LED123S/840 DIA MB 7 WH HE	72 W
910925870771	LL623X LED123S/840 DIA WB 7 WH HE	72 W
910925870772	LL623X LED123S/840 DIA NB 7 WH HE	72 W
910925870805	LL623X LED123S/840 PSD WB 7 WH HE	72 W
910925868648	LL515X 61S/840 PSD WB 7 HE WH	37 W
910925868649	LL515X 80S/840 PSD WB 7 HE WH	50 W
910925868651	LL515X 80S/840 PSD MB 7 HE WH	50 W
910925868653	LL515X 80S/840 PSD NB 7 HE WH	50 W

Controls and Dimming

Order Code	Full Product Name	Embedded control
910925870051	LL512X LED61S/840 PSD O-PC 7 VLC WH XA	Visible light communication
910925870052	LL523X LED123S/840 PSD O-PC 7 VLC WH XA	Visible light communication
910925870055	LL523X LED123S/840 SIA O-PC 7 WH HE	-
910925870056	LL523X LED100S/840 SIA O-PC 7 WH HE	-
910925870057	LL523X LED62S/840 SIA O-PC 7 WH HE	-
910925870058	LL512X LED61S/840 SIA O-PC 7 WH HE	-
910925870059	LL512X LED31S/840 SIA O-PC 7 WH HE	-
910925870061	LL523X LED62S/840 DIA O-PC 7 WH HE	-
910925870062	LL523X LED62S/840 DIA O-PC 13 ELP3 WH HE	-
910925870063	LL523X LED100S/840 DIA O-PC 7 WH HE	-
910925870064	LL523X LED123S/840 DIA O-PC 7 WH HE	-
910925870065	LL512X LED31S/840 DIA O-PC 7 WH HE	-
910925870066	LL512X LED50S/840 DIA O-PC 7 WH HE	-
910925870067	LL512X LED61S/840 DIA O-PC 7 WH HE	-
910925868139	LL512X LED31S/840 PSD WB-OC 7 WH XA	-
910925868958	LL512X LED31S/840 PSD MB 7 WH HE	-
910925868959	LL512X LED31S/840 PSD WB 7 WH HE	-

Order Code	Full Product Name	Embedded control
910925868960	LL512X LED50S/840 PSD MB 7 WH HE	-
910925868961	LL512X LED50S/840 PSD WB 7 WH HE	-
910925868963	LL512X LED61S/840 PSD MB 7 WH HE	-
910925868964	LL512X LED61S/840 PSD WB 7 WH HE	-
910925868965	LL512X LED80S/840 PSD NB 7 WH HE	-
910925868966	LL512X LED80S/840 PSD MB 7 WH HE	-
910925868981	LL512X LED61S/840 SIA MB 7 WH HE	-
910925868982	LL512X LED61S/840 SIA WB 7 WH HE	-
910925868984	LL512X LED80S/840 SIA MB 7 WH HE	-
910925868986	LL512X LED31S/840 SIA WB 7 WH HE	-
910925869743	LL512X LED80S/840 PSD WB 7 WH HE	-
910925870173	LL512X LED31S/840 DIA WB 7 WH UE	-
910925870174	LL512X LED50S/840 DIA WB 7 WH UE	-
910925870175	LL512X LED61S/840 DIA WB 7 WH UE	-
910925870176	LL512X LED80S/840 DIA WB 7 WH UE	-
910925870773	LL512X LED31S/830 DIA WB 7 WH HE	-
910925870775	LL512X LED31S/840 DEIA WB-OC 13 WH HE	-
910925870777	LL512X LED50S/840 DIA DA35W 7 WH HE	-
910925870779	LL512X LED80S/840 DIA WB 7 WH HE	-
910925870801	LL512X LED50S/840 PSD WB 7 BK HE	-
910925870804	LL512X LED50S/840 PSED WB 7 WH HE	-
910925870806	LL512X LED31S/840 PSD DA35W 7 WH HE	-
910925870807	LL512X LED31S/840 PSD WB 7 BK HE	-
910925870808	LL512X LED61S/840 PSD WB 7 BK HE	-
910925867812	LL523X LED123S/830 PSD DA45W 7 WH XA	-
910925867813	LL523X LED123S/840 PSD DA45W 7 WH XA	-
910925867816	LL523X LED123S/840 PSD WB 7 WH XA	-
910925867820	LL523X LED160S/840 PSD MB 7 WH XA	-
910925867839	LL523X LED160S/840 PSD MB 7 WH XA	-
910925867854	LL523X LED123S/840 PSD NB 7 VLC WH XA	Visible light communication
910925867855	LL523X LED160S/840 PSD NB 7 WH XA	-
910925868138	LL523X LED62S/840 PSD WB-OC 7 WH XA	-
910925868949	LL523X LED62S/840 PSD MB 7 WH HE	-
910925868950	LL523X LED62S/840 PSD WB 7 WH HE	-
910925868951	LL523X LED100S/840 PSD MB 7 WH HE	-
910925868952	LL523X LED100S/840 PSD WB 7 WH HE	-
910925868953	LL523X LED123S/840 PSD NB 7 WH HE	-
910925868954	LL523X LED123S/840 PSD MB 7 WH HE	-
910925868955	LL523X LED123S/840 PSD WB 7 WH HE	-
910925868956	LL523X LED160S/840 PSD NB 7 WH HE	-
910925868957	LL523X LED160S/840 PSD MB 7 WH HE	-
910925868967	LL523X LED100S/840 SIA MB 7 WH HE	-

Order Code	Full Product Name	Embedded control
910925868968	LL523X LED100S/840 SIA WB 7 WH HE	-
910925868969	LL523X LED123S/840 SIA NB 7 WH HE	-
910925868970	LL523X LED123S/840 SIA MB 7 WH HE	-
910925868971	LL523X LED123S/840 SIA WB 7 WH HE	-
910925868972	LL523X LED160S/840 SIA NB 7 WH HE	-
910925868973	LL523X LED160S/840 SIA MB 7 WH HE	-
910925868974	LL523X LED62S/840 SIA WB 7 WH HE	-
910925869742	LL523X LED160S/840 PSD WB 7 WH HE	-
910925870169	LL523X LED62S/840 DIA WB 7 WH UE	-
910925870170	LL523X LED100S/840 DIA WB 7 WH UE	-
910925870171	LL523X LED123S/840 DIA WB 7 WH UE	-
910925870172	LL523X LED160S/840 DIA WB 7 WH UE	-
910925870371	LL523X LED62S/840 DIA MB 7 WH HE	-
910925870372	LL523X LED62S/840 DIA WB 7 WH HE	-
910925870373	LL523X LED100S/840 DIA MB 7 WH HE	-
910925870374	LL523X LED123S/840 DIA MB 7 WH HE	-
910925870375	LL523X LED100S/840 DIA WB 7 WH HE	-
910925870376	LL523X LED123S/840 DIA NB 7 WH HE	-
910925870377	LL523X LED123S/840 DIA WB 7 WH HE	-
910925870378	LL523X LED160S/840 DIA NB 7 WH HE	-
910925870379	LL523X LED160S/840 DIA MB 7 WH HE	-
910925870380	LL512X LED31S/840 DIA MB 7 WH HE	-
910925870381	LL512X LED31S/840 DIA WB 7 WH HE	-
910925870382	LL512X LED50S/840 DIA MB 7 WH HE	-
910925870383	LL512X LED50S/840 DIA WB 7 WH HE	-
910925870384	LL512X LED61S/840 DIA NB 7 WH HE	-
910925870385	LL512X LED61S/840 DIA MB 7 WH HE	-
910925870386	LL512X LED61S/840 DIA WB 7 WH HE	-
910925870387	LL512X LED80S/840 DIA NB 7 WH HE	-
910925870388	LL512X LED80S/840 DIA MB 7 WH HE	-
910925870756	LL523X LED62S/840 DEIA WB-OC 13 WH HE	-
910925870758	LL523X LED62S/840 DIA DA25N 7 WH HE	-
910925870759	LL523X LED62S/840 DIA DA25W 7 WH HE	-
910925870760	LL523X LED62S/840 DIA DA35W 7 WH HE	-
910925870761	LL523X LED100S/840 DIA NB 7 WH HE	-
910925870763	LL523X LED100S/840 DIA A20 7 WH HE	-
910925870764	LL523X LED100S/840 DIA DA35W 7 WH HE	-
910925870766	LL523X LED123S/840 DIA A20 7 WH HE	-
910925870767	LL523X LED123S/840 DIA DA25W 7 WH HE	-
910925870768	LL523X LED123S/840 DIA DA35W 7 WH HE	-
910925870769	LL523X LED160S/840 DIA WB 7 WH HE	-
910925870796	LL523X LED123S/840 PSD A20 7 WH HE	-

Order Code	Full Product Name	Embedded control
910925870797	LL523X LED160S/840 PSD XNB 7 WH HE	-
910925870798	LL523X LED100S/840 PSD WB 7 SI HE	-
910925870799	LL523X LED123S/840 PSD WB 7 BK HE	-
910925870802	LL523X LED62S/840 PSD WB 7 SI HE	-
910925870809	LL523X LED100S/840 PSD DA35W 7 WH HE	-
910925870810	LL523X LED100S/840 PSD WB 7 BK HE	-
910925870811	LL523X LED123S/840 PSD DA35W 7 WH HE	-
910925870812	LL523X LED62S/840 PSD DA35W 7 WH HE	-
910925870819	LL523X LED123S/840 DIA WB 13 ELP3 WH HE	-
910925870780	LL612X LED61S/840 DIA WB 7 WH HE	-
910925870794	LL612X LED61S/840 DIA MB 7 WH HE	-
910925870795	LL612X LED61S/840 DIA NB 7 WH HE	-
910925870803	LL612X LED61S/840 PSD NB 7 WH HE	-
910925870770	LL623X LED123S/840 DIA MB 7 WH HE	-
910925870771	LL623X LED123S/840 DIA WB 7 WH HE	-
910925870772	LL623X LED123S/840 DIA NB 7 WH HE	-
910925870805	LL623X LED123S/840 PSD WB 7 WH HE	-
910925868648	LL515X 61S/840 PSD WB 7 HE WH	-
910925868649	LL515X 80S/840 PSD WB 7 HE WH	-
910925868651	LL515X 80S/840 PSD MB 7 HE WH	-
910925868653	LL515X 80S/840 PSD NB 7 HE WH	-

Mechanical and Housing

Order Code	Full Product Name	Housing Color	Ingress protection code	Mech. impact protection code
910925870051	LL512X LED61S/840 PSD O-PC 7 VLC WH XA	White	IP20	IK02
910925870052	LL523X LED123S/840 PSD O-PC 7 VLC WH XA	White	IP20	IK02
910925870055	LL523X LED123S/840 SIA O-PC 7 WH HE	White	IP20	IK02
910925870056	LL523X LED100S/840 SIA O-PC 7 WH HE	White	IP20	IK02
910925870057	LL523X LED62S/840 SIA O-PC 7 WH HE	White	IP20	IK02
910925870058	LL512X LED61S/840 SIA O-PC 7 WH HE	White	IP20	IK02
910925870059	LL512X LED31S/840 SIA O-PC 7 WH HE	White	IP20	IK02
910925870061	LL523X LED62S/840 DIA O-PC 7 WH HE	White	IP20	IK02
910925870062	LL523X LED62S/840 DIA O-PC 13 ELP3 WH HE	White	IP20	IK02
910925870063	LL523X LED100S/840 DIA O-PC 7 WH HE	White	IP20	IK02
910925870064	LL523X LED123S/840 DIA O-PC 7 WH HE	White	IP20	IK02
910925870065	LL512X LED31S/840 DIA O-PC 7 WH HE	White	IP20	IK02
910925870066	LL512X LED50S/840 DIA O-PC 7 WH HE	White	IP20	IK02
910925870067	LL512X LED61S/840 DIA O-PC 7 WH HE	White	IP20	IK02
910925868139	LL512X LED31S/840 PSD WB-OC 7 WH XA	White	IP20	IK02
910925868958	LL512X LED31S/840 PSD MB 7 WH HE	White	IP20	IK02
910925868959	LL512X LED31S/840 PSD WB 7 WH HE	White	IP20	IK02

Order Code	Full Product Name	Housing Color	Ingress protection code	Mech. impact protection code
910925868960	LL512X LED50S/840 PSD MB 7 WH HE	White	IP20	IK02
910925868961	LL512X LED50S/840 PSD WB 7 WH HE	White	IP20	IK02
910925868963	LL512X LED61S/840 PSD MB 7 WH HE	White	IP20	IK02
910925868964	LL512X LED61S/840 PSD WB 7 WH HE	White	IP20	IK02
910925868965	LL512X LED80S/840 PSD NB 7 WH HE	White	IP20	IK02
910925868966	LL512X LED80S/840 PSD MB 7 WH HE	White	IP20	IK02
910925868981	LL512X LED61S/840 SIA MB 7 WH HE	White	IP20	IK02
910925868982	LL512X LED61S/840 SIA WB 7 WH HE	White	IP20	IK02
910925868984	LL512X LED80S/840 SIA MB 7 WH HE	White	IP20	IK02
910925868986	LL512X LED31S/840 SIA WB 7 WH HE	White	IP20	IK02
910925869743	LL512X LED80S/840 PSD WB 7 WH HE	White	IP20	IK02
910925870173	LL512X LED31S/840 DIA WB 7 WH UE	White	IP20	IK02
910925870174	LL512X LED50S/840 DIA WB 7 WH UE	White	IP20	IK02
910925870175	LL512X LED61S/840 DIA WB 7 WH UE	White	IP20	IK02
910925870176	LL512X LED80S/840 DIA WB 7 WH UE	White	IP20	IK02
910925870773	LL512X LED31S/830 DIA WB 7 WH HE	White	IP20	IK02
910925870775	LL512X LED31S/840 DEIA WB-OC 13 WH HE	White	IP20	IK02
910925870777	LL512X LED50S/840 DIA DA35W 7 WH HE	White	IP20	IK02
910925870779	LL512X LED80S/840 DIA WB 7 WH HE	White	IP20	IK02
910925870801	LL512X LED50S/840 PSD WB 7 BK HE	Black	IP20	IK02
910925870804	LL512X LED50S/840 PSED WB 7 WH HE	White	IP20	IK02
910925870806	LL512X LED31S/840 PSD DA35W 7 WH HE	White	IP20	IK02
910925870807	LL512X LED31S/840 PSD WB 7 BK HE	Black	IP20	IK02
910925870808	LL512X LED61S/840 PSD WB 7 BK HE	Black	IP20	IK02
910925867812	LL523X LED123S/830 PSD DA45W 7 WH XA	White	IP20	IK02
910925867813	LL523X LED123S/840 PSD DA45W 7 WH XA	White	IP20	IK02
910925867816	LL523X LED123S/840 PSD WB 7 WH XA	White	IP20	IK02
910925867820	LL523X LED160S/840 PSD MB 7 WH XA	White	IP20	IK02
910925867839	LL523X LED160S/840 PSD MB 7 WH XA	White	IP20	IK02
910925867854	LL523X LED123S/840 PSD NB 7 VLC WH XA	White	IP20	IK02
910925867855	LL523X LED160S/840 PSD NB 7 WH XA	White	IP20	IK02
910925868138	LL523X LED62S/840 PSD WB-OC 7 WH XA	White	IP20	IK02
910925868949	LL523X LED62S/840 PSD MB 7 WH HE	White	IP20	IK02
910925868950	LL523X LED62S/840 PSD WB 7 WH HE	White	IP20	IK02
910925868951	LL523X LED100S/840 PSD MB 7 WH HE	White	IP20	IK02
910925868952	LL523X LED100S/840 PSD WB 7 WH HE	White	IP20	IK02
910925868953	LL523X LED123S/840 PSD NB 7 WH HE	White	IP20	IK02
910925868954	LL523X LED123S/840 PSD MB 7 WH HE	White	IP20	IK02
910925868955	LL523X LED123S/840 PSD WB 7 WH HE	White	IP20	IK02
910925868956	LL523X LED160S/840 PSD NB 7 WH HE	White	IP20	IK02
910925868957	LL523X LED160S/840 PSD MB 7 WH HE	White	IP20	IK02
910925868967	LL523X LED100S/840 SIA MB 7 WH HE	White	IP20	IK02

Order Code	Full Product Name	Housing Color	Ingress protection code	Mech. impact protection code
910925868968	LL523X LED100S/840 SIA WB 7 WH HE	White	IP20	IK02
910925868969	LL523X LED123S/840 SIA NB 7 WH HE	White	IP20	IK02
910925868970	LL523X LED123S/840 SIA MB 7 WH HE	White	IP20	IK02
910925868971	LL523X LED123S/840 SIA WB 7 WH HE	White	IP20	IK02
910925868972	LL523X LED160S/840 SIA NB 7 WH HE	White	IP20	IK02
910925868973	LL523X LED160S/840 SIA MB 7 WH HE	White	IP20	IK02
910925868974	LL523X LED62S/840 SIA WB 7 WH HE	White	IP20	IK02
910925869742	LL523X LED160S/840 PSD WB 7 WH HE	White	IP20	IK02
910925870169	LL523X LED62S/840 DIA WB 7 WH UE	White	IP20	IK02
910925870170	LL523X LED100S/840 DIA WB 7 WH UE	White	IP20	IK02
910925870171	LL523X LED123S/840 DIA WB 7 WH UE	White	IP20	IK02
910925870172	LL523X LED160S/840 DIA WB 7 WH UE	White	IP20	IK02
910925870371	LL523X LED62S/840 DIA MB 7 WH HE	White	IP20	IK02
910925870372	LL523X LED62S/840 DIA WB 7 WH HE	White	IP20	IK02
910925870373	LL523X LED100S/840 DIA MB 7 WH HE	White	IP20	IK02
910925870374	LL523X LED123S/840 DIA MB 7 WH HE	White	IP20	IK02
910925870375	LL523X LED100S/840 DIA WB 7 WH HE	White	IP20	IK02
910925870376	LL523X LED123S/840 DIA NB 7 WH HE	White	IP20	IK02
910925870377	LL523X LED123S/840 DIA WB 7 WH HE	White	IP20	IK02
910925870378	LL523X LED160S/840 DIA NB 7 WH HE	White	IP20	IK02
910925870379	LL523X LED160S/840 DIA MB 7 WH HE	White	IP20	IK02
910925870380	LL512X LED31S/840 DIA MB 7 WH HE	White	IP20	IK02
910925870381	LL512X LED31S/840 DIA WB 7 WH HE	White	IP20	IK02
910925870382	LL512X LED50S/840 DIA MB 7 WH HE	White	IP20	IK02
910925870383	LL512X LED50S/840 DIA WB 7 WH HE	White	IP20	IK02
910925870384	LL512X LED61S/840 DIA NB 7 WH HE	White	IP20	IK02
910925870385	LL512X LED61S/840 DIA MB 7 WH HE	White	IP20	IK02
910925870386	LL512X LED61S/840 DIA WB 7 WH HE	White	IP20	IK02
910925870387	LL512X LED80S/840 DIA NB 7 WH HE	White	IP20	IK02
910925870388	LL512X LED80S/840 DIA MB 7 WH HE	White	IP20	IK02
910925870756	LL523X LED62S/840 DEIA WB-OC 13 WH HE	White	IP20	IK02
910925870758	LL523X LED62S/840 DIA DA25N 7 WH HE	White	IP20	IK02
910925870759	LL523X LED62S/840 DIA DA25W 7 WH HE	White	IP20	IK02
910925870760	LL523X LED62S/840 DIA DA35W 7 WH HE	White	IP20	IK02
910925870761	LL523X LED100S/840 DIA NB 7 WH HE	White	IP20	IK02
910925870763	LL523X LED100S/840 DIA A20 7 WH HE	White	IP20	IK02
910925870764	LL523X LED100S/840 DIA DA35W 7 WH HE	White	IP20	IK02
910925870766	LL523X LED123S/840 DIA A20 7 WH HE	White	IP20	IK02
910925870767	LL523X LED123S/840 DIA DA25W 7 WH HE	White	IP20	IK02
910925870768	LL523X LED123S/840 DIA DA35W 7 WH HE	White	IP20	IK02
910925870769	LL523X LED160S/840 DIA WB 7 WH HE	White	IP20	IK02
910925870796	LL523X LED123S/840 PSD A20 7 WH HE	White	IP20	IK02

Order Code	Full Product Name	Housing Color	Ingress protection code	Mech. impact protection code
910925870797	LL523X LED160S/840 PSD XNB 7 WH HE	White	IP20	IK02
910925870798	LL523X LED100S/840 PSD WB 7 SI HE	Silver	IP20	IK02
910925870799	LL523X LED123S/840 PSD WB 7 BK HE	Black	IP20	IK02
910925870802	LL523X LED62S/840 PSD WB 7 SI HE	Silver	IP20	IK02
910925870809	LL523X LED100S/840 PSD DA35W 7 WH HE	White	IP20	IK02
910925870810	LL523X LED100S/840 PSD WB 7 BK HE	Black	IP20	IK02
910925870811	LL523X LED123S/840 PSD DA35W 7 WH HE	White	IP20	IK02
910925870812	LL523X LED62S/840 PSD DA35W 7 WH HE	White	IP20	IK02
910925870819	LL523X LED123S/840 DIA WB 13 ELP3 WH HE	White	IP20	IK03
910925870780	LL612X LED61S/840 DIA WB 7 WH HE	White	IP54	IK02
910925870794	LL612X LED61S/840 DIA MB 7 WH HE	White	IP54	IK02
910925870795	LL612X LED61S/840 DIA NB 7 WH HE	White	IP54	IK02
910925870803	LL612X LED61S/840 PSD NB 7 WH HE	White	IP54	IK02
910925870770	LL623X LED123S/840 DIA MB 7 WH HE	White	IP54	IK02
910925870771	LL623X LED123S/840 DIA WB 7 WH HE	White	IP54	IK02
910925870772	LL623X LED123S/840 DIA NB 7 WH HE	White	IP54	IK02
910925870805	LL623X LED123S/840 PSD WB 7 WH HE	White	IP54	IK02
910925868648	LL515X 61S/840 PSD WB 7 HE WH	White	IP20	IK02
910925868649	LL515X 80S/840 PSD WB 7 HE WH	White	IP20	IK02
910925868651	LL515X 80S/840 PSD MB 7 HE WH	White	IP20	IK02
910925868653	LL515X 80S/840 PSD NB 7 HE WH	White	IP20	IK02

Emergency Operation

Order Code	Full Product Name	Central Emergency	Emergency lighting
910925870051	LL512X LED61S/840 PSD O-PC 7 VLC WH XA	-	-
910925870052	LL523X LED123S/840 PSD O-PC 7 VLC WH XA	-	-
910925870055	LL523X LED123S/840 SIA O-PC 7 WH HE	-	-
910925870056	LL523X LED100S/840 SIA O-PC 7 WH HE	-	-
910925870057	LL523X LED62S/840 SIA O-PC 7 WH HE	-	-
910925870058	LL512X LED61S/840 SIA O-PC 7 WH HE	-	-
910925870059	LL512X LED31S/840 SIA O-PC 7 WH HE	-	-
910925870061	LL523X LED62S/840 DIA O-PC 7 WH HE	-	-
910925870062	LL523X LED62S/840 DIA O-PC 13 ELP3 WH HE	-	Emergency lighting 3 hours duration Pro version
910925870063	LL523X LED100S/840 DIA O-PC 7 WH HE	-	-
910925870064	LL523X LED123S/840 DIA O-PC 7 WH HE	-	-
910925870065	LL512X LED31S/840 DIA O-PC 7 WH HE	-	-
910925870066	LL512X LED50S/840 DIA O-PC 7 WH HE	-	-
910925870067	LL512X LED61S/840 DIA O-PC 7 WH HE	-	-
910925868139	LL512X LED31S/840 PSD WB-OC 7 WH XA	-	-
910925868958	LL512X LED31S/840 PSD MB 7 WH HE	-	-
910925868959	LL512X LED31S/840 PSD WB 7 WH HE	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting
910925868960	LL512X LED50S/840 PSD MB 7 WH HE	-	-
910925868961	LL512X LED50S/840 PSD WB 7 WH HE	-	-
910925868963	LL512X LED61S/840 PSD MB 7 WH HE	-	-
910925868964	LL512X LED61S/840 PSD WB 7 WH HE	-	-
910925868965	LL512X LED80S/840 PSD NB 7 WH HE	-	-
910925868966	LL512X LED80S/840 PSD MB 7 WH HE	-	-
910925868981	LL512X LED61S/840 SIA MB 7 WH HE	-	-
910925868982	LL512X LED61S/840 SIA WB 7 WH HE	-	-
910925868984	LL512X LED80S/840 SIA MB 7 WH HE	-	-
910925868986	LL512X LED31S/840 SIA WB 7 WH HE	-	-
910925869743	LL512X LED80S/840 PSD WB 7 WH HE	-	-
910925870173	LL512X LED31S/840 DIA WB 7 WH UE	No	-
910925870174	LL512X LED50S/840 DIA WB 7 WH UE	No	-
910925870175	LL512X LED61S/840 DIA WB 7 WH UE	No	-
910925870176	LL512X LED80S/840 DIA WB 7 WH UE	No	-
910925870773	LL512X LED31S/830 DIA WB 7 WH HE	No	-
910925870775	LL512X LED31S/840 DEIA WB-OC 13 WH HE	Yes	DC operated central emergency lighting
910925870777	LL512X LED50S/840 DIA DA35W 7 WH HE	No	-
910925870779	LL512X LED80S/840 DIA WB 7 WH HE	No	-
910925870801	LL512X LED50S/840 PSD WB 7 BK HE	-	-
910925870804	LL512X LED50S/840 PSED WB 7 WH HE	Yes	DC operated central emergency lighting
910925870806	LL512X LED31S/840 PSD DA35W 7 WH HE	-	-
910925870807	LL512X LED31S/840 PSD WB 7 BK HE	-	-
910925870808	LL512X LED61S/840 PSD WB 7 BK HE	-	-
910925867812	LL523X LED123S/830 PSD DA45W 7 WH XA	-	-
910925867813	LL523X LED123S/840 PSD DA45W 7 WH XA	-	-
910925867816	LL523X LED123S/840 PSD WB 7 WH XA	-	-
910925867820	LL523X LED160S/840 PSD MB 7 WH XA	-	-
910925867839	LL523X LED160S/840 PSD MB 7 WH XA	-	-
910925867854	LL523X LED123S/840 PSD NB 7 VLC WH XA	-	-
910925867855	LL523X LED160S/840 PSD NB 7 WH XA	-	-
910925868138	LL523X LED62S/840 PSD WB-OC 7 WH XA	-	-
910925868949	LL523X LED62S/840 PSD MB 7 WH HE	-	-
910925868950	LL523X LED62S/840 PSD WB 7 WH HE	-	-
910925868951	LL523X LED100S/840 PSD MB 7 WH HE	-	-
910925868952	LL523X LED100S/840 PSD WB 7 WH HE	-	-
910925868953	LL523X LED123S/840 PSD NB 7 WH HE	-	-
910925868954	LL523X LED123S/840 PSD MB 7 WH HE	-	-
910925868955	LL523X LED123S/840 PSD WB 7 WH HE	-	-
910925868956	LL523X LED160S/840 PSD NB 7 WH HE	-	-
910925868957	LL523X LED160S/840 PSD MB 7 WH HE	-	-
910925868967	LL523X LED100S/840 SIA MB 7 WH HE	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting
910925868968	LL523X LED100S/840 SIA WB 7 WH HE	-	-
910925868969	LL523X LED123S/840 SIA NB 7 WH HE	-	-
910925868970	LL523X LED123S/840 SIA MB 7 WH HE	-	-
910925868971	LL523X LED123S/840 SIA WB 7 WH HE	-	-
910925868972	LL523X LED160S/840 SIA NB 7 WH HE	-	-
910925868973	LL523X LED160S/840 SIA MB 7 WH HE	-	-
910925868974	LL523X LED62S/840 SIA WB 7 WH HE	-	-
910925869742	LL523X LED160S/840 PSD WB 7 WH HE	-	-
910925870169	LL523X LED62S/840 DIA WB 7 WH UE	No	-
910925870170	LL523X LED100S/840 DIA WB 7 WH UE	No	-
910925870171	LL523X LED123S/840 DIA WB 7 WH UE	No	-
910925870172	LL523X LED160S/840 DIA WB 7 WH UE	No	-
910925870371	LL523X LED62S/840 DIA MB 7 WH HE	No	-
910925870372	LL523X LED62S/840 DIA WB 7 WH HE	No	-
910925870373	LL523X LED100S/840 DIA MB 7 WH HE	No	-
910925870374	LL523X LED123S/840 DIA MB 7 WH HE	No	-
910925870375	LL523X LED100S/840 DIA WB 7 WH HE	No	-
910925870376	LL523X LED123S/840 DIA NB 7 WH HE	No	-
910925870377	LL523X LED123S/840 DIA WB 7 WH HE	No	-
910925870378	LL523X LED160S/840 DIA NB 7 WH HE	No	-
910925870379	LL523X LED160S/840 DIA MB 7 WH HE	No	-
910925870380	LL512X LED31S/840 DIA MB 7 WH HE	No	-
910925870381	LL512X LED31S/840 DIA WB 7 WH HE	No	-
910925870382	LL512X LED50S/840 DIA MB 7 WH HE	No	-
910925870383	LL512X LED50S/840 DIA WB 7 WH HE	No	-
910925870384	LL512X LED61S/840 DIA NB 7 WH HE	No	-
910925870385	LL512X LED61S/840 DIA MB 7 WH HE	No	-
910925870386	LL512X LED61S/840 DIA WB 7 WH HE	No	-
910925870387	LL512X LED80S/840 DIA NB 7 WH HE	No	-
910925870388	LL512X LED80S/840 DIA MB 7 WH HE	No	-
910925870756	LL523X LED62S/840 DEIA WB-OC 13 WH HE	Yes	DC operated central emergency lighting
910925870758	LL523X LED62S/840 DIA DA25N 7 WH HE	No	-
910925870759	LL523X LED62S/840 DIA DA25W 7 WH HE	No	-
910925870760	LL523X LED62S/840 DIA DA35W 7 WH HE	No	-
910925870761	LL523X LED100S/840 DIA NB 7 WH HE	No	-
910925870763	LL523X LED100S/840 DIA A20 7 WH HE	No	-
910925870764	LL523X LED100S/840 DIA DA35W 7 WH HE	No	-
910925870766	LL523X LED123S/840 DIA A20 7 WH HE	No	-
910925870767	LL523X LED123S/840 DIA DA25W 7 WH HE	No	-
910925870768	LL523X LED123S/840 DIA DA35W 7 WH HE	No	-
910925870769	LL523X LED160S/840 DIA WB 7 WH HE	No	-
910925870796	LL523X LED123S/840 PSD A20 7 WH HE	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting
910925870797	LL523X LED160S/840 PSD XNB 7 WH HE	-	-
910925870798	LL523X LED100S/840 PSD WB 7 SI HE	-	-
910925870799	LL523X LED123S/840 PSD WB 7 BK HE	-	-
910925870802	LL523X LED62S/840 PSD WB 7 SI HE	-	-
910925870809	LL523X LED100S/840 PSD DA35W 7 WH HE	-	-
910925870810	LL523X LED100S/840 PSD WB 7 BK HE	-	-
910925870811	LL523X LED123S/840 PSD DA35W 7 WH HE	-	-
910925870812	LL523X LED62S/840 PSD DA35W 7 WH HE	-	-
910925870819	LL523X LED123S/840 DIA WB 13 ELP3 WH HE	No	Emergency lighting 3 hours duration Pro version
910925870780	LL612X LED61S/840 DIA WB 7 WH HE	No	-
910925870794	LL612X LED61S/840 DIA MB 7 WH HE	No	-
910925870795	LL612X LED61S/840 DIA NB 7 WH HE	No	-
910925870803	LL612X LED61S/840 PSD NB 7 WH HE	-	-
910925870770	LL623X LED123S/840 DIA MB 7 WH HE	No	-
910925870771	LL623X LED123S/840 DIA WB 7 WH HE	No	-
910925870772	LL623X LED123S/840 DIA NB 7 WH HE	No	-
910925870805	LL623X LED123S/840 PSD WB 7 WH HE	-	-
910925868648	LL515X 61S/840 PSD WB 7 HE WH	-	-
910925868649	LL515X 80S/840 PSD WB 7 HE WH	-	-
910925868651	LL515X 80S/840 PSD MB 7 HE WH	-	-
910925868653	LL515X 80S/840 PSD NB 7 HE WH	-	-

Approval and Application

Order Code	Full Product Name	Flammability mark
910925870051	LL512X LED61S/840 PSD O-PC 7 VLC WH XA	For mounting on normally flammable surfaces
910925870052	LL523X LED123S/840 PSD O-PC 7 VLC WH XA	For mounting on normally flammable surfaces
910925870055	LL523X LED123S/840 SIA O-PC 7 WH HE	For mounting on normally flammable surfaces
910925870056	LL523X LED100S/840 SIA O-PC 7 WH HE	For mounting on normally flammable surfaces
910925870057	LL523X LED62S/840 SIA O-PC 7 WH HE	For mounting on normally flammable surfaces
910925870058	LL512X LED61S/840 SIA O-PC 7 WH HE	For mounting on normally flammable surfaces
910925870059	LL512X LED31S/840 SIA O-PC 7 WH HE	For mounting on normally flammable surfaces
910925870061	LL523X LED62S/840 DIA O-PC 7 WH HE	For mounting on normally flammable surfaces
910925870062	LL523X LED62S/840 DIA O-PC 13 ELP3 WH HE	For mounting on normally flammable surfaces
910925870063	LL523X LED100S/840 DIA O-PC 7 WH HE	For mounting on normally flammable surfaces
910925870064	LL523X LED123S/840 DIA O-PC 7 WH HE	For mounting on normally flammable surfaces
910925870065	LL512X LED31S/840 DIA O-PC 7 WH HE	For mounting on normally flammable surfaces
910925870066	LL512X LED50S/840 DIA O-PC 7 WH HE	For mounting on normally flammable surfaces
910925870067	LL512X LED61S/840 DIA O-PC 7 WH HE	For mounting on normally flammable surfaces
910925868139	LL512X LED31S/840 PSD WB-OC 7 WH XA	For mounting on normally flammable surfaces
910925868958	LL512X LED31S/840 PSD MB 7 WH HE	For mounting on normally flammable surfaces
910925868959	LL512X LED31S/840 PSD WB 7 WH HE	For mounting on normally flammable surfaces

Order Code	Full Product Name	Flammability mark
910925868960	LL512X LED50S/840 PSD MB 7 WH HE	For mounting on normally flammable surfaces
910925868961	LL512X LED50S/840 PSD WB 7 WH HE	For mounting on normally flammable surfaces
910925868963	LL512X LED61S/840 PSD MB 7 WH HE	For mounting on normally flammable surfaces
910925868964	LL512X LED61S/840 PSD WB 7 WH HE	For mounting on normally flammable surfaces
910925868965	LL512X LED80S/840 PSD NB 7 WH HE	For mounting on normally flammable surfaces
910925868966	LL512X LED80S/840 PSD MB 7 WH HE	For mounting on normally flammable surfaces
910925868981	LL512X LED61S/840 SIA MB 7 WH HE	For mounting on normally flammable surfaces
910925868982	LL512X LED61S/840 SIA WB 7 WH HE	For mounting on normally flammable surfaces
910925868984	LL512X LED80S/840 SIA MB 7 WH HE	For mounting on normally flammable surfaces
910925868986	LL512X LED31S/840 SIA WB 7 WH HE	For mounting on normally flammable surfaces
910925869743	LL512X LED80S/840 PSD WB 7 WH HE	For mounting on normally flammable surfaces
910925870173	LL512X LED31S/840 DIA WB 7 WH UE	For mounting on normally flammable surfaces
910925870174	LL512X LED50S/840 DIA WB 7 WH UE	For mounting on normally flammable surfaces
910925870175	LL512X LED61S/840 DIA WB 7 WH UE	For mounting on normally flammable surfaces
910925870176	LL512X LED80S/840 DIA WB 7 WH UE	For mounting on normally flammable surfaces
910925870773	LL512X LED31S/830 DIA WB 7 WH HE	For mounting on normally flammable surfaces
910925870775	LL512X LED31S/840 DEIA WB-OC 13 WH HE	For mounting on normally flammable surfaces
910925870777	LL512X LED50S/840 DIA DA35W 7 WH HE	For mounting on normally flammable surfaces
910925870779	LL512X LED80S/840 DIA WB 7 WH HE	For mounting on normally flammable surfaces
910925870801	LL512X LED50S/840 PSD WB 7 BK HE	For mounting on normally flammable surfaces
910925870804	LL512X LED50S/840 PSED WB 7 WH HE	For mounting on normally flammable surfaces
910925870806	LL512X LED31S/840 PSD DA35W 7 WH HE	For mounting on normally flammable surfaces
910925870807	LL512X LED31S/840 PSD WB 7 BK HE	For mounting on normally flammable surfaces
910925870808	LL512X LED61S/840 PSD WB 7 BK HE	For mounting on normally flammable surfaces
910925867812	LL523X LED123S/830 PSD DA45W 7 WH XA	For mounting on normally flammable surfaces
910925867813	LL523X LED123S/840 PSD DA45W 7 WH XA	For mounting on normally flammable surfaces
910925867816	LL523X LED123S/840 PSD WB 7 WH XA	For mounting on normally flammable surfaces
910925867820	LL523X LED160S/840 PSD MB 7 WH XA	For mounting on normally flammable surfaces
910925867839	LL523X LED160S/840 PSD MB 7 WH XA	For mounting on normally flammable surfaces
910925867854	LL523X LED123S/840 PSD NB 7 VLC WH XA	For mounting on normally flammable surfaces
910925867855	LL523X LED160S/840 PSD NB 7 WH XA	For mounting on normally flammable surfaces
910925868138	LL523X LED62S/840 PSD WB-OC 7 WH XA	For mounting on normally flammable surfaces
910925868949	LL523X LED62S/840 PSD MB 7 WH HE	For mounting on normally flammable surfaces
910925868950	LL523X LED62S/840 PSD WB 7 WH HE	For mounting on normally flammable surfaces
910925868951	LL523X LED100S/840 PSD MB 7 WH HE	For mounting on normally flammable surfaces
910925868952	LL523X LED100S/840 PSD WB 7 WH HE	For mounting on normally flammable surfaces
910925868953	LL523X LED123S/840 PSD NB 7 WH HE	For mounting on normally flammable surfaces
910925868954	LL523X LED123S/840 PSD MB 7 WH HE	For mounting on normally flammable surfaces
910925868955	LL523X LED123S/840 PSD WB 7 WH HE	For mounting on normally flammable surfaces
910925868956	LL523X LED160S/840 PSD NB 7 WH HE	For mounting on normally flammable surfaces
910925868957	LL523X LED160S/840 PSD MB 7 WH HE	For mounting on normally flammable surfaces
910925868967	LL523X LED100S/840 SIA MB 7 WH HE	For mounting on normally flammable surfaces

Order Code	Full Product Name	Flammability mark
910925868968	LL523X LED100S/840 SIA WB 7 WH HE	For mounting on normally flammable surfaces
910925868969	LL523X LED123S/840 SIA NB 7 WH HE	For mounting on normally flammable surfaces
910925868970	LL523X LED123S/840 SIA MB 7 WH HE	For mounting on normally flammable surfaces
910925868971	LL523X LED123S/840 SIA WB 7 WH HE	For mounting on normally flammable surfaces
910925868972	LL523X LED160S/840 SIA NB 7 WH HE	For mounting on normally flammable surfaces
910925868973	LL523X LED160S/840 SIA MB 7 WH HE	For mounting on normally flammable surfaces
910925868974	LL523X LED62S/840 SIA WB 7 WH HE	For mounting on normally flammable surfaces
910925869742	LL523X LED160S/840 PSD WB 7 WH HE	For mounting on normally flammable surfaces
910925870169	LL523X LED62S/840 DIA WB 7 WH UE	For mounting on normally flammable surfaces
910925870170	LL523X LED100S/840 DIA WB 7 WH UE	For mounting on normally flammable surfaces
910925870171	LL523X LED123S/840 DIA WB 7 WH UE	For mounting on normally flammable surfaces
910925870172	LL523X LED160S/840 DIA WB 7 WH UE	For mounting on normally flammable surfaces
910925870371	LL523X LED62S/840 DIA MB 7 WH HE	For mounting on normally flammable surfaces
910925870372	LL523X LED62S/840 DIA WB 7 WH HE	For mounting on normally flammable surfaces
910925870373	LL523X LED100S/840 DIA MB 7 WH HE	For mounting on normally flammable surfaces
910925870374	LL523X LED123S/840 DIA MB 7 WH HE	For mounting on normally flammable surfaces
910925870375	LL523X LED100S/840 DIA WB 7 WH HE	For mounting on normally flammable surfaces
910925870376	LL523X LED123S/840 DIA NB 7 WH HE	For mounting on normally flammable surfaces
910925870377	LL523X LED123S/840 DIA WB 7 WH HE	For mounting on normally flammable surfaces
910925870378	LL523X LED160S/840 DIA NB 7 WH HE	For mounting on normally flammable surfaces
910925870379	LL523X LED160S/840 DIA MB 7 WH HE	For mounting on normally flammable surfaces
910925870380	LL512X LED31S/840 DIA MB 7 WH HE	For mounting on normally flammable surfaces
910925870381	LL512X LED31S/840 DIA WB 7 WH HE	For mounting on normally flammable surfaces
910925870382	LL512X LED50S/840 DIA MB 7 WH HE	For mounting on normally flammable surfaces
910925870383	LL512X LED50S/840 DIA WB 7 WH HE	For mounting on normally flammable surfaces
910925870384	LL512X LED61S/840 DIA NB 7 WH HE	For mounting on normally flammable surfaces
910925870385	LL512X LED61S/840 DIA MB 7 WH HE	For mounting on normally flammable surfaces
910925870386	LL512X LED61S/840 DIA WB 7 WH HE	For mounting on normally flammable surfaces
910925870387	LL512X LED80S/840 DIA NB 7 WH HE	For mounting on normally flammable surfaces
910925870388	LL512X LED80S/840 DIA MB 7 WH HE	For mounting on normally flammable surfaces
910925870756	LL523X LED62S/840 DEIA WB-OC 13 WH HE	For mounting on normally flammable surfaces
910925870758	LL523X LED62S/840 DIA DA25N 7 WH HE	For mounting on normally flammable surfaces
910925870759	LL523X LED62S/840 DIA DA25W 7 WH HE	For mounting on normally flammable surfaces
910925870760	LL523X LED62S/840 DIA DA35W 7 WH HE	For mounting on normally flammable surfaces
910925870761	LL523X LED100S/840 DIA NB 7 WH HE	For mounting on normally flammable surfaces
910925870763	LL523X LED100S/840 DIA A20 7 WH HE	For mounting on normally flammable surfaces
910925870764	LL523X LED100S/840 DIA DA35W 7 WH HE	For mounting on normally flammable surfaces
910925870766	LL523X LED123S/840 DIA A20 7 WH HE	For mounting on normally flammable surfaces
910925870767	LL523X LED123S/840 DIA DA25W 7 WH HE	For mounting on normally flammable surfaces
910925870768	LL523X LED123S/840 DIA DA35W 7 WH HE	For mounting on normally flammable surfaces
910925870769	LL523X LED160S/840 DIA WB 7 WH HE	For mounting on normally flammable surfaces
910925870796	LL523X LED123S/840 PSD A20 7 WH HE	For mounting on normally flammable surfaces

Order Code	Full Product Name	Flammability mark
910925870797	LL523X LED160S/840 PSD XNB 7 WH HE	For mounting on normally flammable surfaces
910925870798	LL523X LED100S/840 PSD WB 7 SI HE	For mounting on normally flammable surfaces
910925870799	LL523X LED123S/840 PSD WB 7 BK HE	For mounting on normally flammable surfaces
910925870802	LL523X LED62S/840 PSD WB 7 SI HE	For mounting on normally flammable surfaces
910925870809	LL523X LED100S/840 PSD DA35W 7 WH HE	For mounting on normally flammable surfaces
910925870810	LL523X LED100S/840 PSD WB 7 BK HE	For mounting on normally flammable surfaces
910925870811	LL523X LED123S/840 PSD DA35W 7 WH HE	For mounting on normally flammable surfaces
910925870812	LL523X LED62S/840 PSD DA35W 7 WH HE	For mounting on normally flammable surfaces
910925870819	LL523X LED123S/840 DIA WB 13 ELP3 WH HE	For mounting on normally flammable surfaces
910925870780	LL612X LED61S/840 DIA WB 7 WH HE	For mounting on easily flammable surfaces
910925870794	LL612X LED61S/840 DIA MB 7 WH HE	For mounting on easily flammable surfaces
910925870795	LL612X LED61S/840 DIA NB 7 WH HE	For mounting on easily flammable surfaces
910925870803	LL612X LED61S/840 PSD NB 7 WH HE	For mounting on easily flammable surfaces
910925870770	LL623X LED123S/840 DIA MB 7 WH HE	For mounting on easily flammable surfaces
910925870771	LL623X LED123S/840 DIA WB 7 WH HE	For mounting on easily flammable surfaces
910925870772	LL623X LED123S/840 DIA NB 7 WH HE	For mounting on easily flammable surfaces
910925870805	LL623X LED123S/840 PSD WB 7 WH HE	For mounting on easily flammable surfaces
910925868648	LL515X 61S/840 PSD WB 7 HE WH	For mounting on normally flammable surfaces
910925868649	LL515X 80S/840 PSD WB 7 HE WH	For mounting on normally flammable surfaces
910925868651	LL515X 80S/840 PSD MB 7 HE WH	For mounting on normally flammable surfaces
910925868653	LL515X 80S/840 PSD NB 7 HE WH	For mounting on normally flammable surfaces

Product Data


Order Code	Full Product Name	Product family code
910925870051	LL512X LED61S/840 PSD O-PC 7 VLC WH XA	LL512X
910925870052	LL523X LED123S/840 PSD O-PC 7 VLC WH XA	LL523X
910925870055	LL523X LED123S/840 SIA O-PC 7 WH HE	LL523X
910925870056	LL523X LED100S/840 SIA O-PC 7 WH HE	LL523X
910925870057	LL523X LED62S/840 SIA O-PC 7 WH HE	LL523X
910925870058	LL512X LED61S/840 SIA O-PC 7 WH HE	LL512X
910925870059	LL512X LED31S/840 SIA O-PC 7 WH HE	LL512X
910925870061	LL523X LED62S/840 DIA O-PC 7 WH HE	LL523X
910925870062	LL523X LED62S/840 DIA O-PC 13 ELP3 WH HE	LL523X
910925870063	LL523X LED100S/840 DIA O-PC 7 WH HE	LL523X
910925870064	LL523X LED123S/840 DIA O-PC 7 WH HE	LL523X
910925870065	LL512X LED31S/840 DIA O-PC 7 WH HE	LL512X
910925870066	LL512X LED50S/840 DIA O-PC 7 WH HE	LL512X
910925870067	LL512X LED61S/840 DIA O-PC 7 WH HE	LL512X
910925868139	LL512X LED31S/840 PSD WB-OC 7 WH XA	LL512X
910925868958	LL512X LED31S/840 PSD MB 7 WH HE	LL512X
910925868959	LL512X LED31S/840 PSD WB 7 WH HE	LL512X

Order Code	Full Product Name	Product family code
910925868960	LL512X LED50S/840 PSD MB 7 WH HE	LL512X
910925868961	LL512X LED50S/840 PSD WB 7 WH HE	LL512X
910925868963	LL512X LED61S/840 PSD MB 7 WH HE	LL512X
910925868964	LL512X LED61S/840 PSD WB 7 WH HE	LL512X
910925868965	LL512X LED80S/840 PSD NB 7 WH HE	LL512X
910925868966	LL512X LED80S/840 PSD MB 7 WH HE	LL512X
910925868981	LL512X LED61S/840 SIA MB 7 WH HE	LL512X
910925868982	LL512X LED61S/840 SIA WB 7 WH HE	LL512X
910925868984	LL512X LED80S/840 SIA MB 7 WH HE	LL512X
910925868986	LL512X LED31S/840 SIA WB 7 WH HE	LL512X
910925869743	LL512X LED80S/840 PSD WB 7 WH HE	LL512X
910925870173	LL512X LED31S/840 DIA WB 7 WH UE	LL512X
910925870174	LL512X LED50S/840 DIA WB 7 WH UE	LL512X
910925870175	LL512X LED61S/840 DIA WB 7 WH UE	LL512X
910925870176	LL512X LED80S/840 DIA WB 7 WH UE	LL512X
910925870773	LL512X LED31S/830 DIA WB 7 WH HE	LL512X
910925870775	LL512X LED31S/840 DEIA WB-OC 13 WH HE	LL512X
910925870777	LL512X LED50S/840 DIA DA35W 7 WH HE	LL512X
910925870779	LL512X LED80S/840 DIA WB 7 WH HE	LL512X
910925870801	LL512X LED50S/840 PSD WB 7 BK HE	LL512X
910925870804	LL512X LED50S/840 PSED WB 7 WH HE	LL512X
910925870806	LL512X LED31S/840 PSD DA35W 7 WH HE	LL512X
910925870807	LL512X LED31S/840 PSD WB 7 BK HE	LL512X
910925870808	LL512X LED61S/840 PSD WB 7 BK HE	LL512X
910925867812	LL523X LED123S/830 PSD DA45W 7 WH XA	LL523X
910925867813	LL523X LED123S/840 PSD DA45W 7 WH XA	LL523X
910925867816	LL523X LED123S/840 PSD WB 7 WH XA	LL523X
910925867820	LL523X LED160S/840 PSD MB 7 WH XA	LL523X
910925867839	LL523X LED160S/840 PSD MB 7 WH XA	LL523X
910925867854	LL523X LED123S/840 PSD NB 7 VLC WH XA	LL523X
910925867855	LL523X LED160S/840 PSD NB 7 WH XA	LL523X
910925868138	LL523X LED62S/840 PSD WB-OC 7 WH XA	LL523X
910925868949	LL523X LED62S/840 PSD MB 7 WH HE	LL523X
910925868950	LL523X LED62S/840 PSD WB 7 WH HE	LL523X
910925868951	LL523X LED100S/840 PSD MB 7 WH HE	LL523X
910925868952	LL523X LED100S/840 PSD WB 7 WH HE	LL523X
910925868953	LL523X LED123S/840 PSD NB 7 WH HE	LL523X
910925868954	LL523X LED123S/840 PSD MB 7 WH HE	LL523X
910925868955	LL523X LED123S/840 PSD WB 7 WH HE	LL523X
910925868956	LL523X LED160S/840 PSD NB 7 WH HE	LL523X
910925868957	LL523X LED160S/840 PSD MB 7 WH HE	LL523X
910925868967	LL523X LED100S/840 SIA MB 7 WH HE	LL523X


Order Code	Full Product Name	Product family code
910925868968	LL523X LED100S/840 SIA WB 7 WH HE	LL523X
910925868969	LL523X LED123S/840 SIA NB 7 WH HE	LL523X
910925868970	LL523X LED123S/840 SIA MB 7 WH HE	LL523X
910925868971	LL523X LED123S/840 SIA WB 7 WH HE	LL523X
910925868972	LL523X LED160S/840 SIA NB 7 WH HE	LL523X
910925868973	LL523X LED160S/840 SIA MB 7 WH HE	LL523X
910925868974	LL523X LED62S/840 SIA WB 7 WH HE	LL523X
910925869742	LL523X LED160S/840 PSD WB 7 WH HE	LL523X
910925870169	LL523X LED62S/840 DIA WB 7 WH UE	LL523X
910925870170	LL523X LED100S/840 DIA WB 7 WH UE	LL523X
910925870171	LL523X LED123S/840 DIA WB 7 WH UE	LL523X
910925870172	LL523X LED160S/840 DIA WB 7 WH UE	LL523X
910925870371	LL523X LED62S/840 DIA MB 7 WH HE	LL523X
910925870372	LL523X LED62S/840 DIA WB 7 WH HE	LL523X
910925870373	LL523X LED100S/840 DIA MB 7 WH HE	LL523X
910925870374	LL523X LED123S/840 DIA MB 7 WH HE	LL523X
910925870375	LL523X LED100S/840 DIA WB 7 WH HE	LL523X
910925870376	LL523X LED123S/840 DIA NB 7 WH HE	LL523X
910925870377	LL523X LED123S/840 DIA WB 7 WH HE	LL523X
910925870378	LL523X LED160S/840 DIA NB 7 WH HE	LL523X
910925870379	LL523X LED160S/840 DIA MB 7 WH HE	LL523X
910925870380	LL512X LED31S/840 DIA MB 7 WH HE	LL512X
910925870381	LL512X LED31S/840 DIA WB 7 WH HE	LL512X
910925870382	LL512X LED50S/840 DIA MB 7 WH HE	LL512X
910925870383	LL512X LED50S/840 DIA WB 7 WH HE	LL512X
910925870384	LL512X LED61S/840 DIA NB 7 WH HE	LL512X
910925870385	LL512X LED61S/840 DIA MB 7 WH HE	LL512X
910925870386	LL512X LED61S/840 DIA WB 7 WH HE	LL512X
910925870387	LL512X LED80S/840 DIA NB 7 WH HE	LL512X
910925870388	LL512X LED80S/840 DIA MB 7 WH HE	LL512X
910925870756	LL523X LED62S/840 DEIA WB-OC 13 WH HE	LL523X
910925870758	LL523X LED62S/840 DIA DA25N 7 WH HE	LL523X
910925870759	LL523X LED62S/840 DIA DA25W 7 WH HE	LL523X
910925870760	LL523X LED62S/840 DIA DA35W 7 WH HE	LL523X
910925870761	LL523X LED100S/840 DIA NB 7 WH HE	LL523X
910925870763	LL523X LED100S/840 DIA A20 7 WH HE	LL523X
910925870764	LL523X LED100S/840 DIA DA35W 7 WH HE	LL523X
910925870766	LL523X LED123S/840 DIA A20 7 WH HE	LL523X
910925870767	LL523X LED123S/840 DIA DA25W 7 WH HE	LL523X
910925870768	LL523X LED123S/840 DIA DA35W 7 WH HE	LL523X
910925870769	LL523X LED160S/840 DIA WB 7 WH HE	LL523X
910925870796	LL523X LED123S/840 PSD A20 7 WH HE	LL523X

Order Code	Full Product Name	Product family code
910925870797	LL523X LED160S/840 PSD XNB 7 WH HE	LL523X
910925870798	LL523X LED100S/840 PSD WB 7 SI HE	LL523X
910925870799	LL523X LED123S/840 PSD WB 7 BK HE	LL523X
910925870802	LL523X LED62S/840 PSD WB 7 SI HE	LL523X
910925870809	LL523X LED100S/840 PSD DA35W 7 WH HE	LL523X
910925870810	LL523X LED100S/840 PSD WB 7 BK HE	LL523X
910925870811	LL523X LED123S/840 PSD DA35W 7 WH HE	LL523X
910925870812	LL523X LED62S/840 PSD DA35W 7 WH HE	LL523X
910925870819	LL523X LED123S/840 DIA WB 13 ELP3 WH HE	LL523X
910925870780	LL612X LED61S/840 DIA WB 7 WH HE	LL612X
910925870794	LL612X LED61S/840 DIA MB 7 WH HE	LL612X
910925870795	LL612X LED61S/840 DIA NB 7 WH HE	LL612X
910925870803	LL612X LED61S/840 PSD NB 7 WH HE	LL612X
910925870770	LL623X LED123S/840 DIA MB 7 WH HE	LL623X
910925870771	LL623X LED123S/840 DIA WB 7 WH HE	LL623X
910925870772	LL623X LED123S/840 DIA NB 7 WH HE	LL623X
910925870805	LL623X LED123S/840 PSD WB 7 WH HE	LL623X
910925868648	LL515X 61S/840 PSD WB 7 HE WH	LL515X
910925868649	LL515X 80S/840 PSD WB 7 HE WH	LL515X
910925868651	LL515X 80S/840 PSD MB 7 HE WH	LL515X
910925868653	LL515X 80S/840 PSD NB 7 HE WH	LL515X


Polar normal diagrams




LL500XI - 910925868953




LL500XI - 910925868956




LL500XI - 910925868950




LL500XI - 910925868970




LL500XI - 910925868955




LL500XI - 910925869742




LL500XI - 910925868972




LL500XI - 910925868973




LL500XI - 910925867816




LL500XI - 910925867820




LL500XI - 910925867855




LL500XI - 910925868139




LL500XI - 910925868138




LL500XI - 910925868952




LL500XI - 910925868954




LL500XI - 910925868957




LL500XI - 910925868961




LL500XI - 910925868969




LL500XI - 910925868971




LL500XI - 910925869743




LL500XI - 910925868949




LL500XI - 910925868951




LL500XI - 910925868958




LL500XI - 910925868960




LL500XI - 910925868964




LL500XI - 910925868963




LL500XI - 910925868966




LL500XI - 910925868967




LL500XI - 910925868965




LL500XI - 910925868968




LL500XI - 910925868974




LL500XI - 910925868984




LL500XI - 910925868981




LL500XI - 910925868982




LL500XI - 910925868986




LL500XI - 910925867812




LL500XI - 910925867813




LL500XI - 910925867839




LL500XI - 910925867854




LL500XI - 910925870375




LL500XI - 910925870384




LL500XI - 910925870373




LL500XI - 910925870371




LL500XI - 910925870388




LL500XI - 910925870387




LL500XI - 910925870377




LL500XI - 910925870374




LL500XI - 910925870381




LL500XI - 910925870385




LL500XI - 910925870378




LL500XI - 910925870382




LL500XI - 910925870380




LL500XI - 910925870379




LL500XI - 910925870376




LL500XI - 910925870386




LL500XI - 910925870768




LL500XI - 910925870780




LL500XI - 910925870773




LL500XI - 910925870767




LL500XI - 910925870772




LL500XI - 910925870770




LL500XI - 910925870769




LL500XI - 910925870758




LL500XI - 910925870761




LL500XI - 910925870775




LL500XI - 910925870756




LL500XI - 910925870763




LL500XI - 910925870777




LL500XI - 910925870764




LL500XI - 910925870766




LL500XI - 910925870759




LL500XI - 910925870771




LL500XI - 910925870779




LL500XI - 910925870760




LL500XI - 910925870802




LL500XI - 910925870808




LL500XI - 910925870798




LL500XI - 910925870810




LL500XI - 910925870797




LL500XI - 910925870811




LL500XI - 910925870796




LL500XI - 910925870805




LL500XI - 910925870806




LL500XI - 910925870804




LL500XI - 910925870809




LL500XI - 910925870803




LL500XI - 910925870799




LL500XI - 910925870801




LL500XI - 910925870807




LL500XI - 910925870812




LL500XI - 910925870794




LL500XI - 910925870795




LL500XI - 910925870819




LL500XI - 910925870051




LL500XI - 910925870057




LL500XI - 910925870052




LL500XI - 910925870055




LL500XI - 910925870056




LL500XI - 910925870064




LL500XI - 910925870059




LL500XI - 910925870063




LL500XI - 910925870062




LL500XI - 910925870061




LL500XI - 910925870058




LL500XI - 910925870066




LL500XI - 910925870067




LL500XI - 910925870065




LL500XI - 910925868959




910925870170




910925870172




910925870176




910925870174




910925870169



910925870171



910925870173



910925870175