



Guaranteed performance, thinking ahead

Maxos fusion

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

Benefits

- Freedom of (re-)positioning enables you to direct the light where needed
- Family of fixtures to create the desired atmosphere; wide variety of beam shapes to suit diversity of applications
- With up to 13-wire track, emergency lighting and third-party hardware can be integrated to declutter ceilings

Features

- Track system inside the trunk with up to 13 wires
- High uniformity and artefact-free light distributions
- Linear fixtures, non-linear fixtures and spots can be easily installed onto the trunk
- Eight optics, including (double) asymmetric distributions and a frosted cover
- IP54 optional, silicone-free
- StoreWise, Indoor Positioning and GreenWarehouse-ready

Maxos fusion

Application


- (Food) retail
- Industrial halls/areas
- Warehouses/distribution centers

Versions




Maxos Fusion Panel-LL523X WB WH

Dimensional drawing



Polar Wide Diagrams



Polar Normal (separate) - LL500XI -
910925867816

Maxos fusion

