



New standard in trunking

An adaptable LED trunking system, combining the well proven advantages of an electrical track which allows flexible positioning of linear panels offering multiple flux/ length combinations with specially designed lenses to direct the light where needed. A solution allowing for new projects to be designed with optimal number of linear panels and a solution for retrofitting old installations - Bringing your application right up to date with the latest lighting possibilities. Now, and in the future.

Benefits

- Easy retrofit 'old' Maxos and TTX400 electrical units with significant energy savings with UE portfolio
- Upgrade to Interact systems to unlock more savings
- Flexible trunking infrastructure with a solution for all electrical scenarios and beyond
- Reliable and long lasting performance across the full offer

Features

- Simplified panel offer -> 1,5m and 2,25m built on modular components.
- High efficacy upto 200lm/W in UE range
- Lumen maintenance L85 100k hrs across the range
- Dedicated sensor units to upgrade to interact system propositions


Applications

- Food and Large Retailers
- Manufacturing
- Warehouses

Versions



Dimensional drawing



Product details



Very Wide beam lens detail



Maxos unify optical design

General Information	
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes
Light Technical	
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	>80
Beam angle of light source	120 degree(s)
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Not applicable
Protection class IEC	Safety class I
Controls and Dimming	
Maximum dim level	1%
Mechanical and Housing	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Emergency Operation	
Central Emergency	No
Emergency lighting	-

Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Ambient temperature range	-20 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.34. 0.35) SDCM <3

Light Technical

Order Code	Full Product Name	Luminous Flux	Luminous Efficacy (rated) (Nom)	Optic type
910925871026	LL552X 84S/840 NE DIA VWB WH	8,400 lm	169 lm/W	Very wide beam
910925871027	LL552X 123S/840 NE DIA VWB WH	12,300 lm	164 lm/W	Very wide beam
910925870859	LL553X 40S/840 NE DIA WB WH	4,000 lm	167 lm/W	Wide beam
910925870860	LL553X 80S/840 NE DIA WB WH	8,000 lm	167 lm/W	Wide beam
910925870861	LL553X 80S/840 NE DIA NB WH	8,000 lm	167 lm/W	Narrow beam
910925870862	LL553X 105S/840 NE DIA NB WH	10,500 lm	162 lm/W	Narrow beam
910925870863	LL553X 40S/840 UE DIA WB WH	4,000 lm	195 lm/W	Wide beam
910925870864	LL553X 80S/840 UE DIA WB WH	8,000 lm	195 lm/W	Wide beam
910925870865	LL553X 80S/840 UE DIA NB WH	8,000 lm	195 lm/W	Narrow beam
910925870866	LL553X 105S/840 UE DIA NB WH	10,500 lm	188 lm/W	Narrow beam
910925870929	LL553X 105S/840 NE DIA WB WH	10,500 lm	162 lm/W	Wide beam
910925870930	LL553X 40S/840 NE DIA WB C-2R WH	4,000 lm	167 lm/W	Wide beam
910925870931	LL553X 80S/840 NE DIA WB C-2R WH	8,000 lm	167 lm/W	Wide beam
910925870932	LL553X 80S/840 NE DIA NB C-2R WH	8,000 lm	167 lm/W	Narrow beam
910925870933	LL553X 105S/840 NE DIA WB C-2R WH	10,500 lm	162 lm/W	Wide beam
910925870934	LL553X 105S/840 NE DIA NB C-2R WH	10,500 lm	162 lm/W	Narrow beam
910925870850	LL552X 62S/840 NE DIA WB WH	6,200 lm	175 lm/W	Wide beam
910925870851	LL552X 160S/840 NE DIA NB WH	16,000 lm	163 lm/W	Narrow beam
910925870852	LL552X 62S/840 UE DIA WB WH	6,200 lm	200 lm/W	Wide beam
910925870853	LL552X 160S/840 UE DIA NB WH	16,000 lm	191 lm/W	Narrow beam
910925870854	LL552X 62S/840 NE SIA WB WH	6,200 lm	180 lm/W	Wide beam
910925870855	LL552X 160S/840 NE SIA NB WH	16,000 lm	163 lm/W	Narrow beam
910925870856	LL552X 62S/840 UE SIA WB WH	6,200 lm	197 lm/W	Wide beam
910925870857	LL552X 100S/840 UE SIA WB WH	10,000 lm	196 lm/W	Wide beam
910925870858	LL552X 160S/840 UE SIA NB WH	16,000 lm	191 lm/W	Narrow beam
910925871032	LL552X 200S/840 NE DIA WB WH	20,000 lm	161 lm/W	Wide beam
910925871033	LL552X 200S/840 UE DIA WB WH	20,000 lm	185 lm/W	Wide beam

Order Code	Full Product Name	Luminous Flux	Luminous Efficacy (rated) (Nom)	Optic type
910925871034	LL552X 240S/840 UE DIA NB WH	24,000 lm	185 lm/W	Narrow beam
910925871035	LL552X 200S/840 UE DIA NB WH	20,000 lm	185 lm/W	Narrow beam
910925871036	LL552X BV 240S/840 UE DIA NB WH	24,000 lm	185 lm/W	Narrow beam
910925871037	LL552X BV 200S/840 UE DIA NB WH	20,000 lm	185 lm/W	Narrow beam
910925871913	LL552X 160S/840 NE DIA WB WH	24,000 lm	185 lm/W	Wide beam
910925871914	LL552X 200S/840 NE DIA NB WH	24,000 lm	185 lm/W	Narrow beam
910925871915	LL552X 240S/840 UE DIA WB WH	24,000 lm	185 lm/W	Wide beam
910925870846	LL551X 40S/840 UE DIA WB BK	4,000 lm	195 lm/W	Wide beam
910925870847	LL551X 80S/840 UE DIA WB BK	8,000 lm	195 lm/W	Wide beam
910925870848	LL551X 80S/840 UE DIA NB BK	8,000 lm	195 lm/W	Narrow beam
910925870849	LL551X 105S/840 UE DIA NB BK	10,500 lm	188 lm/W	Narrow beam
910925870842	LL551X 40S/840 NE DIA WB WH	4,000 lm	167 lm/W	Wide beam
910925870843	LL551X 80S/840 NE DIA WB WH	8,000 lm	167 lm/W	Wide beam
910925870844	LL551X 80S/840 NE DIA NB WH	8,000 lm	167 lm/W	Narrow beam
910925870845	LL551X 105S/840 NE DIA NB WH	10,500 lm	162 lm/W	Narrow beam
910925870925	LL551X 105S/840 NE DIA WB WH	10,500 lm	162 lm/W	Wide beam
910925871016	LL551X 43_49_60_72S/840 NE PSU WB WH	4,400 lm 5,000 lm 6,100 lm 7,200 lm	180 lm/W 169 lm/W	Wide beam
910925871018	LL551X 43_49_60_72S/840 NE PSU NB WH	4,400 lm 5,000 lm 6,100 lm 7,200 lm	180 lm/W 169 lm/W	Narrow beam
910925871019	LL551X 47_54_66_80S/840 UE PSU WB WH	4,800 lm 5,500 lm 6,700 lm 8,000 lm	196 lm/W 193 lm/W	Wide beam
910925871021	LL551X 47_54_66_80S/840 UE PSU NB WH	4,800 lm 5,500 lm 6,700 lm 8,000 lm	196 lm/W 193 lm/W	Narrow beam
910925871028	LL551X 133S/840 NE DIA WB WH	13,300 lm	151 lm/W	Wide beam
910925871029	LL551X 133S/840 HE DIA WB WH	13,300 lm	182 lm/W	Wide beam
910925871030	LL551X 133S/840 HE DIA NB WH	13,300 lm	182 lm/W	Narrow beam
910925871031	LL551X 160S/840 HE DIA NB WH	16,000 lm	176 lm/W	Narrow beam
910925871912	LL551X 133S/840 NE DIA NB WH	13,300 lm	151 lm/W	Narrow beam
910925871017	LL551X 43_49_60_72S/840 NE PSU VWB WH	4,400 lm 5,000 lm 6,100 lm 7,200 lm	180 lm/W 169 lm/W	Very wide beam
910925871020	LL551X 47_54_66_80S/840 UE PSU VWB WH	4,800 lm 5,500 lm 6,700 lm 8,000 lm	196 lm/W 193 lm/W	Very wide beam
910925871022	LL551X 40S/840 NE DIA VWB WH	4,000 lm	163 lm/W	Very wide beam
910925871023	LL551X 80S/840 NE DIA VWB WH	8,000 lm	163 lm/W	Very wide beam
910925871024	LL553X 55S/840 NE DIA VWB WH	5,500 lm	177 lm/W	Very wide beam
910925871025	LL553X 66S/840 NE DIA VWB WH	6,600 lm	166 lm/W	Very wide beam

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910925871026	LL552X 84S/840 NE DIA VWB WH	48.5 W
910925871027	LL552X 123S/840 NE DIA VWB WH	74 W
910925870859	LL553X 40S/840 NE DIA WB WH	24 W
910925870860	LL553X 80S/840 NE DIA WB WH	48 W
910925870861	LL553X 80S/840 NE DIA NB WH	48 W
910925870862	LL553X 105S/840 NE DIA NB WH	65 W
910925870863	LL553X 40S/840 UE DIA WB WH	20.5 W
910925870864	LL553X 80S/840 UE DIA WB WH	41 W
910925870865	LL553X 80S/840 UE DIA NB WH	41 W
910925870866	LL553X 105S/840 UE DIA NB WH	56 W
910925870929	LL553X 105S/840 NE DIA WB WH	65 W
910925870930	LL553X 40S/840 NE DIA WB C-2R WH	24 W
910925870931	LL553X 80S/840 NE DIA WB C-2R WH	48 W
910925870932	LL553X 80S/840 NE DIA NB C-2R WH	48 W
910925870933	LL553X 105S/840 NE DIA WB C-2R WH	65 W
910925870934	LL553X 105S/840 NE DIA NB C-2R WH	65 W
910925870850	LL552X 62S/840 NE DIA WB WH	35.5 W
910925870851	LL552X 160S/840 NE DIA NB WH	98 W
910925870852	LL552X 62S/840 UE DIA WB WH	31 W
910925870853	LL552X 160S/840 UE DIA NB WH	84 W
910925870854	LL552X 62S/840 NE SIA WB WH	34.5 W
910925870855	LL552X 160S/840 NE SIA NB WH	98 W
910925870856	LL552X 62S/840 UE SIA WB WH	31.5 W
910925870857	LL552X 100S/840 UE SIA WB WH	51 W
910925870858	LL552X 160S/840 UE SIA NB WH	84 W
910925871032	LL552X 200S/840 NE DIA WB WH	124 W
910925871033	LL552X 200S/840 UE DIA WB WH	108 W
910925871034	LL552X 240S/840 UE DIA NB WH	130 W
910925871035	LL552X 200S/840 UE DIA NB WH	108 W
910925871036	LL552X BV 240S/840 UE DIA NB WH	130 W
910925871037	LL552X BV 200S/840 UE DIA NB WH	108 W
910925871913	LL552X 160S/840 NE DIA WB WH	98 W
910925871914	LL552X 200S/840 NE DIA NB WH	124 W
910925871915	LL552X 240S/840 UE DIA WB WH	130 W
910925870846	LL551X 40S/840 UE DIA WB BK	20.5 W
910925870847	LL551X 80S/840 UE DIA WB BK	41 W
910925870848	LL551X 80S/840 UE DIA NB BK	41 W
910925870849	LL551X 105S/840 UE DIA NB BK	56 W
910925870842	LL551X 40S/840 NE DIA WB WH	24 W
910925870843	LL551X 80S/840 NE DIA WB WH	48 W
910925870844	LL551X 80S/840 NE DIA NB WH	48 W

Order Code	Full Product Name	Power Consumption
910925870845	LL551X 105S/840 NE DIA NB WH	65 W
910925870925	LL551X 105S/840 NE DIA WB WH	65 W
910925871016	LL551X 43_49_60_72S/840 NE PSU WB WH	42.5 W
910925871018	LL551X 43_49_60_72S/840 NE PSU NB WH	42.5 W
910925871019	LL551X 47_54_66_80S/840 UE PSU WB WH	41.5 W
910925871021	LL551X 47_54_66_80S/840 UE PSU NB WH	41.5 W
910925871028	LL551X 133S/840 NE DIA WB WH	88 W
910925871029	LL551X 133S/840 HE DIA WB WH	73 W
910925871030	LL551X 133S/840 HE DIA NB WH	73 W
910925871031	LL551X 160S/840 HE DIA NB WH	91 W
910925871912	LL551X 133S/840 NE DIA NB WH	88 W
910925871017	LL551X 43_49_60_72S/840 NE PSU VWB WH	42.5 W
910925871020	LL551X 47_54_66_80S/840 UE PSU VWB WH	41.5 W
910925871022	LL551X 40S/840 NE DIA VWB WH	24 W
910925871023	LL551X 80S/840 NE DIA VWB WH	48 W
910925871024	LL553X 55S/840 NE DIA VWB WH	30.5 W
910925871025	LL553X 66S/840 NE DIA VWB WH	38.5 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
910925871026	LL552X 84S/840 NE DIA VWB WH	Yes
910925871027	LL552X 123S/840 NE DIA VWB WH	Yes
910925870859	LL553X 40S/840 NE DIA WB WH	Yes
910925870860	LL553X 80S/840 NE DIA WB WH	Yes
910925870861	LL553X 80S/840 NE DIA NB WH	Yes
910925870862	LL553X 105S/840 NE DIA NB WH	Yes
910925870863	LL553X 40S/840 UE DIA WB WH	Yes
910925870864	LL553X 80S/840 UE DIA WB WH	Yes
910925870865	LL553X 80S/840 UE DIA NB WH	Yes
910925870866	LL553X 105S/840 UE DIA NB WH	Yes
910925870929	LL553X 105S/840 NE DIA WB WH	Yes
910925870930	LL553X 40S/840 NE DIA WB C-2R WH	Yes
910925870931	LL553X 80S/840 NE DIA WB C-2R WH	Yes
910925870932	LL553X 80S/840 NE DIA NB C-2R WH	Yes
910925870933	LL553X 105S/840 NE DIA WB C-2R WH	Yes
910925870934	LL553X 105S/840 NE DIA NB C-2R WH	Yes
910925870850	LL552X 62S/840 NE DIA WB WH	Yes
910925870851	LL552X 160S/840 NE DIA NB WH	Yes
910925870852	LL552X 62S/840 UE DIA WB WH	Yes
910925870853	LL552X 160S/840 UE DIA NB WH	Yes
910925870854	LL552X 62S/840 NE SIA WB WH	Yes

Order Code	Full Product Name	Dimmable
910925870855	LL552X 160S/840 NE SIA NB WH	Yes
910925870856	LL552X 62S/840 UE SIA WB WH	Yes
910925870857	LL552X 100S/840 UE SIA WB WH	Yes
910925870858	LL552X 160S/840 UE SIA NB WH	Yes
910925871032	LL552X 200S/840 NE DIA WB WH	Yes
910925871033	LL552X 200S/840 UE DIA WB WH	Yes
910925871034	LL552X 240S/840 UE DIA NB WH	Yes
910925871035	LL552X 200S/840 UE DIA NB WH	Yes
910925871036	LL552X BV 240S/840 UE DIA NB WH	Yes
910925871037	LL552X BV 200S/840 UE DIA NB WH	Yes
910925871913	LL552X 160S/840 NE DIA WB WH	Yes
910925871914	LL552X 200S/840 NE DIA NB WH	Yes
910925871915	LL552X 240S/840 UE DIA WB WH	Yes
910925870846	LL551X 40S/840 UE DIA WB BK	Yes
910925870847	LL551X 80S/840 UE DIA WB BK	Yes
910925870848	LL551X 80S/840 UE DIA NB BK	Yes
910925870849	LL551X 105S/840 UE DIA NB BK	Yes
910925870842	LL551X 40S/840 NE DIA WB WH	Yes
910925870843	LL551X 80S/840 NE DIA WB WH	Yes
910925870844	LL551X 80S/840 NE DIA NB WH	Yes
910925870845	LL551X 105S/840 NE DIA NB WH	Yes
910925870925	LL551X 105S/840 NE DIA WB WH	Yes
910925871016	LL551X 43_49_60_72S/840 NE PSU WB WH	No
910925871018	LL551X 43_49_60_72S/840 NE PSU NB WH	No
910925871019	LL551X 47_54_66_80S/840 UE PSU WB WH	No
910925871021	LL551X 47_54_66_80S/840 UE PSU NB WH	No
910925871028	LL551X 133S/840 NE DIA WB WH	Yes
910925871029	LL551X 133S/840 HE DIA WB WH	Yes
910925871030	LL551X 133S/840 HE DIA NB WH	Yes
910925871031	LL551X 160S/840 HE DIA NB WH	Yes
910925871912	LL551X 133S/840 NE DIA NB WH	Yes
910925871017	LL551X 43_49_60_72S/840 NE PSU VWB WH	No
910925871020	LL551X 47_54_66_80S/840 UE PSU VWB WH	No
910925871022	LL551X 40S/840 NE DIA VWB WH	Yes
910925871023	LL551X 80S/840 NE DIA VWB WH	Yes
910925871024	LL553X 55S/840 NE DIA VWB WH	Yes
910925871025	LL553X 66S/840 NE DIA VWB WH	Yes

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910925871026	LL552X 84S/840 NE DIA VWB WH	White

Order Code	Full Product Name	Housing Color
910925871027	LL552X 123S/840 NE DIA VWB WH	White
910925870859	LL553X 40S/840 NE DIA WB WH	White
910925870860	LL553X 80S/840 NE DIA WB WH	White
910925870861	LL553X 80S/840 NE DIA NB WH	White
910925870862	LL553X 105S/840 NE DIA NB WH	White
910925870863	LL553X 40S/840 UE DIA WB WH	White
910925870864	LL553X 80S/840 UE DIA WB WH	White
910925870865	LL553X 80S/840 UE DIA NB WH	White
910925870866	LL553X 105S/840 UE DIA NB WH	White
910925870929	LL553X 105S/840 NE DIA WB WH	White
910925870930	LL553X 40S/840 NE DIA WB C-2R WH	White
910925870931	LL553X 80S/840 NE DIA WB C-2R WH	White
910925870932	LL553X 80S/840 NE DIA NB C-2R WH	White
910925870933	LL553X 105S/840 NE DIA WB C-2R WH	White
910925870934	LL553X 105S/840 NE DIA NB C-2R WH	White
910925870850	LL552X 62S/840 NE DIA WB WH	White
910925870851	LL552X 160S/840 NE DIA NB WH	White
910925870852	LL552X 62S/840 UE DIA WB WH	White
910925870853	LL552X 160S/840 UE DIA NB WH	White
910925870854	LL552X 62S/840 NE SIA WB WH	White
910925870855	LL552X 160S/840 NE SIA NB WH	White
910925870856	LL552X 62S/840 UE SIA WB WH	White
910925870857	LL552X 100S/840 UE SIA WB WH	White
910925870858	LL552X 160S/840 UE SIA NB WH	White
910925871032	LL552X 200S/840 NE DIA WB WH	White
910925871033	LL552X 200S/840 UE DIA WB WH	White
910925871034	LL552X 240S/840 UE DIA NB WH	White
910925871035	LL552X 200S/840 UE DIA NB WH	White
910925871036	LL552X BV 240S/840 UE DIA NB WH	White
910925871037	LL552X BV 200S/840 UE DIA NB WH	White
910925871913	LL552X 160S/840 NE DIA WB WH	White
910925871914	LL552X 200S/840 NE DIA NB WH	White
910925871915	LL552X 240S/840 UE DIA WB WH	White
910925870846	LL551X 40S/840 UE DIA WB BK	Black
910925870847	LL551X 80S/840 UE DIA WB BK	Black
910925870848	LL551X 80S/840 UE DIA NB BK	Black
910925870849	LL551X 105S/840 UE DIA NB BK	Black
910925870842	LL551X 40S/840 NE DIA WB WH	White
910925870843	LL551X 80S/840 NE DIA WB WH	White
910925870844	LL551X 80S/840 NE DIA NB WH	White
910925870845	LL551X 105S/840 NE DIA NB WH	White
910925870925	LL551X 105S/840 NE DIA WB WH	White


Order Code	Full Product Name	Housing Color
910925871016	LL551X 43_49_60_72S/840 NE PSU WB WH	White
910925871018	LL551X 43_49_60_72S/840 NE PSU NB WH	White
910925871019	LL551X 47_54_66_80S/840 UE PSU WB WH	White
910925871021	LL551X 47_54_66_80S/840 UE PSU NB WH	White
910925871028	LL551X 133S/840 NE DIA WB WH	White
910925871029	LL551X 133S/840 HE DIA WB WH	White
910925871030	LL551X 133S/840 HE DIA NB WH	White
910925871031	LL551X 160S/840 HE DIA NB WH	White
910925871912	LL551X 133S/840 NE DIA NB WH	White
910925871017	LL551X 43_49_60_72S/840 NE PSU VWB WH	White
910925871020	LL551X 47_54_66_80S/840 UE PSU VWB WH	White
910925871022	LL551X 40S/840 NE DIA VWB WH	White
910925871023	LL551X 80S/840 NE DIA VWB WH	White
910925871024	LL553X 55S/840 NE DIA VWB WH	White
910925871025	LL553X 66S/840 NE DIA VWB WH	White

Product Data

Order Code	Full Product Name	Product family code
910925871026	LL552X 84S/840 NE DIA VWB WH	LL552X
910925871027	LL552X 123S/840 NE DIA VWB WH	LL552X
910925870859	LL553X 40S/840 NE DIA WB WH	LL553X
910925870860	LL553X 80S/840 NE DIA WB WH	LL553X
910925870861	LL553X 80S/840 NE DIA NB WH	LL553X
910925870862	LL553X 105S/840 NE DIA NB WH	LL553X
910925870863	LL553X 40S/840 UE DIA WB WH	LL553X
910925870864	LL553X 80S/840 UE DIA WB WH	LL553X
910925870865	LL553X 80S/840 UE DIA NB WH	LL553X
910925870866	LL553X 105S/840 UE DIA NB WH	LL553X
910925870929	LL553X 105S/840 NE DIA WB WH	LL553X
910925870930	LL553X 40S/840 NE DIA WB C-2R WH	LL553X
910925870931	LL553X 80S/840 NE DIA WB C-2R WH	LL553X
910925870932	LL553X 80S/840 NE DIA NB C-2R WH	LL553X
910925870933	LL553X 105S/840 NE DIA WB C-2R WH	LL553X
910925870934	LL553X 105S/840 NE DIA NB C-2R WH	LL553X
910925870850	LL552X 62S/840 NE DIA WB WH	LL552X
910925870851	LL552X 160S/840 NE DIA NB WH	LL552X
910925870852	LL552X 62S/840 UE DIA WB WH	LL552X
910925870853	LL552X 160S/840 UE DIA NB WH	LL552X
910925870854	LL552X 62S/840 NE SIA WB WH	LL552X
910925870855	LL552X 160S/840 NE SIA NB WH	LL552X
910925870856	LL552X 62S/840 UE SIA WB WH	LL552X

Order Code	Full Product Name	Product family code
910925870857	LL552X 100S/840 UE SIA WB WH	LL552X
910925870858	LL552X 160S/840 UE SIA NB WH	LL552X
910925871032	LL552X 200S/840 NE DIA WB WH	LL552X
910925871033	LL552X 200S/840 UE DIA WB WH	LL552X
910925871034	LL552X 240S/840 UE DIA NB WH	LL552X
910925871035	LL552X 200S/840 UE DIA NB WH	LL552X
910925871036	LL552X BV 240S/840 UE DIA NB WH	LL552X
910925871037	LL552X BV 200S/840 UE DIA NB WH	LL552X
910925871913	LL552X 160S/840 NE DIA WB WH	LL552X
910925871914	LL552X 200S/840 NE DIA NB WH	LL552X
910925871915	LL552X 240S/840 UE DIA WB WH	LL552X
910925870846	LL551X 40S/840 UE DIA WB BK	LL551X
910925870847	LL551X 80S/840 UE DIA WB BK	LL551X
910925870848	LL551X 80S/840 UE DIA NB BK	LL551X
910925870849	LL551X 105S/840 UE DIA NB BK	LL551X
910925870842	LL551X 40S/840 NE DIA WB WH	LL551X
910925870843	LL551X 80S/840 NE DIA WB WH	LL551X
910925870844	LL551X 80S/840 NE DIA NB WH	LL551X
910925870845	LL551X 105S/840 NE DIA NB WH	LL551X
910925870925	LL551X 105S/840 NE DIA WB WH	LL551X
910925871016	LL551X 43_49_60_72S/840 NE PSU WB WH	LL551X
910925871018	LL551X 43_49_60_72S/840 NE PSU NB WH	LL551X
910925871019	LL551X 47_54_66_80S/840 UE PSU WB WH	LL551X
910925871021	LL551X 47_54_66_80S/840 UE PSU NB WH	LL551X
910925871028	LL551X 133S/840 NE DIA WB WH	LL551X
910925871029	LL551X 133S/840 HE DIA WB WH	LL551X
910925871030	LL551X 133S/840 HE DIA NB WH	LL551X
910925871031	LL551X 160S/840 HE DIA NB WH	LL551X
910925871912	LL551X 133S/840 NE DIA NB WH	LL551X
910925871017	LL551X 43_49_60_72S/840 NE PSU VWB WH	LL551X
910925871020	LL551X 47_54_66_80S/840 UE PSU VWB WH	LL551X
910925871022	LL551X 40S/840 NE DIA VWB WH	LL551X
910925871023	LL551X 80S/840 NE DIA VWB WH	LL551X
910925871024	LL553X 55S/840 NE DIA VWB WH	LL553X
910925871025	LL553X 66S/840 NE DIA VWB WH	LL553X


Polar normal diagrams



910925871030

910925871029


910925871031



910925871022

910925871018


910925871017




910925871016

910925871021


910925871020




910925871019




910925871023




910925871027




910925871035




910925871033




910925871032




910925871034




910925871026




910925871037




910925871036




910925871024




910925871025




910925871028




LL550XI - 910925871912




LL550XI - 910925871913




LL550XI - 910925871914




LL550XI - 910925871915




LL550XI - 910925870860




LL550XI - 910925870856




LL550XI - 910925870848




LL550XI - 910925870843




LL550XI - 910925870854




LL550XI - 910925870851




LL550XI - 910925870845




LL550XI - 910925870849




LL550XI - 910925870855




LL550XI - 910925870853




LL550XI - 910925870865




LL550XI - 910925870842




LL550XI - 910925870864




LL550XI - 910925870846




LL550XI - 910925870852




LL550XI - 910925870850




LL550XI - 910925870857




LL550XI - 910925870847




LL550XI - 910925870862




LL550XI - 910925870844




LL550XI - 910925870866




LL550XI - 910925870863




LL550XI - 910925870859




LL550XI - 910925870858




LL550XI - 910925870861




LL550XI - 910925870925




LL550XI - 910925870934




LL550XI - 910925870933




LL550XI - 910925870929



LL550XI - 910925870930



LL550XI - 910925870932



LL550XI - 910925870931