

PHILIPS

Lighting



Değer ve performansın en uygun birleşimi olan MASTER Value LEDspot MV, spot aydınlatma için mükemmel bir seçimdir.

MASTER LEDspot MV

Sağladığı sıcak, halojen benzeri vurgu ışığı ile MASTER LEDspot GU10, konaklama sektöründe spot aydınlatma (yürüyüş yolu, koridor, asansör lobileri, sergileme bölmeleri ve kabinleri) için idealdir. Özellikle ışığın 7 gün 24 saat açık kaldığı lobiler, koridorlar ve merdivenler gibi ortak alanlar için çok uygundur. MASTER LEDspot GU10, büyük enerji tasarrufu sağlar ve aydınlatma parlaklığından ödün vermeden bakım giderlerini en düşük düzeye indirerek, konaklama tesisi sahiplerinin yaptıkları yatırımı bir sene içinde amorti etmesine olanak tanır. GU10 duyuna sahip mevcut armatürlerin pek çoğuyla uyumludur ve 35 ya da 50 W halojen lambalar için bir yükseltme alternatifi olarak tasarlanmıştır.

Faydaları

- %85 enerji tasarrufu
- Bir sene içinde yatırım amortismanı

MASTER LEDspot MV

Özellikler

- Dimmer anahtarlar ile uyumlu
- 25.000 ila 45.000 saat kullanım ömrü
- Vurgu aydınlatması
- Isıya duyarlı nesnelere için koruma ve daha az ısı sağlamak amacıyla UV'siz ve IR'siz ışık

Uygulama

- Konaklama
- Perakende
- Konut

Güvenlik ve uyarılar

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Versions




PAR16 GU10



LEDspots VLE D 650lm GU10 930 120D

MASTER LEDspot MV

Boyutlu çizim



Product	D	C
MAS LED spot VLE D 2.8-35W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 2.8-35W GU10 927 60D	50 mm	54 mm
MAS LED spot VLE D 2.8-35W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 2.8-35W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 927 60D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 930 60D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 940 60D	50 mm	54 mm
MAS LED spot VLE D 5.5-80W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 5.5-80W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 5.5-80W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE D 5.5-80W GU10 965 36D	50 mm	54 mm
MAS LED spot VLE D 650lm GU10 930 120D	50 mm	55,5 mm
MAS LED spot VLE D 680lm GU10 940 120D	50 mm	55,5 mm
MAS LED spot VLE D 680lm GU10 965 120D	50 mm	55,5 mm
MAS LED spot VLE DT 2.8-35W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE DT 3.7-50W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE DT 5.5-80W GU10 927 36D	50 mm	54 mm
MAS LED spot VLEDT3.7-50W GU10 927 36DUK	50 mm	54 mm
MAS LEDspot VLE D 3.7-50W GU10 92736D5CT	50 mm	54 mm
MAS LEDspot VLE D 3.7-50W GU10 93036D5CT	50 mm	54 mm
MAS LEDspotVLE D 3.7-50W GU10 930 36D UK	50 mm	54 mm
MAS LEDspotVLE D 3.7-50W GU10 940 36D UK	50 mm	54 mm
MASLEDspot VLE D 5.5-80W GU10 927 36D UK	50 mm	54 mm
MASLEDspot VLE D 5.5-80W GU10 930 36D UK	50 mm	54 mm
MASLEDspot VLE D 5.5-80W GU10 940 36D UK	50 mm	54 mm

MASTER LEDspot MV

Genel Bilgiler

Kapak Tabanı	GU10
Nominal kullanım ömrü	25.000 h

Işık Teknik Ayrıntıları

Renk oluşturma dizini (CRI)	90
Nominal Kullanım Ömrü Sonundaki LLMF (Nom)	70 %

Çalıştırma ve Elektrik

Giriş Frekansı	50 ila 60 Hz
Başlangıç Saati (Nom)	0,5 s

Kontroller ve Dim Etme

Dim Edilebilir	Yalnızca belirli karartıcılarla
----------------	---------------------------------

Mekanik ve Muhafaza

Lamba Biçimi	PAR16
--------------	-------

Onay ve Uygulama

Ortam sıcaklığı aralığı	-20 ila +45 °C
-------------------------	----------------

Genel Bilgiler

Order Code	Full Product Name	Anahtar Döngüsü
03821000	MASTER LED spot VLE DT 5.5-80W GU10 927 36D	50.000
03835700	MASTER LED spot VLE D 5.5-80W GU10 927 36D	50.000
03841800	MASTERLEDspot VLE D 5.5-80W GU10 927 36D UK	50.000
03827200	MASTER LED spot VLE D 5.5-80W GU10 930 36D	50.000
03837100	MASTERLEDspot VLE D 5.5-80W GU10 930 36D UK	50.000
03823400	MASTER LED spot VLE D 5.5-80W GU10 940 36D	50.000
03839500	MASTERLEDspot VLE D 5.5-80W GU10 940 36D UK	50.000
03825800	MASTER LED spot VLE D 5.5-80W GU10 965 36D	50.000
39914300	MASTER LED spot VLE DT 2.8-35W GU10 927 36D	50.000
39948800	MASTER LED spot VLE DT 3.7-50W GU10 927 36D	50.000
39926600	MASTER LED spot VLEDT3.7-50W GU10 927 36DUK	50.000
39912900	MASTER LED spot VLE D 2.8-35W GU10 927 36D	50.000
39928000	MASTER LED spot VLE D 2.8-35W GU10 930 36D	50.000
39930300	MASTER LED spot VLE D 2.8-35W GU10 940 36D	50.000
39916700	MASTER LED spot VLE D 2.8-35W GU10 927 60D	50.000
39920400	MASTER LED spot VLE D 3.7-50W GU10 927 36D	50.000
39944000	MASTER LED spot VLE D 3.7-50W GU10 930 36D	50.000
39922800	MASTER LEDspotVLE D 3.7-50W GU10 930 36D UK	50.000
39946400	MASTER LED spot VLE D 3.7-50W GU10 940 36D	50.000
39924200	MASTER LEDspotVLE D 3.7-50W GU10 940 36D UK	50.000
39934100	MASTER LED spot VLE D 3.7-50W GU10 927 60D	25.000
39936500	MASTER LED spot VLE D 3.7-50W GU10 930 60D	25.000
39938900	MASTER LED spot VLE D 3.7-50W GU10 940 60D	25.000
05236000	MASTER LEDspot VLE D 3.7-50W GU10 92736D5CT	50.000
05238400	MASTER LEDspot VLE D 3.7-50W GU10 93036D5CT	50.000
03829600	MASTER LED spot VLE D 650lm GU10 930 120D	50.000
03831900	MASTER LED spot VLE D 680lm GU10 940 120D	50.000
03833300	MASTER LED spot VLE D 680lm GU10 965 120D	50.000

Işık Teknik Ayrıntıları (1/2)

Order Code	Full Product Name	İlişkili Renk			
		Işın Açısı (Nom)	Sıcaklığı (Nom.)	Renk Kodu	Işık Akısı
03821000	MASTER LED spot VLE DT 5.5-80W GU10 927 36D	36 °	2200 K	922-927	575 lm
03835700	MASTER LED spot VLE D 5.5-80W GU10 927 36D	36 °	2700 K	927	575 lm
03841800	MASTERLEDspot VLE D 5.5-80W GU10 927 36D UK	36 °	2700 K	927	575 lm
03827200	MASTER LED spot VLE D 5.5-80W GU10 930 36D	36 °	3000 K	930	575 lm
03837100	MASTERLEDspot VLE D 5.5-80W GU10 930 36D UK	36 °	3000 K	930	575 lm
03823400	MASTER LED spot VLE D 5.5-80W GU10 940 36D	36 °	4000 K	940	575 lm
03839500	MASTERLEDspot VLE D 5.5-80W GU10 940 36D UK	36 °	4000 K	940	575 lm
03825800	MASTER LED spot VLE D 5.5-80W GU10 965 36D	36 °	6500 K	965	575 lm

Order Code	Full Product Name	İlişkili Renk			
		Işın Açısı (Nom)	Sıcaklığı (Nom.)	Renk Kodu	Işık Akısı
39914300	MASTER LED spot VLE DT 2.8-35W GU10 927 36D	36 °	2200 K	922-927	280 lm
39948800	MASTER LED spot VLE DT 3.7-50W GU10 927 36D	36 °	2200 K	922-927	355 lm
39926600	MASTER LED spot VLEDT3.7-50W GU10 927 36DUK	36 °	2200 K	922-927	355 lm
39912900	MASTER LED spot VLE D 2.8-35W GU10 927 36D	36 °	2700 K	927	270 lm
39928000	MASTER LED spot VLE D 2.8-35W GU10 930 36D	36 °	3000 K	930	270 lm
39930300	MASTER LED spot VLE D 2.8-35W GU10 940 36D	36 °	4000 K	940	285 lm
39916700	MASTER LED spot VLE D 2.8-35W GU10 927 60D	60 °	2700 K	927	270 lm

MASTER LEDspot MV

Order Code	Full Product Name	İlişkili Renk			
		Işın Açısı (Nom)	Sıcaklığı (Nom.)	Renk Kodu	Işık Akısı
39920400	MASTER LED spot VLE D 3.7-50W GU10 927 36D	36 °	2700 K	927	355 lm
39944000	MASTER LED spot VLE D 3.7-50W GU10 930 36D	36 °	3000 K	930	365 lm
39922800	MASTER LEDspotVLE D 3.7-50W GU10 930 36D UK	36 °	3000 K	930	365 lm
39946400	MASTER LED spot VLE D 3.7-50W GU10 940 36D	36 °	4000 K	940	380 lm
39924200	MASTER LEDspotVLE D 3.7-50W GU10 940 36D UK	36 °	4000 K	940	380 lm
39934100	MASTER LED spot VLE D 3.7-50W GU10 927 60D	60 °	2700 K	927	355 lm
39936500	MASTER LED spot VLE D 3.7-50W GU10 930 60D	60 °	3000 K	930	365 lm

Order Code	Full Product Name	İlişkili Renk			
		Işın Açısı (Nom)	Sıcaklığı (Nom.)	Renk Kodu	Işık Akısı
39938900	MASTER LED spot VLE D 3.7-50W GU10 940 60D	60 °	4000 K	940	370 lm
05236000	MASTER LEDspot VLE D 3.7-50W GU10 92736D5CT	36 °	2700 K	927	355 lm
05238400	MASTER LEDspot VLE D 3.7-50W GU10 93036D5CT	36 °	3000 K	930	365 lm
03829600	MASTER LED spot VLE D 650lm GU10 930 120D	120 °	3000 K	930	650 lm
03831900	MASTER LED spot VLE D 680lm GU10 940 120D	120 °	4000 K	940	680 lm
03833300	MASTER LED spot VLE D 680lm GU10 965 120D	120 °	6500 K	965	680 lm

Işık Teknik Ayrıntıları (2/2)

Order Code	Full Product Name	Işık Yoğunluğu (Nom)
03821000	MASTER LED spot VLE DT 5.5-80W GU10 927 36D	950 cd
03835700	MASTER LED spot VLE D 5.5-80W GU10 927 36D	950 cd
03841800	MASTERLEDspot VLE D 5.5-80W GU10 927 36D UK	950 cd
03827200	MASTER LED spot VLE D 5.5-80W GU10 930 36D	1.000 cd
03837100	MASTERLEDspot VLE D 5.5-80W GU10 930 36D UK	1.000 cd
03823400	MASTER LED spot VLE D 5.5-80W GU10 940 36D	1.000 cd
03839500	MASTERLEDspot VLE D 5.5-80W GU10 940 36D UK	1.000 cd
03825800	MASTER LED spot VLE D 5.5-80W GU10 965 36D	1.000 cd
39914300	MASTER LED spot VLE DT 2.8-35W GU10 927 36D	550 cd
39948800	MASTER LED spot VLE DT 3.7-50W GU10 927 36D	700 cd
39926600	MASTER LED spot VLEDT3.7-50W GU10 927 36DUK	700 cd
39912900	MASTER LED spot VLE D 2.8-35W GU10 927 36D	600 cd
39928000	MASTER LED spot VLE D 2.8-35W GU10 930 36D	600 cd
39930300	MASTER LED spot VLE D 2.8-35W GU10 940 36D	600 cd

Order Code	Full Product Name	Işık Yoğunluğu (Nom)
39916700	MASTER LED spot VLE D 2.8-35W GU10 927 60D	300 cd
39920400	MASTER LED spot VLE D 3.7-50W GU10 927 36D	750 cd
39944000	MASTER LED spot VLE D 3.7-50W GU10 930 36D	750 cd
39922800	MASTER LEDspotVLE D 3.7-50W GU10 930 36D UK	750 cd
39946400	MASTER LED spot VLE D 3.7-50W GU10 940 36D	800 cd
39924200	MASTER LEDspotVLE D 3.7-50W GU10 940 36D UK	800 cd
39934100	MASTER LED spot VLE D 3.7-50W GU10 927 60D	400 cd
39936500	MASTER LED spot VLE D 3.7-50W GU10 930 60D	400 cd
39938900	MASTER LED spot VLE D 3.7-50W GU10 940 60D	420 cd
05236000	MASTER LEDspot VLE D 3.7-50W GU10 92736D5CT	750 cd
05238400	MASTER LEDspot VLE D 3.7-50W GU10 93036D5CT	750 cd
03829600	MASTER LED spot VLE D 650lm GU10 930 120D	220 cd
03831900	MASTER LED spot VLE D 680lm GU10 940 120D	220 cd
03833300	MASTER LED spot VLE D 680lm GU10 965 120D	220 cd

Çalıştırma ve Elektrik

Order Code	Full Product Name	Güç Tüketimi	Güç Eşleniği
03821000	MASTER LED spot VLE DT 5.5-80W GU10 927 36D	5,5 W	80 W
03835700	MASTER LED spot VLE D 5.5-80W GU10 927 36D	5,5 W	80 W
03841800	MASTERLEDspot VLE D 5.5-80W GU10 927 36D UK	5,5 W	80 W
03827200	MASTER LED spot VLE D 5.5-80W GU10 930 36D	5,5 W	80 W
03837100	MASTERLEDspot VLE D 5.5-80W GU10 930 36D UK	5,5 W	80 W
03823400	MASTER LED spot VLE D 5.5-80W GU10 940 36D	5,5 W	80 W

Order Code	Full Product Name	Güç Tüketimi	Güç Eşleniği
03839500	MASTERLEDspot VLE D 5.5-80W GU10 940 36D UK	5,5 W	80 W
03825800	MASTER LED spot VLE D 5.5-80W GU10 965 36D	5,5 W	80 W
39914300	MASTER LED spot VLE DT 2.8-35W GU10 927 36D	2,8 W	35 W
39948800	MASTER LED spot VLE DT 3.7-50W GU10 927 36D	3,7 W	50 W
39926600	MASTER LED spot VLEDT3.7-50W GU10 927 36DUK	3,7 W	50 W
39912900	MASTER LED spot VLE D 2.8-35W GU10 927 36D	2,8 W	35 W

MASTER LEDspot MV

Order Code	Full Product Name	Güç Tüketimi	Güç Eşleniği
39928000	MASTER LED spot VLE D 2.8-35W GU10 930 36D	2,8 W	35 W
39930300	MASTER LED spot VLE D 2.8-35W GU10 940 36D	2,8 W	35 W
39916700	MASTER LED spot VLE D 2.8-35W GU10 927 60D	2,8 W	35 W
39920400	MASTER LED spot VLE D 3.7-50W GU10 927 36D	3,7 W	50 W
39944000	MASTER LED spot VLE D 3.7-50W GU10 930 36D	3,7 W	50 W
39922800	MASTER LEDspotVLE D 3.7-50W GU10 930 36D UK	3,7 W	50 W
39946400	MASTER LED spot VLE D 3.7-50W GU10 940 36D	3,7 W	50 W
39924200	MASTER LEDspotVLE D 3.7-50W GU10 940 36D UK	3,7 W	50 W

Order Code	Full Product Name	Güç Tüketimi	Güç Eşleniği
39934100	MASTER LED spot VLE D 3.7-50W GU10 927 60D	3,7 W	50 W
39936500	MASTER LED spot VLE D 3.7-50W GU10 930 60D	3,7 W	50 W
39938900	MASTER LED spot VLE D 3.7-50W GU10 940 60D	3,7 W	50 W
05236000	MASTER LEDspot VLE D 3.7-50W GU10 92736D5CT	3,7 W	50 W
05238400	MASTER LEDspot VLE D 3.7-50W GU10 93036D5CT	3,7 W	50 W
03829600	MASTER LED spot VLE D 650lm GU10 930 120D	5,5 W	-
03831900	MASTER LED spot VLE D 680lm GU10 940 120D	5,5 W	-
03833300	MASTER LED spot VLE D 680lm GU10 965 120D	5,5 W	-

Sıcaklık

Order Code	Full Product Name	Muhafaza Maksimumu (Nom.)
03821000	MASTER LED spot VLE DT 5.5-80W GU10 927 36D	66 °C
03835700	MASTER LED spot VLE D 5.5-80W GU10 927 36D	66 °C
03841800	MASTERLEDspot VLE D 5.5-80W GU10 927 36D UK	66 °C
03827200	MASTER LED spot VLE D 5.5-80W GU10 930 36D	66 °C
03837100	MASTERLEDspot VLE D 5.5-80W GU10 930 36D UK	66 °C
03823400	MASTER LED spot VLE D 5.5-80W GU10 940 36D	66 °C
03839500	MASTERLEDspot VLE D 5.5-80W GU10 940 36D UK	66 °C
03825800	MASTER LED spot VLE D 5.5-80W GU10 965 36D	66 °C
39914300	MASTER LED spot VLE DT 2.8-35W GU10 927 36D	52 °C
39948800	MASTER LED spot VLE DT 3.7-50W GU10 927 36D	60 °C
39926600	MASTER LED spot VLEDT3.7-50W GU10 927 36DUK	60 °C
39912900	MASTER LED spot VLE D 2.8-35W GU10 927 36D	50 °C
39928000	MASTER LED spot VLE D 2.8-35W GU10 930 36D	50 °C
39930300	MASTER LED spot VLE D 2.8-35W GU10 940 36D	50 °C

Order Code	Full Product Name	Muhafaza Maksimumu (Nom.)
39916700	MASTER LED spot VLE D 2.8-35W GU10 927 60D	50 °C
39920400	MASTER LED spot VLE D 3.7-50W GU10 927 36D	66 °C
39944000	MASTER LED spot VLE D 3.7-50W GU10 930 36D	66 °C
39922800	MASTER LEDspotVLE D 3.7-50W GU10 930 36D UK	66 °C
39946400	MASTER LED spot VLE D 3.7-50W GU10 940 36D	66 °C
39924200	MASTER LEDspotVLE D 3.7-50W GU10 940 36D UK	66 °C
39934100	MASTER LED spot VLE D 3.7-50W GU10 927 60D	62 °C
39936500	MASTER LED spot VLE D 3.7-50W GU10 930 60D	62 °C
39938900	MASTER LED spot VLE D 3.7-50W GU10 940 60D	62 °C
05236000	MASTER LEDspot VLE D 3.7-50W GU10 92736D5CT	66 °C
05238400	MASTER LEDspot VLE D 3.7-50W GU10 93036D5CT	66 °C
03829600	MASTER LED spot VLE D 650lm GU10 930 120D	66 °C
03831900	MASTER LED spot VLE D 680lm GU10 940 120D	66 °C
03833300	MASTER LED spot VLE D 680lm GU10 965 120D	66 °C

Mekanik ve Muhafaza

Order Code	Full Product Name	Lamba Kaplaması
03821000	MASTER LED spot VLE DT 5.5-80W GU10 927 36D	Şeffaf
03835700	MASTER LED spot VLE D 5.5-80W GU10 927 36D	Şeffaf
03841800	MASTERLEDspot VLE D 5.5-80W GU10 927 36D UK	Şeffaf
03827200	MASTER LED spot VLE D 5.5-80W GU10 930 36D	Şeffaf
03837100	MASTERLEDspot VLE D 5.5-80W GU10 930 36D UK	Şeffaf
03823400	MASTER LED spot VLE D 5.5-80W GU10 940 36D	Şeffaf
03839500	MASTERLEDspot VLE D 5.5-80W GU10 940 36D UK	Şeffaf
03825800	MASTER LED spot VLE D 5.5-80W GU10 965 36D	Şeffaf
39914300	MASTER LED spot VLE DT 2.8-35W GU10 927 36D	Şeffaf
39948800	MASTER LED spot VLE DT 3.7-50W GU10 927 36D	Şeffaf
39926600	MASTER LED spot VLEDT3.7-50W GU10 927 36DUK	Şeffaf
39912900	MASTER LED spot VLE D 2.8-35W GU10 927 36D	Şeffaf

Order Code	Full Product Name	Lamba Kaplaması
39928000	MASTER LED spot VLE D 2.8-35W GU10 930 36D	Şeffaf
39930300	MASTER LED spot VLE D 2.8-35W GU10 940 36D	Şeffaf
39916700	MASTER LED spot VLE D 2.8-35W GU10 927 60D	Şeffaf
39920400	MASTER LED spot VLE D 3.7-50W GU10 927 36D	Şeffaf
39944000	MASTER LED spot VLE D 3.7-50W GU10 930 36D	Şeffaf
39922800	MASTER LEDspotVLE D 3.7-50W GU10 930 36D UK	Şeffaf
39946400	MASTER LED spot VLE D 3.7-50W GU10 940 36D	Şeffaf
39924200	MASTER LEDspotVLE D 3.7-50W GU10 940 36D UK	Şeffaf
39934100	MASTER LED spot VLE D 3.7-50W GU10 927 60D	Şeffaf
39936500	MASTER LED spot VLE D 3.7-50W GU10 930 60D	Şeffaf
39938900	MASTER LED spot VLE D 3.7-50W GU10 940 60D	Şeffaf
05236000	MASTER LEDspot VLE D 3.7-50W GU10 92736D5CT	Şeffaf






MASTER LEDspot MV

Order Code	Full Product Name	Lamba Kaplaması
05238400	MASTER LEDspot VLE D 3.7-50W GU10 93036D5CT	Şeffaf
03829600	MASTER LED spot VLE D 650lm GU10 930 120D	Buzlu











Order Code	Full Product Name	Lamba Kaplaması
03831900	MASTER LED spot VLE D 680lm GU10 940 120D	Buzlu
03833300	MASTER LED spot VLE D 680lm GU10 965 120D	Buzlu

Onay ve Uygulama



Order Code	Full Product Name	Enerji Tüketimi kWh/ 1000 sa.
03821000	MASTER LED spot VLE DT 5.5-80W GU10 927 36D	6 kWh
03835700	MASTER LED spot VLE D 5.5-80W GU10 927 36D	6 kWh
03841800	MASTERLEDspot VLE D 5.5-80W GU10 927 36D UK	6 kWh
03827200	MASTER LED spot VLE D 5.5-80W GU10 930 36D	6 kWh
03837100	MASTERLEDspot VLE D 5.5-80W GU10 930 36D UK	6 kWh
03823400	MASTER LED spot VLE D 5.5-80W GU10 940 36D	6 kWh
03839500	MASTERLEDspot VLE D 5.5-80W GU10 940 36D UK	6 kWh
03825800	MASTER LED spot VLE D 5.5-80W GU10 965 36D	6 kWh
39914300	MASTER LED spot VLE DT 2.8-35W GU10 927 36D	3 kWh
39948800	MASTER LED spot VLE DT 3.7-50W GU10 927 36D	4 kWh
39926600	MASTER LED spot VLEDT3.7-50W GU10 927 36DUK	4 kWh
39912900	MASTER LED spot VLE D 2.8-35W GU10 927 36D	3 kWh
39928000	MASTER LED spot VLE D 2.8-35W GU10 930 36D	3 kWh
39930300	MASTER LED spot VLE D 2.8-35W GU10 940 36D	3 kWh
39916700	MASTER LED spot VLE D 2.8-35W GU10 927 60D	3 kWh
39920400	MASTER LED spot VLE D 3.7-50W GU10 927 36D	4 kWh
39944000	MASTER LED spot VLE D 3.7-50W GU10 930 36D	4 kWh
39922800	MASTER LEDspotVLE D 3.7-50W GU10 930 36D UK	4 kWh
39946400	MASTER LED spot VLE D 3.7-50W GU10 940 36D	4 kWh
39924200	MASTER LEDspotVLE D 3.7-50W GU10 940 36D UK	4 kWh
39934100	MASTER LED spot VLE D 3.7-50W GU10 927 60D	4 kWh
39936500	MASTER LED spot VLE D 3.7-50W GU10 930 60D	4 kWh
39938900	MASTER LED spot VLE D 3.7-50W GU10 940 60D	4 kWh
05236000	MASTER LEDspot VLE D 3.7-50W GU10 92736D5CT	4 kWh
05238400	MASTER LEDspot VLE D 3.7-50W GU10 93036D5CT	4 kWh
03829600	MASTER LED spot VLE D 650lm GU10 930 120D	6 kWh
03831900	MASTER LED spot VLE D 680lm GU10 940 120D	6 kWh
03833300	MASTER LED spot VLE D 680lm GU10 965 120D	6 kWh




MASTER LEDspot MV




MASTER LEDspot MV




Accent Diagrams




Accent Diagram - MAS LED spot VLE D 2.8-35W
GU10 930 36D




Accent Diagram - MASLEDspot VLE D 5.5-80W
GU10 927 36D UK




Accent Diagram - MAS LED spot VLE DT
5.5-80W GU10 927 36D




Accent Diagram - MASLEDspot VLE D 5.5-80W
GU10 930 36D UK




Accent Diagram - MAS LED spot VLE D 3.7-50W
GU10 927 60D




Accent Diagram - MAS LED spot VLE D 2.8-35W
GU10 940 36D



Accent Diagram - MAS LEDspotVLE D 3.7-50W
GU10 940 36D UK




Accent Diagram - MAS LEDspotVLE D 3.7-50W
GU10 930 36D UK




Accent Diagram - MAS LEDspot VLE D 3.7-50W
GU10 92736D5CT


Accent Diagrams




Accent Diagram - MAS LED spot VLE D 2.8-35W GU10 927 36D




Accent Diagram - MAS LED spot VLE D 3.7-50W GU10 940 60D




Accent Diagram - MAS LED spot VLE D 2.8-35W GU10 927 60D



Accent Diagram - MAS LED spot VLE D 3.7-50W GU10 930 60D




Accent Diagram - MAS LED spot VLE DT 2.8-35W GU10 927 36D




Accent Diagram - MAS LED spot VLE DT 3.7-50W GU10 927 36D


Beam Diagrams



Beam diagram - MAS LED spot VLE DT 5.5-80W GU10 927 36D




Beam diagram - MAS LED spot VLE D 2.8-35W GU10 940 36D




Beam diagram - MAS LEDspotVLE D 3.7-50W GU10 940 36D UK


Beam Diagrams




Beam diagram - MAS LED spot VLE D 2.8-35W
GU10 927 60D




Beam diagram - MAS LED spot VLE DT 2.8-35W
GU10 927 36D




Beam diagram - MAS LED spot VLE D 2.8-35W
GU10 930 36D




Beam diagram - MASLEDspot VLE D 5.5-80W
GU10 930 36D UK




Beam diagram - MAS LEDspot VLE D 3.7-50W
GU10 92736D5CT




Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 927 60D



Beam diagram - MASLEDspot VLE D 5.5-80W
GU10 927 36D UK




Beam diagram - MAS LED spot VLE DT 3.7-50W
GU10 927 36D




Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 930 60D


Beam Diagrams



Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 940 60D



Beam diagram - MAS LED spot VLE D 2.8-35W
GU10 927 36D



Beam diagram - MAS LEDspotVLE D 3.7-50W
GU10 930 36D UK

