PHILIPS

Lighting

MASTER LEDspot PAR - The energy-saving alternative for lighting in public areas

MASTER LED spot PAR

With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. There is a choice of dimmable and non-dimmable versions. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of halogen/incandescent lamps, MASTER LEDspot PAR deliver huge energy savings and minimize maintenance cost without any reduction in brightness. The IP44-rated outdoor version of the PAR 38 lamp is one of the few energy-saving alternatives to incandescent PAR38 outdoor lamps available today. The dimmable PAR 20 is a perfect replacement for an incandescent spot.

Benefits

- Up to 80% energy saving compared to halogen lamps
- Retrofittable and compatible with existing fixtures with E27 holder
- Lower maintenance costs

Features

- Lifetime of 45,000 hours
- Dimmable (except PAR38 OD)
- UV- and IR-free light for less heat and protection for heat-sensitive objects
- Free of mercury and hazardous materials

MASTER LED spot PAR

Application

- Especially suitable for public areas like lobbies, corridors, stairwells and restaurants/bars

Versions

LEDclassic PAR38 25D POS2

Dimensional drawing



Product	D	C
MAS LEDspot D 13-100W E27 927 PAR38 25D	124 mm	130 mm



MASTER LED spot PAR

Accent Diagrams



Accent Diagram - MAS LEDspot D 13-100W E27 927 PAR38 25D

Beam Diagrams



h (m)	E_0 (lx)	d(m) VBA	$^1/_2I_{max}$	$^1/_2E_0$
1.0	3248		0.50	0.46
1.5	1443		0.75	0.69
2.0	812		1.00	0.92
2.5	520		1.25	1.15
3.0	361		1.50	1.39
3.5	265		1.75	1.62
4.0	203		1.99	1.85
4.5	160		2.24	2.08

Beam diagram - MAS LEDspot D 13-100W E27 927 PAR38 25D

© 2026 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.