



SmartBright Plus Panel: Trusted performance. Everyday.

SmartBright Plus Panel

The Philips SmartBright Plus panel (RC048B+) range features a selection of popular off-the-shelf LED luminaires that come with Philips high quality levels at a competitive price. Reliable, high energy efficient and affordable, this latest generation of SmartBright Plus LED panel lights are designed for diffuse, comfortable lighting in a wide range of general lighting applications. Our range of SmartBright Plus panel lighting is also available with accessories for easy installation on different types of ceilings – just what you need.

Benefits

- Philips quality and reliability
- High energy saving
- Diffuse, comfortable light
- Suitable for office working place
- Diverse ceiling installation possible

Features

- Modern, unobtrusive design
- Two lumen choices 3500 lumen & 4100 lumen for W60L60 & W30L120
- Offer 6000lm for W60L120
- Long lifetime of 50,000 hours @L60
- Energy efficient up to 130 lm/W
- Flicker free, RG0, R9
- Accessories for plaster ceiling, surface mounted and suspension available

SmartBright Plus Panel

Application

- Offices
- Hospitals and Care Centers
- Retail





Versions



SmartBright Plus Panel

SmartBright Plus Panel

Dimensional drawing



Product details



SmartBright Plus Panel



SmartBright Plus Panel




SmartBright Plus Panel

SmartBright Plus Panel

Product details

SmartBright Plus Panel



Light Technical		
Color rendering index (CRI)	>80	
Luminous Efficacy (rated) (Nom)	130 lm/W	
Luminous Flux	4,100 lm	
Operating and Electrical		
Protection class IEC	Safety class II	
Input Voltage	220-240 V	
Line Frequency	50 or 60 Hz	
Power Consumption	31.5 W	
Controls and Dimming		
Dimmable	No	
Mechanical and Housing		
Optical cover type	PS	
Housing Color	White RAL 9003	
Mech. impact protection code	IK02	
Ingress protection code	IP20/40	
Approval and Application		
Ambient temperature range	-10 to +40 °C	
CE mark	Yes	
Initial Performance (IEC Compliant)		
Luminous flux tolerance	-10% / +10%	
Light Technical		
Order Code	Full Product Name	Correlated Color Temperature (Nom)
911401881387	RC048B+ LED41S/840 PSU W30L120 2IN1W PCV	4000 K
911401888187	RC048B+ LED41S/865 PSU W30L120 2IN1W PCV	6500 K
911401881187	RC048B+ LED41S/840 PSU W60L60 2IN1W PCV	4000 K
911401888087	RC048B+ LED41S/865 PSU W60L60 2IN1W PCV	6500 K

