



# SmartBright Plus Panel: Trusted performance. Everyday.

## SmartBright Plus Panel

The Philips SmartBright Plus panel (RC048B+) range features a selection of popular off-the-shelf LED luminaires that come with Philips high quality levels at a competitive price. Reliable, high energy efficient and affordable, this latest generation of SmartBright Plus LED panel lights are designed for diffuse, comfortable lighting in a wide range of general lighting applications. Our range of SmartBright Plus panel lighting is also available with accessories for easy installation on different types of ceilings – just what you need.

### Benefits

- Philips quality and reliability
- High energy saving
- Diffuse, comfortable light
- Suitable for office working place
- Diverse ceiling installation possible

### Features

- Modern, unobtrusive design
- Two lumen choices 3500 lumen & 4100 lumen for W60L60 & W30L120
- Offer 6000lm for W60L120
- Long lifetime of 50,000 hours @L60
- Energy efficient up to 130 lm/W
- Flicker free, RG0, R9
- Accessories for plaster ceiling, surface mounted and suspension available

# SmartBright Plus Panel

## Application


- Offices
- Hospitals and Care Centers
- Retail

## Versions




### SmartBright Plus Panel

## Dimensional drawing



# SmartBright Plus Panel

## Dimensional drawing



## Product details



SmartBright Plus Panel



SmartBright Plus Panel



SmartBright Plus Panel



SmartBright Plus Panel



SmartBright Plus Panel

# SmartBright Plus Panel

## Light Technical

Color rendering index (CRI)	>80
Luminous Efficacy (rated) (Nom)	130 lm/W

## Operating and Electrical

Protection class IEC	Safety class II
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz

## Controls and Dimming

Dimmable	No
----------	----

## Mechanical and Housing

Optical cover type	PS
Housing Color	White RAL 9003
Mech. impact protection code	IK02
Ingress protection code	IP20/40

## Approval and Application

Ambient temperature range	-10 to +40 °C
CE mark	Yes

## Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
-------------------------	-------------

## Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Flux
911401880987	RC048B+ LED41S/840 PSU W30L120 G2	4000 K	4,100 lm
911401881087	RC048B+ LED41S/865 PSU W30L120 G2	6500 K	4,100 lm
911401880787	RC048B+ LED41S/840 PSU W60L60 G2	4000 K	4,100 lm
911401880887	RC048B+ LED41S/865 PSU W60L60 G2	6500 K	4,100 lm
911401881787	RC048B+ LED41S/840 PSU W603L603 G2	4000 K	4,100 lm
911401881887	RC048B+ LED41S/865 PSU W603L603 G2	6500 K	4,100 lm
911401881587	RC048B+ LED60S/840 PSU W60L120 G2	4000 K	6,000 lm
911401881687	RC048B+ LED60S/865 PSU W60L120 G2	6500 K	6,000 lm
911401881987	RC048B+ LED60S/840 PSU W603L1210 G2	4000 K	6,000 lm
911401882087	RC048B+ LED60S/865 PSU W603L1210 G2	6500 K	6,000 lm

## Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401880987	RC048B+ LED41S/840 PSU W30L120 G2	31.5 W
911401881087	RC048B+ LED41S/865 PSU W30L120 G2	31.5 W
911401880787	RC048B+ LED41S/840 PSU W60L60 G2	31.5 W
911401880887	RC048B+ LED41S/865 PSU W60L60 G2	31.5 W
911401881787	RC048B+ LED41S/840 PSU W603L603 G2	31.5 W

Order Code	Full Product Name	Power Consumption
911401881887	RC048B+ LED41S/865 PSU W603L603 G2	31.5 W
911401881587	RC048B+ LED60S/840 PSU W60L120 G2	46 W
911401881687	RC048B+ LED60S/865 PSU W60L120 G2	46 W
911401881987	RC048B+ LED60S/840 PSU W603L1210 G2	46 W
911401882087	RC048B+ LED60S/865 PSU W603L1210 G2	46 W

